

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026510

Luminaire Tested: S124RDIP-B575D810UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026510
REPORT IS A COMBINATION OF REPORTS P999600 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D810UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5177.6 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026510

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026510

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52			45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44			39
2	88	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38			33
3	81	72	64	59	74	66	60	55	55	51	47	46	42	39	36	34	32			28
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28			24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	24			21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17			15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6907 cd/sqm

TEST NUMBER: P1026510

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.8
10°-20°	265.4	5.1
20°-30°	383.2	7.4
30°-40°	434.3	8.4
40°-50°	419.3	8.1
50°-60°	348.6	6.7
60°-70°	240.6	4.6
70°-80°	121.6	2.3
80°-90°	32.4	0.6
90°-100°	288.8	5.6
100°-110°	587.3	11.3
110°-120°	523.5	10.1
120°-130°	439.8	8.5
130°-140°	367.0	7.1
140°-150°	280.3	5.4
150°-160°	197.0	3.8
160°-170°	115.9	2.2
170°-180°	37.7	0.7
0°-30°	743.8	14.4
0°-40°	1178.0	22.8
0°-60°	1945.9	37.6
0°-90°	2340.5	45.2
90°-120°	1399.6	27.0
90°-150°	2486.6	48.0
90°-180°	2837.0	54.8
0°-180°	5177.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	1	6	14	15	16	4
95°	25	79	622	308	186	28
105°	89	129	501	1079	1075	95
115°	157	197	447	858	1032	156
125°	219	260	444	731	823	195
135°	260	310	441	648	736	201
145°	300	344	438	547	601	188
155°	341	369	426	483	503	157
165°	372	383	409	433	439	105
175°	388	389	392	397	396	37
180°	389	389	389	389	389	

TEST NUMBER: P1026510

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	0.8	6.1	13.7	15.3	16.0
92.5°	10.7	58.8	299.4	99.0	69.5
95°	25.2	79.4	622.5	308.2	186.4
97.5°	42.0	87.8	666.0	629.4	447.6
100°	58.0	99.3	614.1	870.8	700.4
102.5°	73.3	113.0	549.2	1022.0	920.4
105°	89.4	129.4	501.0	1078.8	1074.6
107.5°	106.9	146.2	469.7	1061.6	1148.0
110°	124.5	163.1	455.2	1000.6	1149.5

TEST NUMBER: P1026510

CATALOG NUMBER: S124RDIP-B575D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.3	179.9	448.3	925.7	1104.4
115°	157.3	197.4	446.8	858.5	1031.9
117.5°	174.1	213.9	446.0	805.8	960.8
120°	190.9	229.9	446.0	770.3	902.8
122.5°	206.2	245.6	445.3	747.0	857.0
125°	219.2	260.5	444.5	730.6	823.4
127.5°	231.4	274.2	443.0	714.9	802.0
130°	241.4	287.6	442.2	696.2	783.6
132.5°	251.3	299.0	441.5	674.0	763.0
135°	260.4	310.1	440.7	648.4	736.3
137.5°	269.6	319.6	440.7	621.0	705.0
140°	279.5	328.5	439.9	594.2	670.6
142.5°	290.2	336.4	439.9	569.4	633.9
145°	300.2	343.7	438.4	546.9	601.1
147.5°	311.6	350.5	436.1	528.2	570.5
150°	322.3	357.0	433.8	511.0	545.3
152.5°	332.2	363.2	430.0	496.4	522.4
155°	341.4	368.6	426.2	482.7	503.3
157.5°	350.6	373.5	422.4	469.7	485.8
160°	359.0	377.7	417.8	456.8	469.7
162.5°	366.6	381.2	413.2	444.2	454.4
165°	372.0	383.4	408.6	432.7	439.2
167.5°	378.1	385.3	404.0	422.8	427.0
170°	381.9	386.8	399.5	412.8	415.5
172.5°	385.7	388.0	394.9	404.0	404.0
175°	388.0	388.8	391.8	397.2	395.6
177.5°	389.5	388.8	389.5	392.2	389.5
180°	388.8	388.8	388.8	388.8	388.8

(END OF REPORT)