

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026736

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026736
REPORT IS A COMBINATION OF REPORTS P1001420 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6814.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026736

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026736

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10915	10915	10915
5°	10916	10662	10682
10°	10825	10417	10384
15°	10683	10125	10034
20°	10491	9786	9632
25°	10285	9416	9202
30°	10036	9031	8749
35°	9769	8627	8241
40°	9495	8200	7789
45°	9198	7784	7309
50°	8871	7313	6750
55°	8547	6792	6235
60°	8162	6243	5637
65°	7700	5608	5018
70°	7229	4878	4305
75°	6440	4017	3480
80°	5487	3000	2560
85°	4237	1775	1410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9198 cd/sqm

TEST NUMBER: P1026736

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.4
10°-20°	454.1	6.7
20°-30°	670.4	9.8
30°-40°	782.1	11.5
40°-50°	785.5	11.5
50°-60°	689.5	10.1
60°-70°	513.6	7.5
70°-80°	293.3	4.3
80°-90°	85.8	1.3
90°-100°	26.3	0.4
100°-110°	174.8	2.6
110°-120°	314.7	4.6
120°-130°	404.0	5.9
130°-140°	434.5	6.4
140°-150°	407.8	6.0
150°-160°	329.9	4.8
160°-170°	213.3	3.1
170°-180°	73.6	1.1
0°-30°	1285.2	18.9
0°-40°	2067.3	30.3
0°-60°	3542.4	52.0
0°-90°	4435.1	65.1
90°-120°	515.8	7.6
90°-150°	1762.1	25.9
90°-180°	2379.0	34.9
0°-180°	6814.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1704	1704	1704	1704	1704	
5°	1701	1698	1685	1697	1696	161
15°	1621	1617	1602	1609	1609	457
25°	1472	1465	1448	1450	1446	677
35°	1271	1266	1247	1240	1229	795
45°	1040	1035	1019	1003	999	802
55°	792	788	770	757	748	707
65°	535	532	518	505	500	531
75°	284	282	275	271	266	303
85°	74	76	76	74	71	81
90°	1	5	9	12	14	7
95°	33	31	9	12	12	40
105°	169	171	171	171	170	179
115°	317	320	320	318	315	314
125°	451	455	455	452	451	403
135°	562	566	564	563	560	433
145°	652	653	653	653	650	408
155°	718	714	715	717	712	331
165°	757	754	754	758	753	214
175°	774	771	772	776	771	74
180°	774	774	774	774	774	

TEST NUMBER: P1026736

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1703.6	1703.6	1703.6	1703.6	1703.6
2.5°	1709.0	1704.9	1691.5	1704.9	1703.6
5°	1700.9	1698.2	1684.7	1696.8	1695.5
7.5°	1688.8	1686.1	1671.2	1683.4	1682.0
10°	1671.2	1668.5	1653.7	1664.5	1663.1
12.5°	1649.7	1644.3	1630.8	1638.9	1638.9
15°	1621.4	1617.3	1602.5	1609.2	1609.2
17.5°	1591.7	1585.0	1570.2	1578.2	1571.5
20°	1552.6	1549.9	1532.4	1541.8	1535.1
22.5°	1513.5	1508.2	1492.0	1497.4	1493.3
25°	1471.8	1465.0	1447.5	1450.2	1446.2
27.5°	1423.2	1419.2	1401.7	1403.0	1399.0
30°	1376.1	1372.0	1351.8	1349.1	1345.1
32.5°	1324.9	1318.1	1300.6	1295.2	1287.1
35°	1270.9	1265.6	1246.7	1239.9	1229.2
37.5°	1215.7	1208.9	1191.4	1182.0	1175.3
40°	1159.1	1152.3	1133.5	1121.3	1117.3
42.5°	1098.4	1093.0	1074.2	1063.4	1056.7
45°	1040.5	1035.1	1018.9	1002.7	998.7
47.5°	977.1	978.5	958.3	942.1	932.7
50°	916.5	912.4	896.3	878.7	869.3
52.5°	854.5	851.8	834.3	819.4	808.7
55°	792.5	788.4	769.6	757.4	748.0
57.5°	726.4	725.1	708.9	692.8	688.7
60°	664.5	659.1	644.2	630.8	621.3
62.5°	599.8	595.7	583.6	568.8	562.0
65°	535.1	532.4	517.5	505.4	500.0
67.5°	471.7	466.3	455.5	444.8	442.1
70°	412.4	405.7	393.5	385.5	380.1
72.5°	347.7	343.7	336.9	327.5	322.1
75°	284.4	281.7	274.9	270.9	265.5
77.5°	225.1	223.7	219.7	217.0	212.9
80°	169.8	169.8	167.1	165.8	163.1
82.5°	121.3	118.6	118.6	115.9	115.9
85°	74.1	75.5	75.5	74.1	71.4
87.5°	36.4	36.4	35.0	35.0	32.3
90°	0.6	5.2	9.2	12.1	13.8
92.5°	10.9	5.7	9.2	12.1	12.6
95°	32.7	31.0	9.2	12.1	12.1
97.5°	61.4	64.9	10.3	11.5	12.1
100°	95.9	97.6	99.9	14.4	12.1
102.5°	130.9	133.2	134.3	135.5	87.3
105°	168.8	171.1	171.1	171.1	170.5
107.5°	207.8	207.8	209.0	209.5	207.2
110°	245.7	245.7	246.8	245.1	245.7

TEST NUMBER: P1026736

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.3	283.0	283.6	281.3	280.1
115°	316.9	319.8	320.3	318.0	314.6
117.5°	354.2	354.2	356.5	353.1	351.9
120°	388.6	388.1	389.8	388.6	385.8
122.5°	419.1	421.9	422.5	421.4	417.9
125°	450.6	454.7	454.7	452.4	450.6
127.5°	481.1	483.9	483.4	482.2	477.6
130°	508.6	511.5	512.1	510.3	507.5
132.5°	536.2	539.6	537.9	537.9	535.0
135°	562.0	565.5	564.3	563.2	559.7
137.5°	586.1	589.6	588.4	588.4	585.6
140°	609.7	610.8	610.2	611.4	607.9
142.5°	630.9	631.5	632.6	632.6	629.2
145°	651.6	652.7	652.7	653.3	649.8
147.5°	669.9	669.9	670.5	671.1	667.1
150°	687.2	686.0	687.2	688.3	683.7
152.5°	703.8	700.9	702.1	703.2	699.2
155°	717.6	714.1	715.3	717.0	712.4
157.5°	728.5	726.8	726.8	728.5	723.9
160°	740.0	736.5	737.1	739.4	734.8
162.5°	749.2	745.7	746.3	749.7	744.6
165°	757.2	753.8	754.3	757.8	753.2
167.5°	763.5	760.1	760.6	764.7	759.5
170°	768.7	764.7	765.2	769.8	764.7
172.5°	772.1	768.1	769.3	773.3	768.1
175°	774.4	771.0	771.5	776.1	771.0
177.5°	776.1	772.7	773.3	777.3	772.7
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)