

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026750

Luminaire Tested: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026750
REPORT IS A COMBINATION OF REPORTS P1001479 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7582.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026750

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026750

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	29	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1026750

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.1
10°-20°	452.1	6.0
20°-30°	667.5	8.8
30°-40°	778.8	10.3
40°-50°	782.2	10.3
50°-60°	686.6	9.1
60°-70°	511.4	6.7
70°-80°	292.1	3.9
80°-90°	85.8	1.1
90°-100°	35.0	0.5
100°-110°	232.6	3.1
110°-120°	418.8	5.5
120°-130°	537.6	7.1
130°-140°	578.2	7.6
140°-150°	542.6	7.2
150°-160°	438.9	5.8
160°-170°	283.9	3.7
170°-180°	97.9	1.3
0°-30°	1279.7	16.9
0°-40°	2058.4	27.1
0°-60°	3527.2	46.5
0°-90°	4416.5	58.3
90°-120°	686.3	9.1
90°-150°	2344.8	30.9
90°-180°	3165.0	41.7
0°-180°	7582.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	7	12	16	18	7
95°	44	41	12	16	16	53
105°	225	228	228	228	227	238
115°	422	426	426	423	419	418
125°	600	605	605	602	600	536
135°	748	752	751	749	745	577
145°	867	869	869	869	865	542
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1026750

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	0.8	6.9	12.2	16.0	18.3
92.5°	14.5	7.6	12.2	16.0	16.8
95°	43.5	41.3	12.2	16.0	16.0
97.5°	81.7	86.3	13.8	15.3	16.0
100°	127.6	129.9	132.9	19.1	16.0
102.5°	174.2	177.2	178.8	180.3	116.1
105°	224.6	227.6	227.6	227.6	226.9
107.5°	276.5	276.5	278.1	278.8	275.8
110°	326.9	326.9	328.5	326.2	326.9



TEST NUMBER: P1026750

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.3	376.6	377.4	374.3	372.8
115°	421.7	425.5	426.3	423.2	418.6
117.5°	471.3	471.3	474.4	469.8	468.3
120°	517.2	516.4	518.7	517.2	513.3
122.5°	557.6	561.5	562.2	560.7	556.1
125°	599.7	605.0	605.0	602.0	599.7
127.5°	640.1	644.0	643.2	641.7	635.6
130°	676.8	680.6	681.4	679.1	675.3
132.5°	713.5	718.1	715.8	715.8	712.0
135°	747.9	752.4	750.9	749.4	744.8
137.5°	779.9	784.5	783.0	783.0	779.2
140°	811.3	812.8	812.0	813.6	809.0
142.5°	839.5	840.3	841.8	841.8	837.2
145°	867.0	868.6	868.6	869.3	864.7
147.5°	891.5	891.5	892.2	893.0	887.6
150°	914.4	912.9	914.4	915.9	909.8
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)