

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026759

Luminaire Tested: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026759
REPORT IS A COMBINATION OF REPORTS P1001533 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8958.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026759

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026759

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	97	93	88	85	90	86	82	79	73	70	67	61	59	57	49	48	47
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39
3	80	70	63	57	74	65	59	53	55	50	46	46	43	39	38	35	33
4	73	62	54	48	67	58	50	45	49	44	39	41	37	34	34	31	28
5	67	55	47	41	62	51	44	38	44	38	34	37	32	29	30	27	24
6	62	50	41	35	57	46	39	33	39	34	29	33	29	25	27	24	21
7	57	45	37	31	53	42	34	29	36	30	26	30	26	22	25	22	19
8	53	41	33	27	49	38	31	26	33	27	23	28	23	20	23	20	17
9	49	37	29	24	46	35	28	23	30	24	20	25	21	18	21	18	15
10	46	34	27	22	43	32	25	21	27	22	18	23	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10124	10124	10124
5°	10140	9912	9936
10°	10065	9710	9682
15°	9942	9475	9370
20°	9776	9191	9059
25°	9581	8889	8684
30°	9344	8559	8343
35°	9122	8255	8028
40°	8897	7935	7711
45°	8641	7657	7426
50°	8397	7356	7169
55°	8103	7068	6870
60°	7782	6741	6564
65°	7445	6396	6219
70°	7061	5934	5859
75°	6453	5478	5421
80°	5658	4923	4937
85°	4871	4479	4682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8641 cd/sqm

TEST NUMBER: P1026759

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	1.7
10°-20°	424.5	4.7
20°-30°	631.2	7.0
30°-40°	747.5	8.3
40°-50°	772.8	8.6
50°-60°	711.9	7.9
60°-70°	575.5	6.4
70°-80°	385.1	4.3
80°-90°	201.0	2.2
90°-100°	157.0	1.8
100°-110°	381.0	4.3
110°-120°	592.6	6.6
120°-130°	721.0	8.0
130°-140°	755.5	8.4
140°-150°	698.9	7.8
150°-160°	563.1	6.3
160°-170°	364.2	4.1
170°-180°	125.6	1.4
0°-30°	1205.2	13.5
0°-40°	1952.7	21.8
0°-60°	3437.5	38.4
0°-90°	4599.1	51.3
90°-120°	1130.6	12.6
90°-150°	3305.9	36.9
90°-180°	4359.0	48.7
0°-180°	8958.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1577	1566	1579	1577	150
15°	1509	1510	1500	1509	1503	425
25°	1371	1376	1366	1373	1365	631
35°	1187	1198	1193	1198	1198	743
45°	978	995	1002	1013	1015	754
55°	751	776	801	818	824	672
65°	517	553	590	614	620	513
75°	285	325	375	406	414	302
85°	85	136	190	225	237	89
90°	26	83	143	183	197	20
95°	76	113	129	168	179	84
105°	302	331	377	408	418	320
115°	550	566	607	631	635	546
125°	776	781	812	833	838	692
135°	962	967	976	994	996	742
145°	1114	1114	1114	1123	1123	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1026759

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.1	1580.1	1580.1	1580.1	1580.1
2.5°	1584.8	1581.7	1570.8	1581.7	1580.1
5°	1580.1	1577.0	1566.2	1578.6	1577.0
7.5°	1569.3	1567.7	1556.9	1567.7	1566.2
10°	1553.8	1553.8	1541.4	1552.3	1550.7
12.5°	1532.1	1533.7	1524.4	1532.1	1527.5
15°	1508.9	1510.4	1499.6	1508.9	1502.7
17.5°	1479.4	1482.5	1471.7	1479.4	1474.8
20°	1446.9	1450.0	1439.2	1443.8	1443.8
22.5°	1409.7	1415.9	1403.5	1409.7	1405.1
25°	1371.0	1375.7	1366.4	1372.6	1364.8
27.5°	1329.2	1335.4	1324.5	1329.2	1326.1
30°	1281.2	1290.4	1281.2	1284.3	1282.7
32.5°	1237.8	1245.5	1239.3	1242.4	1240.9
35°	1186.7	1197.5	1192.9	1197.5	1197.5
37.5°	1137.1	1146.4	1144.8	1151.0	1149.5
40°	1086.0	1098.4	1096.8	1103.0	1106.1
42.5°	1030.2	1047.2	1051.9	1059.6	1059.6
45°	977.5	994.6	1002.3	1013.1	1014.7
47.5°	923.3	938.8	951.2	966.7	969.8
50°	867.5	884.6	901.6	918.7	923.3
52.5°	808.7	830.3	852.0	870.6	873.7
55°	751.3	776.1	800.9	818.0	824.2
57.5°	692.5	721.9	749.8	768.4	773.0
60°	633.6	664.6	695.6	718.8	723.5
62.5°	576.3	607.3	641.4	667.7	673.9
65°	517.4	553.0	590.2	613.5	619.7
67.5°	463.2	497.3	534.5	562.3	570.1
70°	402.8	438.4	478.7	508.1	517.4
72.5°	343.9	381.1	426.0	458.6	464.7
75°	285.0	325.3	374.9	405.9	413.6
77.5°	227.7	274.2	320.7	354.8	361.0
80°	175.1	221.5	274.2	308.3	314.5
82.5°	127.0	176.6	230.8	263.4	275.8
85°	85.2	136.3	190.5	224.6	237.0
87.5°	54.2	103.8	156.5	192.1	202.9
90°	25.8	83.2	142.7	183.3	197.0
92.5°	40.3	76.4	136.5	175.5	187.4
95°	76.0	113.3	128.8	167.8	178.6
97.5°	123.5	166.5	124.5	159.0	170.9
100°	180.7	216.2	269.6	156.2	161.6
102.5°	238.9	272.3	322.2	355.2	282.2
105°	302.0	330.7	377.2	408.2	418.1
107.5°	367.2	388.9	435.7	467.7	473.1
110°	430.2	448.8	494.2	520.7	532.5

TEST NUMBER: P1026759

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	491.0	507.9	550.7	574.7	583.5
115°	550.3	566.0	607.2	631.2	634.6
117.5°	612.4	620.2	662.8	683.3	692.2
120°	671.2	674.9	713.4	737.9	742.3
122.5°	721.6	728.0	763.1	785.9	789.4
125°	775.5	780.8	811.8	832.7	837.5
127.5°	825.9	829.3	854.6	875.9	877.4
130°	872.9	876.3	899.0	917.7	920.5
132.5°	918.4	924.3	936.9	958.6	959.9
135°	962.5	966.8	975.8	993.9	995.8
137.5°	1003.7	1008.0	1012.2	1030.8	1032.1
140°	1042.3	1044.2	1044.9	1063.8	1064.1
142.5°	1078.5	1078.0	1080.0	1093.9	1094.2
145°	1113.8	1114.3	1114.3	1123.0	1123.3
147.5°	1143.7	1143.7	1144.7	1148.7	1145.0
150°	1173.1	1171.1	1173.1	1175.0	1168.7
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)