

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026764

Luminaire Tested: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026764
REPORT IS A COMBINATION OF REPORTS P1001538 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9159.0 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026764

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026764

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	71	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12545	12253	12277
10°	12442	11972	11935
15°	12278	11637	11532
20°	12057	11247	11070
25°	11820	10822	10576
30°	11534	10379	10055
35°	11228	9915	9471
40°	10913	9424	8952
45°	10571	8946	8400
50°	10195	8404	7757
55°	9823	7806	7166
60°	9380	7176	6479
65°	8848	6446	5768
70°	8309	5607	4947
75°	7400	4617	4000
80°	6308	3449	2942
85°	4871	2039	1622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10571 cd/sqm

TEST NUMBER: P1026764

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.0
10°-20°	521.9	5.7
20°-30°	770.4	8.4
30°-40°	898.9	9.8
40°-50°	902.8	9.9
50°-60°	792.5	8.7
60°-70°	590.3	6.4
70°-80°	337.1	3.7
80°-90°	99.3	1.1
90°-100°	44.9	0.5
100°-110°	298.4	3.3
110°-120°	537.3	5.9
120°-130°	689.7	7.5
130°-140°	741.8	8.1
140°-150°	696.2	7.6
150°-160°	563.1	6.1
160°-170°	364.2	4.0
170°-180°	125.6	1.4
0°-30°	1477.1	16.1
0°-40°	2376.0	25.9
0°-60°	4071.3	44.5
0°-90°	5098.0	55.7
90°-120°	880.5	9.6
90°-150°	3008.1	32.8
90°-180°	4061.0	44.3
0°-180°	9159.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	93
90°	1	9	16	21	24	9
95°	56	53	16	21	21	68
105°	288	292	292	292	291	305
115°	541	546	547	543	537	536
125°	769	776	776	772	769	687
135°	959	965	963	961	956	740
145°	1112	1114	1114	1115	1109	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1026764

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	1.0	8.8	15.7	20.6	23.5
92.5°	18.6	9.8	15.7	20.6	21.6
95°	55.9	52.9	15.7	20.6	20.6
97.5°	104.9	110.7	17.6	19.6	20.6
100°	163.7	166.6	170.5	24.5	20.6
102.5°	223.4	227.4	229.3	231.3	149.0
105°	288.1	292.0	292.0	292.0	291.1
107.5°	354.8	354.8	356.7	357.7	353.8
110°	419.4	419.4	421.4	418.5	419.4

TEST NUMBER: P1026764

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	480.2	483.1	484.1	480.2	478.2
115°	541.0	545.9	546.8	542.9	537.0
117.5°	604.7	604.7	608.6	602.7	600.8
120°	663.5	662.5	665.4	663.5	658.6
122.5°	715.4	720.3	721.3	719.3	713.5
125°	769.3	776.2	776.2	772.3	769.3
127.5°	821.3	826.2	825.2	823.2	815.4
130°	868.3	873.2	874.2	871.2	866.3
132.5°	915.3	921.2	918.3	918.3	913.4
135°	959.4	965.3	963.4	961.4	955.5
137.5°	1000.6	1006.5	1004.5	1004.5	999.6
140°	1040.8	1042.7	1041.8	1043.7	1037.8
142.5°	1077.0	1078.0	1080.0	1080.0	1074.1
145°	1112.3	1114.3	1114.3	1115.3	1109.4
147.5°	1143.7	1143.7	1144.7	1145.6	1138.8
150°	1173.1	1171.1	1173.1	1175.0	1167.2
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)