

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026768

Luminaire Tested: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026768
REPORT IS A COMBINATION OF REPORTS P1001542 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8883.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026768

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026768

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	71	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12168	11886	11908
10°	12068	11613	11577
15°	11910	11287	11186
20°	11695	10909	10738
25°	11465	10497	10258
30°	11187	10068	9753
35°	10891	9618	9186
40°	10585	9142	8683
45°	10254	8678	8148
50°	9889	8152	7525
55°	9529	7571	6951
60°	9098	6960	6284
65°	8583	6253	5594
70°	8060	5438	4798
75°	7178	4478	3880
80°	6117	3345	2854
85°	4723	1977	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10254 cd/sqm

TEST NUMBER: P1026768

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	2.0
10°-20°	506.2	5.7
20°-30°	747.3	8.4
30°-40°	871.9	9.8
40°-50°	875.7	9.9
50°-60°	768.7	8.7
60°-70°	572.6	6.4
70°-80°	327.0	3.7
80°-90°	96.3	1.1
90°-100°	43.5	0.5
100°-110°	289.3	3.3
110°-120°	521.0	5.9
120°-130°	668.8	7.5
130°-140°	719.3	8.1
140°-150°	675.1	7.6
150°-160°	546.1	6.1
160°-170°	353.2	4.0
170°-180°	121.8	1.4
0°-30°	1432.7	16.1
0°-40°	2304.6	25.9
0°-60°	3949.0	44.5
0°-90°	4944.9	55.7
90°-120°	853.9	9.6
90°-150°	2917.1	32.8
90°-180°	3938.0	44.3
0°-180°	8883.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	90
90°	1	9	15	20	23	8
95°	54	51	15	20	20	66
105°	279	283	283	283	282	296
115°	525	529	530	526	521	520
125°	746	753	753	749	746	666
135°	930	936	934	932	927	717
145°	1079	1080	1080	1082	1076	675
155°	1188	1182	1184	1187	1179	547
165°	1254	1248	1249	1254	1247	354
175°	1282	1276	1277	1285	1276	122
180°	1282	1282	1282	1282	1282	

TEST NUMBER: P1026768

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	1.0	8.6	15.2	20.0	22.8
92.5°	18.1	9.5	15.2	20.0	20.9
95°	54.2	51.3	15.2	20.0	20.0
97.5°	101.7	107.4	17.1	19.0	20.0
100°	158.7	161.6	165.4	23.8	20.0
102.5°	216.7	220.5	222.4	224.3	144.5
105°	279.4	283.2	283.2	283.2	282.3
107.5°	344.0	344.0	345.9	346.9	343.1
110°	406.7	406.7	408.7	405.8	406.7



TEST NUMBER: P1026768

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	465.7	468.5	469.5	465.7	463.8
115°	524.6	529.3	530.3	526.5	520.8
117.5°	586.4	586.4	590.2	584.5	582.6
120°	643.4	642.4	645.3	643.4	638.6
122.5°	693.8	698.5	699.5	697.6	691.9
125°	746.0	752.7	752.7	748.9	746.0
127.5°	796.4	801.1	800.2	798.3	790.7
130°	842.0	846.8	847.7	844.9	840.1
132.5°	887.6	893.3	890.5	890.5	885.7
135°	930.4	936.1	934.2	932.3	926.6
137.5°	970.3	976.0	974.1	974.1	969.4
140°	1009.3	1011.2	1010.2	1012.1	1006.4
142.5°	1044.4	1045.4	1047.3	1047.3	1041.6
145°	1078.6	1080.5	1080.5	1081.5	1075.8
147.5°	1109.1	1109.1	1110.0	1111.0	1104.3
150°	1137.6	1135.7	1137.6	1139.5	1131.9
152.5°	1165.1	1160.4	1162.3	1164.2	1157.5
155°	1187.9	1182.2	1184.1	1187.0	1179.4
157.5°	1206.0	1203.1	1203.1	1206.0	1198.4
160°	1225.0	1219.3	1220.2	1224.1	1216.4
162.5°	1240.2	1234.5	1235.5	1241.2	1232.6
165°	1253.5	1247.8	1248.8	1254.5	1246.9
167.5°	1264.0	1258.3	1259.2	1265.9	1257.3
170°	1272.5	1265.9	1266.8	1274.4	1265.9
172.5°	1278.2	1271.6	1273.5	1280.1	1271.6
175°	1282.0	1276.3	1277.3	1284.9	1276.3
177.5°	1284.9	1279.2	1280.1	1286.8	1279.2
180°	1282.0	1282.0	1282.0	1282.0	1282.0

(END OF REPORT)