

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026563

Luminaire Tested: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026563
REPORT IS A COMBINATION OF REPORTS P999663 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7332.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026563

CATALOG NUMBER: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026563

CATALOG NUMBER: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11290	11290	11290
5°	11291	10954	10956
10°	11195	10609	10482
15°	11041	10178	9925
20°	10840	9688	9288
25°	10588	9158	8666
30°	10342	8618	7969
35°	10071	8071	7287
40°	9749	7481	6586
45°	9446	6897	5892
50°	9103	6258	5188
55°	8732	5603	4460
60°	8319	4909	3741
65°	7921	4112	3050
70°	7356	3272	2331
75°	6628	2381	1629
80°	5536	1462	1171
85°	4162	843	643

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9446 cd/sqm

TEST NUMBER: P1026563

CATALOG NUMBER: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.8
10°-20°	363.0	5.0
20°-30°	524.1	7.1
30°-40°	593.9	8.1
40°-50°	573.5	7.8
50°-60°	476.8	6.5
60°-70°	329.1	4.5
70°-80°	166.3	2.3
80°-90°	45.4	0.6
90°-100°	97.0	1.3
100°-110°	290.6	4.0
110°-120°	493.7	6.7
120°-130°	651.1	8.9
130°-140°	731.2	10.0
140°-150°	718.7	9.8
150°-160°	604.5	8.2
160°-170°	402.2	5.5
170°-180°	140.8	1.9
0°-30°	1017.2	13.9
0°-40°	1611.2	22.0
0°-60°	2661.4	36.3
0°-90°	3202.2	43.7
90°-120°	881.3	12.0
90°-150°	2982.3	40.7
90°-180°	4130.0	56.3
0°-180°	7332.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1384	1384	1384	1384	1384	
5°	1382	1378	1365	1376	1374	131
15°	1317	1307	1281	1278	1271	371
25°	1190	1171	1128	1110	1099	549
35°	1029	995	942	906	887	643
45°	840	800	737	685	666	647
55°	636	594	525	470	450	569
65°	432	387	319	274	261	427
75°	230	191	141	117	110	243
85°	57	36	33	31	31	63
90°	4	16	25	32	34	8
95°	69	79	88	91	91	75
105°	268	269	274	277	281	284
115°	502	502	500	498	497	495
125°	731	731	730	728	725	652
135°	943	950	950	947	944	729
145°	1145	1150	1151	1150	1146	717
155°	1312	1312	1311	1316	1311	604
165°	1429	1425	1423	1430	1425	403
175°	1486	1480	1479	1487	1479	141
180°	1488	1488	1488	1488	1488	

TEST NUMBER: P1026563

CATALOG NUMBER: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1384.5	1384.5	1384.5	1384.5	1384.5
2.5°	1388.7	1384.5	1372.8	1384.5	1383.4
5°	1382.4	1378.1	1365.4	1376.0	1373.9
7.5°	1372.8	1368.6	1352.7	1360.1	1356.9
10°	1358.0	1352.7	1333.6	1337.8	1333.6
12.5°	1338.9	1332.5	1309.2	1311.3	1305.0
15°	1316.6	1307.1	1280.6	1278.5	1271.1
17.5°	1291.2	1277.4	1246.7	1241.4	1230.8
20°	1260.5	1246.7	1210.6	1202.1	1188.4
22.5°	1226.5	1210.6	1171.4	1157.6	1147.0
25°	1190.5	1171.4	1127.9	1109.9	1099.3
27.5°	1153.4	1130.1	1084.5	1063.3	1048.4
30°	1114.2	1087.7	1037.8	1011.3	994.4
32.5°	1072.8	1042.1	990.1	958.3	942.4
35°	1029.4	995.4	942.4	906.4	887.3
37.5°	983.8	948.8	890.5	851.3	832.2
40°	935.0	900.0	839.6	795.1	776.0
42.5°	888.4	851.3	787.7	742.1	721.9
45°	839.6	800.4	736.8	684.8	665.7
47.5°	789.8	749.5	683.8	629.7	608.5
50°	738.9	697.5	629.7	576.7	556.6
52.5°	686.9	646.7	576.7	522.6	501.4
55°	636.1	593.7	524.7	469.6	449.5
57.5°	586.2	541.7	473.9	417.7	402.8
60°	532.2	489.8	421.9	366.8	349.8
62.5°	483.4	438.9	368.9	319.1	306.4
65°	432.5	386.9	319.1	273.5	260.8
67.5°	379.5	336.1	272.4	232.2	217.3
70°	329.7	285.2	224.7	189.8	179.2
72.5°	276.7	237.5	181.3	152.7	143.1
75°	230.0	190.8	141.0	116.6	110.2
77.5°	181.3	147.4	104.9	88.0	85.9
80°	134.6	103.9	72.1	68.9	67.8
82.5°	94.3	66.8	51.9	49.8	48.8
85°	57.2	36.0	32.9	30.7	30.7
87.5°	24.4	15.9	14.8	13.8	14.8
90°	3.5	16.1	25.3	32.2	34.5
92.5°	29.9	44.9	50.7	54.1	55.3
95°	69.1	79.4	87.5	90.9	90.9
97.5°	110.5	119.7	128.9	133.5	133.5
100°	161.2	165.8	176.1	178.4	178.4
102.5°	214.1	215.3	224.5	227.9	229.1
105°	268.2	269.4	274.0	277.4	280.9
107.5°	324.6	325.8	326.9	331.5	330.4
110°	382.2	384.5	383.3	381.0	384.5

TEST NUMBER: P1026563

CATALOG NUMBER: S124RDIP-B795D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	442.0	442.0	439.7	439.7	439.7
115°	501.9	501.9	499.6	498.4	497.3
117.5°	558.3	558.3	557.2	553.7	550.2
120°	614.7	619.3	615.9	610.1	612.4
122.5°	673.4	674.6	673.4	670.0	664.2
125°	731.0	731.0	729.8	727.5	725.2
127.5°	782.8	786.2	783.9	781.6	780.5
130°	838.0	841.5	841.5	839.2	834.6
132.5°	894.4	896.7	895.6	893.3	892.1
135°	942.8	949.7	949.7	947.4	943.9
137.5°	996.9	1000.3	1002.6	999.2	1000.3
140°	1051.0	1053.3	1053.3	1052.1	1051.0
142.5°	1100.5	1102.8	1101.6	1101.6	1101.6
145°	1145.4	1150.0	1151.1	1150.0	1146.5
147.5°	1191.4	1197.2	1196.0	1194.9	1193.7
150°	1232.9	1237.5	1237.5	1237.5	1236.3
152.5°	1272.0	1274.3	1275.5	1278.9	1275.5
155°	1312.3	1312.3	1311.1	1315.7	1311.1
157.5°	1346.8	1344.5	1344.5	1348.0	1344.5
160°	1376.8	1375.6	1374.5	1377.9	1372.2
162.5°	1404.4	1400.9	1399.8	1406.7	1400.9
165°	1428.6	1425.1	1422.8	1429.7	1425.1
167.5°	1448.1	1443.5	1443.5	1450.4	1443.5
170°	1464.2	1458.5	1459.6	1466.5	1458.5
172.5°	1475.8	1471.2	1471.2	1479.2	1471.2
175°	1486.1	1480.4	1479.2	1487.3	1479.2
177.5°	1490.7	1485.0	1485.0	1493.0	1483.8
180°	1488.4	1488.4	1488.4	1488.4	1488.4

(END OF REPORT)