

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026785

Luminaire Tested: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026785
REPORT IS A COMBINATION OF REPORTS P1001649 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6668.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	104	100	96	93	100	96	92	89	87	85	82	80	78	76	73	71	70
2	95	88	82	76	91	84	78	74	77	73	69	71	67	64	65	62	59
3	87	78	70	64	83	74	67	62	68	63	58	63	58	54	57	54	51
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	52	47	44
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	47	42	39
6	68	56	47	41	65	53	46	40	49	43	38	46	40	36	42	38	34
7	63	50	42	36	60	48	41	35	45	38	34	42	36	32	39	34	30
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27
9	55	42	34	29	52	41	33	28	38	31	27	35	30	26	33	28	25
10	51	39	31	26	49	37	30	26	35	29	24	33	27	23	30	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11793	11793	11793	11793
5°	11802	13378	11812	10149
10°	11730	15249	11710	8712
15°	11644	16534	11572	7872
20°	11497	18118	11391	7186
25°	11367	20759	11159	6780
30°	11179	21901	10985	6412
35°	10882	17556	10653	6117
40°	10419	12134	10265	5806
45°	9834	9034	9724	5546
50°	9165	7437	9014	5338
55°	8443	6343	8376	5158
60°	7734	5429	7600	5018
65°	6970	4689	6858	4814
70°	6163	3893	6081	4460
75°	5307	3011	5237	3871
80°	4191	2036	4039	2846
85°	2682	1019	2590	1450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18013 cd/sqm

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.2	2.7
10°-20°	527.7	7.9
20°-30°	857.1	12.9
30°-40°	1047.5	15.7
40°-50°	950.2	14.2
50°-60°	756.8	11.3
60°-70°	527.1	7.9
70°-80°	280.8	4.2
80°-90°	70.3	1.1
90°-100°	16.3	0.2
100°-110°	108.2	1.6
110°-120°	194.9	2.9
120°-130°	250.2	3.8
130°-140°	269.1	4.0
140°-150°	252.6	3.8
150°-160°	204.3	3.1
160°-170°	132.1	2.0
170°-180°	45.6	0.7
0°-30°	1561.9	23.4
0°-40°	2609.4	39.1
0°-60°	4316.4	64.7
0°-90°	5194.7	77.9
90°-120°	319.5	4.8
90°-150°	1091.3	16.4
90°-180°	1473.0	22.1
0°-180°	6668.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1841	1841	1841	1841	1841	
5°	1839	2123	1841	1611	1839	175
15°	1767	2652	1756	1262	1767	499
25°	1627	3262	1597	1066	1627	749
35°	1416	2619	1386	912	1416	884
45°	1112	1234	1100	758	1112	857
55°	783	761	777	619	783	700
65°	484	467	477	480	484	481
75°	234	230	231	295	234	249
85°	47	52	45	73	47	56
90°	0	8	0	8	0	4
95°	20	8	20	8	20	25
105°	104	106	104	106	104	111
115°	196	195	196	195	196	195
125°	279	279	279	279	279	249
135°	348	347	348	347	348	268
145°	404	402	404	402	404	252
155°	444	441	444	441	444	205
165°	469	466	469	466	469	132
175°	480	478	480	478	480	46
180°	480	480	480	480	480	

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1843.8	1854.7	1867.2	1876.6	1892.2	1896.9	1904.7	1909.4	1914.1	1918.8	1921.9
5°	1839.1	1865.6	1889.1	1906.3	1935.9	1946.9	1960.9	1978.1	1998.4	2015.6	2026.6
7.5°	1826.6	1868.8	1900.0	1934.4	1975.0	2001.6	2015.6	2051.6	2084.4	2109.4	2142.2
10°	1810.9	1860.9	1909.4	1960.9	2018.8	2048.4	2076.6	2126.6	2171.9	2212.5	2245.3
12.5°	1793.8	1854.7	1912.5	1979.7	2057.8	2093.8	2112.5	2198.4	2254.7	2276.6	2340.6
15°	1767.2	1839.1	1921.9	2004.7	2070.3	2112.5	2164.1	2232.8	2289.1	2337.5	2389.1
17.5°	1742.2	1820.3	1904.7	1996.9	2092.2	2146.9	2185.9	2246.9	2307.8	2370.3	2418.8
20°	1701.6	1803.1	1889.1	1987.5	2100.0	2139.1	2179.7	2251.6	2317.2	2384.4	2445.3
22.5°	1668.8	1765.6	1882.8	1976.6	2071.9	2110.9	2160.9	2235.9	2314.1	2390.6	2479.7
25°	1626.6	1734.4	1835.9	1935.9	2034.4	2076.6	2121.9	2218.8	2300.0	2398.4	2496.9
27.5°	1581.3	1692.2	1793.8	1884.4	1976.6	2034.4	2082.8	2184.4	2292.2	2400.0	2528.1
30°	1532.8	1637.5	1734.4	1823.4	1925.0	1984.4	2032.8	2151.6	2271.9	2409.4	2562.5
32.5°	1481.3	1579.7	1662.5	1753.1	1860.9	1915.6	1981.3	2110.9	2253.1	2417.2	2609.4
35°	1415.6	1509.4	1582.8	1675.0	1782.8	1853.1	1921.9	2067.2	2232.8	2415.6	2635.9
37.5°	1350.0	1423.4	1493.8	1592.2	1717.2	1781.3	1853.1	2012.5	2201.6	2410.9	2646.9
40°	1271.9	1343.8	1404.7	1504.7	1635.9	1709.4	1784.4	1951.6	2165.6	2393.8	2607.8
42.5°	1193.8	1254.7	1321.9	1426.6	1553.1	1631.3	1710.9	1896.9	2118.8	2343.8	2500.0
45°	1112.5	1159.4	1232.8	1328.1	1462.5	1537.5	1628.1	1829.7	2053.1	2253.1	2331.3
47.5°	1028.1	1075.0	1143.8	1235.9	1368.8	1457.8	1543.8	1745.3	1970.3	2125.0	2125.0
50°	946.9	984.4	1051.6	1143.8	1278.1	1359.4	1446.9	1660.9	1842.2	1956.3	1854.7
52.5°	859.4	901.6	957.8	1054.7	1187.5	1260.9	1356.3	1539.1	1710.9	1757.8	1601.6
55°	782.8	817.2	870.3	962.5	1085.9	1162.5	1243.8	1418.8	1564.1	1560.9	1393.8
57.5°	703.1	731.3	787.5	871.9	985.9	1054.7	1135.9	1287.5	1406.3	1364.1	1206.3
60°	629.7	650.0	704.7	773.4	882.8	946.9	1025.0	1148.4	1239.1	1179.7	1020.3
62.5°	553.1	576.6	620.3	687.5	784.4	835.9	893.8	1018.8	1076.6	1023.4	860.9
65°	484.4	503.1	542.2	598.4	685.9	732.8	782.8	885.9	940.6	864.1	729.7
67.5°	415.6	437.5	465.6	515.6	584.4	628.1	671.9	760.9	785.9	717.2	604.7
70°	351.6	370.3	396.9	432.8	490.6	529.7	562.5	635.9	653.1	589.1	500.0
72.5°	289.1	301.6	323.4	353.1	406.3	428.1	462.5	512.5	534.4	476.6	412.5
75°	234.4	243.8	257.8	279.7	315.6	339.1	367.2	414.1	412.5	371.9	326.6
77.5°	181.3	182.8	198.4	218.8	240.6	260.9	275.0	307.8	310.9	285.9	248.4
80°	129.7	134.4	140.6	156.3	175.0	182.8	200.0	220.3	223.4	204.7	179.7
82.5°	82.8	85.9	90.6	100.0	112.5	121.9	131.3	139.1	146.9	135.9	115.6
85°	46.9	48.4	53.1	56.3	62.5	67.2	75.0	82.8	81.3	73.4	67.2
87.5°	23.4	23.4	23.4	26.6	29.7	29.7	32.8	34.4	35.9	32.8	29.7
90°	0.4	1.0	1.6	2.3	2.9	3.2	3.5	4.0	4.6	5.1	5.7
92.5°	6.8	6.1	5.4	4.7	4.0	3.6	3.8	4.3	4.8	5.2	5.7
95°	20.3	20.1	19.8	19.6	19.3	19.2	17.7	14.7	11.7	8.7	5.7
97.5°	38.0	38.5	39.0	39.5	40.0	40.2	36.4	28.9	21.4	13.9	6.4
100°	59.4	59.6	59.8	60.1	60.3	60.4	60.6	60.9	61.2	61.6	61.9
102.5°	81.1	81.4	81.7	82.0	82.3	82.5	82.6	82.7	82.9	83.0	83.2
105°	104.5	104.8	105.1	105.4	105.7	105.9	105.9	105.9	105.9	105.9	105.9
107.5°	128.7	128.7	128.7	128.7	128.7	128.7	128.8	128.9	129.1	129.2	129.4
110°	152.2	152.2	152.2	152.2	152.2	152.2	152.3	152.4	152.6	152.7	152.9



TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.2	174.4	174.7	174.9	175.2	175.3	175.3	175.4	175.5	175.5	175.6
115°	196.3	196.7	197.1	197.4	197.8	198.0	198.0	198.1	198.2	198.3	198.4
117.5°	219.4	219.4	219.4	219.4	219.4	219.4	219.6	219.9	220.2	220.5	220.8
120°	240.7	240.6	240.5	240.4	240.3	240.3	240.4	240.7	240.9	241.2	241.4
122.5°	259.5	259.9	260.3	260.7	261.1	261.3	261.3	261.4	261.5	261.6	261.7
125°	279.1	279.7	280.2	280.8	281.3	281.6	281.6	281.6	281.6	281.6	281.6
127.5°	297.9	298.3	298.7	299.1	299.5	299.7	299.7	299.6	299.5	299.5	299.4
130°	315.0	315.4	315.8	316.2	316.6	316.8	316.8	316.9	317.0	317.0	317.1
132.5°	332.1	332.6	333.0	333.5	334.0	334.2	334.1	333.8	333.6	333.3	333.1
135°	348.1	348.6	349.0	349.5	350.0	350.2	350.1	350.0	349.8	349.7	349.5
137.5°	363.0	363.5	363.9	364.4	364.9	365.1	365.0	364.9	364.7	364.6	364.4
140°	377.6	377.8	377.9	378.1	378.2	378.3	378.3	378.2	378.1	378.0	377.9
142.5°	390.7	390.8	390.9	391.0	391.1	391.1	391.2	391.3	391.5	391.6	391.8
145°	403.5	403.7	403.8	404.0	404.1	404.2	404.2	404.2	404.2	404.2	404.2
147.5°	414.9	414.9	414.9	414.9	414.9	414.9	414.9	415.0	415.1	415.2	415.3
150°	425.6	425.4	425.3	425.1	425.0	424.9	425.0	425.1	425.3	425.4	425.6
152.5°	435.9	435.5	435.1	434.7	434.3	434.1	434.2	434.3	434.5	434.6	434.8
155°	444.4	443.9	443.5	443.0	442.5	442.3	442.4	442.5	442.7	442.8	443.0
157.5°	451.2	451.0	450.7	450.5	450.2	450.1	450.1	450.1	450.1	450.1	450.1
160°	458.3	457.8	457.4	456.9	456.4	456.2	456.2	456.3	456.4	456.4	456.5
162.5°	464.0	463.5	463.0	462.5	462.0	461.8	461.8	461.9	462.0	462.1	462.2
165°	469.0	468.5	468.0	467.5	467.0	466.8	466.8	466.9	467.0	467.1	467.2
167.5°	472.9	472.4	471.9	471.4	470.9	470.7	470.7	470.8	470.9	471.0	471.1
170°	476.1	475.5	475.0	474.4	473.9	473.6	473.6	473.7	473.8	473.8	473.9
172.5°	478.2	477.6	477.1	476.5	476.0	475.7	475.8	475.9	476.1	476.2	476.4
175°	479.6	479.1	478.7	478.2	477.7	477.5	477.5	477.6	477.7	477.7	477.8
177.5°	480.7	480.2	479.8	479.3	478.8	478.6	478.6	478.7	478.8	478.8	478.9
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1925.0	1935.9	1945.3	1953.1	1959.4	1968.8	1962.5	1964.1	1967.2	1973.4	1973.4
5°	2050.0	2067.2	2076.6	2107.8	2115.6	2114.1	2109.4	2134.4	2132.8	2123.4	2121.9
7.5°	2171.9	2201.6	2228.1	2253.1	2260.9	2281.3	2285.9	2296.9	2293.8	2309.4	2301.6
10°	2282.8	2329.7	2354.7	2392.2	2401.6	2410.9	2423.4	2429.7	2443.8	2442.2	2442.2
12.5°	2368.8	2425.0	2457.8	2467.2	2503.1	2514.1	2525.0	2545.3	2540.6	2542.2	2551.6
15°	2435.9	2490.6	2518.8	2562.5	2587.5	2600.0	2618.8	2640.6	2637.5	2651.6	2648.4
17.5°	2485.9	2537.5	2589.1	2654.7	2656.3	2689.1	2732.8	2742.2	2762.5	2748.4	2748.4
20°	2526.6	2595.3	2668.8	2753.1	2762.5	2782.8	2835.9	2871.9	2895.3	2887.5	2892.2
22.5°	2570.3	2668.8	2754.7	2839.1	2884.4	2920.3	2971.9	3028.1	3048.5	3061.0	3057.8
25°	2626.6	2729.7	2856.3	2973.5	3020.3	3089.1	3157.8	3212.5	3228.1	3262.5	3231.3
27.5°	2684.4	2829.7	2987.5	3125.0	3184.4	3240.6	3323.5	3364.1	3384.4	3400.0	3389.1
30°	2732.8	2932.8	3104.7	3231.3	3273.5	3306.3	3353.1	3362.5	3354.7	3367.2	3382.8
32.5°	2807.8	3003.1	3148.5	3209.4	3204.7	3203.1	3167.2	3117.2	3106.3	3076.6	3117.2
35°	2848.4	3004.7	3061.0	2979.7	2946.9	2887.5	2773.4	2698.4	2632.8	2618.8	2621.9
37.5°	2825.0	2886.0	2818.8	2604.7	2551.6	2460.9	2309.4	2203.1	2154.7	2117.2	2165.6
40°	2698.4	2631.3	2446.9	2185.9	2109.4	2023.4	1881.3	1823.4	1754.7	1740.6	1804.7
42.5°	2489.1	2284.4	2023.4	1821.9	1742.2	1693.8	1575.0	1520.3	1471.9	1450.0	1485.9
45°	2204.7	1956.3	1693.8	1528.1	1460.9	1403.1	1332.8	1275.0	1243.8	1234.4	1264.1
47.5°	1910.9	1648.4	1439.1	1315.6	1245.3	1201.6	1135.9	1103.1	1078.1	1081.3	1085.9
50°	1629.7	1390.6	1229.7	1106.3	1071.9	1037.5	993.8	965.6	953.1	957.8	954.7
52.5°	1387.5	1193.8	1057.8	962.5	946.9	914.1	878.1	854.7	850.0	851.6	856.3
55°	1175.0	1023.4	915.6	846.9	829.7	806.3	784.4	768.8	756.3	760.9	759.4
57.5°	1014.1	881.3	798.4	742.2	729.7	715.6	695.3	687.5	682.8	673.4	681.3
60°	871.9	764.1	692.2	657.8	646.9	637.5	615.6	606.3	603.1	598.4	610.9
62.5°	737.5	660.9	606.3	575.0	564.1	554.7	543.8	535.9	537.5	531.3	537.5
65°	631.3	568.8	529.7	501.6	487.5	481.3	479.7	467.2	465.6	467.2	468.8
67.5°	532.8	479.7	450.0	432.8	421.9	415.6	410.9	403.1	409.4	404.7	407.8
70°	443.8	407.8	376.6	359.4	354.7	356.3	348.4	345.3	346.9	343.8	346.9
72.5°	357.8	328.1	315.6	303.1	296.9	295.3	290.6	285.9	290.6	289.1	289.1
75°	285.9	264.1	250.0	242.2	242.2	239.1	231.3	231.3	231.3	229.7	231.3
77.5°	220.3	201.6	195.3	187.5	187.5	182.8	181.3	181.3	178.1	182.8	179.7
80°	164.1	150.0	140.6	135.9	135.9	134.4	131.3	129.7	131.3	129.7	129.7
82.5°	106.3	100.0	95.3	90.6	89.1	90.6	89.1	85.9	87.5	85.9	89.1
85°	60.9	54.7	54.7	51.6	53.1	50.0	51.6	48.4	46.9	51.6	48.4
87.5°	26.6	25.0	25.0	21.9	21.9	21.9	20.3	21.9	20.3	18.8	20.3
90°	6.1	6.5	6.9	7.3	7.5	7.6	7.8	8.1	8.3	8.5	8.3
92.5°	6.1	6.5	6.9	7.3	7.5	7.5	7.6	7.7	7.7	7.8	7.7
95°	6.1	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5	7.5	7.5
97.5°	6.6	6.7	6.9	7.0	7.1	7.1	7.2	7.3	7.4	7.5	7.4
100°	50.1	38.3	26.6	14.8	8.9	8.7	8.4	8.1	7.8	7.5	7.8
102.5°	83.4	83.5	83.7	83.8	83.9	80.6	73.9	67.3	60.6	54.0	60.6
105°	105.9	105.9	105.9	105.9	105.9	105.9	105.8	105.7	105.7	105.6	105.7
107.5°	129.5	129.6	129.7	129.8	129.8	129.6	129.3	129.0	128.6	128.3	128.6
110°	152.7	152.4	152.2	151.9	151.8	151.8	151.9	152.0	152.1	152.2	152.1

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	175.3	175.0	174.7	174.4	174.2	174.1	174.0	173.8	173.7	173.5	173.7
115°	198.1	197.8	197.5	197.2	197.0	196.8	196.3	195.8	195.3	194.8	195.3
117.5°	220.3	219.9	219.4	218.9	218.7	218.6	218.4	218.3	218.1	217.9	218.1
120°	241.2	241.1	240.9	240.8	240.7	240.5	240.1	239.7	239.3	238.9	239.3
122.5°	261.5	261.4	261.2	261.1	261.0	260.8	260.3	259.8	259.3	258.8	259.3
125°	281.3	281.0	280.7	280.4	280.2	280.1	279.8	279.6	279.3	279.1	279.3
127.5°	299.2	299.1	298.9	298.8	298.7	298.4	297.7	297.1	296.4	295.8	296.4
130°	316.9	316.7	316.4	316.2	316.1	315.9	315.5	315.1	314.7	314.3	314.7
132.5°	333.1	333.1	333.1	333.1	333.1	332.9	332.5	332.2	331.8	331.4	331.8
135°	349.3	349.2	349.0	348.9	348.8	348.6	348.1	347.6	347.1	346.6	347.1
137.5°	364.4	364.4	364.4	364.4	364.4	364.2	363.8	363.4	363.0	362.6	363.0
140°	378.1	378.2	378.4	378.5	378.6	378.4	377.9	377.4	377.0	376.5	377.0
142.5°	391.8	391.8	391.8	391.8	391.8	391.6	391.1	390.6	390.2	389.7	390.2
145°	404.3	404.4	404.5	404.6	404.6	404.4	403.9	403.4	403.0	402.5	403.0
147.5°	415.4	415.4	415.5	415.6	415.6	415.3	414.8	414.2	413.7	413.1	413.7
150°	425.8	425.9	426.1	426.2	426.3	426.0	425.3	424.7	424.0	423.4	424.0
152.5°	435.0	435.1	435.3	435.4	435.5	435.2	434.7	434.1	433.6	433.0	433.6
155°	443.2	443.5	443.7	444.0	444.1	443.8	443.1	442.5	441.8	441.2	441.8
157.5°	450.3	450.6	450.8	451.1	451.2	450.9	450.2	449.6	448.9	448.3	448.9
160°	456.8	457.1	457.4	457.7	457.9	457.6	457.0	456.3	455.7	455.1	455.7
162.5°	462.7	463.1	463.6	464.1	464.3	463.9	463.2	462.5	461.8	461.1	461.8
165°	467.7	468.1	468.6	469.1	469.3	469.0	468.4	467.7	467.1	466.5	467.1
167.5°	471.7	472.2	472.8	473.3	473.6	473.2	472.5	471.8	471.1	470.4	471.1
170°	474.5	475.2	475.8	476.5	476.8	476.4	475.7	475.0	474.3	473.6	474.3
172.5°	477.0	477.5	478.1	478.6	478.9	478.5	477.8	477.1	476.4	475.7	476.4
175°	478.4	479.1	479.7	480.4	480.7	480.3	479.6	478.9	478.2	477.5	478.2
177.5°	479.5	480.0	480.6	481.1	481.4	481.1	480.5	479.8	479.2	478.6	479.2
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1970.3	1959.4	1962.5	1959.4	1951.6	1946.9	1934.4	1918.8	1912.5	1904.7	1900.0
5°	2128.1	2120.3	2118.8	2106.3	2103.1	2084.4	2053.1	2037.5	2018.8	2000.0	1981.3
7.5°	2300.0	2290.6	2259.4	2254.7	2257.8	2234.4	2193.8	2162.5	2123.4	2096.9	2060.9
10°	2442.2	2423.4	2396.9	2398.4	2387.5	2356.3	2315.6	2282.8	2226.6	2192.2	2140.6
12.5°	2528.1	2512.5	2509.4	2493.8	2484.4	2443.8	2395.3	2353.1	2310.9	2264.1	2225.0
15°	2632.8	2612.5	2598.4	2576.6	2570.3	2528.1	2475.0	2426.6	2378.1	2334.4	2251.6
17.5°	2748.4	2726.6	2673.4	2668.8	2631.3	2590.6	2539.1	2467.2	2415.6	2353.1	2292.2
20°	2879.7	2848.4	2779.7	2762.5	2732.8	2665.6	2595.3	2515.6	2432.8	2368.8	2296.9
22.5°	3026.6	2971.9	2921.9	2867.2	2845.3	2762.5	2665.6	2568.8	2468.8	2381.3	2295.3
25°	3217.2	3145.3	3075.0	3020.3	2982.8	2875.0	2745.3	2617.2	2501.6	2387.5	2275.0
27.5°	3367.2	3304.7	3228.1	3156.3	3107.8	2979.7	2831.3	2665.6	2521.9	2382.8	2262.5
30°	3378.1	3359.4	3312.5	3273.5	3220.3	3082.8	2918.8	2731.3	2553.1	2384.4	2237.5
32.5°	3173.5	3211.0	3231.3	3237.5	3226.6	3146.9	2996.9	2790.6	2581.3	2370.3	2215.6
35°	2732.8	2832.8	2956.3	3003.1	3048.5	3090.6	3012.5	2832.8	2590.6	2367.2	2181.3
37.5°	2250.0	2340.6	2545.3	2639.1	2692.2	2859.4	2923.5	2826.6	2609.4	2370.3	2148.4
40°	1815.6	1959.4	2106.3	2232.8	2315.6	2503.1	2701.6	2723.4	2582.8	2340.6	2106.3
42.5°	1528.1	1612.5	1723.4	1840.6	1914.1	2135.9	2404.7	2562.5	2500.0	2292.2	2054.7
45°	1301.6	1364.1	1468.8	1507.8	1601.6	1814.1	2098.4	2326.6	2357.8	2215.6	1995.3
47.5°	1117.2	1170.3	1237.5	1285.9	1360.9	1520.3	1760.9	2012.5	2162.5	2110.9	1912.5
50°	984.4	1028.1	1084.4	1112.5	1160.9	1304.7	1485.9	1735.9	1937.5	1954.7	1804.7
52.5°	873.4	898.4	942.2	973.4	1012.5	1100.0	1264.1	1470.3	1696.9	1790.6	1671.9
55°	776.6	796.9	835.9	856.3	876.6	951.6	1079.7	1267.2	1479.7	1603.1	1535.9
57.5°	689.1	706.3	739.1	757.8	768.8	840.6	939.1	1085.9	1276.6	1426.6	1389.1
60°	617.2	632.8	651.6	665.6	678.1	737.5	806.3	925.0	1095.3	1240.6	1231.3
62.5°	540.6	554.7	575.0	589.1	600.0	637.5	695.3	785.9	931.3	1065.6	1092.2
65°	473.4	484.4	498.4	504.7	518.8	546.9	593.8	675.0	793.8	914.1	932.8
67.5°	412.5	415.6	425.0	439.1	442.2	467.2	509.4	570.3	662.5	760.9	790.6
70°	346.9	351.6	359.4	370.3	376.6	392.2	428.1	468.8	548.4	634.4	656.3
72.5°	289.1	295.3	298.4	304.7	307.8	332.8	348.4	389.1	443.8	515.6	539.1
75°	234.4	240.6	242.2	245.3	248.4	259.4	281.3	306.3	351.6	398.4	429.7
77.5°	185.9	184.4	187.5	192.2	190.6	200.0	214.1	235.9	265.6	304.7	325.0
80°	131.3	131.3	135.9	140.6	139.1	148.4	153.1	168.8	193.8	218.8	226.6
82.5°	87.5	87.5	92.2	92.2	95.3	96.9	103.1	110.9	131.3	143.8	148.4
85°	50.0	50.0	51.6	51.6	51.6	54.7	59.4	62.5	68.8	76.6	79.7
87.5°	20.3	21.9	21.9	21.9	21.9	25.0	25.0	28.1	29.7	32.8	32.8
90°	8.1	7.8	7.6	7.5	7.3	6.9	6.5	6.1	5.7	5.1	4.6
92.5°	7.7	7.6	7.5	7.5	7.3	6.9	6.5	6.1	5.7	5.2	4.8
95°	7.5	7.5	7.5	7.5	7.3	6.9	6.5	6.1	5.7	8.7	11.7
97.5°	7.3	7.2	7.1	7.1	7.0	6.9	6.7	6.6	6.4	13.9	21.4
100°	8.1	8.4	8.7	8.9	14.8	26.6	38.3	50.1	61.9	61.6	61.2
102.5°	67.3	73.9	80.6	83.9	83.8	83.7	83.5	83.4	83.2	83.0	82.9
105°	105.7	105.8	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9
107.5°	129.0	129.3	129.6	129.8	129.8	129.7	129.6	129.5	129.4	129.2	129.1
110°	152.0	151.9	151.8	151.8	151.9	152.2	152.4	152.7	152.9	152.7	152.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	173.8	174.0	174.1	174.2	174.4	174.7	175.0	175.3	175.6	175.5	175.5
115°	195.8	196.3	196.8	197.0	197.2	197.5	197.8	198.1	198.4	198.3	198.2
117.5°	218.3	218.4	218.6	218.7	218.9	219.4	219.9	220.3	220.8	220.5	220.2
120°	239.7	240.1	240.5	240.7	240.8	240.9	241.1	241.2	241.4	241.2	240.9
122.5°	259.8	260.3	260.8	261.0	261.1	261.2	261.4	261.5	261.7	261.6	261.5
125°	279.6	279.8	280.1	280.2	280.4	280.7	281.0	281.3	281.6	281.6	281.6
127.5°	297.1	297.7	298.4	298.7	298.8	298.9	299.1	299.2	299.4	299.5	299.5
130°	315.1	315.5	315.9	316.1	316.2	316.4	316.7	316.9	317.1	317.0	317.0
132.5°	332.2	332.5	332.9	333.1	333.1	333.1	333.1	333.1	333.1	333.3	333.6
135°	347.6	348.1	348.6	348.8	348.9	349.0	349.2	349.3	349.5	349.7	349.8
137.5°	363.4	363.8	364.2	364.4	364.4	364.4	364.4	364.4	364.4	364.6	364.7
140°	377.4	377.9	378.4	378.6	378.5	378.4	378.2	378.1	377.9	378.0	378.1
142.5°	390.6	391.1	391.6	391.8	391.8	391.8	391.8	391.8	391.8	391.6	391.5
145°	403.4	403.9	404.4	404.6	404.6	404.5	404.4	404.3	404.2	404.2	404.2
147.5°	414.2	414.8	415.3	415.6	415.6	415.5	415.4	415.4	415.3	415.2	415.1
150°	424.7	425.3	426.0	426.3	426.2	426.1	425.9	425.8	425.6	425.4	425.3
152.5°	434.1	434.7	435.2	435.5	435.4	435.3	435.1	435.0	434.8	434.6	434.5
155°	442.5	443.1	443.8	444.1	444.0	443.7	443.5	443.2	443.0	442.8	442.7
157.5°	449.6	450.2	450.9	451.2	451.1	450.8	450.6	450.3	450.1	450.1	450.1
160°	456.3	457.0	457.6	457.9	457.7	457.4	457.1	456.8	456.5	456.4	456.4
162.5°	462.5	463.2	463.9	464.3	464.1	463.6	463.1	462.7	462.2	462.1	462.0
165°	467.7	468.4	469.0	469.3	469.1	468.6	468.1	467.7	467.2	467.1	467.0
167.5°	471.8	472.5	473.2	473.6	473.3	472.8	472.2	471.7	471.1	471.0	470.9
170°	475.0	475.7	476.4	476.8	476.5	475.8	475.2	474.5	473.9	473.8	473.8
172.5°	477.1	477.8	478.5	478.9	478.6	478.1	477.5	477.0	476.4	476.2	476.1
175°	478.9	479.6	480.3	480.7	480.4	479.7	479.1	478.4	477.8	477.7	477.7
177.5°	479.8	480.5	481.1	481.4	481.1	480.6	480.0	479.5	478.9	478.8	478.8
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1893.8	1885.9	1876.6	1876.6	1865.6	1860.9	1851.6	1848.4	1840.6	1828.1	1818.8
5°	1960.9	1940.6	1928.1	1917.2	1893.8	1876.6	1859.4	1840.6	1821.9	1800.0	1775.0
7.5°	2026.6	1989.1	1971.9	1953.1	1918.8	1882.8	1848.4	1823.4	1798.4	1764.1	1732.8
10°	2095.3	2048.4	2017.2	1992.2	1939.1	1893.8	1843.8	1807.8	1768.8	1725.0	1684.4
12.5°	2153.1	2092.2	2065.6	2018.8	1957.8	1903.1	1840.6	1785.9	1734.4	1682.8	1632.8
15°	2201.6	2143.8	2078.1	2059.4	1975.0	1896.9	1826.6	1756.3	1692.2	1640.6	1582.8
17.5°	2217.2	2143.8	2110.9	2065.6	1965.6	1884.4	1795.3	1718.8	1657.8	1581.3	1535.9
20°	2221.9	2151.6	2106.3	2064.1	1975.0	1867.2	1779.7	1685.9	1612.5	1535.9	1464.1
22.5°	2209.4	2126.6	2082.8	2042.2	1942.2	1850.0	1748.4	1645.3	1559.4	1489.1	1417.2
25°	2185.9	2089.1	2046.9	2003.1	1907.8	1806.3	1695.3	1596.9	1517.2	1432.8	1362.5
27.5°	2154.7	2043.8	1995.3	1950.0	1856.3	1760.9	1656.3	1554.7	1465.6	1376.6	1310.9
30°	2115.6	1987.5	1943.8	1884.4	1793.8	1703.1	1607.8	1506.3	1406.3	1321.9	1250.0
32.5°	2065.6	1931.3	1873.4	1817.2	1718.8	1635.9	1545.3	1450.0	1353.1	1270.3	1195.3
35°	2020.3	1867.2	1803.1	1746.9	1637.5	1550.0	1475.0	1385.9	1300.0	1214.1	1146.9
37.5°	1959.4	1803.1	1726.6	1668.8	1557.8	1468.8	1398.4	1329.7	1239.1	1156.3	1093.8
40°	1895.3	1723.4	1651.6	1593.8	1478.1	1381.3	1314.1	1253.1	1179.7	1103.1	1037.5
42.5°	1837.5	1646.9	1570.3	1500.0	1382.8	1296.9	1228.1	1181.3	1114.1	1045.3	985.9
45°	1764.1	1565.6	1482.8	1409.4	1296.9	1203.1	1137.5	1100.0	1050.0	982.8	931.3
47.5°	1689.1	1478.1	1392.2	1320.3	1198.4	1115.6	1051.6	1015.6	981.3	928.1	876.6
50°	1590.6	1385.9	1307.8	1225.0	1104.7	1020.3	967.2	931.3	904.7	867.2	823.4
52.5°	1482.8	1290.6	1206.3	1134.4	1015.6	939.1	878.1	857.8	831.3	803.1	765.6
55°	1368.8	1187.5	1106.3	1035.9	926.6	848.4	798.4	776.6	756.3	734.4	709.4
57.5°	1254.7	1079.7	1003.1	940.6	839.1	764.1	723.4	693.8	679.7	667.2	646.9
60°	1112.5	964.1	904.7	848.4	748.4	679.7	640.6	618.8	606.3	600.0	590.6
62.5°	987.5	865.6	800.0	745.3	665.6	604.7	567.2	550.0	539.1	535.9	525.0
65°	854.7	750.0	698.4	651.6	582.8	528.1	496.9	476.6	468.8	467.2	467.2
67.5°	729.7	645.3	593.8	560.9	501.6	453.1	423.4	415.6	410.9	404.7	403.1
70°	612.5	545.3	500.0	471.9	418.8	382.8	359.4	346.9	346.9	342.2	339.1
72.5°	509.4	442.2	412.5	389.1	345.3	314.1	296.9	293.8	282.8	281.3	281.3
75°	398.4	348.4	328.1	307.8	275.0	253.1	239.1	231.3	225.0	225.0	226.6
77.5°	300.0	265.6	246.9	231.3	207.8	193.8	182.8	179.7	173.4	173.4	173.4
80°	212.5	193.8	179.7	167.2	150.0	137.5	131.3	125.0	125.0	123.4	125.0
82.5°	137.5	121.9	114.1	112.5	96.9	92.2	84.4	85.9	81.3	79.7	82.8
85°	79.7	71.9	62.5	59.4	53.1	46.9	43.8	45.3	43.8	42.2	43.8
87.5°	31.3	26.6	25.0	25.0	20.3	18.8	17.2	18.8	15.6	15.6	17.2
90°	4.0	3.5	3.2	2.9	2.3	1.6	1.0	0.4	1.0	1.6	2.3
92.5°	4.3	3.8	3.6	4.0	4.7	5.4	6.1	6.8	6.1	5.4	4.7
95°	14.7	17.7	19.2	19.3	19.6	19.8	20.1	20.3	20.1	19.8	19.6
97.5°	28.9	36.4	40.2	40.0	39.5	39.0	38.5	38.0	38.5	39.0	39.5
100°	60.9	60.6	60.4	60.3	60.1	59.8	59.6	59.4	59.6	59.8	60.1
102.5°	82.7	82.6	82.5	82.3	82.0	81.7	81.4	81.1	81.4	81.7	82.0
105°	105.9	105.9	105.9	105.7	105.4	105.1	104.8	104.5	104.8	105.1	105.4
107.5°	128.9	128.8	128.7	128.7	128.7	128.7	128.7	128.7	128.7	128.7	128.7
110°	152.4	152.3	152.2	152.2	152.2	152.2	152.2	152.2	152.2	152.2	152.2

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	175.4	175.3	175.3	175.2	174.9	174.7	174.4	174.2	174.4	174.7	174.9
115°	198.1	198.0	198.0	197.8	197.4	197.1	196.7	196.3	196.7	197.1	197.4
117.5°	219.9	219.6	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4	219.4
120°	240.7	240.4	240.3	240.3	240.4	240.5	240.6	240.7	240.6	240.5	240.4
122.5°	261.4	261.3	261.3	261.1	260.7	260.3	259.9	259.5	259.9	260.3	260.7
125°	281.6	281.6	281.6	281.3	280.8	280.2	279.7	279.1	279.7	280.2	280.8
127.5°	299.6	299.7	299.7	299.5	299.1	298.7	298.3	297.9	298.3	298.7	299.1
130°	316.9	316.8	316.8	316.6	316.2	315.8	315.4	315.0	315.4	315.8	316.2
132.5°	333.8	334.1	334.2	334.0	333.5	333.0	332.6	332.1	332.6	333.0	333.5
135°	350.0	350.1	350.2	350.0	349.5	349.0	348.6	348.1	348.6	349.0	349.5
137.5°	364.9	365.0	365.1	364.9	364.4	363.9	363.5	363.0	363.5	363.9	364.4
140°	378.2	378.3	378.3	378.2	378.1	377.9	377.8	377.6	377.8	377.9	378.1
142.5°	391.3	391.2	391.1	391.1	391.0	390.9	390.8	390.7	390.8	390.9	391.0
145°	404.2	404.2	404.2	404.1	404.0	403.8	403.7	403.5	403.7	403.8	404.0
147.5°	415.0	414.9	414.9	414.9	414.9	414.9	414.9	414.9	414.9	414.9	414.9
150°	425.1	425.0	424.9	425.0	425.1	425.3	425.4	425.6	425.4	425.3	425.1
152.5°	434.3	434.2	434.1	434.3	434.7	435.1	435.5	435.9	435.5	435.1	434.7
155°	442.5	442.4	442.3	442.5	443.0	443.5	443.9	444.4	443.9	443.5	443.0
157.5°	450.1	450.1	450.1	450.2	450.5	450.7	451.0	451.2	451.0	450.7	450.5
160°	456.3	456.2	456.2	456.4	456.9	457.4	457.8	458.3	457.8	457.4	456.9
162.5°	461.9	461.8	461.8	462.0	462.5	463.0	463.5	464.0	463.5	463.0	462.5
165°	466.9	466.8	466.8	467.0	467.5	468.0	468.5	469.0	468.5	468.0	467.5
167.5°	470.8	470.7	470.7	470.9	471.4	471.9	472.4	472.9	472.4	471.9	471.4
170°	473.7	473.6	473.6	473.9	474.4	475.0	475.5	476.1	475.5	475.0	474.4
172.5°	475.9	475.8	475.7	476.0	476.5	477.1	477.6	478.2	477.6	477.1	476.5
175°	477.6	477.5	477.5	477.7	478.2	478.7	479.1	479.6	479.1	478.7	478.2
177.5°	478.7	478.6	478.6	478.8	479.3	479.8	480.2	480.7	480.2	479.8	479.3
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1815.6	1812.5	1804.7	1800.0	1784.4	1765.6	1759.4	1743.8	1750.0	1739.1	1739.1
5°	1767.2	1753.1	1743.8	1729.7	1700.0	1679.7	1657.8	1646.9	1640.6	1632.8	1626.6
7.5°	1704.7	1693.8	1684.4	1657.8	1625.0	1596.9	1570.3	1559.4	1539.1	1525.0	1518.8
10°	1650.0	1634.4	1612.5	1581.3	1546.9	1510.9	1487.5	1464.1	1448.4	1440.6	1423.4
12.5°	1593.8	1575.0	1551.6	1506.3	1468.8	1446.9	1404.7	1382.8	1375.0	1368.8	1348.4
15°	1535.9	1515.6	1487.5	1445.3	1412.5	1360.9	1335.9	1318.8	1300.0	1298.4	1282.8
17.5°	1484.4	1459.4	1435.9	1384.4	1343.8	1298.4	1284.4	1265.6	1248.4	1229.7	1221.9
20°	1418.8	1395.3	1378.1	1321.9	1276.6	1248.4	1225.0	1209.4	1198.4	1179.7	1176.6
22.5°	1359.4	1334.4	1310.9	1268.8	1229.7	1193.8	1165.6	1148.4	1143.8	1135.9	1121.9
25°	1301.6	1276.6	1248.4	1209.4	1168.8	1143.8	1118.8	1107.8	1098.4	1085.9	1075.0
27.5°	1253.1	1229.7	1203.1	1154.7	1120.3	1101.6	1075.0	1062.5	1050.0	1043.8	1039.1
30°	1195.3	1168.8	1148.4	1110.9	1073.4	1048.4	1029.7	1018.8	1007.8	1001.6	998.4
32.5°	1139.1	1114.1	1100.0	1059.4	1029.7	1000.0	985.9	978.1	971.9	965.6	959.4
35°	1093.8	1068.8	1046.9	1009.4	979.7	959.4	948.4	935.9	931.3	925.0	925.0
37.5°	1037.5	1018.8	996.9	960.9	934.4	918.8	909.4	893.8	892.2	889.1	884.4
40°	989.1	970.3	950.0	918.8	895.3	876.6	864.1	856.3	851.6	848.4	845.3
42.5°	937.5	917.2	907.8	871.9	851.6	832.8	826.6	818.8	817.2	810.9	803.1
45°	887.5	870.3	851.6	825.0	807.8	792.2	782.8	776.6	768.8	767.2	762.5
47.5°	843.8	823.4	806.3	781.3	762.5	750.0	742.2	734.4	728.1	723.4	718.8
50°	787.5	771.9	757.8	731.3	715.6	703.1	692.2	685.9	679.7	679.7	679.7
52.5°	732.8	718.8	706.3	687.5	668.8	657.8	645.3	640.6	637.5	632.8	637.5
55°	679.7	665.6	653.1	639.1	617.2	607.8	595.3	590.6	592.2	592.2	596.9
57.5°	623.4	612.5	604.7	587.5	567.2	557.8	550.0	545.3	545.3	551.6	553.1
60°	568.8	557.8	543.8	528.1	515.6	504.7	500.0	501.6	501.6	504.7	512.5
62.5°	507.8	501.6	493.8	471.9	464.1	456.3	450.0	454.7	453.1	460.9	471.9
65°	451.6	445.3	434.4	423.4	414.1	406.3	404.7	406.3	409.4	417.2	429.7
67.5°	389.1	389.1	379.7	370.3	362.5	354.7	356.3	357.8	360.9	370.3	389.1
70°	337.5	331.3	321.9	315.6	309.4	306.3	303.1	309.4	318.8	325.0	339.1
72.5°	281.3	276.6	268.8	262.5	260.9	257.8	256.3	259.4	268.8	279.7	295.3
75°	221.9	223.4	218.8	214.1	214.1	209.4	212.5	212.5	221.9	232.8	245.3
77.5°	171.9	170.3	168.8	165.6	164.1	164.1	164.1	167.2	176.6	182.8	195.3
80°	121.9	123.4	118.8	120.3	118.8	120.3	120.3	126.6	131.3	139.1	148.4
82.5°	81.3	81.3	78.1	79.7	79.7	79.7	81.3	84.4	90.6	96.9	103.1
85°	45.3	46.9	43.8	46.9	46.9	46.9	48.4	50.0	54.7	56.3	62.5
87.5°	17.2	20.3	20.3	17.2	18.8	20.3	21.9	20.3	23.4	26.6	28.1
90°	2.9	3.2	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.9	7.3
92.5°	4.0	3.6	3.8	4.3	4.8	5.2	5.7	6.1	6.5	6.9	7.3
95°	19.3	19.2	17.7	14.7	11.7	8.7	5.7	6.1	6.5	6.9	7.3
97.5°	40.0	40.2	36.4	28.9	21.4	13.9	6.4	6.6	6.7	6.9	7.0
100°	60.3	60.4	60.6	60.9	61.2	61.6	61.9	50.1	38.3	26.6	14.8
102.5°	82.3	82.5	82.6	82.7	82.9	83.0	83.2	83.4	83.5	83.7	83.8
105°	105.7	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9
107.5°	128.7	128.7	128.8	128.9	129.1	129.2	129.4	129.5	129.6	129.7	129.8
110°	152.2	152.2	152.3	152.4	152.6	152.7	152.9	152.7	152.4	152.2	151.9

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	175.2	175.3	175.3	175.4	175.5	175.5	175.6	175.3	175.0	174.7	174.4
115°	197.8	198.0	198.0	198.1	198.2	198.3	198.4	198.1	197.8	197.5	197.2
117.5°	219.4	219.4	219.6	219.9	220.2	220.5	220.8	220.3	219.9	219.4	218.9
120°	240.3	240.3	240.4	240.7	240.9	241.2	241.4	241.2	241.1	240.9	240.8
122.5°	261.1	261.3	261.3	261.4	261.5	261.6	261.7	261.5	261.4	261.2	261.1
125°	281.3	281.6	281.6	281.6	281.6	281.6	281.6	281.3	281.0	280.7	280.4
127.5°	299.5	299.7	299.7	299.6	299.5	299.5	299.4	299.2	299.1	298.9	298.8
130°	316.6	316.8	316.8	316.9	317.0	317.0	317.1	316.9	316.7	316.4	316.2
132.5°	334.0	334.2	334.1	333.8	333.6	333.3	333.1	333.1	333.1	333.1	333.1
135°	350.0	350.2	350.1	350.0	349.8	349.7	349.5	349.3	349.2	349.0	348.9
137.5°	364.9	365.1	365.0	364.9	364.7	364.6	364.4	364.4	364.4	364.4	364.4
140°	378.2	378.3	378.3	378.2	378.1	378.0	377.9	378.1	378.2	378.4	378.5
142.5°	391.1	391.1	391.2	391.3	391.5	391.6	391.8	391.8	391.8	391.8	391.8
145°	404.1	404.2	404.2	404.2	404.2	404.2	404.2	404.3	404.4	404.5	404.6
147.5°	414.9	414.9	414.9	415.0	415.1	415.2	415.3	415.4	415.4	415.5	415.6
150°	425.0	424.9	425.0	425.1	425.3	425.4	425.6	425.8	425.9	426.1	426.2
152.5°	434.3	434.1	434.2	434.3	434.5	434.6	434.8	435.0	435.1	435.3	435.4
155°	442.5	442.3	442.4	442.5	442.7	442.8	443.0	443.2	443.5	443.7	444.0
157.5°	450.2	450.1	450.1	450.1	450.1	450.1	450.1	450.3	450.6	450.8	451.1
160°	456.4	456.2	456.2	456.3	456.4	456.4	456.5	456.8	457.1	457.4	457.7
162.5°	462.0	461.8	461.8	461.9	462.0	462.1	462.2	462.7	463.1	463.6	464.1
165°	467.0	466.8	466.8	466.9	467.0	467.1	467.2	467.7	468.1	468.6	469.1
167.5°	470.9	470.7	470.7	470.8	470.9	471.0	471.1	471.7	472.2	472.8	473.3
170°	473.9	473.6	473.6	473.7	473.8	473.8	473.9	474.5	475.2	475.8	476.5
172.5°	476.0	475.7	475.8	475.9	476.1	476.2	476.4	477.0	477.5	478.1	478.6
175°	477.7	477.5	477.5	477.6	477.7	477.7	477.8	478.4	479.1	479.7	480.4
177.5°	478.8	478.6	478.6	478.7	478.8	478.8	478.9	479.5	480.0	480.6	481.1
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1745.3	1734.4	1732.8	1735.9	1729.7	1739.1	1735.9	1739.1	1731.3	1739.1	1734.4
5°	1625.0	1621.9	1615.6	1607.8	1609.4	1610.9	1618.8	1610.9	1617.2	1618.8	1626.6
7.5°	1512.5	1506.3	1510.9	1507.8	1493.8	1490.6	1493.8	1498.4	1507.8	1514.1	1518.8
10°	1421.9	1418.8	1412.5	1407.8	1400.0	1395.3	1401.6	1395.3	1407.8	1418.8	1418.8
12.5°	1353.1	1340.6	1332.8	1331.3	1314.1	1317.2	1323.4	1328.1	1342.2	1348.4	1348.4
15°	1281.3	1271.9	1268.8	1262.5	1256.3	1262.5	1259.4	1264.1	1270.3	1276.6	1279.7
17.5°	1218.8	1217.2	1218.8	1203.1	1207.8	1200.0	1201.6	1209.4	1204.7	1209.4	1218.8
20°	1162.5	1165.6	1160.9	1154.7	1154.7	1145.3	1156.3	1153.1	1154.7	1164.1	1178.1
22.5°	1120.3	1118.8	1114.1	1109.4	1103.1	1104.7	1106.3	1103.1	1115.6	1123.4	1125.0
25°	1075.0	1071.9	1070.3	1065.6	1059.4	1065.6	1064.1	1065.6	1068.8	1081.3	1071.9
27.5°	1032.8	1026.6	1029.7	1025.0	1023.4	1025.0	1025.0	1026.6	1029.7	1031.3	1032.8
30°	996.9	990.6	989.1	985.9	984.4	985.9	989.1	985.9	998.4	996.9	996.9
32.5°	957.8	953.1	950.0	950.0	948.4	946.9	948.4	950.0	959.4	953.1	959.4
35°	920.3	917.2	917.2	914.1	912.5	912.5	912.5	918.8	915.6	920.3	920.3
37.5°	884.4	884.4	882.8	879.7	878.1	879.7	878.1	881.3	879.7	881.3	882.8
40°	846.9	843.8	842.2	842.2	837.5	832.8	837.5	837.5	839.1	843.8	845.3
42.5°	801.6	803.1	803.1	796.9	796.9	796.9	798.4	800.0	800.0	803.1	803.1
45°	762.5	759.4	759.4	759.4	756.3	757.8	760.9	760.9	760.9	760.9	757.8
47.5°	718.8	718.8	720.3	720.3	725.0	723.4	723.4	721.9	718.8	718.8	720.3
50°	678.1	682.8	684.4	684.4	685.9	687.5	687.5	684.4	682.8	678.1	678.1
52.5°	639.1	642.2	645.3	650.0	653.1	651.6	651.6	648.4	642.2	640.6	639.1
55°	596.9	601.6	607.8	612.5	617.2	618.8	618.8	612.5	606.3	598.4	598.4
57.5°	557.8	562.5	573.4	578.1	584.4	584.4	581.3	576.6	567.2	560.9	556.3
60°	518.8	526.6	534.4	543.8	551.6	553.1	548.4	542.2	531.3	523.4	517.2
62.5°	476.6	484.4	500.0	509.4	515.6	515.6	515.6	507.8	493.8	482.8	473.4
65°	435.9	443.8	457.8	470.3	475.0	479.7	475.0	467.2	456.3	443.8	434.4
67.5°	393.8	403.1	417.2	426.6	432.8	437.5	434.4	428.1	414.1	396.9	390.6
70°	346.9	351.6	371.9	381.3	390.6	393.8	390.6	381.3	367.2	348.4	342.2
72.5°	303.1	307.8	326.6	334.4	342.2	345.3	340.6	334.4	321.9	304.7	296.9
75°	253.1	260.9	270.3	282.8	292.2	295.3	290.6	285.9	270.3	259.4	253.1
77.5°	200.0	207.8	220.3	231.3	240.6	239.1	232.8	234.4	217.2	204.7	200.0
80°	151.6	157.8	167.2	176.6	181.3	181.3	179.7	173.4	167.2	157.8	150.0
82.5°	104.7	112.5	120.3	126.6	126.6	128.1	125.0	123.4	117.2	109.4	107.8
85°	62.5	64.1	70.3	70.3	76.6	73.4	71.9	76.6	70.3	65.6	64.1
87.5°	28.1	26.6	28.1	28.1	26.6	29.7	29.7	28.1	29.7	28.1	28.1
90°	7.5	7.6	7.8	8.1	8.3	8.5	8.3	8.1	7.8	7.6	7.5
92.5°	7.5	7.5	7.6	7.7	7.7	7.8	7.7	7.7	7.6	7.5	7.5
95°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
97.5°	7.1	7.1	7.2	7.3	7.4	7.5	7.4	7.3	7.2	7.1	7.1
100°	8.9	8.7	8.4	8.1	7.8	7.5	7.8	8.1	8.4	8.7	8.9
102.5°	83.9	80.6	73.9	67.3	60.6	54.0	60.6	67.3	73.9	80.6	83.9
105°	105.9	105.9	105.8	105.7	105.7	105.6	105.7	105.7	105.8	105.9	105.9
107.5°	129.8	129.6	129.3	129.0	128.6	128.3	128.6	129.0	129.3	129.6	129.8
110°	151.8	151.8	151.9	152.0	152.1	152.2	152.1	152.0	151.9	151.8	151.8

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	174.2	174.1	174.0	173.8	173.7	173.5	173.7	173.8	174.0	174.1	174.2
115°	197.0	196.8	196.3	195.8	195.3	194.8	195.3	195.8	196.3	196.8	197.0
117.5°	218.7	218.6	218.4	218.3	218.1	217.9	218.1	218.3	218.4	218.6	218.7
120°	240.7	240.5	240.1	239.7	239.3	238.9	239.3	239.7	240.1	240.5	240.7
122.5°	261.0	260.8	260.3	259.8	259.3	258.8	259.3	259.8	260.3	260.8	261.0
125°	280.2	280.1	279.8	279.6	279.3	279.1	279.3	279.6	279.8	280.1	280.2
127.5°	298.7	298.4	297.7	297.1	296.4	295.8	296.4	297.1	297.7	298.4	298.7
130°	316.1	315.9	315.5	315.1	314.7	314.3	314.7	315.1	315.5	315.9	316.1
132.5°	333.1	332.9	332.5	332.2	331.8	331.4	331.8	332.2	332.5	332.9	333.1
135°	348.8	348.6	348.1	347.6	347.1	346.6	347.1	347.6	348.1	348.6	348.8
137.5°	364.4	364.2	363.8	363.4	363.0	362.6	363.0	363.4	363.8	364.2	364.4
140°	378.6	378.4	377.9	377.4	377.0	376.5	377.0	377.4	377.9	378.4	378.6
142.5°	391.8	391.6	391.1	390.6	390.2	389.7	390.2	390.6	391.1	391.6	391.8
145°	404.6	404.4	403.9	403.4	403.0	402.5	403.0	403.4	403.9	404.4	404.6
147.5°	415.6	415.3	414.8	414.2	413.7	413.1	413.7	414.2	414.8	415.3	415.6
150°	426.3	426.0	425.3	424.7	424.0	423.4	424.0	424.7	425.3	426.0	426.3
152.5°	435.5	435.2	434.7	434.1	433.6	433.0	433.6	434.1	434.7	435.2	435.5
155°	444.1	443.8	443.1	442.5	441.8	441.2	441.8	442.5	443.1	443.8	444.1
157.5°	451.2	450.9	450.2	449.6	448.9	448.3	448.9	449.6	450.2	450.9	451.2
160°	457.9	457.6	457.0	456.3	455.7	455.1	455.7	456.3	457.0	457.6	457.9
162.5°	464.3	463.9	463.2	462.5	461.8	461.1	461.8	462.5	463.2	463.9	464.3
165°	469.3	469.0	468.4	467.7	467.1	466.5	467.1	467.7	468.4	469.0	469.3
167.5°	473.6	473.2	472.5	471.8	471.1	470.4	471.1	471.8	472.5	473.2	473.6
170°	476.8	476.4	475.7	475.0	474.3	473.6	474.3	475.0	475.7	476.4	476.8
172.5°	478.9	478.5	477.8	477.1	476.4	475.7	476.4	477.1	477.8	478.5	478.9
175°	480.7	480.3	479.6	478.9	478.2	477.5	478.2	478.9	479.6	480.3	480.7
177.5°	481.4	481.1	480.5	479.8	479.2	478.6	479.2	479.8	480.5	481.1	481.4
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1748.4	1739.1	1750.0	1735.9	1739.1	1756.3	1754.7	1770.3	1779.7	1778.1	1785.9
5°	1632.8	1632.8	1637.5	1635.9	1651.6	1665.6	1684.4	1700.0	1717.2	1726.6	1737.5
7.5°	1518.8	1534.4	1537.5	1545.3	1564.1	1587.5	1606.3	1629.7	1654.7	1671.9	1684.4
10°	1425.0	1437.5	1450.0	1456.3	1476.6	1507.8	1534.4	1571.9	1603.1	1621.9	1639.1
12.5°	1342.2	1356.3	1362.5	1390.6	1404.7	1425.0	1462.5	1503.1	1537.5	1557.8	1571.9
15°	1282.8	1290.6	1304.7	1321.9	1335.9	1360.9	1392.2	1437.5	1470.3	1487.5	1535.9
17.5°	1232.8	1242.2	1250.0	1257.8	1279.7	1306.3	1335.9	1375.0	1417.2	1446.9	1471.9
20°	1181.3	1185.9	1195.3	1207.8	1223.4	1248.4	1275.0	1315.6	1353.1	1376.6	1409.4
22.5°	1120.3	1134.4	1143.8	1153.1	1170.3	1198.4	1223.4	1253.1	1300.0	1326.6	1360.9
25°	1084.4	1090.6	1096.9	1107.8	1120.3	1145.3	1173.4	1204.7	1242.2	1270.3	1300.0
27.5°	1037.5	1046.9	1054.7	1068.8	1076.6	1096.9	1123.4	1154.7	1200.0	1223.4	1248.4
30°	998.4	1007.8	1014.1	1020.3	1031.3	1053.1	1078.1	1103.1	1145.3	1175.0	1200.0
32.5°	959.4	968.8	976.6	981.3	992.2	1006.3	1026.6	1057.8	1093.8	1114.1	1146.9
35°	925.0	925.0	934.4	940.6	950.0	962.5	981.3	1004.7	1042.2	1068.8	1098.4
37.5°	885.9	887.5	895.3	900.0	909.4	921.9	940.6	962.5	993.8	1014.1	1043.8
40°	845.3	850.0	853.1	860.9	871.9	876.6	895.3	920.3	951.6	970.3	995.3
42.5°	804.7	807.8	815.6	821.9	831.3	839.1	851.6	875.0	898.4	926.6	946.9
45°	759.4	767.2	771.9	782.8	787.5	795.3	807.8	826.6	854.7	871.9	895.3
47.5°	720.3	723.4	726.6	740.6	750.0	754.7	767.2	778.1	807.8	823.4	845.3
50°	678.1	678.1	682.8	689.1	700.0	709.4	720.3	732.8	756.3	771.9	793.8
52.5°	639.1	634.4	637.5	640.6	651.6	660.9	671.9	689.1	710.9	720.3	739.1
55°	596.9	589.1	593.8	598.4	601.6	614.1	626.6	637.5	654.7	668.8	685.9
57.5°	551.6	550.0	546.9	548.4	556.3	564.1	573.4	587.5	607.8	618.8	628.1
60°	510.9	501.6	498.4	501.6	506.3	510.9	523.4	535.9	553.1	564.1	575.0
62.5°	468.8	459.4	453.1	448.4	453.1	464.1	471.9	481.3	495.3	507.8	517.2
65°	428.1	414.1	407.8	404.7	403.1	410.9	417.2	429.7	442.2	446.9	457.8
67.5°	382.8	370.3	362.5	357.8	357.8	357.8	364.1	376.6	389.1	390.6	401.6
70°	337.5	323.4	315.6	309.4	306.3	309.4	317.2	318.8	329.7	332.8	339.1
72.5°	289.1	276.6	267.2	259.4	260.9	264.1	264.1	267.2	273.4	281.3	281.3
75°	243.8	226.6	221.9	215.6	212.5	212.5	212.5	218.8	223.4	229.7	228.1
77.5°	192.2	182.8	173.4	170.3	165.6	164.1	167.2	167.2	170.3	175.0	176.6
80°	148.4	137.5	131.3	128.1	121.9	120.3	121.9	121.9	126.6	125.0	126.6
82.5°	103.1	95.3	90.6	85.9	82.8	84.4	82.8	82.8	84.4	82.8	82.8
85°	59.4	57.8	54.7	53.1	51.6	48.4	51.6	50.0	48.4	46.9	50.0
87.5°	28.1	26.6	26.6	23.4	23.4	21.9	23.4	23.4	21.9	21.9	21.9
90°	7.3	6.9	6.5	6.1	5.7	5.1	4.6	4.0	3.5	3.2	2.9
92.5°	7.3	6.9	6.5	6.1	5.7	5.2	4.8	4.3	3.8	3.6	4.0
95°	7.3	6.9	6.5	6.1	5.7	8.7	11.7	14.7	17.7	19.2	19.3
97.5°	7.0	6.9	6.7	6.6	6.4	13.9	21.4	28.9	36.4	40.2	40.0
100°	14.8	26.6	38.3	50.1	61.9	61.6	61.2	60.9	60.6	60.4	60.3
102.5°	83.8	83.7	83.5	83.4	83.2	83.0	82.9	82.7	82.6	82.5	82.3
105°	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.7
107.5°	129.8	129.7	129.6	129.5	129.4	129.2	129.1	128.9	128.8	128.7	128.7
110°	151.9	152.2	152.4	152.7	152.9	152.7	152.6	152.4	152.3	152.2	152.2

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	174.4	174.7	175.0	175.3	175.6	175.5	175.5	175.4	175.3	175.3	175.2
115°	197.2	197.5	197.8	198.1	198.4	198.3	198.2	198.1	198.0	198.0	197.8
117.5°	218.9	219.4	219.9	220.3	220.8	220.5	220.2	219.9	219.6	219.4	219.4
120°	240.8	240.9	241.1	241.2	241.4	241.2	240.9	240.7	240.4	240.3	240.3
122.5°	261.1	261.2	261.4	261.5	261.7	261.6	261.5	261.4	261.3	261.3	261.1
125°	280.4	280.7	281.0	281.3	281.6	281.6	281.6	281.6	281.6	281.6	281.3
127.5°	298.8	298.9	299.1	299.2	299.4	299.5	299.5	299.6	299.7	299.7	299.5
130°	316.2	316.4	316.7	316.9	317.1	317.0	317.0	316.9	316.8	316.8	316.6
132.5°	333.1	333.1	333.1	333.1	333.1	333.3	333.6	333.8	334.1	334.2	334.0
135°	348.9	349.0	349.2	349.3	349.5	349.7	349.8	350.0	350.1	350.2	350.0
137.5°	364.4	364.4	364.4	364.4	364.4	364.6	364.7	364.9	365.0	365.1	364.9
140°	378.5	378.4	378.2	378.1	377.9	378.0	378.1	378.2	378.3	378.3	378.2
142.5°	391.8	391.8	391.8	391.8	391.8	391.6	391.5	391.3	391.2	391.1	391.1
145°	404.6	404.5	404.4	404.3	404.2	404.2	404.2	404.2	404.2	404.2	404.1
147.5°	415.6	415.5	415.4	415.4	415.3	415.2	415.1	415.0	414.9	414.9	414.9
150°	426.2	426.1	425.9	425.8	425.6	425.4	425.3	425.1	425.0	424.9	425.0
152.5°	435.4	435.3	435.1	435.0	434.8	434.6	434.5	434.3	434.2	434.1	434.3
155°	444.0	443.7	443.5	443.2	443.0	442.8	442.7	442.5	442.4	442.3	442.5
157.5°	451.1	450.8	450.6	450.3	450.1	450.1	450.1	450.1	450.1	450.1	450.2
160°	457.7	457.4	457.1	456.8	456.5	456.4	456.4	456.3	456.2	456.2	456.4
162.5°	464.1	463.6	463.1	462.7	462.2	462.1	462.0	461.9	461.8	461.8	462.0
165°	469.1	468.6	468.1	467.7	467.2	467.1	467.0	466.9	466.8	466.8	467.0
167.5°	473.3	472.8	472.2	471.7	471.1	471.0	470.9	470.8	470.7	470.7	470.9
170°	476.5	475.8	475.2	474.5	473.9	473.8	473.8	473.7	473.6	473.6	473.9
172.5°	478.6	478.1	477.5	477.0	476.4	476.2	476.1	475.9	475.8	475.7	476.0
175°	480.4	479.7	479.1	478.4	477.8	477.7	477.7	477.6	477.5	477.5	477.7
177.5°	481.1	480.6	480.0	479.5	478.9	478.8	478.8	478.7	478.6	478.6	478.8
180°	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6	479.6

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1840.6	1840.6	1840.6	1840.6
2.5°	1796.9	1812.5	1823.4	1843.8
5°	1756.3	1784.4	1810.9	1839.1
7.5°	1715.6	1748.4	1790.6	1826.6
10°	1670.3	1712.5	1762.5	1810.9
12.5°	1625.0	1675.0	1729.7	1793.8
15°	1570.3	1634.4	1698.4	1767.2
17.5°	1521.9	1587.5	1656.3	1742.2
20°	1467.2	1539.1	1614.1	1701.6
22.5°	1418.8	1498.4	1576.6	1668.8
25°	1364.1	1442.2	1528.1	1626.6
27.5°	1318.8	1390.6	1475.0	1581.3
30°	1264.1	1342.2	1426.6	1532.8
32.5°	1212.5	1287.5	1376.6	1481.3
35°	1159.4	1235.9	1315.6	1415.6
37.5°	1109.4	1175.0	1254.7	1350.0
40°	1053.1	1125.0	1196.9	1271.9
42.5°	1001.6	1067.2	1134.4	1193.8
45°	943.8	1000.0	1064.1	1112.5
47.5°	890.6	940.6	990.6	1028.1
50°	837.5	876.6	914.1	946.9
52.5°	775.0	818.8	839.1	859.4
55°	718.8	743.8	762.5	782.8
57.5°	664.1	675.0	684.4	703.1
60°	592.2	604.7	615.6	629.7
62.5°	529.7	535.9	539.1	553.1
65°	470.3	468.8	476.6	484.4
67.5°	406.3	404.7	412.5	415.6
70°	343.8	342.2	343.8	351.6
72.5°	284.4	284.4	285.9	289.1
75°	229.7	229.7	231.3	234.4
77.5°	173.4	176.6	175.0	181.3
80°	126.6	123.4	126.6	129.7
82.5°	82.8	85.9	85.9	82.8
85°	46.9	46.9	46.9	46.9
87.5°	20.3	20.3	21.9	23.4
90°	2.3	1.6	1.0	0.4
92.5°	4.7	5.4	6.1	6.8
95°	19.6	19.8	20.1	20.3
97.5°	39.5	39.0	38.5	38.0
100°	60.1	59.8	59.6	59.4
102.5°	82.0	81.7	81.4	81.1
105°	105.4	105.1	104.8	104.5
107.5°	128.7	128.7	128.7	128.7
110°	152.2	152.2	152.2	152.2

TEST NUMBER: P1026785

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	174.9	174.7	174.4	174.2
115°	197.4	197.1	196.7	196.3
117.5°	219.4	219.4	219.4	219.4
120°	240.4	240.5	240.6	240.7
122.5°	260.7	260.3	259.9	259.5
125°	280.8	280.2	279.7	279.1
127.5°	299.1	298.7	298.3	297.9
130°	316.2	315.8	315.4	315.0
132.5°	333.5	333.0	332.6	332.1
135°	349.5	349.0	348.6	348.1
137.5°	364.4	363.9	363.5	363.0
140°	378.1	377.9	377.8	377.6
142.5°	391.0	390.9	390.8	390.7
145°	404.0	403.8	403.7	403.5
147.5°	414.9	414.9	414.9	414.9
150°	425.1	425.3	425.4	425.6
152.5°	434.7	435.1	435.5	435.9
155°	443.0	443.5	443.9	444.4
157.5°	450.5	450.7	451.0	451.2
160°	456.9	457.4	457.8	458.3
162.5°	462.5	463.0	463.5	464.0
165°	467.5	468.0	468.5	469.0
167.5°	471.4	471.9	472.4	472.9
170°	474.4	475.0	475.5	476.1
172.5°	476.5	477.1	477.6	478.2
175°	478.2	478.7	479.1	479.6
177.5°	479.3	479.8	480.2	480.7
180°	479.6	479.6	479.6	479.6

(END OF REPORT)