

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026581

Luminaire Tested: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026581
REPORT IS A COMBINATION OF REPORTS P999691 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7353.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026581

CATALOG NUMBER: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026581

CATALOG NUMBER: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11322	11322	11322
5°	11323	10985	10986
10°	11227	10639	10512
15°	11072	10207	9952
20°	10870	9715	9314
25°	10617	9184	8691
30°	10371	8643	7991
35°	10099	8094	7307
40°	9776	7503	6605
45°	9473	6916	5908
50°	9128	6276	5202
55°	8755	5619	4472
60°	8343	4923	3752
65°	7942	4123	3058
70°	7376	3282	2338
75°	6648	2388	1635
80°	5552	1466	1175
85°	4177	846	646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9473 cd/sqm

TEST NUMBER: P1026581

CATALOG NUMBER: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	1.8
10°-20°	364.0	5.0
20°-30°	525.5	7.1
30°-40°	595.6	8.1
40°-50°	575.1	7.8
50°-60°	478.1	6.5
60°-70°	330.0	4.5
70°-80°	166.8	2.3
80°-90°	45.5	0.6
90°-100°	97.3	1.3
100°-110°	291.4	4.0
110°-120°	495.1	6.7
120°-130°	652.9	8.9
130°-140°	733.4	10.0
140°-150°	720.8	9.8
150°-160°	606.2	8.2
160°-170°	403.4	5.5
170°-180°	141.2	1.9
0°-30°	1020.1	13.9
0°-40°	1615.7	22.0
0°-60°	2668.9	36.3
0°-90°	3211.2	43.7
90°-120°	883.8	12.0
90°-150°	2990.9	40.7
90°-180°	4142.0	56.3
0°-180°	7353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1369	1380	1378	132
15°	1320	1311	1284	1282	1275	372
25°	1194	1175	1131	1113	1102	550
35°	1032	998	945	909	890	645
45°	842	803	739	687	668	649
55°	638	595	526	471	451	571
65°	434	388	320	274	262	428
75°	231	191	141	117	111	243
85°	57	36	33	31	31	63
90°	4	16	25	32	35	8
95°	69	80	88	91	91	75
105°	269	270	275	278	282	285
115°	503	503	501	500	499	496
125°	733	733	732	730	727	653
135°	946	952	952	950	947	731
145°	1149	1153	1154	1153	1150	719
155°	1316	1316	1315	1320	1315	606
165°	1433	1429	1427	1434	1429	404
175°	1490	1485	1484	1492	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1026581

CATALOG NUMBER: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.4	1388.4	1388.4	1388.4	1388.4
2.5°	1392.6	1388.4	1376.7	1388.4	1387.3
5°	1386.3	1382.0	1369.2	1379.9	1377.7
7.5°	1376.7	1372.4	1356.5	1363.9	1360.7
10°	1361.8	1356.5	1337.4	1341.6	1337.4
12.5°	1342.7	1336.3	1312.9	1315.0	1308.6
15°	1320.3	1310.8	1284.2	1282.1	1274.6
17.5°	1294.8	1281.0	1250.2	1244.9	1234.2
20°	1264.0	1250.2	1214.0	1205.5	1191.7
22.5°	1230.0	1214.0	1174.7	1160.9	1150.3
25°	1193.8	1174.7	1131.1	1113.0	1102.4
27.5°	1156.6	1133.2	1087.5	1066.3	1051.4
30°	1117.3	1090.7	1040.8	1014.2	997.2
32.5°	1075.8	1045.0	992.9	961.0	945.1
35°	1032.2	998.2	945.1	908.9	889.8
37.5°	986.5	951.5	893.0	853.7	834.5
40°	937.6	902.6	842.0	797.3	778.2
42.5°	890.9	853.7	789.9	744.2	724.0
45°	842.0	802.6	738.8	686.7	667.6
47.5°	792.0	751.6	685.7	631.5	610.2
50°	741.0	699.5	631.5	578.3	558.1
52.5°	688.9	648.5	578.3	524.1	502.8
55°	637.8	595.3	526.2	470.9	450.7
57.5°	587.9	543.2	475.2	418.9	404.0
60°	533.7	491.1	423.1	367.8	350.8
62.5°	484.8	440.1	370.0	320.0	307.2
65°	433.7	388.0	320.0	274.3	261.5
67.5°	380.6	337.0	273.2	232.8	217.9
70°	330.6	286.0	225.4	190.3	179.7
72.5°	277.5	238.1	181.8	153.1	143.5
75°	230.7	191.4	141.4	116.9	110.6
77.5°	181.8	147.8	105.2	88.2	86.1
80°	135.0	104.2	72.3	69.1	68.0
82.5°	94.6	67.0	52.1	50.0	48.9
85°	57.4	36.1	33.0	30.8	30.8
87.5°	24.5	15.9	14.9	13.8	14.9
90°	3.5	16.2	25.4	32.3	34.6
92.5°	30.0	45.0	50.8	54.3	55.4
95°	69.3	79.7	87.7	91.2	91.2
97.5°	110.8	120.1	129.3	133.9	133.9
100°	161.6	166.2	176.6	178.9	178.9
102.5°	214.7	215.9	225.1	228.6	229.7
105°	269.0	270.1	274.8	278.2	281.7
107.5°	325.6	326.7	327.9	332.5	331.3
110°	383.3	385.6	384.4	382.1	385.6

TEST NUMBER: P1026581

CATALOG NUMBER: S124RDIP-B795D1205UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.3	443.3	441.0	441.0	441.0
115°	503.4	503.4	501.0	499.9	498.7
117.5°	559.9	559.9	558.8	555.3	551.8
120°	616.5	621.1	617.6	611.9	614.2
122.5°	675.4	676.5	675.4	671.9	666.1
125°	733.1	733.1	731.9	729.6	727.3
127.5°	785.0	788.5	786.2	783.9	782.7
130°	840.5	843.9	843.9	841.6	837.0
132.5°	897.0	899.3	898.2	895.9	894.7
135°	945.5	952.4	952.4	950.1	946.7
137.5°	999.8	1003.2	1005.6	1002.1	1003.2
140°	1054.0	1056.3	1056.3	1055.2	1054.0
142.5°	1103.7	1106.0	1104.8	1104.8	1104.8
145°	1148.7	1153.3	1154.5	1153.3	1149.9
147.5°	1194.9	1200.7	1199.5	1198.3	1197.2
150°	1236.4	1241.1	1241.1	1241.1	1239.9
152.5°	1275.7	1278.0	1279.2	1282.6	1279.2
155°	1316.1	1316.1	1315.0	1319.6	1315.0
157.5°	1350.7	1348.4	1348.4	1351.9	1348.4
160°	1380.8	1379.6	1378.4	1381.9	1376.1
162.5°	1408.5	1405.0	1403.8	1410.8	1405.0
165°	1432.7	1429.2	1426.9	1433.9	1429.2
167.5°	1452.3	1447.7	1447.7	1454.6	1447.7
170°	1468.5	1462.7	1463.9	1470.8	1462.7
172.5°	1480.0	1475.4	1475.4	1483.5	1475.4
175°	1490.4	1484.7	1483.5	1491.6	1483.5
177.5°	1495.1	1489.3	1489.3	1497.4	1488.1
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)