

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026791

Luminaire Tested: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026791
REPORT IS A COMBINATION OF REPORTS P1001655 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6440.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026791

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026791

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72	72	72
1	102	97	92	88	96	92	88	84	83	79	77	74	72	69	66	64	63	59	59	59
2	92	84	77	71	87	80	74	68	72	67	63	64	61	57	58	55	52	48	48	48
3	84	74	65	59	79	70	63	57	63	57	52	57	52	48	51	47	44	40	40	40
4	77	65	56	50	72	62	54	48	56	49	44	50	45	41	45	41	37	34	34	34
5	70	58	49	43	66	55	47	41	50	43	38	45	40	35	41	36	32	30	30	30
6	65	52	43	37	61	50	42	36	45	38	33	41	35	31	37	32	29	26	26	26
7	60	47	38	33	57	45	37	31	41	34	29	37	31	27	34	29	25	23	23	23
8	56	43	34	29	53	41	33	28	37	31	26	34	28	24	31	26	23	20	20	20
9	52	39	31	26	49	37	30	25	34	28	23	31	26	22	28	24	20	18	18	18
10	49	36	28	23	46	34	27	23	32	25	21	29	24	20	26	22	19	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10256	10256	10256
5°	10273	10042	10066
10°	10196	9837	9809
15°	10072	9599	9492
20°	9904	9311	9178
25°	9706	9004	8798
30°	9466	8671	8452
35°	9241	8362	8133
40°	9013	8038	7812
45°	8754	7757	7523
50°	8507	7452	7263
55°	8210	7161	6960
60°	7884	6830	6649
65°	7543	6479	6301
70°	7152	6011	5936
75°	6539	5549	5492
80°	5729	4988	5002
85°	4934	4538	4743

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8754 cd/sqm

TEST NUMBER: P1026791

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	2.4
10°-20°	430.0	6.7
20°-30°	639.5	9.9
30°-40°	757.3	11.8
40°-50°	782.9	12.2
50°-60°	721.2	11.2
60°-70°	583.0	9.1
70°-80°	390.1	6.1
80°-90°	202.4	3.1
90°-100°	129.9	2.0
100°-110°	192.5	3.0
110°-120°	251.9	3.9
120°-130°	283.1	4.4
130°-140°	284.3	4.4
140°-150°	256.5	4.0
150°-160°	205.3	3.2
160°-170°	132.7	2.1
170°-180°	45.8	0.7
0°-30°	1221.0	19.0
0°-40°	1978.3	30.7
0°-60°	3482.4	54.1
0°-90°	4658.0	72.3
90°-120°	574.3	8.9
90°-150°	1398.2	21.7
90°-180°	1782.0	27.7
0°-180°	6440.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1601	1601	1601	1601	1601	
5°	1601	1598	1587	1599	1598	152
15°	1529	1530	1519	1529	1522	431
25°	1389	1394	1384	1390	1383	639
35°	1202	1213	1208	1213	1213	753
45°	990	1008	1015	1026	1028	764
55°	761	786	811	829	835	680
65°	524	560	598	622	628	520
75°	289	330	380	411	419	306
85°	86	138	193	228	240	90
90°	26	78	134	172	184	18
95°	41	80	120	157	168	41
105°	119	146	193	224	235	126
115°	207	219	260	287	295	205
125°	287	288	319	343	350	256
135°	353	354	364	383	389	272
145°	407	406	406	414	418	254
155°	446	444	445	446	443	206
165°	471	469	469	472	469	133
175°	482	480	480	483	480	46
180°	482	482	482	482	482	

TEST NUMBER: P1026791

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1600.8	1600.8	1600.8	1600.8	1600.8
2.5°	1605.5	1602.4	1591.4	1602.4	1600.8
5°	1600.8	1597.7	1586.7	1599.2	1597.7
7.5°	1589.8	1588.2	1577.3	1588.2	1586.7
10°	1574.1	1574.1	1561.6	1572.6	1571.0
12.5°	1552.1	1553.7	1544.3	1552.1	1547.4
15°	1528.6	1530.2	1519.2	1528.6	1522.3
17.5°	1498.8	1501.9	1490.9	1498.8	1494.1
20°	1465.8	1469.0	1458.0	1462.7	1462.7
22.5°	1428.2	1434.4	1421.9	1428.2	1423.5
25°	1388.9	1393.6	1384.2	1390.5	1382.7
27.5°	1346.6	1352.8	1341.8	1346.6	1343.4
30°	1297.9	1307.3	1297.9	1301.0	1299.5
32.5°	1254.0	1261.8	1255.5	1258.7	1257.1
35°	1202.2	1213.2	1208.4	1213.2	1213.2
37.5°	1151.9	1161.4	1159.8	1166.1	1164.5
40°	1100.2	1112.7	1111.1	1117.4	1120.6
42.5°	1043.7	1060.9	1065.6	1073.5	1073.5
45°	990.3	1007.6	1015.4	1026.4	1028.0
47.5°	935.4	951.1	963.6	979.3	982.5
50°	878.9	896.1	913.4	930.7	935.4
52.5°	819.2	841.2	863.2	882.0	885.1
55°	761.2	786.3	811.4	828.6	834.9
57.5°	701.5	731.3	759.6	778.4	783.1
60°	641.9	673.3	704.7	728.2	732.9
62.5°	583.8	615.2	649.7	676.4	682.7
65°	524.2	560.3	597.9	621.5	627.8
67.5°	469.3	503.8	541.4	569.7	577.5
70°	408.0	444.1	484.9	514.8	524.2
72.5°	348.4	386.1	431.6	464.5	470.8
75°	288.8	329.6	379.8	411.2	419.0
77.5°	230.7	277.8	324.9	359.4	365.7
80°	177.3	224.4	277.8	312.3	318.6
82.5°	128.7	178.9	233.8	266.8	279.4
85°	86.3	138.1	193.0	227.6	240.1
87.5°	54.9	105.2	158.5	194.6	205.6
90°	25.5	78.5	134.4	172.3	184.4
92.5°	28.8	71.1	128.1	164.4	175.8
95°	40.8	80.5	120.3	156.6	167.6
97.5°	57.0	96.9	114.7	148.3	159.7
100°	77.0	110.9	162.6	142.3	150.3
102.5°	97.1	128.4	177.8	209.9	189.3
105°	119.1	145.7	192.8	224.2	234.8
107.5°	141.9	163.8	210.0	241.8	249.8
110°	163.9	182.7	227.4	256.1	267.5



TEST NUMBER: P1026791

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	186.0	201.2	244.0	270.7	281.0
115°	206.6	219.4	260.5	287.4	294.7
117.5°	228.2	236.1	276.7	301.3	311.6
120°	249.6	254.1	291.3	317.1	324.8
122.5°	267.1	270.4	305.3	329.7	337.0
125°	286.7	287.6	319.0	342.7	349.5
127.5°	304.1	304.2	330.6	353.5	360.0
130°	321.2	321.4	343.7	364.7	370.7
132.5°	336.7	338.9	353.5	375.5	380.0
135°	352.8	353.5	363.8	383.4	389.1
137.5°	367.8	368.5	374.0	392.9	397.4
140°	381.0	381.7	382.8	400.8	405.0
142.5°	394.2	392.9	393.7	407.8	411.9
145°	407.1	406.2	406.2	414.3	418.5
147.5°	416.9	416.9	417.2	420.7	421.4
150°	427.6	426.9	427.6	428.3	427.1
152.5°	438.0	436.2	436.9	437.6	435.1
155°	446.5	444.4	445.1	446.2	443.3
157.5°	453.3	452.2	452.2	453.3	450.5
160°	460.5	458.3	458.7	460.1	457.2
162.5°	466.2	464.0	464.4	466.5	463.3
165°	471.2	469.0	469.4	471.5	468.7
167.5°	475.1	473.0	473.3	475.8	472.6
170°	478.3	475.8	476.2	479.0	475.8
172.5°	480.5	478.0	478.7	481.2	478.0
175°	481.9	479.8	480.1	483.0	479.8
177.5°	483.0	480.8	481.2	483.7	480.8
180°	481.9	481.9	481.9	481.9	481.9

(END OF REPORT)