

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026594

Luminaire Tested: S124RDIP-B795D365UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026594
REPORT IS A COMBINATION OF REPORTS P999704 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D365UB27-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4509.6 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026594

CATALOG NUMBER: S124RDIP-B795D365UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026594

CATALOG NUMBER: S124RDIP-B795D365UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75
1	103	99	95	91	97	94	90	87	84	81	79	75	73	72	67	66	65
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47
4	79	68	60	54	75	65	58	52	59	53	48	53	48	44	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32
7	62	50	42	36	59	48	40	35	43	37	33	40	34	31	36	32	28
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11290	11290	11290
5°	11291	10954	10956
10°	11195	10609	10482
15°	11041	10178	9925
20°	10840	9688	9288
25°	10588	9158	8666
30°	10342	8618	7969
35°	10071	8071	7287
40°	9749	7481	6586
45°	9446	6897	5892
50°	9103	6258	5188
55°	8732	5603	4460
60°	8319	4909	3741
65°	7921	4112	3050
70°	7356	3272	2331
75°	6628	2381	1629
80°	5536	1462	1171
85°	4162	843	643

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9446 cd/sqm

TEST NUMBER: P1026594

CATALOG NUMBER: S124RDIP-B795D365UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	2.9
10°-20°	363.0	8.0
20°-30°	524.1	11.6
30°-40°	593.9	13.2
40°-50°	573.5	12.7
50°-60°	476.8	10.6
60°-70°	329.1	7.3
70°-80°	166.3	3.7
80°-90°	42.9	1.0
90°-100°	133.3	3.0
100°-110°	271.2	6.0
110°-120°	241.7	5.4
120°-130°	203.0	4.5
130°-140°	169.4	3.8
140°-150°	129.4	2.9
150°-160°	91.0	2.0
160°-170°	53.5	1.2
170°-180°	17.4	0.4
0°-30°	1017.2	22.6
0°-40°	1611.2	35.7
0°-60°	2661.4	59.0
0°-90°	3199.7	71.0
90°-120°	646.2	14.3
90°-150°	1148.1	25.5
90°-180°	1310.0	29.0
0°-180°	4509.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1384	1384	1384	1384	1384	
5°	1382	1378	1365	1376	1374	131
15°	1317	1307	1281	1278	1271	371
25°	1190	1171	1128	1110	1099	549
35°	1029	995	942	906	887	643
45°	840	800	737	685	666	647
55°	636	594	525	470	450	569
65°	432	387	319	274	261	427
75°	230	191	141	117	110	243
85°	57	36	33	31	31	63
90°	0	3	6	7	7	4
95°	12	37	287	142	86	13
105°	41	60	231	498	496	44
115°	73	91	206	396	476	72
125°	101	120	205	337	380	90
135°	120	143	204	299	340	93
145°	139	159	202	252	278	87
155°	158	170	197	223	232	73
165°	172	177	189	200	203	49
175°	179	180	181	183	183	17
180°	180	180	180	180	180	

TEST NUMBER: P1026594

CATALOG NUMBER: S124RDIP-B795D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1384.5	1384.5	1384.5	1384.5	1384.5
2.5°	1388.7	1384.5	1372.8	1384.5	1383.4
5°	1382.4	1378.1	1365.4	1376.0	1373.9
7.5°	1372.8	1368.6	1352.7	1360.1	1356.9
10°	1358.0	1352.7	1333.6	1337.8	1333.6
12.5°	1338.9	1332.5	1309.2	1311.3	1305.0
15°	1316.6	1307.1	1280.6	1278.5	1271.1
17.5°	1291.2	1277.4	1246.7	1241.4	1230.8
20°	1260.5	1246.7	1210.6	1202.1	1188.4
22.5°	1226.5	1210.6	1171.4	1157.6	1147.0
25°	1190.5	1171.4	1127.9	1109.9	1099.3
27.5°	1153.4	1130.1	1084.5	1063.3	1048.4
30°	1114.2	1087.7	1037.8	1011.3	994.4
32.5°	1072.8	1042.1	990.1	958.3	942.4
35°	1029.4	995.4	942.4	906.4	887.3
37.5°	983.8	948.8	890.5	851.3	832.2
40°	935.0	900.0	839.6	795.1	776.0
42.5°	888.4	851.3	787.7	742.1	721.9
45°	839.6	800.4	736.8	684.8	665.7
47.5°	789.8	749.5	683.8	629.7	608.5
50°	738.9	697.5	629.7	576.7	556.6
52.5°	686.9	646.7	576.7	522.6	501.4
55°	636.1	593.7	524.7	469.6	449.5
57.5°	586.2	541.7	473.9	417.7	402.8
60°	532.2	489.8	421.9	366.8	349.8
62.5°	483.4	438.9	368.9	319.1	306.4
65°	432.5	386.9	319.1	273.5	260.8
67.5°	379.5	336.1	272.4	232.2	217.3
70°	329.7	285.2	224.7	189.8	179.2
72.5°	276.7	237.5	181.3	152.7	143.1
75°	230.0	190.8	141.0	116.6	110.2
77.5°	181.3	147.4	104.9	88.0	85.9
80°	134.6	103.9	72.1	68.9	67.8
82.5°	94.3	66.8	51.9	49.8	48.8
85°	57.2	36.0	32.9	30.7	30.7
87.5°	24.4	15.9	14.8	13.8	14.8
90°	0.4	2.8	6.3	7.1	7.4
92.5°	4.9	27.2	138.2	45.7	32.1
95°	11.6	36.7	287.4	142.3	86.0
97.5°	19.4	40.6	307.5	290.6	206.6
100°	26.8	45.8	283.5	402.0	323.4
102.5°	33.9	52.2	253.5	471.8	424.9
105°	41.3	59.8	231.3	498.1	496.2
107.5°	49.4	67.5	216.9	490.2	530.0
110°	57.5	75.2	210.2	462.0	530.7



TEST NUMBER: P1026594

CATALOG NUMBER: S124RDIP-B795D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.2	83.0	207.0	427.4	509.9
115°	72.6	91.2	206.3	396.4	476.4
117.5°	80.4	98.8	205.9	372.0	443.6
120°	88.2	106.2	205.9	355.6	416.8
122.5°	95.2	113.4	205.6	344.9	395.7
125°	101.2	120.2	205.2	337.3	380.1
127.5°	106.8	126.6	204.5	330.0	370.3
130°	111.4	132.8	204.2	321.5	361.8
132.5°	116.0	138.0	203.8	311.2	352.3
135°	120.2	143.2	203.5	299.4	339.9
137.5°	124.5	147.6	203.5	286.7	325.5
140°	129.1	151.6	203.1	274.4	309.6
142.5°	134.0	155.4	203.1	262.9	292.7
145°	138.6	158.7	202.4	252.5	277.5
147.5°	143.9	161.9	201.4	243.8	263.4
150°	148.8	164.8	200.3	235.9	251.8
152.5°	153.4	167.7	198.5	229.2	241.2
155°	157.6	170.2	196.8	222.9	232.4
157.5°	161.9	172.4	195.0	216.8	224.3
160°	165.7	174.4	192.9	210.9	216.9
162.5°	169.3	176.0	190.8	205.0	209.8
165°	171.7	177.0	188.7	199.8	202.8
167.5°	174.6	177.9	186.5	195.2	197.1
170°	176.3	178.6	184.4	190.6	191.8
172.5°	178.1	179.2	182.3	186.6	186.5
175°	179.1	179.5	180.9	183.4	182.7
177.5°	179.8	179.5	179.8	181.1	179.8
180°	179.5	179.5	179.5	179.5	179.5

(END OF REPORT)