Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026597

Luminaire Tested: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1026597
	REPORT IS A COMBINATION OF REPORTS P999717 AND P1007351
Test Lab:	INNOVATION CENTER
Issue Date:	5/7/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	NEO-RAY
Catalog Number:	S124RDIP-B795D365UB30-4F0-XX-W2A-A4
Description:	Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4673.0 lumens
Efficiency:	N/A
Efficacy:	103.4 lumens/watt
Spacing Criteria (0/90/45):	1.22 / 1.27 / 1.38
Luminous Opening:	Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type:	Semi-Direct

Input Watts (W):	45.2
Input Voltage (V):	
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	51	49	46
4	80	69	61	55	75	66	59	53	60	54	50	54	50	46	49	46	42	40
5	74	62	54	48	70	59	52	46	54	48	43	49	44	40	45	41	37	35
6	68	56	48	42	64	53	46	41	49	43	38	45	40	36	41	36	33	31
7	63	51	43	37	60	49	41	36	45	38	34	41	36	32	37	33	30	27
8	59	46	38	33	56	44	37	32	41	35	30	37	32	29	34	30	27	25
9	55	42	35	30	52	41	34	29	38	32	27	35	29	26	32	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10819	10819	10819	10819
5°	10820	12225	10837	9344
10°	10762	14093	10753	8127
15°	10633	15861	10633	6803
20°	10500	17197	10444	5992
25°	10336	17270	10288	5411
30°	10162	14685	10082	5012
35°	9916	11081	9790	4715
40°	9642	8030	9452	4483
45°	9190	6103	8961	4277
50°	8653	4932	8416	3976
55°	8071	4084	7808	3575
60°	7488	3454	7153	2973
65°	6756	2814	6540	2364
70°	6082	2281	5796	1919
75°	5331	1644	4960	1408
80°	4397	1090	4002	1035
85°	3187	560	2649	560

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°
Vertical Angle: 45°
Luminance: 13545 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	2.7
10°-20°	388.0	8.3
20°-30°	607.7	13.0
30°-40°	674.9	14.4
40°-50°	598.0	12.8
50°-60°	466.0	10.0
60°-70°	304.9	6.5
70°-80°	149.6	3.2
80°-90°	37.1	0.8
90°-100°	131.2	2.8
100°-110°	273.9	5.9
110°-120°	243.5	5.2
120°-130°	204.9	4.4
130°-140°	171.0	3.7
140°-150°	130.5	2.8
150°-160°	91.8	2.0
160°-170°	54.0	1.2
170°-180°	17.6	0.4
0°-30°	1124.2	24.1
0°-40°	1799.1	38.5
0°-60°	2863.1	61.3
0°-90°	3354.7	71.8
90°-120°	648.5	13.9
90°-150°	1155.0	24.7
90°-180°	1318.0	28.2
0°-180°	4673.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1327	1327	1327	1327	1327	
5°	1325	1533	1327	1172	1325	126
15°	1268	2031	1268	871	1268	358
25°	1162	2191	1157	686	1162	536
35°	1014	1349	1001	574	1014	633
45°	817	690	796	483	817	630
55°	588	412	569	360	588	526
65°	369	241	357	202	369	368
75°	185	111	172	95	185	196
85°	44	27	36	27	44	49
90°	0	8	0	8	0	4
95°	12	87	12	87	12	13
105°	42	500	42	500	42	44
115°	73	480	73	480	73	73
125°	102	383	102	383	102	91
135°	121	343	121	343	121	94
145°	140	280	140	280	140	88
155°	159	234	159	234	159	73
165°	173	204	173	204	173	49
175°	181	184	181	184	181	17
180°	181	181	181	181	181	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
2.5°	1328.9	1340.7	1347.1	1352.5	1363.2	1367.4	1376.0	1378.1	1386.7	1385.6	1382.4
5°	1324.7	1345.0	1359.9	1376.0	1395.2	1405.9	1417.7	1434.8	1443.3	1455.1	1462.6
7.5°	1317.2	1345.0	1369.6	1394.2	1425.2	1442.3	1457.2	1484.0	1506.4	1525.7	1547.0
10°	1305.4	1340.7	1377.1	1410.2	1453.0	1473.3	1495.7	1535.3	1566.3	1593.0	1627.2
12.5°	1287.2	1336.4	1377.1	1422.0	1476.5	1504.3	1534.2	1581.3	1617.6	1661.4	1704.2
15°	1268.0	1322.5	1376.0	1434.8	1496.8	1528.9	1558.8	1621.9	1677.5	1727.7	1774.8
17.5°	1246.6	1306.5	1365.3	1430.5	1505.3	1544.9	1580.2	1656.1	1717.0	1782.3	1829.3
20°	1221.0	1286.2	1353.5	1426.2	1510.7	1554.5	1594.1	1680.7	1748.0	1818.6	1877.4
22.5°	*1193.2*	*1263.7*	*1337.5*	*1416.6*	*1504.3*	*1552.4*	*1598.4*	*1691.4*	*1769.4*	*1834.6*	*1913.8*
25°	1162.2	1237.0	1312.9	1396.3	1494.7	1547.0	1594.1	1686.0	1769.4	1855.0	1931.9
27.5°	1130.1	1207.1	1286.2	1373.8	1474.3	1525.7	1579.1	1667.9	1765.1	1858.2	1936.2
30°	1094.8	1169.6	1253.0	1336.4	1443.3	1494.7	1549.2	1645.4	1751.3	1844.3	1928.7
32.5°	1056.3	1133.3	1212.4	1299.0	1403.8	1459.4	1509.6	1618.7	1726.7	1818.6	1897.7
35°	1013.5	1086.2	1161.1	1249.8	1353.5	1403.8	1463.7	1577.0	1686.0	1783.3	1834.6
37.5°	967.6	1037.1	1106.6	1194.2	1293.7	1354.6	1413.4	1527.8	1643.3	1708.5	1735.2
40°	924.8	985.7	1046.7	1131.1	1231.6	1294.7	1354.6	1473.3	1574.8	1625.1	1604.8
42.5°	870.3	933.4	987.9	1065.9	1167.5	1226.3	1287.2	1410.2	1492.5	1512.8	1462.6
45°	816.8	869.2	921.6	997.5	1104.4	1154.7	1219.9	1334.3	1402.7	1384.5	1310.8
47.5°	764.4	807.2	856.4	930.2	1026.4	1086.2	1147.2	1246.6	1294.7	1269.1	1166.4
50°	702.4	745.2	796.5	860.7	953.7	1011.4	1059.5	1151.5	1187.8	1124.7	1000.7
52.5°	643.6	681.0	724.9	784.7	873.5	925.9	978.3	1057.4	1069.1	996.4	866.0
55°	588.0	618.0	663.9	712.0	793.3	848.9	885.2	952.6	949.4	858.5	746.3
57.5°	530.3	558.1	589.1	639.3	716.3	758.0	797.6	856.4	825.4	748.4	637.2
60°	479.0	495.0	526.0	574.1	639.3	675.7	706.7	738.8	712.0	628.7	543.1
62.5°	422.3	440.5	462.9	501.4	559.2	593.4	615.8	629.7	601.9	537.8	459.7
65°	368.9	384.9	408.4	442.6	486.5	512.1	523.9	533.5	518.5	445.8	383.8
67.5°	320.7	331.4	352.8	375.3	422.3	428.7	444.8	449.0	419.1	363.5	314.3
70°	272.6	283.3	292.9	319.7	341.1	352.8	356.0	356.0	326.1	289.7	249.1
72.5°	227.7	234.1	243.8	261.9	273.7	282.3	286.5	281.2	253.4	223.5	193.5
75°	185.0	188.2	196.7	208.5	218.1	214.9	213.8	207.4	187.1	165.7	148.6
77.5°	142.2	144.3	154.0	157.2	157.2	160.4	156.1	149.7	132.6	116.5	109.1
80°	106.9	110.1	111.2	113.3	111.2	111.2	108.0	97.3	88.7	81.3	75.9
82.5°	73.8	75.9	77.0	73.8	75.9	72.7	67.4	59.9	54.5	53.5	51.3
85°	43.8	44.9	43.8	43.8	40.6	39.6	35.3	34.2	32.1	32.1	31.0
87.5°	21.4	20.3	18.2	16.0	16.0	15.0	16.0	13.9	16.0	15.0	13.9
90°	0.4	1.1	2.1	2.5	2.8	2.8	2.8	5.0	5.0	5.7	6.4
92.5°	5.0	7.1	11.0	16.4	22.8	27.4	32.0	54.1	88.5	122.0	139.4
95°	11.7	12.8	16.4	21.0	29.5	37.0	44.5	75.4	133.7	218.7	289.8
97.5°	19.6	19.6	22.8	27.0	34.5	40.9	47.3	71.8	122.0	209.5	310.1
100°	27.0	27.0	29.5	33.8	40.5	46.2	51.9	72.9	113.1	185.6	285.9
102.5°	34.1	34.8	37.0	40.9	47.3	52.6	58.0	76.5	110.6	169.6	255.7
105°	41.6	42.7	44.5	48.7	55.1	60.2	65.4	82.5	112.0	161.8	233.3
107.5°	49.8	50.5	52.3	56.9	62.9	68.1	73.3	88.9	116.3	159.7	218.7
110°	58.0	58.7	60.5	64.7	71.1	75.9	80.7	96.4	121.3	160.4	211.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.8	66.5	68.6	72.5	78.9	83.7	88.5	103.5	126.6	162.5	208.7
115°	73.3	74.3	76.8	80.4	87.1	91.9	96.7	110.9	132.3	165.4	208.0
117.5°	81.1	82.1	84.3	88.2	94.6	99.6	104.5	118.1	138.0	168.2	207.7
120°	88.9	89.6	92.1	96.0	102.1	107.0	112.0	125.5	144.0	171.4	207.7
122.5°	96.0	96.7	99.2	102.8	109.5	114.3	119.1	132.6	149.7	174.6	207.3
125°	102.1	103.5	105.6	109.5	116.3	121.2	126.2	139.0	155.4	177.8	207.0
127.5°	107.7	108.8	111.3	115.6	122.7	127.6	132.6	145.1	160.4	180.3	206.3
130°	112.4	113.8	116.6	122.0	128.7	133.8	139.0	151.1	165.0	183.1	205.9
132.5°	117.0	118.1	122.0	127.0	134.4	139.2	144.0	156.1	169.6	185.6	205.5
135°	121.3	122.7	126.2	132.3	139.8	144.4	149.0	160.7	173.5	188.1	205.2
137.5°	125.5	127.0	130.9	136.6	144.4	148.9	153.3	164.3	176.4	189.5	205.2
140°	130.2	131.2	135.1	141.2	148.6	152.9	157.2	167.8	179.2	191.3	204.8
142.5°	135.1	136.2	139.8	145.4	152.6	156.6	160.7	171.0	181.4	192.7	204.8
145°	139.8	140.8	144.4	149.4	156.1	160.0	163.9	173.2	182.8	193.1	204.1
147.5°	145.1	145.4	148.6	154.0	159.7	163.2	166.8	175.7	184.2	193.4	203.1
150°	150.1	150.4	153.3	157.5	162.9	166.2	169.6	177.4	185.3	193.4	202.0
152.5°	154.7	154.7	157.5	161.4	166.1	169.1	172.1	178.9	186.0	192.7	200.2
155°	159.0	159.3	161.4	165.0	168.9	171.6	174.2	180.3	186.3	192.0	198.4
157.5°	163.2	163.2	165.4	168.2	171.8	173.9	176.0	181.4	186.3	191.3	196.6
160°	167.1	167.1	168.6	171.0	173.9	175.9	177.8	182.1	186.3	190.2	194.5
162.5°	170.7	170.3	171.4	173.5	176.0	177.4	178.9	182.8	186.3	189.2	192.4
165°	173.2	173.2	173.9	175.7	177.4	178.5	179.6	182.8	185.6	187.8	190.2
167.5°	176.0	175.7	176.0	177.4	178.5	179.4	180.3	182.8	184.9	186.3	188.1
170°	177.8	177.4	177.8	178.9	179.6	180.1	180.6	182.4	184.2	184.9	186.0
172.5°	179.6	179.2	179.2	179.9	180.3	180.6	181.0	182.1	183.5	183.5	183.8
175°	180.6	180.3	180.3	180.6	181.0	181.0	181.0	181.7	182.8	182.4	182.4
177.5°	181.4	181.0	180.6	181.0	181.0	181.0	181.0	181.4	182.1	181.4	181.4
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	*1326.8*	1326.8	1326.8
2.5°	1391.0	1402.7	1403.8	1414.5	1411.3	1405.9	1415.5	1409.1	*1422.0*	1417.7	1423.0
5°	1472.2	1488.2	1502.1	1510.7	1525.7	1522.5	1538.5	1533.1	*1544.9*	1533.1	1548.1
7.5°	1567.4	1594.1	1608.0	1630.4	1636.9	1637.9	1657.2	1661.4	*1668.9*	1661.4	1670.0
10°	1660.4	1692.4	1724.5	1742.7	1754.5	1770.5	1787.6	1795.1	*1800.4*	1792.9	1798.3
12.5°	1744.8	1795.1	1830.4	1866.7	1875.3	1889.2	1907.3	1905.2	*1926.6*	1922.3	1931.9
15°	1822.9	1878.5	1921.2	1950.1	1973.6	1985.4	2019.6	2021.7	*2020.7*	2031.4	2025.0
17.5°	1892.4	1939.4	2000.4	2037.8	2066.6	2066.6	2085.9	2125.4	*2122.2*	2121.2	2127.6
20°	1949.0	2002.5	2059.2	2122.2	2145.8	2150.0	2176.8	2197.1	*2200.3*	2200.3	2200.3
22.5°	*1991.8*	*2054.9*	*2115.8*	*2160.7*	*2178.9*	*2193.9*	*2217.4*	*2230.2*	*2234.5*	*2232.4*	*2234.5*
25°	2013.2	2073.1	2135.1	2175.7	2186.4	2194.9	2197.1	2204.6	*2203.5*	2190.7	2198.2
27.5°	2017.5	2075.2	2115.8	2126.5	2121.2	2115.8	2081.6	2084.8	*2075.2*	2056.0	2063.4
30°	1998.2	2029.2	2028.2	1995.0	1985.4	1962.9	1931.9	1886.0	*1848.5*	1832.5	1837.9
32.5°	1928.7	1928.7	1890.2	1815.4	1782.3	1741.6	1686.0	1644.3	*1595.2*	1584.5	1604.8
35°	1832.5	1778.0	1707.4	1609.1	1558.8	1528.9	1432.6	1402.7	*1361.0*	1349.3	1358.9
37.5°	1682.8	1591.9	1489.3	1397.4	1354.6	1301.1	1216.7	1173.9	*1144.0*	1123.7	1133.3
40°	1515.0	1404.8	1297.9	1184.6	1137.6	1093.7	1030.7	992.2	*944.1*	946.2	949.4
42.5°	1354.6	1225.2	1105.5	1000.7	955.8	919.5	875.6	828.6	*811.5*	806.1	800.8
45°	1184.6	1046.7	934.4	856.4	815.8	781.5	740.9	714.2	*693.9*	689.6	694.9
47.5°	1024.2	907.7	800.8	728.1	694.9	677.8	645.8	621.2	*608.3*	597.6	604.1
50°	878.8	769.8	684.2	623.3	599.8	588.0	558.1	545.3	*532.4*	529.2	528.2
52.5°	759.1	666.1	592.3	543.1	524.9	518.5	496.1	477.9	*467.2*	470.4	472.6
55°	650.0	570.9	513.2	473.6	458.7	451.2	435.1	422.3	*414.8*	411.6	413.8
57.5°	553.8	485.4	443.7	411.6	399.9	396.7	379.5	375.3	*369.9*	366.7	366.7
60°	466.1	418.0	379.5	361.4	348.5	345.3	332.5	327.2	*326.1*	322.9	320.7
62.5°	392.4	352.8	326.1	306.8	301.5	300.4	291.9	285.5	*282.3*	280.1	280.1
65°	328.2	299.4	276.9	263.0	258.7	256.6	247.0	244.8	*242.7*	240.6	239.5
67.5°	273.7	248.0	232.0	222.4	217.0	218.1	212.8	208.5	*208.5*	207.4	206.3
70°	221.3	205.3	191.4	186.0	183.9	181.8	179.6	176.4	*175.3*	175.3	175.3
72.5°	174.3	163.6	156.1	152.9	150.7	148.6	146.5	146.5	*146.5*	145.4	145.4
75°	133.6	129.4	124.0	120.8	120.8	123.0	119.7	116.5	*113.3*	111.2	112.3
77.5°	100.5	98.4	95.2	89.8	90.9	88.7	88.7	86.6	*87.7*	87.7	85.5
80°	73.8	70.6	69.5	66.3	67.4	66.3	65.2	65.2	*63.1*	63.1	63.1
82.5°	51.3	48.1	48.1	47.0	46.0	46.0	44.9	44.9	*46.0*	43.8	43.8
85°	31.0	29.9	29.9	27.8	27.8	27.8	27.8	28.9	*27.8*	26.7	26.7
87.5°	13.9	15.0	13.9	12.8	12.8	12.8	11.8	11.8	*10.7*	11.8	11.8
90°	6.0	6.4	6.8	7.1	7.1	7.1	7.5	7.8	*7.5*	7.5	7.5
92.5°	115.9	85.7	64.0	50.5	46.0	41.6	36.3	33.8	*32.4*	32.4	32.4
95°	298.0	263.5	208.4	160.7	143.4	126.2	108.8	97.8	*91.4*	86.8	91.4
97.5°	373.7	379.4	352.0	312.9	293.0	273.1	248.9	227.6	*216.9*	208.4	216.9
100°	376.9	428.9	436.0	418.5	405.4	392.2	361.3	339.6	*328.9*	326.1	328.9
102.5°	350.3	426.4	468.7	479.4	475.8	472.2	456.2	442.0	*430.6*	428.5	430.6
105°	316.8	398.3	459.8	495.0	502.3	509.6	510.3	507.4	*502.5*	500.3	502.5
107.5°	289.5	363.8	430.3	479.4	494.3	509.2	524.9	531.3	*534.1*	534.5	534.1
110°	269.9	333.2	394.7	446.3	465.8	485.4	510.6	525.6	*532.0*	535.2	532.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	258.9	310.8	363.4	411.4	431.0	450.6	480.1	498.9	*508.5*	514.2	508.5
115°	252.8	297.3	341.0	382.6	399.7	416.8	444.9	466.2	*477.6*	480.4	477.6
117.5°	249.6	289.5	326.4	360.2	375.2	390.1	415.0	433.5	*445.6*	447.4	445.6
120°	247.1	284.5	317.6	346.0	358.6	371.3	391.5	407.2	*416.4*	420.3	416.4
122.5°	244.3	280.2	311.9	337.1	347.8	358.4	374.8	387.6	*395.1*	399.0	395.1
125°	241.1	275.2	305.8	330.4	340.2	349.9	364.1	374.5	*381.2*	383.3	381.2
127.5°	236.8	269.5	299.1	323.6	332.8	342.1	356.3	365.6	*371.3*	373.4	371.3
130°	232.9	262.4	290.5	314.7	324.2	333.6	348.1	357.0	*362.7*	364.9	362.7
132.5°	229.4	255.0	280.9	304.4	313.8	323.2	337.5	347.8	*353.1*	355.2	353.1
135°	225.8	248.2	271.3	293.0	301.9	310.8	325.0	335.0	*340.7*	342.8	340.7
137.5°	222.6	241.8	262.1	280.9	289.1	297.3	310.8	321.1	*325.7*	328.2	325.7
140°	220.1	236.5	253.2	269.2	276.6	284.1	296.6	304.4	*309.4*	312.2	309.4
142.5°	218.0	231.5	245.7	258.9	265.1	271.3	282.0	289.1	*293.4*	295.2	293.4
145°	215.5	226.9	239.0	249.6	254.6	259.6	268.5	274.5	*278.1*	279.9	278.1
147.5°	213.4	223.0	232.9	241.8	245.9	250.0	256.7	262.1	*264.9*	265.6	264.9
150°	210.9	219.4	227.6	234.7	237.9	241.1	246.8	251.4	*253.5*	253.9	253.5
152.5°	208.0	215.5	222.3	228.7	231.2	233.6	238.3	241.8	*242.9*	243.2	242.9
155°	205.2	211.6	217.3	222.6	224.8	226.9	230.4	233.3	*234.3*	234.3	234.3
157.5°	202.3	207.3	212.3	216.9	218.7	220.5	223.3	225.5	*226.2*	226.2	226.2
160°	199.1	203.4	207.3	211.2	212.6	214.1	216.2	218.3	*218.7*	218.7	218.7
162.5°	196.3	199.5	202.7	205.5	206.8	208.0	209.5	211.6	*211.9*	211.6	211.9
165°	193.1	195.9	198.1	200.6	201.4	202.3	203.8	205.2	*204.8*	204.5	204.8
167.5°	190.2	192.4	194.2	196.3	196.9	197.4	198.1	199.1	*199.1*	198.8	199.1
170°	187.4	189.2	190.2	191.7	192.2	192.7	193.4	193.8	*193.4*	193.4	193.4
172.5°	184.9	186.3	187.0	187.8	188.2	188.5	188.8	189.2	*188.8*	188.1	188.8
175°	183.1	183.8	184.2	184.9	184.9	184.9	184.9	185.6	*184.9*	184.2	184.9
177.5°	181.7	182.1	182.4	182.4	182.6	182.8	182.4	182.8	*182.1*	181.4	182.1
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	*181.0*	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
2.5°	1426.2	1418.7	1417.7	1417.7	1405.9	1412.3	1399.5	1385.6	1379.2	1379.2	1367.4
5°	1544.9	1537.4	1529.9	1518.2	1518.2	1511.8	1491.4	1471.1	1456.2	1443.3	1429.4
7.5°	1666.8	1659.3	1637.9	1626.2	1632.6	1619.7	1593.0	1558.8	1533.1	1512.8	1484.0
10°	1799.4	1779.0	1768.4	1761.9	1739.5	1725.6	1694.6	1644.3	1612.3	1585.5	1548.1
12.5°	1907.3	1913.8	1873.1	1876.3	1853.9	1834.6	1786.5	1738.4	1690.3	1652.9	1597.3
15°	2023.9	2004.6	1980.0	1960.8	1953.3	1929.8	1889.2	1825.0	1772.6	1713.8	1650.8
17.5°	2115.8	2100.9	2077.3	2059.2	2043.1	1986.5	1952.2	1895.6	1824.0	1766.2	1689.2
20°	2193.9	2180.0	2146.8	2135.1	2106.2	2065.6	2016.4	1928.7	1864.6	1801.5	1726.7
22.5°	*2227.0*	*2213.1*	*2184.3*	*2169.3*	*2151.1*	*2111.6*	*2064.5*	*1981.1*	*1902.0*	*1822.9*	*1743.8*
25°	2199.2	2199.2	2185.3	2180.0	2163.9	2128.7	2080.5	2010.0	1925.5	1840.0	1745.9
27.5°	2064.5	2091.2	2100.9	2106.2	2106.2	2107.3	2074.1	2005.7	1923.4	1840.0	1741.6
30°	1869.9	1914.8	1954.4	1966.1	1986.5	2008.9	2022.8	1989.7	1915.9	1828.2	1729.9
32.5°	1625.1	1682.8	1756.6	1774.8	1802.6	1869.9	1907.3	1921.2	1880.6	1803.6	1698.9
35°	1381.3	1454.0	1498.9	1554.5	1580.2	1679.6	1763.0	1813.3	1803.6	1757.7	1662.5
37.5°	1168.6	1210.3	1264.8	1323.6	1374.9	1470.1	1573.8	1671.1	1710.6	1688.2	1616.5
40°	964.4	1013.5	1078.8	1126.9	1162.2	1257.3	1385.6	1491.4	1578.0	1591.9	1548.1
42.5°	820.0	869.2	908.8	961.2	989.0	1080.9	1194.2	1326.8	1429.4	1484.0	1464.7
45°	708.8	738.8	770.8	800.8	835.0	916.3	1021.0	1166.4	1281.9	1358.9	1366.4
47.5°	611.5	638.3	666.1	693.9	713.1	776.2	872.4	991.1	1117.3	1223.1	1264.8
50°	543.1	556.0	576.3	592.3	614.8	669.3	746.3	848.9	982.5	1096.9	1151.5
52.5°	475.8	491.8	507.8	521.7	536.7	575.2	645.8	734.5	850.0	967.6	1034.9
55°	419.1	431.9	446.9	456.5	465.1	499.3	552.7	621.2	720.6	831.8	915.2
57.5°	373.1	378.5	391.3	396.7	406.3	434.1	472.6	533.5	613.7	721.7	790.1
60°	322.9	333.6	343.2	347.5	355.0	374.2	400.9	457.6	527.1	606.2	684.2
62.5°	282.3	286.5	294.0	299.4	304.7	325.0	347.5	390.2	442.6	508.9	580.5
65°	244.8	247.0	251.2	258.7	261.9	276.9	289.7	320.7	369.9	420.2	491.8
67.5°	206.3	208.5	213.8	218.1	221.3	230.9	244.8	267.3	294.0	349.6	389.2
70°	176.4	176.4	179.6	181.8	185.0	189.2	196.7	213.8	238.4	273.7	310.1
72.5°	147.5	147.5	147.5	150.7	150.7	154.0	158.2	170.0	187.1	214.9	238.4
75°	114.4	115.5	117.6	117.6	118.7	123.0	126.2	129.4	137.9	156.1	177.5
77.5°	86.6	88.7	89.8	87.7	89.8	89.8	94.1	98.4	102.6	108.0	124.0
80°	64.1	65.2	63.1	64.1	64.1	66.3	68.4	67.4	69.5	75.9	80.2
82.5°	42.8	43.8	43.8	43.8	43.8	47.0	47.0	46.0	47.0	48.1	49.2
85°	26.7	25.7	25.7	26.7	25.7	25.7	26.7	27.8	26.7	27.8	28.9
87.5°	11.8	11.8	11.8	11.8	10.7	10.7	11.8	10.7	11.8	10.7	9.6
90°	7.8	7.5	7.1	7.1	7.1	6.8	6.4	6.0	6.4	5.7	5.0
92.5°	33.8	36.3	41.6	46.0	50.5	64.0	85.7	115.9	139.4	122.0	88.5
95°	97.8	108.8	126.2	143.4	160.7	208.4	263.5	298.0	289.8	218.7	133.7
97.5°	227.6	248.9	273.1	293.0	312.9	352.0	379.4	373.7	310.1	209.5	122.0
100°	339.6	361.3	392.2	405.4	418.5	436.0	428.9	376.9	285.9	185.6	113.1
102.5°	442.0	456.2	472.2	475.8	479.4	468.7	426.4	350.3	255.7	169.6	110.6
105°	507.4	510.3	509.6	502.3	495.0	459.8	398.3	316.8	233.3	161.8	112.0
107.5°	531.3	524.9	509.2	494.3	479.4	430.3	363.8	289.5	218.7	159.7	116.3
110°	525.6	510.6	485.4	465.8	446.3	394.7	333.2	269.9	211.9	160.4	121.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	498.9	480.1	450.6	431.0	411.4	363.4	310.8	258.9	208.7	162.5	126.6
115°	466.2	444.9	416.8	399.7	382.6	341.0	297.3	252.8	208.0	165.4	132.3
117.5°	433.5	415.0	390.1	375.2	360.2	326.4	289.5	249.6	207.7	168.2	138.0
120°	407.2	391.5	371.3	358.6	346.0	317.6	284.5	247.1	207.7	171.4	144.0
122.5°	387.6	374.8	358.4	347.8	337.1	311.9	280.2	244.3	207.3	174.6	149.7
125°	374.5	364.1	349.9	340.2	330.4	305.8	275.2	241.1	207.0	177.8	155.4
127.5°	365.6	356.3	342.1	332.8	323.6	299.1	269.5	236.8	206.3	180.3	160.4
130°	357.0	348.1	333.6	324.2	314.7	290.5	262.4	232.9	205.9	183.1	165.0
132.5°	347.8	337.5	323.2	313.8	304.4	280.9	255.0	229.4	205.5	185.6	169.6
135°	335.0	325.0	310.8	301.9	293.0	271.3	248.2	225.8	205.2	188.1	173.5
137.5°	321.1	310.8	297.3	289.1	280.9	262.1	241.8	222.6	205.2	189.5	176.4
140°	304.4	296.6	284.1	276.6	269.2	253.2	236.5	220.1	204.8	191.3	179.2
142.5°	289.1	282.0	271.3	265.1	258.9	245.7	231.5	218.0	204.8	192.7	181.4
145°	274.5	268.5	259.6	254.6	249.6	239.0	226.9	215.5	204.1	193.1	182.8
147.5°	262.1	256.7	250.0	245.9	241.8	232.9	223.0	213.4	203.1	193.4	184.2
150°	251.4	246.8	241.1	237.9	234.7	227.6	219.4	210.9	202.0	193.4	185.3
152.5°	241.8	238.3	233.6	231.2	228.7	222.3	215.5	208.0	200.2	192.7	186.0
155°	233.3	230.4	226.9	224.8	222.6	217.3	211.6	205.2	198.4	192.0	186.3
157.5°	225.5	223.3	220.5	218.7	216.9	212.3	207.3	202.3	196.6	191.3	186.3
160°	218.3	216.2	214.1	212.6	211.2	207.3	203.4	199.1	194.5	190.2	186.3
162.5°	211.6	209.5	208.0	206.8	205.5	202.7	199.5	196.3	192.4	189.2	186.3
165°	205.2	203.8	202.3	201.4	200.6	198.1	195.9	193.1	190.2	187.8	185.6
167.5°	199.1	198.1	197.4	196.9	196.3	194.2	192.4	190.2	188.1	186.3	184.9
170°	193.8	193.4	192.7	192.2	191.7	190.2	189.2	187.4	186.0	184.9	184.2
172.5°	189.2	188.8	188.5	188.2	187.8	187.0	186.3	184.9	183.8	183.5	183.5
175°	185.6	184.9	184.9	184.9	184.9	184.2	183.8	183.1	182.4	182.4	182.8
177.5°	182.8	182.4	182.8	182.6	182.4	182.4	182.1	181.7	181.4	181.4	182.1
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
2.5°	1361.0	1355.7	1352.5	1351.4	1341.8	1336.4	1333.2	1331.1	1327.9	1319.3	1311.8
5°	1412.3	1397.4	1389.9	1381.3	1366.4	1349.3	1335.4	1326.8	1316.1	1299.0	1283.0
7.5°	1460.4	1438.0	1423.0	1411.3	1385.6	1357.8	1335.4	1317.2	1296.9	1273.3	1250.9
10°	1510.7	1474.3	1455.1	1436.9	1399.5	1363.2	1331.1	1304.4	1275.5	1244.5	1219.9
12.5°	1550.3	1502.1	1480.8	1455.1	1409.1	1366.4	1325.7	1289.4	1252.0	1218.8	1183.5
15°	1596.2	1536.4	1511.8	1478.6	1415.5	1359.9	1307.6	1268.0	1229.5	1180.3	1142.9
17.5°	1623.0	1553.5	1518.2	1489.3	1420.9	1353.5	1292.6	1243.4	1198.5	1149.3	1109.8
20°	1649.7	1570.6	1531.0	1490.4	1409.1	1337.5	1273.3	1214.5	1167.5	1114.0	1073.4
22.5°	*1658.2*	*1566.3*	*1524.6*	*1487.2*	*1401.6*	*1321.5*	*1247.7*	*1187.8*	*1133.3*	*1079.8*	*1033.9*
25°	1658.2	1565.2	1516.0	1467.9	1378.1	1295.8	1222.0	1156.8	1095.9	1042.4	996.4
27.5°	1641.1	1543.8	1492.5	1448.7	1355.7	1266.9	1191.0	1119.4	1060.6	1007.1	954.7
30°	1619.7	1512.8	1461.5	1409.1	1319.3	1234.9	1152.5	1086.2	1024.2	963.3	916.3
32.5°	1593.0	1479.7	1423.0	1369.6	1274.4	1186.7	1110.8	1045.6	986.8	923.7	871.3
35°	1554.5	1430.5	1367.4	1320.4	1228.4	1137.6	1064.9	1000.7	944.1	878.8	822.2
37.5°	1505.3	1385.6	1321.5	1263.7	1168.6	1085.2	1016.8	954.7	899.1	839.3	776.2
40°	1447.6	1322.5	1266.9	1206.0	1105.5	1026.4	962.2	906.6	851.0	794.4	733.4
42.5°	1382.4	1258.4	1196.4	1137.6	1041.3	963.3	903.4	853.2	801.9	749.5	684.2
45°	1304.4	1187.8	1127.9	1072.3	979.3	899.1	844.6	796.5	752.7	699.2	641.5
47.5°	1216.7	1115.1	1054.2	994.3	903.4	833.9	780.5	739.8	702.4	649.0	596.6
50°	1131.1	1030.7	981.5	920.5	837.1	771.9	717.4	683.2	654.3	601.9	554.9
52.5°	1023.2	947.3	900.2	847.8	767.6	701.4	658.6	628.7	594.4	553.8	512.1
55°	928.0	857.4	820.0	770.8	691.7	632.9	596.6	568.8	542.1	505.7	472.6
57.5°	820.0	776.2	738.8	696.0	618.0	567.7	535.6	512.1	487.5	457.6	430.9
60°	706.7	686.4	650.0	615.8	549.5	505.7	479.0	457.6	434.1	409.5	387.0
62.5°	606.2	594.4	573.1	546.3	484.3	446.9	420.2	404.1	387.0	364.6	343.2
65°	511.0	505.7	485.4	466.1	423.4	390.2	366.7	357.1	337.8	320.7	301.5
67.5°	426.6	420.2	408.4	399.9	363.5	332.5	320.7	307.9	291.9	279.0	263.0
70°	341.1	340.0	332.5	321.8	302.6	280.1	268.4	259.8	243.8	234.1	222.4
72.5°	265.1	270.5	264.1	259.8	247.0	230.9	220.2	214.9	202.1	194.6	186.0
75°	197.8	202.1	205.3	197.8	194.6	187.1	177.5	172.1	165.7	155.0	151.8
77.5°	134.7	144.3	144.3	146.5	147.5	143.3	135.8	131.5	124.0	121.9	117.6
80°	88.7	97.3	98.4	100.5	103.7	103.7	98.4	97.3	89.8	88.7	85.5
82.5°	51.3	58.8	63.1	66.3	65.2	69.5	65.2	64.1	59.9	59.9	57.7
85°	27.8	28.9	31.0	33.1	35.3	37.4	37.4	36.4	35.3	34.2	32.1
87.5°	10.7	10.7	11.8	10.7	11.8	13.9	15.0	15.0	13.9	12.8	10.7
90°	5.0	2.8	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	54.1	32.0	27.4	22.8	16.4	11.0	7.1	5.0	7.1	11.0	16.4
95°	75.4	44.5	37.0	29.5	21.0	16.4	12.8	11.7	12.8	16.4	21.0
97.5°	71.8	47.3	40.9	34.5	27.0	22.8	19.6	19.6	19.6	22.8	27.0
100°	72.9	51.9	46.2	40.5	33.8	29.5	27.0	27.0	27.0	29.5	33.8
102.5°	76.5	58.0	52.6	47.3	40.9	37.0	34.8	34.1	34.8	37.0	40.9
105°	82.5	65.4	60.2	55.1	48.7	44.5	42.7	41.6	42.7	44.5	48.7
107.5°	88.9	73.3	68.1	62.9	56.9	52.3	50.5	49.8	50.5	52.3	56.9
110°	96.4	80.7	75.9	71.1	64.7	60.5	58.7	58.0	58.7	60.5	64.7

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	103.5	88.5	83.7	78.9	72.5	68.6	66.5	65.8	66.5	68.6	72.5
115°	110.9	96.7	91.9	87.1	80.4	76.8	74.3	73.3	74.3	76.8	80.4
117.5°	118.1	104.5	99.6	94.6	88.2	84.3	82.1	81.1	82.1	84.3	88.2
120°	125.5	112.0	107.0	102.1	96.0	92.1	89.6	88.9	89.6	92.1	96.0
122.5°	132.6	119.1	114.3	109.5	102.8	99.2	96.7	96.0	96.7	99.2	102.8
125°	139.0	126.2	121.2	116.3	109.5	105.6	103.5	102.1	103.5	105.6	109.5
127.5°	145.1	132.6	127.6	122.7	115.6	111.3	108.8	107.7	108.8	111.3	115.6
130°	151.1	139.0	133.8	128.7	122.0	116.6	113.8	112.4	113.8	116.6	122.0
132.5°	156.1	144.0	139.2	134.4	127.0	122.0	118.1	117.0	118.1	122.0	127.0
135°	160.7	149.0	144.4	139.8	132.3	126.2	122.7	121.3	122.7	126.2	132.3
137.5°	164.3	153.3	148.9	144.4	136.6	130.9	127.0	125.5	127.0	130.9	136.6
140°	167.8	157.2	152.9	148.6	141.2	135.1	131.2	130.2	131.2	135.1	141.2
142.5°	171.0	160.7	156.6	152.6	145.4	139.8	136.2	135.1	136.2	139.8	145.4
145°	173.2	163.9	160.0	156.1	149.4	144.4	140.8	139.8	140.8	144.4	149.4
147.5°	175.7	166.8	163.2	159.7	154.0	148.6	145.4	145.1	145.4	148.6	154.0
150°	177.4	169.6	166.2	162.9	157.5	153.3	150.4	150.1	150.4	153.3	157.5
152.5°	178.9	172.1	169.1	166.1	161.4	157.5	154.7	154.7	154.7	157.5	161.4
155°	180.3	174.2	171.6	168.9	165.0	161.4	159.3	159.0	159.3	161.4	165.0
157.5°	181.4	176.0	173.9	171.8	168.2	165.4	163.2	163.2	163.2	165.4	168.2
160°	182.1	177.8	175.9	173.9	171.0	168.6	167.1	167.1	167.1	168.6	171.0
162.5°	182.8	178.9	177.4	176.0	173.5	171.4	170.3	170.7	170.3	171.4	173.5
165°	182.8	179.6	178.5	177.4	175.7	173.9	173.2	173.2	173.2	173.9	175.7
167.5°	182.8	180.3	179.4	178.5	177.4	176.0	175.7	176.0	175.7	176.0	177.4
170°	182.4	180.6	180.1	179.6	178.9	177.8	177.4	177.8	177.4	177.8	178.9
172.5°	182.1	181.0	180.6	180.3	179.9	179.2	179.2	179.6	179.2	179.2	179.9
175°	181.7	181.0	181.0	181.0	180.6	180.3	180.3	180.6	180.3	180.3	180.6
177.5°	181.4	181.0	181.0	181.0	181.0	180.6	181.0	181.4	181.0	180.6	181.0
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
2.5°	1305.4	1303.3	1301.1	1292.6	1285.1	1272.3	1261.6	1257.3	1256.2	1257.3	1254.1
5°	1268.0	1266.9	1259.4	1244.5	1230.6	1215.6	1204.9	1194.2	1187.8	1187.8	1180.3
7.5°	1232.7	1225.2	1218.8	1199.6	1183.5	1163.2	1147.2	1137.6	1132.2	1120.5	1120.5
10°	1195.3	1184.6	1176.1	1157.9	1134.4	1114.0	1093.7	1082.0	1072.3	1063.8	1060.6
12.5°	1157.9	1149.3	1133.3	1114.0	1090.5	1064.9	1043.5	1034.9	1012.5	994.3	995.4
15°	1122.6	1103.4	1095.9	1068.1	1040.3	1015.7	984.7	960.1	941.9	930.2	915.2
17.5°	1083.0	1063.8	1049.9	1026.4	990.0	951.5	921.6	888.5	870.3	850.0	840.3
20°	1039.2	1023.2	1012.5	975.1	931.2	885.2	852.1	831.8	811.5	796.5	788.0
22.5°	*1001.8*	*981.5*	*968.6*	*918.4*	*870.3*	*824.3*	*798.6*	*781.5*	*764.4*	*751.6*	*747.3*
25°	953.7	941.9	910.9	867.1	808.3	777.3	754.8	732.4	722.7	714.2	704.6
27.5°	914.1	885.2	863.9	806.1	769.8	734.5	712.0	694.9	683.2	674.6	667.1
30°	864.9	838.2	808.3	760.2	727.0	693.9	673.6	659.7	646.8	641.5	635.1
32.5°	813.6	789.0	760.2	721.7	681.0	655.4	639.3	624.4	615.8	610.5	603.0
35°	767.6	736.6	717.4	681.0	647.9	619.0	604.1	591.2	581.6	579.5	578.4
37.5°	718.5	694.9	676.8	639.3	611.5	587.0	573.1	559.2	553.8	552.7	548.5
40°	675.7	655.4	638.3	603.0	573.1	550.6	539.9	531.4	526.0	526.0	524.9
42.5°	638.3	616.9	599.8	567.7	541.0	520.7	508.9	500.4	498.2	499.3	498.2
45°	596.6	578.4	561.3	528.2	505.7	490.7	477.9	473.6	470.4	471.5	472.6
47.5°	557.0	542.1	524.9	498.2	472.6	456.5	449.0	444.8	444.8	444.8	446.9
50°	521.7	504.6	489.7	461.9	438.3	425.5	419.1	413.8	414.8	415.9	417.0
52.5°	480.0	465.1	454.4	426.6	409.5	393.4	386.0	387.0	386.0	386.0	388.1
55°	443.7	428.7	418.0	392.4	375.3	364.6	358.2	355.0	356.0	353.9	358.2
57.5°	403.1	390.2	382.8	358.2	343.2	333.6	328.2	322.9	325.0	323.9	322.9
60°	367.8	352.8	341.1	323.9	311.1	299.4	296.2	290.8	292.9	290.8	289.7
62.5°	327.2	315.4	306.8	289.7	279.0	269.4	261.9	258.7	257.7	254.5	251.2
65°	286.5	280.1	271.6	254.5	243.8	236.3	232.0	228.8	227.7	219.2	209.6
67.5°	249.1	244.8	236.3	223.5	213.8	206.3	199.9	194.6	188.2	181.8	176.4
70°	213.8	207.4	202.1	190.3	181.8	174.3	167.9	161.4	158.2	151.8	149.7
72.5°	179.6	173.2	167.9	157.2	149.7	142.2	140.1	132.6	129.4	128.3	128.3
75°	144.3	139.0	135.8	126.2	119.7	114.4	111.2	109.1	106.9	104.8	101.6
77.5°	110.1	106.9	104.8	98.4	93.0	89.8	88.7	81.3	79.1	77.0	74.8
80°	80.2	79.1	77.0	71.6	69.5	62.0	62.0	59.9	58.8	58.8	58.8
82.5°	54.5	52.4	51.3	46.0	44.9	43.8	42.8	41.7	42.8	41.7	42.8
85°	28.9	27.8	26.7	26.7	26.7	26.7	26.7	26.7	26.7	25.7	26.7
87.5°	10.7	10.7	10.7	10.7	9.6	10.7	10.7	9.6	10.7	10.7	10.7
90°	2.8	2.8	2.8	5.0	5.0	5.7	6.4	6.0	6.4	6.8	7.1
92.5°	22.8	27.4	32.0	54.1	88.5	122.0	139.4	115.9	85.7	64.0	50.5
95°	29.5	37.0	44.5	75.4	133.7	218.7	289.8	298.0	263.5	208.4	160.7
97.5°	34.5	40.9	47.3	71.8	122.0	209.5	310.1	373.7	379.4	352.0	312.9
100°	40.5	46.2	51.9	72.9	113.1	185.6	285.9	376.9	428.9	436.0	418.5
102.5°	47.3	52.6	58.0	76.5	110.6	169.6	255.7	350.3	426.4	468.7	479.4
105°	55.1	60.2	65.4	82.5	112.0	161.8	233.3	316.8	398.3	459.8	495.0
107.5°	62.9	68.1	73.3	88.9	116.3	159.7	218.7	289.5	363.8	430.3	479.4
110°	71.1	75.9	80.7	96.4	121.3	160.4	211.9	269.9	333.2	394.7	446.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	78.9	83.7	88.5	103.5	126.6	162.5	208.7	258.9	310.8	363.4	411.4
115°	87.1	91.9	96.7	110.9	132.3	165.4	208.0	252.8	297.3	341.0	382.6
117.5°	94.6	99.6	104.5	118.1	138.0	168.2	207.7	249.6	289.5	326.4	360.2
120°	102.1	107.0	112.0	125.5	144.0	171.4	207.7	247.1	284.5	317.6	346.0
122.5°	109.5	114.3	119.1	132.6	149.7	174.6	207.3	244.3	280.2	311.9	337.1
125°	116.3	121.2	126.2	139.0	155.4	177.8	207.0	241.1	275.2	305.8	330.4
127.5°	122.7	127.6	132.6	145.1	160.4	180.3	206.3	236.8	269.5	299.1	323.6
130°	128.7	133.8	139.0	151.1	165.0	183.1	205.9	232.9	262.4	290.5	314.7
132.5°	134.4	139.2	144.0	156.1	169.6	185.6	205.5	229.4	255.0	280.9	304.4
135°	139.8	144.4	149.0	160.7	173.5	188.1	205.2	225.8	248.2	271.3	293.0
137.5°	144.4	148.9	153.3	164.3	176.4	189.5	205.2	222.6	241.8	262.1	280.9
140°	148.6	152.9	157.2	167.8	179.2	191.3	204.8	220.1	236.5	253.2	269.2
142.5°	152.6	156.6	160.7	171.0	181.4	192.7	204.8	218.0	231.5	245.7	258.9
145°	156.1	160.0	163.9	173.2	182.8	193.1	204.1	215.5	226.9	239.0	249.6
147.5°	159.7	163.2	166.8	175.7	184.2	193.4	203.1	213.4	223.0	232.9	241.8
150°	162.9	166.2	169.6	177.4	185.3	193.4	202.0	210.9	219.4	227.6	234.7
152.5°	166.1	169.1	172.1	178.9	186.0	192.7	200.2	208.0	215.5	222.3	228.7
155°	168.9	171.6	174.2	180.3	186.3	192.0	198.4	205.2	211.6	217.3	222.6
157.5°	171.8	173.9	176.0	181.4	186.3	191.3	196.6	202.3	207.3	212.3	216.9
160°	173.9	175.9	177.8	182.1	186.3	190.2	194.5	199.1	203.4	207.3	211.2
162.5°	176.0	177.4	178.9	182.8	186.3	189.2	192.4	196.3	199.5	202.7	205.5
165°	177.4	178.5	179.6	182.8	185.6	187.8	190.2	193.1	195.9	198.1	200.6
167.5°	178.5	179.4	180.3	182.8	184.9	186.3	188.1	190.2	192.4	194.2	196.3
170°	179.6	180.1	180.6	182.4	184.2	184.9	186.0	187.4	189.2	190.2	191.7
172.5°	180.3	180.6	181.0	182.1	183.5	183.5	183.8	184.9	186.3	187.0	187.8
175°	181.0	181.0	181.0	181.7	182.8	182.4	182.4	183.1	183.8	184.2	184.9
177.5°	181.0	181.0	181.0	181.4	182.1	181.4	181.4	181.7	182.1	182.4	182.4
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
2.5°	1254.1	1258.4	1253.0	1256.2	1248.8	1247.7	1248.8	1248.8	1249.8	1250.9	1252.0
5°	1183.5	1182.5	1176.1	1171.8	1168.6	1171.8	1173.9	1176.1	1173.9	1176.1	1177.1
7.5°	1117.3	1114.0	1110.8	1103.4	1105.5	1103.4	1109.8	1106.6	1106.6	1111.9	1116.2
10°	1058.4	1052.0	1049.9	1041.3	1034.9	1033.9	1041.3	1044.5	1047.8	1049.9	1058.4
12.5°	982.5	972.9	965.4	968.6	950.5	957.9	960.1	955.8	968.6	983.6	975.1
15°	901.3	902.4	887.4	882.0	867.1	871.3	872.4	883.1	893.8	892.7	905.6
17.5°	841.4	835.0	822.2	821.1	814.7	817.9	816.8	825.4	822.2	827.5	838.2
20°	785.8	781.5	770.8	766.6	768.7	766.6	767.6	768.7	771.9	783.7	781.5
22.5°	*742.0*	*736.6*	*736.6*	*731.3*	*724.9*	*722.7*	*728.1*	*731.3*	*735.6*	*737.7*	*743.1*
25°	703.5	699.2	693.9	690.7	685.3	686.4	689.6	693.9	697.1	701.4	705.6
27.5°	663.9	663.9	658.6	657.5	655.4	654.3	658.6	660.7	660.7	663.9	668.2
30°	632.9	632.9	627.6	626.5	625.4	625.4	628.7	629.7	630.8	634.0	636.1
32.5°	603.0	601.9	599.8	600.9	599.8	600.9	600.9	601.9	604.1	605.1	609.4
35°	575.2	576.3	574.1	574.1	573.1	574.1	576.3	577.3	578.4	580.5	580.5
37.5°	548.5	550.6	549.5	552.7	552.7	552.7	552.7	554.9	554.9	554.9	553.8
40°	524.9	524.9	523.9	526.0	528.2	528.2	529.2	529.2	530.3	530.3	529.2
42.5°	498.2	500.4	503.6	504.6	506.8	505.7	508.9	507.8	508.9	506.8	504.6
45°	473.6	473.6	477.9	482.2	483.3	483.3	483.3	485.4	483.3	480.0	479.0
47.5°	446.9	449.0	451.2	456.5	457.6	457.6	457.6	457.6	455.5	455.5	455.5
50°	420.2	421.2	422.3	424.4	427.7	426.6	426.6	426.6	430.9	426.6	427.7
52.5°	388.1	389.2	390.2	394.5	393.4	393.4	394.5	394.5	397.7	396.7	394.5
55°	356.0	356.0	358.2	358.2	358.2	360.3	361.4	363.5	362.4	363.5	364.6
57.5°	323.9	321.8	320.7	320.7	323.9	322.9	323.9	323.9	328.2	330.4	331.4
60°	286.5	286.5	285.5	279.0	279.0	278.0	281.2	283.3	285.5	295.1	294.0
62.5°	248.0	243.8	239.5	240.6	234.1	237.3	235.2	237.3	243.8	251.2	252.3
65°	209.6	206.3	202.1	201.0	198.9	202.1	201.0	202.1	205.3	209.6	214.9
67.5°	175.3	174.3	172.1	171.1	171.1	171.1	173.2	173.2	174.3	177.5	180.7
70°	149.7	148.6	149.7	147.5	148.6	147.5	148.6	149.7	150.7	151.8	155.0
72.5°	126.2	126.2	126.2	124.0	126.2	125.1	125.1	126.2	127.2	128.3	130.4
75°	100.5	98.4	96.2	94.1	93.0	95.2	96.2	95.2	98.4	102.6	102.6
77.5°	75.9	74.8	74.8	74.8	75.9	74.8	77.0	75.9	77.0	77.0	79.1
80°	58.8	57.7	58.8	58.8	57.7	59.9	58.8	58.8	59.9	60.9	59.9
82.5°	42.8	43.8	42.8	42.8	42.8	44.9	42.8	42.8	42.8	43.8	43.8
85°	26.7	26.7	26.7	26.7	27.8	26.7	27.8	26.7	28.9	27.8	27.8
87.5°	9.6	10.7	11.8	11.8	11.8	11.8	10.7	11.8	12.8	11.8	12.8
90°	7.1	7.1	7.5	7.8	7.5	7.5	7.5	7.8	7.5	7.1	7.1
92.5°	46.0	41.6	36.3	33.8	32.4	32.4	32.4	33.8	36.3	41.6	46.0
95°	143.4	126.2	108.8	97.8	91.4	86.8	91.4	97.8	108.8	126.2	143.4
97.5°	293.0	273.1	248.9	227.6	216.9	208.4	216.9	227.6	248.9	273.1	293.0
100°	405.4	392.2	361.3	339.6	328.9	326.1	328.9	339.6	361.3	392.2	405.4
102.5°	475.8	472.2	456.2	442.0	430.6	428.5	430.6	442.0	456.2	472.2	475.8
105°	502.3	509.6	510.3	507.4	502.5	500.3	502.5	507.4	510.3	509.6	502.3
107.5°	494.3	509.2	524.9	531.3	534.1	534.5	534.1	531.3	524.9	509.2	494.3
110°	465.8	485.4	510.6	525.6	532.0	535.2	532.0	525.6	510.6	485.4	465.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	431.0	450.6	480.1	498.9	508.5	514.2	508.5	498.9	480.1	450.6	431.0
115°	399.7	416.8	444.9	466.2	477.6	480.4	477.6	466.2	444.9	416.8	399.7
117.5°	375.2	390.1	415.0	433.5	445.6	447.4	445.6	433.5	415.0	390.1	375.2
120°	358.6	371.3	391.5	407.2	416.4	420.3	416.4	407.2	391.5	371.3	358.6
122.5°	347.8	358.4	374.8	387.6	395.1	399.0	395.1	387.6	374.8	358.4	347.8
125°	340.2	349.9	364.1	374.5	381.2	383.3	381.2	374.5	364.1	349.9	340.2
127.5°	332.8	342.1	356.3	365.6	371.3	373.4	371.3	365.6	356.3	342.1	332.8
130°	324.2	333.6	348.1	357.0	362.7	364.9	362.7	357.0	348.1	333.6	324.2
132.5°	313.8	323.2	337.5	347.8	353.1	355.2	353.1	347.8	337.5	323.2	313.8
135°	301.9	310.8	325.0	335.0	340.7	342.8	340.7	335.0	325.0	310.8	301.9
137.5°	289.1	297.3	310.8	321.1	325.7	328.2	325.7	321.1	310.8	297.3	289.1
140°	276.6	284.1	296.6	304.4	309.4	312.2	309.4	304.4	296.6	284.1	276.6
142.5°	265.1	271.3	282.0	289.1	293.4	295.2	293.4	289.1	282.0	271.3	265.1
145°	254.6	259.6	268.5	274.5	278.1	279.9	278.1	274.5	268.5	259.6	254.6
147.5°	245.9	250.0	256.7	262.1	264.9	265.6	264.9	262.1	256.7	250.0	245.9
150°	237.9	241.1	246.8	251.4	253.5	253.9	253.5	251.4	246.8	241.1	237.9
152.5°	231.2	233.6	238.3	241.8	242.9	243.2	242.9	241.8	238.3	233.6	231.2
155°	224.8	226.9	230.4	233.3	234.3	234.3	234.3	233.3	230.4	226.9	224.8
157.5°	218.7	220.5	223.3	225.5	226.2	226.2	226.2	225.5	223.3	220.5	218.7
160°	212.6	214.1	216.2	218.3	218.7	218.7	218.7	218.3	216.2	214.1	212.6
162.5°	206.8	208.0	209.5	211.6	211.9	211.6	211.9	211.6	209.5	208.0	206.8
165°	201.4	202.3	203.8	205.2	204.8	204.5	204.8	205.2	203.8	202.3	201.4
167.5°	196.9	197.4	198.1	199.1	199.1	198.8	199.1	199.1	198.1	197.4	196.9
170°	192.2	192.7	193.4	193.8	193.4	193.4	193.4	193.8	193.4	192.7	192.2
172.5°	188.2	188.5	188.8	189.2	188.8	188.1	188.8	189.2	188.8	188.5	188.2
175°	184.9	184.9	184.9	185.6	184.9	184.2	184.9	185.6	184.9	184.9	184.9
177.5°	182.6	182.8	182.4	182.8	182.1	181.4	182.1	182.8	182.4	182.8	182.6
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8	1326.8
2.5°	1256.2	1261.6	1259.4	1252.0	1255.2	1261.6	1268.0	1276.6	1281.9	1286.2	1288.3
5°	1182.5	1192.1	1190.0	1190.0	1194.2	1204.9	1215.6	1233.8	1240.2	1247.7	1258.4
7.5°	1117.3	1124.7	1131.1	1133.3	1139.7	1153.6	1167.5	1187.8	1203.9	1212.4	1218.8
10°	1059.5	1064.9	1074.5	1079.8	1086.2	1103.4	1123.7	1145.0	1161.1	1176.1	1184.6
12.5°	985.7	1007.1	1020.0	1028.5	1037.1	1062.7	1078.8	1102.3	1121.5	1135.4	1148.3
15°	903.4	929.1	936.6	969.7	991.1	1011.4	1036.0	1063.8	1082.0	1098.0	1115.1
17.5°	833.9	852.1	860.7	895.9	914.1	946.2	981.5	1016.8	1044.5	1056.3	1073.4
20°	790.1	799.7	816.8	828.6	847.8	885.2	923.7	966.5	1008.2	1020.0	1037.1
22.5°	*745.2*	*758.0*	*769.8*	*785.8*	*800.8*	*826.4*	*864.9*	*912.0*	*956.9*	*978.3*	*998.6*
25°	704.6	717.4	724.9	742.0	755.9	781.5	808.3	856.4	909.8	928.0	960.1
27.5°	672.5	680.0	692.8	700.3	716.3	739.8	764.4	800.8	853.2	884.2	915.2
30°	640.4	645.8	656.5	667.1	678.9	694.9	722.7	758.0	806.1	832.9	863.9
32.5°	608.3	616.9	623.3	630.8	643.6	662.9	682.1	716.3	754.8	784.7	815.8
35°	581.6	584.8	593.4	601.9	610.5	627.6	647.9	681.0	715.3	738.8	766.6
37.5°	552.7	558.1	564.5	567.7	581.6	592.3	613.7	639.3	680.0	694.9	722.7
40°	530.3	529.2	535.6	541.0	547.4	564.5	577.3	605.1	637.2	660.7	677.8
42.5°	502.5	502.5	504.6	511.0	519.6	530.3	545.3	568.8	601.9	619.0	639.3
45°	480.0	476.8	477.9	482.2	487.5	498.2	513.2	533.5	566.6	580.5	601.9
47.5°	453.3	450.1	450.1	454.4	458.7	466.1	477.9	501.4	528.2	546.3	562.4
50°	423.4	424.4	423.4	426.6	428.7	436.2	449.0	468.3	492.9	507.8	526.0
52.5°	395.6	393.4	392.4	394.5	398.8	404.1	418.0	435.1	458.7	473.6	489.7
55°	361.4	363.5	363.5	363.5	369.9	372.1	382.8	399.9	423.4	435.1	450.1
57.5°	330.4	329.3	331.4	330.4	335.7	343.2	351.7	364.6	388.1	399.9	413.8
60°	296.2	297.2	298.3	298.3	302.6	310.1	319.7	331.4	350.7	362.4	375.3
62.5°	254.5	259.8	265.1	267.3	273.7	279.0	285.5	298.3	315.4	323.9	335.7
65°	214.9	222.4	229.9	235.2	239.5	244.8	253.4	265.1	279.0	287.6	299.4
67.5°	180.7	186.0	195.7	201.0	209.6	216.0	221.3	230.9	248.0	251.2	260.9
70°	156.1	158.2	162.5	166.8	176.4	181.8	188.2	197.8	210.6	218.1	223.5
72.5°	131.5	132.6	134.7	139.0	143.3	149.7	157.2	165.7	177.5	180.7	188.2
75°	104.8	111.2	111.2	114.4	117.6	120.8	127.2	135.8	143.3	148.6	152.9
77.5°	78.0	81.3	83.4	88.7	93.0	96.2	100.5	106.9	111.2	115.5	118.7
80°	60.9	62.0	63.1	63.1	65.2	69.5	73.8	78.0	83.4	85.5	88.7
82.5°	44.9	44.9	44.9	47.0	48.1	49.2	49.2	51.3	56.7	58.8	62.0
85°	28.9	28.9	28.9	28.9	29.9	31.0	32.1	33.1	33.1	33.1	35.3
87.5°	11.8	13.9	12.8	13.9	13.9	13.9	13.9	15.0	15.0	16.0	16.0
90°	7.1	6.8	6.4	6.0	6.4	5.7	5.0	5.0	2.8	2.8	2.8
92.5°	50.5	64.0	85.7	115.9	139.4	122.0	88.5	54.1	32.0	27.4	22.8
95°	160.7	208.4	263.5	298.0	289.8	218.7	133.7	75.4	44.5	37.0	29.5
97.5°	312.9	352.0	379.4	373.7	310.1	209.5	122.0	71.8	47.3	40.9	34.5
100°	418.5	436.0	428.9	376.9	285.9	185.6	113.1	72.9	51.9	46.2	40.5
102.5°	479.4	468.7	426.4	350.3	255.7	169.6	110.6	76.5	58.0	52.6	47.3
105°	495.0	459.8	398.3	316.8	233.3	161.8	112.0	82.5	65.4	60.2	55.1
107.5°	479.4	430.3	363.8	289.5	218.7	159.7	116.3	88.9	73.3	68.1	62.9
110°	446.3	394.7	333.2	269.9	211.9	160.4	121.3	96.4	80.7	75.9	71.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	411.4	363.4	310.8	258.9	208.7	162.5	126.6	103.5	88.5	83.7	78.9
115°	382.6	341.0	297.3	252.8	208.0	165.4	132.3	110.9	96.7	91.9	87.1
117.5°	360.2	326.4	289.5	249.6	207.7	168.2	138.0	118.1	104.5	99.6	94.6
120°	346.0	317.6	284.5	247.1	207.7	171.4	144.0	125.5	112.0	107.0	102.1
122.5°	337.1	311.9	280.2	244.3	207.3	174.6	149.7	132.6	119.1	114.3	109.5
125°	330.4	305.8	275.2	241.1	207.0	177.8	155.4	139.0	126.2	121.2	116.3
127.5°	323.6	299.1	269.5	236.8	206.3	180.3	160.4	145.1	132.6	127.6	122.7
130°	314.7	290.5	262.4	232.9	205.9	183.1	165.0	151.1	139.0	133.8	128.7
132.5°	304.4	280.9	255.0	229.4	205.5	185.6	169.6	156.1	144.0	139.2	134.4
135°	293.0	271.3	248.2	225.8	205.2	188.1	173.5	160.7	149.0	144.4	139.8
137.5°	280.9	262.1	241.8	222.6	205.2	189.5	176.4	164.3	153.3	148.9	144.4
140°	269.2	253.2	236.5	220.1	204.8	191.3	179.2	167.8	157.2	152.9	148.6
142.5°	258.9	245.7	231.5	218.0	204.8	192.7	181.4	171.0	160.7	156.6	152.6
145°	249.6	239.0	226.9	215.5	204.1	193.1	182.8	173.2	163.9	160.0	156.1
147.5°	241.8	232.9	223.0	213.4	203.1	193.4	184.2	175.7	166.8	163.2	159.7
150°	234.7	227.6	219.4	210.9	202.0	193.4	185.3	177.4	169.6	166.2	162.9
152.5°	228.7	222.3	215.5	208.0	200.2	192.7	186.0	178.9	172.1	169.1	166.1
155°	222.6	217.3	211.6	205.2	198.4	192.0	186.3	180.3	174.2	171.6	168.9
157.5°	216.9	212.3	207.3	202.3	196.6	191.3	186.3	181.4	176.0	173.9	171.8
160°	211.2	207.3	203.4	199.1	194.5	190.2	186.3	182.1	177.8	175.9	173.9
162.5°	205.5	202.7	199.5	196.3	192.4	189.2	186.3	182.8	178.9	177.4	176.0
165°	200.6	198.1	195.9	193.1	190.2	187.8	185.6	182.8	179.6	178.5	177.4
167.5°	196.3	194.2	192.4	190.2	188.1	186.3	184.9	182.8	180.3	179.4	178.5
170°	191.7	190.2	189.2	187.4	186.0	184.9	184.2	182.4	180.6	180.1	179.6
172.5°	187.8	187.0	186.3	184.9	183.8	183.5	183.5	182.1	181.0	180.6	180.3
175°	184.9	184.2	183.8	183.1	182.4	182.4	182.8	181.7	181.0	181.0	181.0
177.5°	182.4	182.4	182.1	181.7	181.4	181.4	182.1	181.4	181.0	181.0	181.0
180°	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0	181.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1326.8	1326.8	1326.8	1326.8
2.5°	1296.9	1303.3	1314.0	1328.9
5°	1266.9	1285.1	1302.2	1324.7
7.5°	1240.2	1261.6	1285.1	1317.2
10°	1209.2	1235.9	1265.9	1305.4
12.5°	1172.8	1210.3	1244.5	1287.2
15°	1146.1	1173.9	1217.7	1268.0
17.5°	1108.7	1146.1	1190.0	1246.6
20°	1073.4	1113.0	1162.2	1221.0
22.5°	*1036.0*	*1080.9*	*1130.1*	*1193.2*
25°	997.5	1045.6	1094.8	1162.2
27.5°	962.2	1006.1	1061.7	1130.1
30°	919.5	969.7	1023.2	1094.8
32.5°	877.8	930.2	984.7	1056.3
35°	832.9	885.2	945.1	1013.5
37.5°	789.0	846.8	901.3	967.6
40°	740.9	800.8	857.4	924.8
42.5°	693.9	755.9	812.5	870.3
45°	650.0	711.0	762.3	816.8
47.5°	608.3	662.9	715.3	764.4
50°	567.7	613.7	661.8	702.4
52.5°	524.9	568.8	607.3	643.6
55°	486.5	520.7	554.9	588.0
57.5°	440.5	474.7	504.6	530.3
60°	402.0	423.4	452.2	479.0
62.5°	358.2	382.8	405.2	422.3
65°	315.4	336.8	353.9	368.9
67.5°	279.0	291.9	304.7	320.7
70°	235.2	245.9	260.9	272.6
72.5°	197.8	206.3	213.8	227.7
75°	160.4	167.9	172.1	185.0
77.5°	124.0	131.5	134.7	142.2
80°	95.2	96.2	100.5	106.9
82.5°	65.2	67.4	68.4	73.8
85°	37.4	42.8	41.7	43.8
87.5°	16.0	17.1	19.2	21.4
90°	2.5	2.1	1.1	0.4
92.5°	16.4	11.0	7.1	5.0
95°	21.0	16.4	12.8	11.7
97.5°	27.0	22.8	19.6	19.6
100°	33.8	29.5	27.0	27.0
102.5°	40.9	37.0	34.8	34.1
105°	48.7	44.5	42.7	41.6
107.5°	56.9	52.3	50.5	49.8
110°	64.7	60.5	58.7	58.0

TEST NUMBER: P1026597
CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	72.5	68.6	66.5	65.8
115°	80.4	76.8	74.3	73.3
117.5°	88.2	84.3	82.1	81.1
120°	96.0	92.1	89.6	88.9
122.5°	102.8	99.2	96.7	96.0
125°	109.5	105.6	103.5	102.1
127.5°	115.6	111.3	108.8	107.7
130°	122.0	116.6	113.8	112.4
132.5°	127.0	122.0	118.1	117.0
135°	132.3	126.2	122.7	121.3
137.5°	136.6	130.9	127.0	125.5
140°	141.2	135.1	131.2	130.2
142.5°	145.4	139.8	136.2	135.1
145°	149.4	144.4	140.8	139.8
147.5°	154.0	148.6	145.4	145.1
150°	157.5	153.3	150.4	150.1
152.5°	161.4	157.5	154.7	154.7
155°	165.0	161.4	159.3	159.0
157.5°	168.2	165.4	163.2	163.2
160°	171.0	168.6	167.1	167.1
162.5°	173.5	171.4	170.3	170.7
165°	175.7	173.9	173.2	173.2
167.5°	177.4	176.0	175.7	176.0
170°	178.9	177.8	177.4	177.8
172.5°	179.9	179.2	179.2	179.6
175°	180.6	180.3	180.3	180.6
177.5°	181.0	180.6	181.0	181.4
180°	181.0	181.0	181.0	181.0

(END OF REPORT)