

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026599

Luminaire Tested: S124RDIP-B795D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026599
REPORT IS A COMBINATION OF REPORTS P999719 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D365UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4503.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026599

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1026599

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36
6	67	55	47	41	64	53	45	40	48	42	37	44	38	35	40	35	32
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	33	29	26
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9528 cd/sqm

TEST NUMBER: P1026599

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.9
10°-20°	366.2	8.1
20°-30°	528.7	11.7
30°-40°	599.1	13.3
40°-50°	578.5	12.8
50°-60°	480.9	10.7
60°-70°	331.9	7.4
70°-80°	167.7	3.7
80°-90°	43.6	1.0
90°-100°	30.0	0.7
100°-110°	89.7	2.0
110°-120°	152.4	3.4
120°-130°	201.0	4.5
130°-140°	225.8	5.0
140°-150°	221.9	4.9
150°-160°	186.6	4.1
160°-170°	124.2	2.8
170°-180°	43.5	1.0
0°-30°	1026.2	22.8
0°-40°	1625.3	36.1
0°-60°	2684.7	59.6
0°-90°	3228.0	71.7
90°-120°	272.1	6.0
90°-150°	920.8	20.4
90°-180°	1275.0	28.3
0°-180°	4503.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	1	5	8	10	11	5
95°	21	24	27	28	28	23
105°	83	83	85	86	87	88
115°	155	155	154	154	154	153
125°	226	226	225	225	224	201
135°	291	293	293	292	291	225
145°	354	355	355	355	354	221
155°	405	405	405	406	405	186
165°	441	440	439	441	440	124
175°	459	457	457	459	457	44
180°	460	460	460	460	460	

TEST NUMBER: P1026599

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	1.1	5.0	7.8	10.0	10.7
92.5°	9.2	13.9	15.6	16.7	17.1
95°	21.3	24.5	27.0	28.1	28.1
97.5°	34.1	37.0	39.8	41.2	41.2
100°	49.8	51.2	54.4	55.1	55.1
102.5°	66.1	66.5	69.3	70.4	70.7
105°	82.8	83.2	84.6	85.7	86.7
107.5°	100.2	100.6	100.9	102.4	102.0
110°	118.0	118.7	118.3	117.6	118.7

TEST NUMBER: P1026599

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	136.5	136.5	135.8	135.8	135.8
115°	155.0	155.0	154.2	153.9	153.5
117.5°	172.4	172.4	172.0	170.9	169.9
120°	189.8	191.2	190.1	188.4	189.1
122.5°	207.9	208.3	207.9	206.8	205.1
125°	225.7	225.7	225.3	224.6	223.9
127.5°	241.7	242.7	242.0	241.3	241.0
130°	258.7	259.8	259.8	259.1	257.7
132.5°	276.1	276.9	276.5	275.8	275.4
135°	291.1	293.2	293.2	292.5	291.4
137.5°	307.8	308.8	309.5	308.5	308.8
140°	324.5	325.2	325.2	324.8	324.5
142.5°	339.8	340.5	340.1	340.1	340.1
145°	353.6	355.0	355.4	355.0	354.0
147.5°	367.8	369.6	369.3	368.9	368.5
150°	380.6	382.1	382.1	382.1	381.7
152.5°	392.7	393.4	393.8	394.8	393.8
155°	405.2	405.2	404.8	406.2	404.8
157.5°	415.8	415.1	415.1	416.2	415.1
160°	425.1	424.7	424.3	425.4	423.6
162.5°	433.6	432.5	432.2	434.3	432.5
165°	441.0	440.0	439.3	441.4	440.0
167.5°	447.1	445.7	445.7	447.8	445.7
170°	452.1	450.3	450.6	452.8	450.3
172.5°	455.6	454.2	454.2	456.7	454.2
175°	458.8	457.0	456.7	459.2	456.7
177.5°	460.2	458.5	458.5	460.9	458.1
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)