

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026808

Luminaire Tested: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026808
REPORT IS A COMBINATION OF REPORTS P1001717 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7026.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026808

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026808

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68
1	100	95	91	87	93	89	85	82	78	75	73	68	66	64	59	57	56
2	91	82	76	70	85	77	72	67	68	64	60	59	56	53	51	49	46
3	82	72	64	58	77	68	61	55	60	54	50	52	48	44	45	42	39
4	75	64	55	49	70	60	52	47	53	47	42	46	42	38	40	37	33
5	69	57	48	42	64	54	46	40	47	41	36	42	37	33	36	32	29
6	64	51	42	36	59	48	40	35	43	36	32	38	32	28	33	29	25
7	59	46	38	32	55	43	36	30	39	32	28	34	29	25	30	26	23
8	55	42	34	28	51	40	32	27	35	29	25	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	25	21	18
10	48	35	28	23	45	33	26	22	30	24	20	27	22	18	24	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9818	9818	9818
5°	9834	9612	9636
10°	9760	9416	9389
15°	9642	9188	9086
20°	9481	8913	8786
25°	9291	8619	8421
30°	9061	8300	8091
35°	8846	8005	7785
40°	8627	7695	7478
45°	8380	7426	7201
50°	8143	7133	6952
55°	7858	6855	6662
60°	7546	6537	6365
65°	7220	6203	6031
70°	6847	5755	5683
75°	6258	5313	5258
80°	5487	4774	4788
85°	4723	4345	4541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8380 cd/sqm

TEST NUMBER: P1026808

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	2.1
10°-20°	411.6	5.9
20°-30°	612.1	8.7
30°-40°	724.9	10.3
40°-50°	749.5	10.7
50°-60°	690.4	9.8
60°-70°	558.1	7.9
70°-80°	373.4	5.3
80°-90°	194.1	2.8
90°-100°	133.9	1.9
100°-110°	247.5	3.5
110°-120°	355.0	5.1
120°-130°	417.2	5.9
130°-140°	429.3	6.1
140°-150°	393.1	5.6
150°-160°	315.9	4.5
160°-170°	204.3	2.9
170°-180°	70.4	1.0
0°-30°	1168.8	16.6
0°-40°	1893.7	27.0
0°-60°	3333.6	47.4
0°-90°	4459.3	63.5
90°-120°	736.4	10.5
90°-150°	1976.1	28.1
90°-180°	2567.0	36.5
0°-180°	7026.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1532	1532	1532	1532	1532	
5°	1532	1529	1519	1531	1529	145
15°	1463	1465	1454	1463	1457	412
25°	1330	1334	1325	1331	1324	612
35°	1151	1161	1157	1161	1161	720
45°	948	964	972	982	984	731
55°	729	753	777	793	799	651
65°	502	536	572	595	601	498
75°	276	316	364	394	401	293
85°	83	132	185	218	230	86
90°	24	77	132	169	182	18
95°	51	88	118	154	165	54
105°	175	201	246	276	286	186
115°	312	326	365	390	396	310
125°	438	440	470	492	498	391
135°	541	543	552	571	575	417
145°	625	625	625	633	636	391
155°	687	684	685	687	682	317
165°	725	722	722	726	721	205
175°	742	738	739	743	738	71
180°	742	742	742	742	742	

TEST NUMBER: P1026808

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1532.4	1532.4	1532.4	1532.4	1532.4
2.5°	1536.9	1533.9	1523.4	1533.9	1532.4
5°	1532.4	1529.4	1518.8	1530.9	1529.4
7.5°	1521.8	1520.3	1509.8	1520.3	1518.8
10°	1506.8	1506.8	1494.8	1505.3	1503.8
12.5°	1485.8	1487.3	1478.3	1485.8	1481.3
15°	1463.3	1464.8	1454.2	1463.3	1457.2
17.5°	1434.7	1437.7	1427.2	1434.7	1430.2
20°	1403.2	1406.2	1395.7	1400.2	1400.2
22.5°	1367.1	1373.1	1361.1	1367.1	1362.6
25°	1329.6	1334.1	1325.0	1331.1	1323.5
27.5°	1289.0	1295.0	1284.5	1289.0	1286.0
30°	1242.4	1251.4	1242.4	1245.4	1243.9
32.5°	1200.4	1207.9	1201.9	1204.9	1203.4
35°	1150.8	1161.3	1156.8	1161.3	1161.3
37.5°	1102.7	1111.7	1110.2	1116.2	1114.7
40°	1053.1	1065.1	1063.6	1069.7	1072.7
42.5°	999.0	1015.6	1020.1	1027.6	1027.6
45°	948.0	964.5	972.0	982.5	984.0
47.5°	895.4	910.4	922.4	937.4	940.5
50°	841.3	857.8	874.3	890.9	895.4
52.5°	784.2	805.2	826.3	844.3	847.3
55°	728.6	752.7	776.7	793.2	799.2
57.5°	671.5	700.1	727.1	745.2	749.7
60°	614.4	644.5	674.5	697.1	701.6
62.5°	558.9	588.9	622.0	647.5	653.5
65°	501.8	536.3	572.4	594.9	600.9
67.5°	449.2	482.2	518.3	545.3	552.9
70°	390.6	425.2	464.2	492.8	501.8
72.5°	333.5	369.6	413.1	444.7	450.7
75°	276.4	315.5	363.6	393.6	401.1
77.5°	220.8	265.9	311.0	344.0	350.0
80°	169.8	214.8	265.9	299.0	305.0
82.5°	123.2	171.3	223.8	255.4	267.4
85°	82.6	132.2	184.8	217.8	229.9
87.5°	52.6	100.7	151.7	186.3	196.8
90°	24.5	77.0	132.0	169.2	181.5
92.5°	31.4	70.1	126.0	161.7	172.8
95°	50.8	88.3	118.5	154.2	164.7
97.5°	76.8	116.2	113.6	146.2	157.2
100°	108.3	141.6	191.7	141.4	148.2
102.5°	140.3	171.1	218.7	249.9	212.8
105°	175.1	201.4	246.4	276.5	286.5
107.5°	211.0	232.1	276.7	307.3	314.1
110°	245.8	263.8	307.0	333.9	345.0



TEST NUMBER: P1026808

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	279.9	295.0	336.2	361.0	370.5
115°	312.4	325.7	365.3	390.1	395.8
117.5°	346.7	354.2	394.0	416.2	425.6
120°	379.7	383.6	419.9	444.3	450.5
122.5°	407.3	411.5	445.2	468.1	473.8
125°	437.5	439.9	470.0	491.8	497.6
127.5°	465.2	466.4	491.4	512.9	517.5
130°	491.5	492.8	514.3	533.8	538.5
132.5°	516.4	519.7	533.1	554.2	557.4
135°	541.2	543.0	552.4	570.8	575.1
137.5°	564.3	566.0	570.9	588.9	592.2
140°	585.3	586.4	587.3	604.9	607.6
142.5°	605.6	604.7	605.8	619.3	622.0
145°	625.4	625.0	625.0	633.1	635.8
147.5°	641.5	641.5	642.1	645.6	644.8
150°	658.0	656.9	658.0	659.1	656.2
152.5°	673.9	671.2	672.3	673.4	669.5
155°	687.1	683.8	684.9	686.6	682.2
157.5°	697.6	695.9	695.9	697.6	693.2
160°	708.6	705.3	705.8	708.0	703.6
162.5°	717.4	714.1	714.6	717.9	713.0
165°	725.1	721.8	722.3	725.6	721.2
167.5°	731.1	727.8	728.4	732.2	727.3
170°	736.1	732.2	732.8	737.2	732.2
172.5°	739.4	735.5	736.6	740.5	735.5
175°	741.6	738.3	738.8	743.2	738.3
177.5°	743.2	739.9	740.5	744.3	739.9
180°	741.6	741.6	741.6	741.6	741.6

(END OF REPORT)