

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026600

Luminaire Tested: S124RDIP-B795D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026600
REPORT IS A COMBINATION OF REPORTS P999720 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D365UB30-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4548.6 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026600

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026600

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75
1	103	99	95	91	97	94	90	87	84	81	79	75	73	72	67	66	65
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47
4	79	68	60	54	75	65	58	52	59	53	48	53	48	44	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32
7	62	50	42	36	59	48	40	35	43	37	33	40	34	31	36	32	28
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1026600

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.9
10°-20°	366.2	8.1
20°-30°	528.7	11.6
30°-40°	599.1	13.2
40°-50°	578.5	12.7
50°-60°	480.9	10.6
60°-70°	331.9	7.3
70°-80°	167.7	3.7
80°-90°	43.3	1.0
90°-100°	134.4	3.0
100°-110°	273.5	6.0
110°-120°	243.7	5.4
120°-130°	204.7	4.5
130°-140°	170.9	3.8
140°-150°	130.5	2.9
150°-160°	91.7	2.0
160°-170°	53.9	1.2
170°-180°	17.5	0.4
0°-30°	1026.2	22.6
0°-40°	1625.3	35.7
0°-60°	2684.7	59.0
0°-90°	3227.7	71.0
90°-120°	651.6	14.3
90°-150°	1157.7	25.5
90°-180°	1321.0	29.0
0°-180°	4548.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	0	3	6	7	8	4
95°	12	37	290	143	87	13
105°	42	60	233	502	500	44
115°	73	92	208	400	480	73
125°	102	121	207	340	383	91
135°	121	144	205	302	343	94
145°	140	160	204	255	280	88
155°	159	172	198	225	234	73
165°	173	178	190	201	204	49
175°	181	181	182	185	184	17
180°	181	181	181	181	181	

TEST NUMBER: P1026600

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	0.4	2.8	6.4	7.1	7.5
92.5°	5.0	27.4	139.4	46.0	32.4
95°	11.7	37.0	289.8	143.4	86.8
97.5°	19.6	40.9	310.1	293.0	208.4
100°	27.0	46.2	285.9	405.4	326.1
102.5°	34.1	52.6	255.7	475.8	428.5
105°	41.6	60.2	233.3	502.3	500.3
107.5°	49.8	68.1	218.7	494.3	534.5
110°	58.0	75.9	211.9	465.8	535.2

TEST NUMBER: P1026600

CATALOG NUMBER: S124RDIP-B795D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.8	83.7	208.7	431.0	514.2
115°	73.3	91.9	208.0	399.7	480.4
117.5°	81.1	99.6	207.7	375.2	447.4
120°	88.9	107.0	207.7	358.6	420.3
122.5°	96.0	114.3	207.3	347.8	399.0
125°	102.1	121.2	207.0	340.2	383.3
127.5°	107.7	127.6	206.3	332.8	373.4
130°	112.4	133.8	205.9	324.2	364.9
132.5°	117.0	139.2	205.5	313.8	355.2
135°	121.3	144.4	205.2	301.9	342.8
137.5°	125.5	148.9	205.2	289.1	328.2
140°	130.2	152.9	204.8	276.6	312.2
142.5°	135.1	156.6	204.8	265.1	295.2
145°	139.8	160.0	204.1	254.6	279.9
147.5°	145.1	163.2	203.1	245.9	265.6
150°	150.1	166.2	202.0	237.9	253.9
152.5°	154.7	169.1	200.2	231.2	243.2
155°	159.0	171.6	198.4	224.8	234.3
157.5°	163.2	173.9	196.6	218.7	226.2
160°	167.1	175.9	194.5	212.6	218.7
162.5°	170.7	177.4	192.4	206.8	211.6
165°	173.2	178.5	190.2	201.4	204.5
167.5°	176.0	179.4	188.1	196.9	198.8
170°	177.8	180.1	186.0	192.2	193.4
172.5°	179.6	180.6	183.8	188.2	188.1
175°	180.6	181.0	182.4	184.9	184.2
177.5°	181.4	181.0	181.4	182.6	181.4
180°	181.0	181.0	181.0	181.0	181.0

(END OF REPORT)