

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026809

Luminaire Tested: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026809
REPORT IS A COMBINATION OF REPORTS P1001718 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7446.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026809

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026809

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73			68
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	62			57
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52			48
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44			41
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38			35
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33			30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29			27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26			24
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23			21
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21			19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12545	12253	12277
10°	12442	11972	11935
15°	12278	11637	11532
20°	12057	11247	11070
25°	11820	10822	10576
30°	11534	10379	10055
35°	11228	9915	9471
40°	10913	9424	8952
45°	10571	8946	8400
50°	10195	8404	7757
55°	9823	7806	7166
60°	9380	7176	6479
65°	8848	6446	5768
70°	8309	5607	4947
75°	7400	4617	4000
80°	6308	3449	2942
85°	4871	2039	1622

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10571 cd/sqm

TEST NUMBER: P1026809

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.5
10°-20°	521.9	7.0
20°-30°	770.4	10.3
30°-40°	898.9	12.1
40°-50°	902.8	12.1
50°-60°	792.5	10.6
60°-70°	590.3	7.9
70°-80°	337.1	4.5
80°-90°	98.5	1.3
90°-100°	26.0	0.3
100°-110°	172.6	2.3
110°-120°	310.8	4.2
120°-130°	398.9	5.4
130°-140°	429.0	5.8
140°-150°	402.7	5.4
150°-160°	325.7	4.4
160°-170°	210.6	2.8
170°-180°	72.6	1.0
0°-30°	1477.1	19.8
0°-40°	2376.0	31.9
0°-60°	4071.3	54.7
0°-90°	5097.1	68.5
90°-120°	509.3	6.8
90°-150°	1739.8	23.4
90°-180°	2349.0	31.5
0°-180°	7446.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	93
90°	1	5	9	12	14	7
95°	32	31	9	12	12	40
105°	167	169	169	169	168	177
115°	313	316	316	314	311	310
125°	445	449	449	447	445	397
135°	555	558	557	556	553	428
145°	643	644	644	645	642	402
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1026809

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.3	30.6	9.1	11.9	11.9
97.5°	60.7	64.1	10.2	11.3	11.9
100°	94.7	96.4	98.6	14.2	11.9
102.5°	129.2	131.5	132.6	133.8	86.2
105°	166.6	168.9	168.9	168.9	168.3
107.5°	205.2	205.2	206.3	206.9	204.6
110°	242.6	242.6	243.7	242.0	242.6



TEST NUMBER: P1026809

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	277.7	279.4	280.0	277.7	276.6
115°	312.9	315.7	316.3	314.0	310.6
117.5°	349.7	349.7	352.0	348.6	347.5
120°	383.7	383.2	384.9	383.7	380.9
122.5°	413.8	416.6	417.2	416.1	412.7
125°	445.0	448.9	448.9	446.7	445.0
127.5°	475.0	477.8	477.3	476.1	471.6
130°	502.2	505.0	505.6	503.9	501.1
132.5°	529.4	532.8	531.1	531.1	528.3
135°	554.9	558.3	557.2	556.1	552.7
137.5°	578.7	582.1	581.0	581.0	578.2
140°	602.0	603.1	602.5	603.7	600.3
142.5°	622.9	623.5	624.6	624.6	621.2
145°	643.4	644.5	644.5	645.1	641.7
147.5°	661.5	661.5	662.1	662.6	658.7
150°	678.5	677.4	678.5	679.6	675.1
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)