

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026606

Luminaire Tested: S124RDIP-B795D365UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026606
REPORT IS A COMBINATION OF REPORTS P999726 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D365UB35-4F0-XX-W2A-F4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4568.6 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026606

CATALOG NUMBER: S124RDIP-B795D365UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1026606

CATALOG NUMBER: S124RDIP-B795D365UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75
1	103	99	95	91	97	94	90	87	84	81	79	75	73	72	67	66	65
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47
4	79	68	60	54	75	65	58	52	59	53	48	53	48	44	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32
7	62	50	42	36	59	48	40	35	43	37	33	40	34	31	36	32	28
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	26
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11438	11438	11438
5°	11439	11098	11099
10°	11342	10748	10620
15°	11186	10312	10055
20°	10982	9815	9410
25°	10727	9279	8781
30°	10478	8732	8073
35°	10203	8177	7382
40°	9877	7579	6672
45°	9570	6987	5970
50°	9222	6341	5256
55°	8846	5677	4519
60°	8429	4974	3790
65°	8025	4166	3090
70°	7451	3316	2361
75°	6717	2412	1652
80°	5610	1481	1187
85°	4221	853	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9570 cd/sqm

TEST NUMBER: P1026606

CATALOG NUMBER: S124RDIP-B795D365UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	2.9
10°-20°	367.8	8.0
20°-30°	530.9	11.6
30°-40°	601.7	13.2
40°-50°	581.0	12.7
50°-60°	483.0	10.6
60°-70°	333.4	7.3
70°-80°	168.5	3.7
80°-90°	43.5	1.0
90°-100°	135.1	3.0
100°-110°	274.7	6.0
110°-120°	244.9	5.4
120°-130°	205.7	4.5
130°-140°	171.6	3.8
140°-150°	131.1	2.9
150°-160°	92.1	2.0
160°-170°	54.2	1.2
170°-180°	17.6	0.4
0°-30°	1030.6	22.6
0°-40°	1632.3	35.7
0°-60°	2696.4	59.0
0°-90°	3241.7	71.0
90°-120°	654.6	14.3
90°-150°	1163.0	25.5
90°-180°	1327.0	29.0
0°-180°	4568.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1400	1396	1383	1394	1392	133
15°	1334	1324	1297	1295	1288	376
25°	1206	1187	1143	1124	1114	556
35°	1043	1008	955	918	899	652
45°	851	811	746	694	674	656
55°	644	601	532	476	455	576
65°	438	392	323	277	264	433
75°	233	193	143	118	112	246
85°	58	36	33	31	31	64
90°	0	3	6	7	8	4
95°	12	37	291	144	87	13
105°	42	61	234	505	503	45
115°	74	92	209	402	483	73
125°	102	122	208	342	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	182	182	183	186	185	17
180°	182	182	182	182	182	

TEST NUMBER: P1026606

CATALOG NUMBER: S124RDIP-B795D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1402.7	1402.7	1402.7	1402.7	1402.7
2.5°	1407.0	1402.7	1390.8	1402.7	1401.6
5°	1400.5	1396.2	1383.3	1394.1	1391.9
7.5°	1390.8	1386.6	1370.4	1378.0	1374.7
10°	1375.8	1370.4	1351.1	1355.4	1351.1
12.5°	1356.5	1350.0	1326.4	1328.6	1322.1
15°	1333.9	1324.3	1297.4	1295.3	1287.7
17.5°	1308.1	1294.2	1263.0	1257.7	1246.9
20°	1277.0	1263.0	1226.5	1217.9	1204.0
22.5°	1242.6	1226.5	1186.8	1172.8	1162.1
25°	1206.1	1186.8	1142.8	1124.5	1113.8
27.5°	1168.5	1144.9	1098.7	1077.2	1062.2
30°	1128.8	1101.9	1051.5	1024.6	1007.4
32.5°	1086.9	1055.8	1003.1	970.9	954.8
35°	1042.9	1008.5	954.8	918.3	898.9
37.5°	996.7	961.2	902.2	862.4	843.1
40°	947.3	911.8	850.6	805.5	786.2
42.5°	900.0	862.4	798.0	751.8	731.4
45°	850.6	810.9	746.4	693.8	674.5
47.5°	800.1	759.3	692.7	638.0	616.5
50°	748.6	706.7	638.0	584.3	563.9
52.5°	696.0	655.1	584.3	529.5	508.0
55°	644.4	601.4	531.6	475.8	455.4
57.5°	593.9	548.8	480.1	423.2	408.1
60°	539.2	496.2	427.5	371.6	354.4
62.5°	489.8	444.6	373.8	323.3	310.4
65°	438.2	392.0	323.3	277.1	264.2
67.5°	384.5	340.5	276.0	235.2	220.2
70°	334.0	288.9	227.7	192.2	181.5
72.5°	280.3	240.6	183.7	154.7	145.0
75°	233.1	193.3	142.8	118.1	111.7
77.5°	183.7	149.3	106.3	89.1	87.0
80°	136.4	105.3	73.0	69.8	68.7
82.5°	95.6	67.7	52.6	50.5	49.4
85°	58.0	36.5	33.3	31.1	31.1
87.5°	24.7	16.1	15.0	14.0	15.0
90°	0.4	2.9	6.4	7.1	7.5
92.5°	5.0	27.5	140.0	46.2	32.5
95°	11.8	37.2	291.1	144.2	87.2
97.5°	19.6	41.1	311.5	294.4	209.3
100°	27.1	46.4	287.2	407.2	327.6
102.5°	34.3	52.8	256.8	478.0	430.5
105°	41.8	60.6	234.3	504.6	502.6
107.5°	50.0	68.4	219.7	496.5	536.9
110°	58.2	76.2	212.9	468.0	537.6

TEST NUMBER: P1026606

CATALOG NUMBER: S124RDIP-B795D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	66.1	84.1	209.7	433.0	516.5
115°	73.6	92.4	209.0	401.5	482.6
117.5°	81.4	100.0	208.6	376.9	449.4
120°	89.3	107.5	208.6	360.2	422.2
122.5°	96.4	114.8	208.3	349.4	400.8
125°	102.5	121.8	207.9	341.7	385.1
127.5°	108.2	128.2	207.2	334.4	375.1
130°	112.9	134.5	206.8	325.6	366.5
132.5°	117.5	139.8	206.5	315.2	356.9
135°	121.8	145.0	206.1	303.3	344.4
137.5°	126.1	149.5	206.1	290.4	329.7
140°	130.7	153.6	205.8	277.9	313.6
142.5°	135.7	157.4	205.8	266.4	296.5
145°	140.4	160.8	205.0	255.8	281.1
147.5°	145.7	164.0	204.0	247.0	266.8
150°	150.7	167.0	202.9	239.0	255.1
152.5°	155.4	169.9	201.1	232.2	244.3
155°	159.7	172.4	199.3	225.8	235.4
157.5°	164.0	174.6	197.5	219.7	227.2
160°	167.9	176.6	195.4	213.6	219.7
162.5°	171.5	178.2	193.3	207.8	212.5
165°	174.0	179.4	191.1	202.4	205.4
167.5°	176.8	180.2	189.0	197.8	199.7
170°	178.6	181.0	186.8	193.0	194.3
172.5°	180.4	181.4	184.7	189.0	189.0
175°	181.5	181.8	183.3	185.8	185.0
177.5°	182.2	181.8	182.2	183.4	182.2
180°	181.8	181.8	181.8	181.8	181.8

(END OF REPORT)