

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026810

Luminaire Tested: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026810
REPORT IS A COMBINATION OF REPORTS P1001719 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7511.0 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026810

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026810

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68		
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	65	63	62	58		
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52	48		
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44	41		
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35		
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33	30		
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27		
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24		
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21		
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21	19		
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1026810

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.5
10°-20°	526.5	7.0
20°-30°	777.2	10.3
30°-40°	906.8	12.1
40°-50°	910.8	12.1
50°-60°	799.5	10.6
60°-70°	595.5	7.9
70°-80°	340.1	4.5
80°-90°	99.3	1.3
90°-100°	26.2	0.3
100°-110°	174.1	2.3
110°-120°	313.4	4.2
120°-130°	402.3	5.4
130°-140°	432.7	5.8
140°-150°	406.1	5.4
150°-160°	328.5	4.4
160°-170°	212.4	2.8
170°-180°	73.3	1.0
0°-30°	1490.1	19.8
0°-40°	2396.9	31.9
0°-60°	4107.2	54.7
0°-90°	5142.1	68.5
90°-120°	513.6	6.8
90°-150°	1754.7	23.4
90°-180°	2369.0	31.5
0°-180°	7511.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	1	5	9	12	14	7
95°	33	31	9	12	12	40
105°	168	170	170	170	170	178
115°	316	318	319	317	313	313
125°	449	453	453	450	449	401
135°	560	563	562	561	557	431
145°	649	650	650	650	647	406
155°	715	711	712	714	709	329
165°	754	751	751	755	750	213
175°	771	768	768	773	768	73
180°	771	771	771	771	771	

TEST NUMBER: P1026810

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	0.6	5.1	9.1	12.0	13.7
92.5°	10.9	5.7	9.1	12.0	12.6
95°	32.6	30.9	9.1	12.0	12.0
97.5°	61.2	64.6	10.3	11.4	12.0
100°	95.5	97.2	99.5	14.3	12.0
102.5°	130.3	132.6	133.8	134.9	86.9
105°	168.1	170.4	170.4	170.4	169.8
107.5°	206.9	206.9	208.1	208.7	206.4
110°	244.7	244.7	245.8	244.1	244.7

TEST NUMBER: P1026810

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	280.1	281.8	282.4	280.1	279.0
115°	315.6	318.4	319.0	316.7	313.3
117.5°	352.7	352.7	355.0	351.6	350.4
120°	387.0	386.4	388.2	387.0	384.2
122.5°	417.3	420.2	420.7	419.6	416.2
125°	448.8	452.8	452.8	450.5	448.8
127.5°	479.0	481.9	481.3	480.2	475.6
130°	506.5	509.3	509.9	508.2	505.3
132.5°	533.9	537.4	535.6	535.6	532.8
135°	559.7	563.1	561.9	560.8	557.4
137.5°	583.7	587.1	585.9	585.9	583.1
140°	607.1	608.2	607.7	608.8	605.4
142.5°	628.3	628.8	630.0	630.0	626.5
145°	648.8	650.0	650.0	650.5	647.1
147.5°	667.1	667.1	667.7	668.3	664.3
150°	684.3	683.1	684.3	685.4	680.8
152.5°	700.9	698.0	699.1	700.3	696.3
155°	714.6	711.1	712.3	714.0	709.4
157.5°	725.4	723.7	723.7	725.4	720.9
160°	736.9	733.4	734.0	736.3	731.7
162.5°	746.0	742.6	743.2	746.6	741.4
165°	754.0	750.6	751.2	754.6	750.0
167.5°	760.3	756.9	757.4	761.4	756.3
170°	765.4	761.4	762.0	766.6	761.4
172.5°	768.9	764.9	766.0	770.0	764.9
175°	771.2	767.7	768.3	772.9	767.7
177.5°	772.9	769.5	770.0	774.0	769.5
180°	771.2	771.2	771.2	771.2	771.2

(END OF REPORT)