

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026812

Luminaire Tested: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026812
REPORT IS A COMBINATION OF REPORTS P1001721 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7468.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026812

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026812

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	62
2	93	85	79	73	87	80	75	70	72	67	64	64	61	58	57	54	52
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38
5	71	59	51	44	67	56	48	43	51	44	39	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	28	24	21
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12582	12582	12582
5°	12582	12289	12313
10°	12478	12008	11970
15°	12314	11671	11566
20°	12093	11280	11103
25°	11855	10854	10607
30°	11568	10410	10084
35°	11262	9944	9498
40°	10945	9452	8978
45°	10602	8973	8425
50°	10225	8429	7780
55°	9852	7829	7187
60°	9407	7197	6498
65°	8875	6465	5785
70°	8333	5623	4961
75°	7422	4630	4011
80°	6324	3458	2951
85°	4883	2046	1626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10602 cd/sqm

TEST NUMBER: P1026812

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.3	2.5
10°-20°	523.4	7.0
20°-30°	772.7	10.3
30°-40°	901.5	12.1
40°-50°	905.5	12.1
50°-60°	794.8	10.6
60°-70°	592.0	7.9
70°-80°	338.1	4.5
80°-90°	98.7	1.3
90°-100°	26.0	0.3
100°-110°	173.1	2.3
110°-120°	311.7	4.2
120°-130°	400.1	5.4
130°-140°	430.3	5.8
140°-150°	403.9	5.4
150°-160°	326.7	4.4
160°-170°	211.3	2.8
170°-180°	72.9	1.0
0°-30°	1481.4	19.8
0°-40°	2383.0	31.9
0°-60°	4083.2	54.7
0°-90°	5112.1	68.5
90°-120°	510.8	6.8
90°-150°	1745.0	23.4
90°-180°	2356.0	31.5
0°-180°	7468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1961	1958	1942	1956	1954	186
15°	1869	1864	1847	1855	1855	527
25°	1696	1689	1668	1672	1667	781
35°	1465	1459	1437	1429	1417	916
45°	1199	1193	1174	1156	1151	924
55°	914	909	887	873	862	815
65°	617	614	597	583	576	612
75°	328	325	317	312	306	349
85°	85	87	87	85	82	94
90°	1	5	9	12	14	7
95°	32	31	9	12	12	40
105°	167	169	169	169	169	177
115°	314	317	317	315	312	311
125°	446	450	450	448	446	399
135°	557	560	559	558	554	429
145°	645	646	646	647	644	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	

TEST NUMBER: P1026812

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1963.7	1963.7	1963.7	1963.7	1963.7
2.5°	1969.9	1965.2	1949.7	1965.2	1963.7
5°	1960.6	1957.5	1941.9	1955.9	1954.4
7.5°	1946.6	1943.5	1926.4	1940.4	1938.8
10°	1926.4	1923.3	1906.2	1918.6	1917.1
12.5°	1901.5	1895.3	1879.8	1889.1	1889.1
15°	1868.9	1864.3	1847.2	1854.9	1854.9
17.5°	1834.7	1827.0	1809.9	1819.2	1811.4
20°	1789.7	1786.6	1766.4	1777.3	1769.5
22.5°	1744.6	1738.4	1719.8	1726.0	1721.3
25°	1696.5	1688.7	1668.5	1671.6	1667.0
27.5°	1640.6	1635.9	1615.7	1617.2	1612.6
30°	1586.2	1581.5	1558.2	1555.1	1550.4
32.5°	1527.1	1519.4	1499.2	1493.0	1483.6
35°	1465.0	1458.8	1437.0	1429.3	1416.8
37.5°	1401.3	1393.5	1373.3	1362.5	1354.7
40°	1336.1	1328.3	1306.5	1292.6	1287.9
42.5°	1266.1	1259.9	1238.2	1225.8	1218.0
45°	1199.3	1193.1	1174.5	1155.8	1151.2
47.5°	1126.3	1127.9	1104.6	1085.9	1075.1
50°	1056.4	1051.8	1033.1	1012.9	1002.0
52.5°	985.0	981.8	961.6	944.6	932.1
55°	913.5	908.8	887.1	873.1	862.2
57.5°	837.4	835.8	817.2	798.5	793.9
60°	765.9	759.7	742.6	727.1	716.2
62.5°	691.3	686.7	672.7	655.6	647.8
65°	616.8	613.7	596.6	582.6	576.4
67.5°	543.7	537.5	525.1	512.7	509.6
70°	475.4	467.6	453.6	444.3	438.1
72.5°	400.8	396.2	388.4	377.5	371.3
75°	327.8	324.7	316.9	312.3	306.0
77.5°	259.4	257.9	253.2	250.1	245.5
80°	195.7	195.7	192.6	191.1	188.0
82.5°	139.8	136.7	136.7	133.6	133.6
85°	85.4	87.0	87.0	85.4	82.3
87.5°	41.9	41.9	40.4	40.4	37.3
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.4	30.7	9.1	11.9	11.9
97.5°	60.8	64.2	10.2	11.4	11.9
100°	94.9	96.6	98.9	14.2	11.9
102.5°	129.6	131.9	133.0	134.2	86.4
105°	167.1	169.4	169.4	169.4	168.9
107.5°	205.8	205.8	206.9	207.5	205.2
110°	243.3	243.3	244.5	242.8	243.3



TEST NUMBER: P1026812

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.6	280.3	280.8	278.6	277.4
115°	313.8	316.7	317.2	315.0	311.5
117.5°	350.8	350.8	353.1	349.6	348.5
120°	384.9	384.3	386.0	384.9	382.0
122.5°	415.0	417.9	418.4	417.3	413.9
125°	446.3	450.3	450.3	448.0	446.3
127.5°	476.4	479.3	478.7	477.6	473.0
130°	503.7	506.6	507.1	505.4	502.6
132.5°	531.0	534.4	532.7	532.7	529.9
135°	556.6	560.0	558.9	557.7	554.3
137.5°	580.5	583.9	582.7	582.7	579.9
140°	603.8	604.9	604.3	605.5	602.1
142.5°	624.8	625.4	626.5	626.5	623.1
145°	645.3	646.4	646.4	647.0	643.6
147.5°	663.5	663.5	664.0	664.6	660.6
150°	680.5	679.4	680.5	681.7	677.1
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)