

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026637

Luminaire Tested: S124RDIP-B795D590UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026637
REPORT IS A COMBINATION OF REPORTS P999767 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D590UB40-4F0-XX-W2A-A
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5688.0 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	58	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	27	23	20
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10758	10758	10758	10758
5°	10759	12157	10776	9291
10°	10701	14013	10692	8080
15°	10573	15772	10573	6765
20°	10440	17099	10386	5957
25°	10278	17173	10231	5380
30°	10104	14602	10025	4984
35°	9860	11018	9735	4688
40°	9588	7985	9399	4457
45°	9138	6069	8911	4253
50°	8604	4904	8368	3954
55°	8026	4061	7764	3555
60°	7446	3434	7113	2956
65°	6717	2797	6503	2350
70°	6048	2268	5763	1909
75°	5300	1635	4934	1399
80°	4372	1083	3977	1028
85°	3173	558	2627	558

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13468 cd/sqm

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	2.2
10°-20°	385.8	6.8
20°-30°	604.3	10.6
30°-40°	671.0	11.8
40°-50°	594.6	10.5
50°-60°	463.4	8.1
60°-70°	303.1	5.3
70°-80°	148.7	2.6
80°-90°	37.8	0.7
90°-100°	25.2	0.4
100°-110°	166.1	2.9
110°-120°	317.2	5.6
120°-130°	402.7	7.1
130°-140°	430.8	7.6
140°-150°	402.8	7.1
150°-160°	324.8	5.7
160°-170°	209.5	3.7
170°-180°	72.2	1.3
0°-30°	1117.8	19.7
0°-40°	1788.9	31.4
0°-60°	2846.9	50.1
0°-90°	3336.6	58.7
90°-120°	508.5	8.9
90°-150°	1744.9	30.7
90°-180°	2351.0	41.3
0°-180°	5688.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1319	1319	1319	1319	1319	
5°	1317	1524	1319	1165	1317	125
15°	1261	2020	1261	866	1261	356
25°	1156	2178	1150	682	1156	533
35°	1008	1342	995	571	1008	630
45°	812	686	792	480	812	626
55°	585	409	566	358	585	523
65°	367	239	355	201	367	366
75°	184	111	171	95	184	195
85°	44	27	36	27	44	49
90°	2	17	2	17	2	5
95°	31	16	31	16	31	39
105°	171	162	171	162	171	179
115°	319	322	319	322	319	314
125°	449	452	449	452	449	401
135°	557	561	557	561	557	429
145°	642	646	642	646	642	401
155°	704	704	704	704	704	325
165°	743	739	743	739	743	210
175°	760	755	760	755	760	72
180°	760	760	760	760	760	

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1321.4	1333.1	1339.5	1344.8	1355.4	1359.7	1368.2	1370.3	1378.8	1377.8	1374.6
5°	1317.2	1337.4	1352.2	1368.2	1387.3	1398.0	1409.6	1426.7	1435.2	1446.9	1454.3
7.5°	1309.7	1337.4	1361.8	1386.3	1417.1	1434.1	1449.0	1475.6	1497.9	1517.0	1538.3
10°	1298.0	1333.1	1369.3	1402.2	1444.7	1464.9	1487.3	1526.6	1557.4	1584.0	1618.0
12.5°	1280.0	1328.9	1369.3	1413.9	1468.1	1495.8	1525.5	1572.3	1608.4	1652.0	1694.6
15°	1260.8	1315.0	1368.2	1426.7	1488.3	1520.2	1550.0	1612.7	1668.0	1717.9	1764.7
17.5°	1239.6	1299.1	1357.6	1422.4	1496.8	1536.2	1571.2	1646.7	1707.3	1772.2	1818.9
20°	1214.0	1278.9	1345.9	1418.2	1502.1	1545.7	1585.1	1671.2	1738.1	1808.3	1866.8
22.5°	1186.4	1256.6	1329.9	1408.6	1495.8	1543.6	1589.3	1681.8	1759.4	1824.3	1902.9
25°	1155.6	1230.0	1305.5	1388.4	1486.2	1538.3	1585.1	1676.5	1759.4	1844.4	1921.0
27.5°	1123.7	1200.2	1278.9	1366.1	1466.0	1517.0	1570.2	1658.4	1755.1	1847.6	1925.2
30°	1088.6	1163.0	1245.9	1328.9	1435.2	1486.2	1540.4	1636.1	1741.3	1833.8	1917.8
32.5°	1050.3	1126.9	1205.5	1291.6	1395.8	1451.1	1501.1	1609.5	1716.9	1808.3	1887.0
35°	1007.8	1080.1	1154.5	1242.7	1345.9	1395.8	1455.4	1568.0	1676.5	1773.2	1824.3
37.5°	962.1	1031.2	1100.3	1187.5	1286.3	1346.9	1405.4	1519.1	1634.0	1698.8	1725.4
40°	919.6	980.2	1040.8	1124.7	1224.7	1287.4	1346.9	1464.9	1565.9	1615.9	1595.7
42.5°	865.3	928.1	982.3	1059.9	1160.9	1219.4	1280.0	1402.2	1484.1	1504.3	1454.3
45°	812.2	864.3	916.4	991.9	1098.2	1148.1	1213.0	1326.7	1394.8	1376.7	1303.3
47.5°	760.1	802.6	851.5	924.9	1020.6	1080.1	1140.7	1239.6	1287.4	1261.9	1159.8
50°	698.4	741.0	792.0	855.8	948.3	1005.7	1053.5	1144.9	1181.1	1118.4	995.0
52.5°	640.0	677.2	720.8	780.3	868.5	920.6	972.7	1051.4	1063.1	990.8	861.1
55°	584.7	614.5	660.2	708.0	788.8	844.1	880.2	947.2	944.0	853.7	742.0
57.5°	527.3	554.9	585.8	635.7	712.3	753.7	793.1	851.5	820.7	744.2	633.6
60°	476.3	492.2	523.0	570.9	635.7	671.9	702.7	734.6	708.0	625.1	540.0
62.5°	419.9	438.0	460.3	498.6	556.0	590.0	612.3	626.2	598.5	534.7	457.1
65°	366.8	382.7	406.1	440.1	483.7	509.2	520.9	530.5	515.6	443.3	381.6
67.5°	318.9	329.6	350.8	373.1	419.9	426.3	442.2	446.5	416.7	361.4	312.5
70°	271.1	281.7	291.3	317.9	339.1	350.8	354.0	354.0	324.2	288.1	247.7
72.5°	226.4	232.8	242.4	260.5	272.1	280.7	284.9	279.6	252.0	222.2	192.4
75°	183.9	187.1	195.6	207.3	216.9	213.7	212.6	206.2	186.0	164.8	147.8
77.5°	141.4	143.5	153.1	156.3	156.3	159.5	155.2	148.8	131.8	115.9	108.4
80°	106.3	109.5	110.6	112.7	110.6	110.6	107.4	96.7	88.2	80.8	75.5
82.5°	73.4	75.5	76.5	73.4	75.5	72.3	67.0	59.5	54.2	53.2	51.0
85°	43.6	44.6	43.6	43.6	40.4	39.3	35.1	34.0	31.9	31.9	30.8
87.5°	21.3	20.2	18.1	15.9	15.9	14.9	15.9	13.8	15.9	14.9	13.8
90°	1.7	3.1	4.5	5.9	7.3	8.0	8.5	9.5	10.5	11.5	12.5
92.5°	8.5	8.3	8.0	7.8	7.5	7.4	7.9	8.9	9.9	10.9	11.9
95°	31.3	27.0	22.7	18.4	14.1	11.9	12.0	12.1	12.2	12.4	12.5
97.5°	59.7	62.5	65.3	68.0	70.8	72.2	65.6	52.3	39.0	25.8	12.5
100°	93.2	95.5	97.7	100.0	102.3	103.4	94.7	77.3	59.8	42.4	25.0
102.5°	130.7	132.2	133.7	135.2	136.7	137.5	138.3	139.8	141.3	142.9	144.4
105°	171.1	171.9	172.6	173.4	174.1	174.5	174.8	175.4	176.1	176.7	177.3
107.5°	208.0	208.4	208.8	209.1	209.5	209.7	210.1	211.0	211.9	212.8	213.7
110°	245.5	245.9	246.3	246.6	247.0	247.2	247.6	248.4	249.1	249.9	250.7

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	281.9	282.7	283.4	284.2	284.9	285.3	285.4	285.7	286.0	286.2	286.5
115°	319.4	319.8	320.2	320.5	320.9	321.1	321.0	320.9	320.8	320.7	320.6
117.5°	353.0	353.5	354.0	354.5	355.0	355.2	355.4	355.8	356.1	356.5	356.9
120°	387.1	387.6	388.1	388.6	389.1	389.3	389.2	389.1	389.0	388.9	388.8
122.5°	418.9	419.1	419.4	419.6	419.9	420.0	420.1	420.4	420.7	420.9	421.2
125°	449.0	449.5	450.0	450.5	451.0	451.3	451.2	450.9	450.6	450.4	450.1
127.5°	478.0	478.1	478.3	478.4	478.5	478.6	478.9	479.5	480.2	480.8	481.4
130°	505.8	505.9	506.1	506.2	506.3	506.4	506.6	507.0	507.3	507.7	508.1
132.5°	531.4	531.7	531.9	532.2	532.5	532.6	532.8	533.3	533.8	534.3	534.8
135°	557.0	556.9	556.7	556.6	556.5	556.4	556.7	557.2	557.7	558.2	558.7
137.5°	579.7	579.7	579.7	579.7	579.7	579.7	580.0	580.7	581.3	582.0	582.6
140°	601.9	602.1	602.4	602.6	602.9	603.0	603.1	603.4	603.7	603.9	604.2
142.5°	621.8	622.3	622.8	623.3	623.8	624.1	624.2	624.3	624.4	624.5	624.6
145°	642.3	642.7	643.1	643.4	643.8	644.0	644.0	644.0	644.0	644.0	644.0
147.5°	658.2	659.0	659.7	660.5	661.2	661.6	661.5	661.4	661.3	661.1	661.0
150°	675.8	676.3	676.8	677.3	677.8	678.1	678.0	677.9	677.8	677.6	677.5
152.5°	690.6	691.0	691.4	691.7	692.1	692.3	692.2	691.9	691.6	691.4	691.1
155°	704.2	704.3	704.5	704.6	704.7	704.8	704.6	704.2	703.9	703.5	703.1
157.5°	716.1	716.1	716.1	716.1	716.1	716.1	715.9	715.4	714.9	714.4	713.9
160°	726.4	726.0	725.6	725.3	724.9	724.7	724.6	724.5	724.4	724.2	724.1
162.5°	735.5	735.0	734.5	734.0	733.5	733.2	733.1	733.0	732.9	732.7	732.6
165°	742.9	742.3	741.6	741.0	740.3	740.0	740.0	740.0	740.0	740.0	740.0
167.5°	749.1	748.5	747.9	747.2	746.6	746.3	746.2	746.1	746.0	745.8	745.7
170°	754.2	753.4	752.7	751.9	751.2	750.8	750.9	751.0	751.1	751.3	751.4
172.5°	757.6	756.8	756.1	755.3	754.6	754.2	754.3	754.4	754.5	754.7	754.8
175°	759.9	759.1	758.4	757.6	756.9	756.5	756.6	756.7	756.8	757.0	757.1
177.5°	761.6	760.7	759.8	758.9	758.0	757.6	757.7	758.0	758.3	758.5	758.8
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1383.1	1394.8	1395.8	1406.5	1403.3	1398.0	1407.5	1401.1	1413.9	1409.6	1415.0
5°	1463.9	1479.8	1493.6	1502.1	1517.0	1513.8	1529.8	1524.5	1536.2	1524.5	1539.3
7.5°	1558.5	1585.1	1598.9	1621.2	1627.6	1628.6	1647.8	1652.0	1659.5	1652.0	1660.5
10°	1651.0	1682.9	1714.8	1732.8	1744.5	1760.5	1777.5	1784.9	1790.2	1782.8	1788.1
12.5°	1735.0	1784.9	1820.0	1856.1	1864.6	1878.5	1896.5	1894.4	1915.7	1911.4	1921.0
15°	1812.6	1867.8	1910.4	1939.1	1962.5	1974.1	2008.2	2010.3	2009.2	2019.9	2013.5
17.5°	1881.7	1928.4	1989.0	2026.2	2054.9	2054.9	2074.1	2113.4	2110.2	2109.2	2115.5
20°	1938.0	1991.2	2047.5	2110.2	2133.6	2137.9	2164.4	2184.6	2187.8	2187.8	2187.8
22.5°	1980.5	2043.2	2103.8	2148.5	2166.6	2181.4	2204.8	2217.6	2221.8	2219.7	2221.8
25°	2001.8	2061.3	2123.0	2163.4	2174.0	2182.5	2184.6	2192.1	2191.0	2178.3	2185.7
27.5°	2006.0	2063.4	2103.8	2114.5	2109.2	2103.8	2069.8	2073.0	2063.4	2044.3	2051.8
30°	1986.9	2017.7	2016.7	1983.7	1974.1	1951.8	1921.0	1875.3	1838.1	1822.1	1827.4
32.5°	1917.8	1917.8	1879.5	1805.1	1772.2	1731.8	1676.5	1635.0	1586.1	1575.5	1595.7
35°	1822.1	1767.9	1697.7	1599.9	1550.0	1520.2	1424.5	1394.8	1353.3	1341.6	1351.2
37.5°	1673.3	1582.9	1480.9	1389.4	1346.9	1293.8	1209.8	1167.3	1137.5	1117.3	1126.9
40°	1506.4	1396.9	1290.6	1177.9	1131.1	1087.5	1024.8	986.5	938.7	940.8	944.0
42.5°	1346.9	1218.3	1099.2	995.0	950.4	914.3	870.7	823.9	806.9	801.6	796.2
45°	1177.9	1040.8	929.1	851.5	811.1	777.1	736.7	710.1	689.9	685.7	691.0
47.5°	1018.4	902.6	796.2	724.0	691.0	674.0	642.1	617.7	604.9	594.3	600.6
50°	873.9	765.4	680.4	619.8	596.4	584.7	554.9	542.2	529.4	526.2	525.2
52.5°	754.8	662.3	588.9	540.0	522.0	515.6	493.3	475.2	464.6	467.8	469.9
55°	646.4	567.7	510.3	470.9	456.1	448.6	432.7	419.9	412.5	409.3	411.4
57.5°	550.7	482.6	441.2	409.3	397.6	394.4	377.4	373.1	367.8	364.6	364.6
60°	463.5	415.7	377.4	359.3	346.6	343.4	330.6	325.3	324.2	321.1	318.9
62.5°	390.2	350.8	324.2	305.1	299.8	298.7	290.2	283.8	280.7	278.5	278.5
65°	326.4	297.7	275.3	261.5	257.3	255.1	245.6	243.4	241.3	239.2	238.1
67.5°	272.1	246.6	230.7	221.1	215.8	216.9	211.6	207.3	207.3	206.2	205.2
70°	220.1	204.1	190.3	185.0	182.9	180.7	178.6	175.4	174.3	174.3	174.3
72.5°	173.3	162.7	155.2	152.0	149.9	147.8	145.6	145.6	145.6	144.6	144.6
75°	132.9	128.6	123.3	120.1	120.1	122.3	119.1	115.9	112.7	110.6	111.6
77.5°	99.9	97.8	94.6	89.3	90.4	88.2	88.2	86.1	87.2	87.2	85.0
80°	73.4	70.2	69.1	65.9	67.0	65.9	64.8	64.8	62.7	62.7	62.7
82.5°	51.0	47.8	47.8	46.8	45.7	45.7	44.6	44.6	45.7	43.6	43.6
85°	30.8	29.8	29.8	27.6	27.6	27.6	27.6	28.7	27.6	26.6	26.6
87.5°	13.8	14.9	13.8	12.8	12.8	12.8	11.7	11.7	10.6	11.7	11.7
90°	13.3	14.0	14.8	15.5	15.9	16.0	16.3	16.6	16.8	17.1	16.8
92.5°	12.7	13.4	14.2	14.9	15.3	15.3	15.3	15.3	15.3	15.3	15.3
95°	13.3	14.0	14.8	15.5	15.9	16.0	16.1	16.2	16.4	16.5	16.4
97.5°	13.1	13.7	14.4	15.0	15.3	15.4	15.5	15.6	15.8	15.9	15.8
100°	22.8	20.7	18.5	16.4	15.3	15.4	15.5	15.6	15.8	15.9	15.8
102.5°	116.0	87.6	59.1	30.7	16.5	16.5	16.5	16.5	16.5	16.5	16.5
105°	178.4	179.6	180.7	181.8	182.4	180.1	175.6	171.1	166.5	162.0	166.5
107.5°	214.3	214.9	215.6	216.2	216.5	216.8	217.3	217.8	218.3	218.8	218.3
110°	250.9	251.2	251.4	251.7	251.8	252.0	252.4	252.7	253.1	253.5	253.1

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.4	286.2	286.1	286.0	285.9	286.2	286.7	287.2	287.7	288.2	287.7
115°	320.8	321.1	321.3	321.6	321.7	321.7	321.7	321.7	321.7	321.7	321.7
117.5°	356.8	356.7	356.6	356.5	356.4	356.4	356.4	356.4	356.4	356.4	356.4
120°	389.0	389.3	389.5	389.8	389.9	389.8	389.5	389.3	389.0	388.8	389.0
122.5°	421.3	421.4	421.5	421.6	421.7	421.6	421.3	421.1	420.8	420.6	420.8
125°	450.5	450.9	451.3	451.7	451.9	452.0	452.1	452.2	452.3	452.4	452.3
127.5°	481.3	481.1	481.0	480.9	480.8	480.7	480.6	480.5	480.4	480.3	480.4
130°	508.2	508.4	508.5	508.6	508.7	508.7	508.7	508.7	508.7	508.7	508.7
132.5°	534.9	535.1	535.2	535.3	535.4	535.3	535.2	535.1	534.9	534.8	534.9
135°	558.9	559.2	559.4	559.7	559.8	559.9	560.2	560.5	560.7	561.0	560.7
137.5°	582.8	583.1	583.3	583.6	583.7	583.6	583.5	583.4	583.2	583.1	583.2
140°	604.6	605.0	605.3	605.7	605.9	606.0	606.1	606.2	606.4	606.5	606.4
142.5°	624.9	625.1	625.4	625.7	625.8	625.8	625.8	625.8	625.8	625.8	625.8
145°	644.1	644.2	644.3	644.4	644.5	644.6	644.9	645.2	645.4	645.7	645.4
147.5°	661.1	661.3	661.4	661.5	661.6	661.7	661.8	661.9	662.1	662.2	662.1
150°	677.5	677.5	677.5	677.5	677.5	677.6	677.7	677.8	678.0	678.1	678.0
152.5°	691.4	691.6	691.9	692.2	692.3	692.2	692.1	692.0	691.8	691.7	691.8
155°	703.6	704.1	704.6	705.1	705.3	705.1	704.7	704.4	704.0	703.6	704.0
157.5°	714.5	715.1	715.8	716.4	716.7	716.4	715.8	715.1	714.5	713.9	714.5
160°	724.9	725.6	726.4	727.1	727.5	727.1	726.4	725.6	724.9	724.1	724.9
162.5°	733.4	734.1	734.9	735.6	736.0	735.6	734.7	733.8	733.0	732.1	733.0
165°	741.0	742.0	743.1	744.1	744.6	744.0	742.9	741.7	740.6	739.4	740.6
167.5°	746.8	748.0	749.1	750.2	750.8	750.2	748.9	747.6	746.4	745.1	746.4
170°	752.4	753.4	754.4	755.4	755.9	755.3	754.0	752.7	751.5	750.2	751.5
172.5°	755.8	756.8	757.8	758.8	759.3	758.6	757.2	755.9	754.5	753.1	754.5
175°	758.2	759.4	760.5	761.6	762.2	761.4	759.9	758.4	756.9	755.4	756.9
177.5°	759.8	760.8	761.8	762.8	763.3	762.5	761.0	759.5	758.0	756.5	758.0
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1418.2	1410.7	1409.6	1409.6	1398.0	1404.3	1391.6	1377.8	1371.4	1371.4	1359.7
5°	1536.2	1528.7	1521.3	1509.6	1509.6	1503.2	1483.0	1462.8	1447.9	1435.2	1421.3
7.5°	1657.3	1649.9	1628.6	1616.9	1623.3	1610.6	1584.0	1550.0	1524.5	1504.3	1475.6
10°	1789.2	1769.0	1758.3	1752.0	1729.6	1715.8	1685.0	1635.0	1603.1	1576.6	1539.3
12.5°	1896.5	1902.9	1862.5	1865.7	1843.4	1824.3	1776.4	1728.6	1680.7	1643.5	1588.2
15°	2012.4	1993.3	1968.8	1949.7	1942.3	1918.9	1878.5	1814.7	1762.6	1704.1	1641.4
17.5°	2103.8	2089.0	2065.6	2047.5	2031.6	1975.2	1941.2	1884.8	1813.6	1756.2	1679.7
20°	2181.4	2167.6	2134.7	2123.0	2094.3	2053.9	2005.0	1917.8	1854.0	1791.3	1716.9
22.5°	2214.4	2200.6	2171.9	2157.0	2138.9	2099.6	2052.8	1969.9	1891.2	1812.6	1733.9
25°	2186.8	2186.8	2172.9	2167.6	2151.7	2116.6	2068.8	1998.6	1914.6	1829.6	1736.0
27.5°	2052.8	2079.4	2089.0	2094.3	2094.3	2095.3	2062.4	1994.3	1912.5	1829.6	1731.8
30°	1859.3	1904.0	1943.3	1955.0	1975.2	1997.5	2011.4	1978.4	1905.0	1817.9	1720.1
32.5°	1615.9	1673.3	1746.6	1764.7	1792.4	1859.3	1896.5	1910.4	1870.0	1793.4	1689.2
35°	1373.5	1445.8	1490.4	1545.7	1571.2	1670.1	1753.0	1803.0	1793.4	1747.7	1653.1
37.5°	1161.9	1203.4	1257.6	1316.1	1367.1	1461.7	1564.9	1661.6	1700.9	1678.6	1607.4
40°	958.9	1007.8	1072.7	1120.5	1155.6	1250.2	1377.8	1483.0	1569.1	1582.9	1539.3
42.5°	815.4	864.3	903.6	955.7	983.4	1074.8	1187.5	1319.3	1421.3	1475.6	1456.4
45°	704.8	734.6	766.5	796.2	830.3	911.1	1015.2	1159.8	1274.6	1351.2	1358.6
47.5°	608.1	634.7	662.3	689.9	709.1	771.8	867.5	985.5	1110.9	1216.2	1257.6
50°	540.0	552.8	573.0	588.9	611.3	665.5	742.0	844.1	977.0	1090.7	1144.9
52.5°	473.1	489.0	505.0	518.8	533.7	571.9	642.1	730.3	845.2	962.1	1029.1
55°	416.7	429.5	444.4	453.9	462.4	496.5	549.6	617.7	716.5	827.1	910.0
57.5°	371.0	376.3	389.1	394.4	404.0	431.6	469.9	530.5	610.2	717.6	785.6
60°	321.1	331.7	341.2	345.5	352.9	372.1	398.7	455.0	524.1	602.8	680.4
62.5°	280.7	284.9	292.3	297.7	303.0	323.2	345.5	388.0	440.1	506.0	577.3
65°	243.4	245.6	249.8	257.3	260.5	275.3	288.1	318.9	367.8	417.8	489.0
67.5°	205.2	207.3	212.6	216.9	220.1	229.6	243.4	265.8	292.3	347.6	387.0
70°	175.4	175.4	178.6	180.7	183.9	188.2	195.6	212.6	237.1	272.1	308.3
72.5°	146.7	146.7	146.7	149.9	149.9	153.1	157.3	169.0	186.0	213.7	237.1
75°	113.7	114.8	116.9	116.9	118.0	122.3	125.4	128.6	137.1	155.2	176.5
77.5°	86.1	88.2	89.3	87.2	89.3	89.3	93.6	97.8	102.1	107.4	123.3
80°	63.8	64.8	62.7	63.8	63.8	65.9	68.0	67.0	69.1	75.5	79.7
82.5°	42.5	43.6	43.6	43.6	43.6	46.8	46.8	45.7	46.8	47.8	48.9
85°	26.6	25.5	25.5	26.6	25.5	25.5	26.6	27.6	26.6	27.6	28.7
87.5°	11.7	11.7	11.7	11.7	10.6	10.6	11.7	10.6	11.7	10.6	9.6
90°	16.6	16.3	16.0	15.9	15.5	14.8	14.0	13.3	12.5	11.5	10.5
92.5°	15.3	15.3	15.3	15.3	14.9	14.2	13.4	12.7	11.9	10.9	9.9
95°	16.2	16.1	16.0	15.9	15.5	14.8	14.0	13.3	12.5	12.4	12.2
97.5°	15.6	15.5	15.4	15.3	15.0	14.4	13.7	13.1	12.5	25.8	39.0
100°	15.6	15.5	15.4	15.3	16.4	18.5	20.7	22.8	25.0	42.4	59.8
102.5°	16.5	16.5	16.5	16.5	30.7	59.1	87.6	116.0	144.4	142.9	141.3
105°	171.1	175.6	180.1	182.4	181.8	180.7	179.6	178.4	177.3	176.7	176.1
107.5°	217.8	217.3	216.8	216.5	216.2	215.6	214.9	214.3	213.7	212.8	211.9
110°	252.7	252.4	252.0	251.8	251.7	251.4	251.2	250.9	250.7	249.9	249.1

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	287.2	286.7	286.2	285.9	286.0	286.1	286.2	286.4	286.5	286.2	286.0
115°	321.7	321.7	321.7	321.7	321.6	321.3	321.1	320.8	320.6	320.7	320.8
117.5°	356.4	356.4	356.4	356.4	356.5	356.6	356.7	356.8	356.9	356.5	356.1
120°	389.3	389.5	389.8	389.9	389.8	389.5	389.3	389.0	388.8	388.9	389.0
122.5°	421.1	421.3	421.6	421.7	421.6	421.5	421.4	421.3	421.2	420.9	420.7
125°	452.2	452.1	452.0	451.9	451.7	451.3	450.9	450.5	450.1	450.4	450.6
127.5°	480.5	480.6	480.7	480.8	480.9	481.0	481.1	481.3	481.4	480.8	480.2
130°	508.7	508.7	508.7	508.7	508.6	508.5	508.4	508.2	508.1	507.7	507.3
132.5°	535.1	535.2	535.3	535.4	535.3	535.2	535.1	534.9	534.8	534.3	533.8
135°	560.5	560.2	559.9	559.8	559.7	559.4	559.2	558.9	558.7	558.2	557.7
137.5°	583.4	583.5	583.6	583.7	583.6	583.3	583.1	582.8	582.6	582.0	581.3
140°	606.2	606.1	606.0	605.9	605.7	605.3	605.0	604.6	604.2	603.9	603.7
142.5°	625.8	625.8	625.8	625.8	625.7	625.4	625.1	624.9	624.6	624.5	624.4
145°	645.2	644.9	644.6	644.5	644.4	644.3	644.2	644.1	644.0	644.0	644.0
147.5°	661.9	661.8	661.7	661.6	661.5	661.4	661.3	661.1	661.0	661.1	661.3
150°	677.8	677.7	677.6	677.5	677.5	677.5	677.5	677.5	677.5	677.6	677.8
152.5°	692.0	692.1	692.2	692.3	692.2	691.9	691.6	691.4	691.1	691.4	691.6
155°	704.4	704.7	705.1	705.3	705.1	704.6	704.1	703.6	703.1	703.5	703.9
157.5°	715.1	715.8	716.4	716.7	716.4	715.8	715.1	714.5	713.9	714.4	714.9
160°	725.6	726.4	727.1	727.5	727.1	726.4	725.6	724.9	724.1	724.2	724.4
162.5°	733.8	734.7	735.6	736.0	735.6	734.9	734.1	733.4	732.6	732.7	732.9
165°	741.7	742.9	744.0	744.6	744.1	743.1	742.0	741.0	740.0	740.0	740.0
167.5°	747.6	748.9	750.2	750.8	750.2	749.1	748.0	746.8	745.7	745.8	746.0
170°	752.7	754.0	755.3	755.9	755.4	754.4	753.4	752.4	751.4	751.3	751.1
172.5°	755.9	757.2	758.6	759.3	758.8	757.8	756.8	755.8	754.8	754.7	754.5
175°	758.4	759.9	761.4	762.2	761.6	760.5	759.4	758.2	757.1	757.0	756.8
177.5°	759.5	761.0	762.5	763.3	762.8	761.8	760.8	759.8	758.8	758.5	758.3
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1353.3	1348.0	1344.8	1343.7	1334.2	1328.9	1325.7	1323.5	1320.3	1311.8	1304.4
5°	1404.3	1389.4	1382.0	1373.5	1358.6	1341.6	1327.8	1319.3	1308.7	1291.6	1275.7
7.5°	1452.2	1429.8	1415.0	1403.3	1377.8	1350.1	1327.8	1309.7	1289.5	1266.1	1243.8
10°	1502.1	1466.0	1446.9	1428.8	1391.6	1355.4	1323.5	1297.0	1268.3	1237.4	1213.0
12.5°	1541.5	1493.6	1472.4	1446.9	1401.1	1358.6	1318.2	1282.1	1244.9	1211.9	1176.8
15°	1587.2	1527.7	1503.2	1470.2	1407.5	1352.2	1300.2	1260.8	1222.5	1173.6	1136.4
17.5°	1613.8	1544.7	1509.6	1480.9	1412.8	1345.9	1285.3	1236.4	1191.7	1142.8	1103.5
20°	1640.3	1561.7	1522.3	1481.9	1401.1	1329.9	1266.1	1207.7	1160.9	1107.7	1067.3
22.5°	1648.8	1557.4	1516.0	1478.7	1393.7	1314.0	1240.6	1181.1	1126.9	1073.7	1028.0
25°	1648.8	1556.4	1507.5	1459.6	1370.3	1288.5	1215.1	1150.3	1089.7	1036.5	990.8
27.5°	1631.8	1535.1	1484.1	1440.5	1348.0	1259.8	1184.3	1113.0	1054.6	1001.4	949.3
30°	1610.6	1504.3	1453.2	1401.1	1311.8	1227.9	1146.0	1080.1	1018.4	957.8	911.1
32.5°	1584.0	1471.3	1415.0	1361.8	1267.2	1180.0	1104.5	1039.7	981.2	918.5	866.4
35°	1545.7	1422.4	1359.7	1312.9	1221.5	1131.1	1058.8	995.0	938.7	873.9	817.5
37.5°	1496.8	1377.8	1314.0	1256.6	1161.9	1079.0	1011.0	949.3	894.1	834.5	771.8
40°	1439.4	1315.0	1259.8	1199.2	1099.2	1020.6	956.8	901.5	846.2	789.9	729.3
42.5°	1374.6	1251.2	1189.6	1131.1	1035.4	957.8	898.3	848.3	797.3	745.2	680.4
45°	1297.0	1181.1	1121.6	1066.3	973.8	894.1	839.8	792.0	748.4	695.3	637.8
47.5°	1209.8	1108.8	1048.2	988.7	898.3	829.2	776.1	735.7	698.4	645.3	593.2
50°	1124.7	1024.8	975.9	915.3	832.4	767.5	713.3	679.3	650.6	598.5	551.7
52.5°	1017.4	941.9	895.1	843.0	763.3	697.4	654.9	625.1	591.1	550.7	509.2
55°	922.8	852.6	815.4	766.5	687.8	629.3	593.2	565.6	539.0	502.8	469.9
57.5°	815.4	771.8	734.6	692.1	614.5	564.5	532.6	509.2	484.8	455.0	428.4
60°	702.7	682.5	646.4	612.3	546.4	502.8	476.3	455.0	431.6	407.2	384.8
62.5°	602.8	591.1	569.8	543.2	481.6	444.4	417.8	401.8	384.8	362.5	341.2
65°	508.2	502.8	482.6	463.5	421.0	388.0	364.6	355.1	335.9	318.9	299.8
67.5°	424.2	417.8	406.1	397.6	361.4	330.6	318.9	306.2	290.2	277.5	261.5
70°	339.1	338.1	330.6	320.0	300.9	278.5	266.8	258.3	242.4	232.8	221.1
72.5°	263.6	269.0	262.6	258.3	245.6	229.6	219.0	213.7	200.9	193.5	185.0
75°	196.7	200.9	204.1	196.7	193.5	186.0	176.5	171.2	164.8	154.1	151.0
77.5°	133.9	143.5	143.5	145.6	146.7	142.5	135.0	130.8	123.3	121.2	116.9
80°	88.2	96.7	97.8	99.9	103.1	103.1	97.8	96.7	89.3	88.2	85.0
82.5°	51.0	58.5	62.7	65.9	64.8	69.1	64.8	63.8	59.5	59.5	57.4
85°	27.6	28.7	30.8	33.0	35.1	37.2	37.2	36.1	35.1	34.0	31.9
87.5°	10.6	10.6	11.7	10.6	11.7	13.8	14.9	14.9	13.8	12.8	10.6
90°	9.5	8.5	8.0	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	8.9	7.9	7.4	7.5	7.8	8.0	8.3	8.5	8.3	8.0	7.8
95°	12.1	12.0	11.9	14.1	18.4	22.7	27.0	31.3	27.0	22.7	18.4
97.5°	52.3	65.6	72.2	70.8	68.0	65.3	62.5	59.7	62.5	65.3	68.0
100°	77.3	94.7	103.4	102.3	100.0	97.7	95.5	93.2	95.5	97.7	100.0
102.5°	139.8	138.3	137.5	136.7	135.2	133.7	132.2	130.7	132.2	133.7	135.2
105°	175.4	174.8	174.5	174.1	173.4	172.6	171.9	171.1	171.9	172.6	173.4
107.5°	211.0	210.1	209.7	209.5	209.1	208.8	208.4	208.0	208.4	208.8	209.1
110°	248.4	247.6	247.2	247.0	246.6	246.3	245.9	245.5	245.9	246.3	246.6

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.7	285.4	285.3	284.9	284.2	283.4	282.7	281.9	282.7	283.4	284.2
115°	320.9	321.0	321.1	320.9	320.5	320.2	319.8	319.4	319.8	320.2	320.5
117.5°	355.8	355.4	355.2	355.0	354.5	354.0	353.5	353.0	353.5	354.0	354.5
120°	389.1	389.2	389.3	389.1	388.6	388.1	387.6	387.1	387.6	388.1	388.6
122.5°	420.4	420.1	420.0	419.9	419.6	419.4	419.1	418.9	419.1	419.4	419.6
125°	450.9	451.2	451.3	451.0	450.5	450.0	449.5	449.0	449.5	450.0	450.5
127.5°	479.5	478.9	478.6	478.5	478.4	478.3	478.1	478.0	478.1	478.3	478.4
130°	507.0	506.6	506.4	506.3	506.2	506.1	505.9	505.8	505.9	506.1	506.2
132.5°	533.3	532.8	532.6	532.5	532.2	531.9	531.7	531.4	531.7	531.9	532.2
135°	557.2	556.7	556.4	556.5	556.6	556.7	556.9	557.0	556.9	556.7	556.6
137.5°	580.7	580.0	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7
140°	603.4	603.1	603.0	602.9	602.6	602.4	602.1	601.9	602.1	602.4	602.6
142.5°	624.3	624.2	624.1	623.8	623.3	622.8	622.3	621.8	622.3	622.8	623.3
145°	644.0	644.0	644.0	643.8	643.4	643.1	642.7	642.3	642.7	643.1	643.4
147.5°	661.4	661.5	661.6	661.2	660.5	659.7	659.0	658.2	659.0	659.7	660.5
150°	677.9	678.0	678.1	677.8	677.3	676.8	676.3	675.8	676.3	676.8	677.3
152.5°	691.9	692.2	692.3	692.1	691.7	691.4	691.0	690.6	691.0	691.4	691.7
155°	704.2	704.6	704.8	704.7	704.6	704.5	704.3	704.2	704.3	704.5	704.6
157.5°	715.4	715.9	716.1	716.1	716.1	716.1	716.1	716.1	716.1	716.1	716.1
160°	724.5	724.6	724.7	724.9	725.3	725.6	726.0	726.4	726.0	725.6	725.3
162.5°	733.0	733.1	733.2	733.5	734.0	734.5	735.0	735.5	735.0	734.5	734.0
165°	740.0	740.0	740.0	740.3	741.0	741.6	742.3	742.9	742.3	741.6	741.0
167.5°	746.1	746.2	746.3	746.6	747.2	747.9	748.5	749.1	748.5	747.9	747.2
170°	751.0	750.9	750.8	751.2	751.9	752.7	753.4	754.2	753.4	752.7	751.9
172.5°	754.4	754.3	754.2	754.6	755.3	756.1	756.8	757.6	756.8	756.1	755.3
175°	756.7	756.6	756.5	756.9	757.6	758.4	759.1	759.9	759.1	758.4	757.6
177.5°	758.0	757.7	757.6	758.0	758.9	759.8	760.7	761.6	760.7	759.8	758.9
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1298.0	1295.9	1293.8	1285.3	1277.8	1265.1	1254.4	1250.2	1249.1	1250.2	1247.0
5°	1260.8	1259.8	1252.3	1237.4	1223.6	1208.7	1198.1	1187.5	1181.1	1181.1	1173.6
7.5°	1225.7	1218.3	1211.9	1192.8	1176.8	1156.6	1140.7	1131.1	1125.8	1114.1	1114.1
10°	1188.5	1177.9	1169.4	1151.3	1127.9	1107.7	1087.5	1075.8	1066.3	1057.8	1054.6
12.5°	1151.3	1142.8	1126.9	1107.7	1084.3	1058.8	1037.6	1029.1	1006.7	988.7	989.7
15°	1116.2	1097.1	1089.7	1062.0	1034.4	1009.9	979.1	954.6	936.6	924.9	910.0
17.5°	1076.9	1057.8	1043.9	1020.6	984.4	946.1	916.4	883.4	865.3	845.2	835.6
20°	1033.3	1017.4	1006.7	969.5	925.9	880.2	847.3	827.1	806.9	792.0	783.5
22.5°	996.1	975.9	963.2	913.2	865.3	819.6	794.1	777.1	760.1	747.3	743.1
25°	948.3	936.6	905.7	862.2	803.7	772.9	750.5	728.2	718.6	710.1	700.6
27.5°	908.9	880.2	859.0	801.6	765.4	730.3	708.0	691.0	679.3	670.8	663.4
30°	860.0	833.5	803.7	755.9	722.9	689.9	669.7	655.9	643.2	637.8	631.5
32.5°	809.0	784.6	755.9	717.6	677.2	651.7	635.7	620.8	612.3	607.0	599.6
35°	763.3	732.5	713.3	677.2	644.2	615.5	600.6	587.9	578.3	576.2	575.1
37.5°	714.4	691.0	672.9	635.7	608.1	583.6	569.8	556.0	550.7	549.6	545.4
40°	671.9	651.7	634.7	599.6	569.8	547.5	536.9	528.4	523.0	523.0	522.0
42.5°	634.7	613.4	596.4	564.5	537.9	517.7	506.0	497.5	495.4	496.5	495.4
45°	593.2	575.1	558.1	525.2	502.8	488.0	475.2	470.9	467.8	468.8	469.9
47.5°	553.9	539.0	522.0	495.4	469.9	453.9	446.5	442.2	442.2	442.2	444.4
50°	518.8	501.8	486.9	459.3	435.9	423.1	416.7	411.4	412.5	413.5	414.6
52.5°	477.3	462.4	451.8	424.2	407.2	391.2	383.8	384.8	383.8	383.8	385.9
55°	441.2	426.3	415.7	390.2	373.1	362.5	356.1	352.9	354.0	351.9	356.1
57.5°	400.8	388.0	380.6	356.1	341.2	331.7	326.4	321.1	323.2	322.1	321.1
60°	365.7	350.8	339.1	322.1	309.4	297.7	294.5	289.2	291.3	289.2	288.1
62.5°	325.3	313.6	305.1	288.1	277.5	267.9	260.5	257.3	256.2	253.0	249.8
65°	284.9	278.5	270.0	253.0	242.4	234.9	230.7	227.5	226.4	217.9	208.4
67.5°	247.7	243.4	234.9	222.2	212.6	205.2	198.8	193.5	187.1	180.7	175.4
70°	212.6	206.2	200.9	189.2	180.7	173.3	166.9	160.5	157.3	151.0	148.8
72.5°	178.6	172.2	166.9	156.3	148.8	141.4	139.3	131.8	128.6	127.6	127.6
75°	143.5	138.2	135.0	125.4	119.1	113.7	110.6	108.4	106.3	104.2	101.0
77.5°	109.5	106.3	104.2	97.8	92.5	89.3	88.2	80.8	78.7	76.5	74.4
80°	79.7	78.7	76.5	71.2	69.1	61.7	61.7	59.5	58.5	58.5	58.5
82.5°	54.2	52.1	51.0	45.7	44.6	43.6	42.5	41.5	42.5	41.5	42.5
85°	28.7	27.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	25.5	26.6
87.5°	10.6	10.6	10.6	10.6	9.6	10.6	10.6	9.6	10.6	10.6	10.6
90°	7.3	8.0	8.5	9.5	10.5	11.5	12.5	13.3	14.0	14.8	15.5
92.5°	7.5	7.4	7.9	8.9	9.9	10.9	11.9	12.7	13.4	14.2	14.9
95°	14.1	11.9	12.0	12.1	12.2	12.4	12.5	13.3	14.0	14.8	15.5
97.5°	70.8	72.2	65.6	52.3	39.0	25.8	12.5	13.1	13.7	14.4	15.0
100°	102.3	103.4	94.7	77.3	59.8	42.4	25.0	22.8	20.7	18.5	16.4
102.5°	136.7	137.5	138.3	139.8	141.3	142.9	144.4	116.0	87.6	59.1	30.7
105°	174.1	174.5	174.8	175.4	176.1	176.7	177.3	178.4	179.6	180.7	181.8
107.5°	209.5	209.7	210.1	211.0	211.9	212.8	213.7	214.3	214.9	215.6	216.2
110°	247.0	247.2	247.6	248.4	249.1	249.9	250.7	250.9	251.2	251.4	251.7

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	284.9	285.3	285.4	285.7	286.0	286.2	286.5	286.4	286.2	286.1	286.0
115°	320.9	321.1	321.0	320.9	320.8	320.7	320.6	320.8	321.1	321.3	321.6
117.5°	355.0	355.2	355.4	355.8	356.1	356.5	356.9	356.8	356.7	356.6	356.5
120°	389.1	389.3	389.2	389.1	389.0	388.9	388.8	389.0	389.3	389.5	389.8
122.5°	419.9	420.0	420.1	420.4	420.7	420.9	421.2	421.3	421.4	421.5	421.6
125°	451.0	451.3	451.2	450.9	450.6	450.4	450.1	450.5	450.9	451.3	451.7
127.5°	478.5	478.6	478.9	479.5	480.2	480.8	481.4	481.3	481.1	481.0	480.9
130°	506.3	506.4	506.6	507.0	507.3	507.7	508.1	508.2	508.4	508.5	508.6
132.5°	532.5	532.6	532.8	533.3	533.8	534.3	534.8	534.9	535.1	535.2	535.3
135°	556.5	556.4	556.7	557.2	557.7	558.2	558.7	558.9	559.2	559.4	559.7
137.5°	579.7	579.7	580.0	580.7	581.3	582.0	582.6	582.8	583.1	583.3	583.6
140°	602.9	603.0	603.1	603.4	603.7	603.9	604.2	604.6	605.0	605.3	605.7
142.5°	623.8	624.1	624.2	624.3	624.4	624.5	624.6	624.9	625.1	625.4	625.7
145°	643.8	644.0	644.0	644.0	644.0	644.0	644.0	644.1	644.2	644.3	644.4
147.5°	661.2	661.6	661.5	661.4	661.3	661.1	661.0	661.1	661.3	661.4	661.5
150°	677.8	678.1	678.0	677.9	677.8	677.6	677.5	677.5	677.5	677.5	677.5
152.5°	692.1	692.3	692.2	691.9	691.6	691.4	691.1	691.4	691.6	691.9	692.2
155°	704.7	704.8	704.6	704.2	703.9	703.5	703.1	703.6	704.1	704.6	705.1
157.5°	716.1	716.1	715.9	715.4	714.9	714.4	713.9	714.5	715.1	715.8	716.4
160°	724.9	724.7	724.6	724.5	724.4	724.2	724.1	724.9	725.6	726.4	727.1
162.5°	733.5	733.2	733.1	733.0	732.9	732.7	732.6	733.4	734.1	734.9	735.6
165°	740.3	740.0	740.0	740.0	740.0	740.0	740.0	741.0	742.0	743.1	744.1
167.5°	746.6	746.3	746.2	746.1	746.0	745.8	745.7	746.8	748.0	749.1	750.2
170°	751.2	750.8	750.9	751.0	751.1	751.3	751.4	752.4	753.4	754.4	755.4
172.5°	754.6	754.2	754.3	754.4	754.5	754.7	754.8	755.8	756.8	757.8	758.8
175°	756.9	756.5	756.6	756.7	756.8	757.0	757.1	758.2	759.4	760.5	761.6
177.5°	758.0	757.6	757.7	758.0	758.3	758.5	758.8	759.8	760.8	761.8	762.8
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1247.0	1251.2	1245.9	1249.1	1241.7	1240.6	1241.7	1241.7	1242.7	1243.8	1244.9
5°	1176.8	1175.8	1169.4	1165.1	1161.9	1165.1	1167.3	1169.4	1167.3	1169.4	1170.5
7.5°	1110.9	1107.7	1104.5	1097.1	1099.2	1097.1	1103.5	1100.3	1100.3	1105.6	1109.9
10°	1052.5	1046.1	1043.9	1035.4	1029.1	1028.0	1035.4	1038.6	1041.8	1043.9	1052.5
12.5°	977.0	967.4	960.0	963.2	945.1	952.5	954.6	950.4	963.2	978.0	969.5
15°	896.2	897.2	882.4	877.0	862.2	866.4	867.5	878.1	888.7	887.7	900.4
17.5°	836.6	830.3	817.5	816.4	810.1	813.3	812.2	820.7	817.5	822.8	833.5
20°	781.4	777.1	766.5	762.2	764.4	762.2	763.3	764.4	767.5	779.2	777.1
22.5°	737.8	732.5	732.5	727.1	720.8	718.6	724.0	727.1	731.4	733.5	738.8
25°	699.5	695.3	689.9	686.8	681.4	682.5	685.7	689.9	693.1	697.4	701.6
27.5°	660.2	660.2	654.9	653.8	651.7	650.6	654.9	657.0	657.0	660.2	664.4
30°	629.3	629.3	624.0	623.0	621.9	621.9	625.1	626.2	627.2	630.4	632.5
32.5°	599.6	598.5	596.4	597.5	596.4	597.5	597.5	598.5	600.6	601.7	606.0
35°	571.9	573.0	570.9	570.9	569.8	570.9	573.0	574.1	575.1	577.3	577.3
37.5°	545.4	547.5	546.4	549.6	549.6	549.6	549.6	551.7	551.7	551.7	550.7
40°	522.0	522.0	520.9	523.0	525.2	525.2	526.2	526.2	527.3	527.3	526.2
42.5°	495.4	497.5	500.7	501.8	503.9	502.8	506.0	505.0	506.0	503.9	501.8
45°	470.9	470.9	475.2	479.5	480.5	480.5	480.5	482.6	480.5	477.3	476.3
47.5°	444.4	446.5	448.6	453.9	455.0	455.0	455.0	455.0	452.9	452.9	452.9
50°	417.8	418.9	419.9	422.0	425.2	424.2	424.2	424.2	428.4	424.2	425.2
52.5°	385.9	387.0	388.0	392.3	391.2	391.2	392.3	392.3	395.5	394.4	392.3
55°	354.0	354.0	356.1	356.1	356.1	358.3	359.3	361.4	360.4	361.4	362.5
57.5°	322.1	320.0	318.9	318.9	322.1	321.1	322.1	322.1	326.4	328.5	329.6
60°	284.9	284.9	283.8	277.5	277.5	276.4	279.6	281.7	283.8	293.4	292.3
62.5°	246.6	242.4	238.1	239.2	232.8	236.0	233.9	236.0	242.4	249.8	250.9
65°	208.4	205.2	200.9	199.9	197.7	200.9	199.9	200.9	204.1	208.4	213.7
67.5°	174.3	173.3	171.2	170.1	170.1	170.1	172.2	172.2	173.3	176.5	179.7
70°	148.8	147.8	148.8	146.7	147.8	146.7	147.8	148.8	149.9	151.0	154.1
72.5°	125.4	125.4	125.4	123.3	125.4	124.4	124.4	125.4	126.5	127.6	129.7
75°	99.9	97.8	95.7	93.6	92.5	94.6	95.7	94.6	97.8	102.1	102.1
77.5°	75.5	74.4	74.4	74.4	75.5	74.4	76.5	75.5	76.5	76.5	78.7
80°	58.5	57.4	58.5	58.5	57.4	59.5	58.5	58.5	59.5	60.6	59.5
82.5°	42.5	43.6	42.5	42.5	42.5	44.6	42.5	42.5	42.5	43.6	43.6
85°	26.6	26.6	26.6	26.6	27.6	26.6	27.6	26.6	28.7	27.6	27.6
87.5°	9.6	10.6	11.7	11.7	11.7	11.7	10.6	11.7	12.8	11.7	12.8
90°	15.9	16.0	16.3	16.6	16.8	17.1	16.8	16.6	16.3	16.0	15.9
92.5°	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3
95°	15.9	16.0	16.1	16.2	16.4	16.5	16.4	16.2	16.1	16.0	15.9
97.5°	15.3	15.4	15.5	15.6	15.8	15.9	15.8	15.6	15.5	15.4	15.3
100°	15.3	15.4	15.5	15.6	15.8	15.9	15.8	15.6	15.5	15.4	15.3
102.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
105°	182.4	180.1	175.6	171.1	166.5	162.0	166.5	171.1	175.6	180.1	182.4
107.5°	216.5	216.8	217.3	217.8	218.3	218.8	218.3	217.8	217.3	216.8	216.5
110°	251.8	252.0	252.4	252.7	253.1	253.5	253.1	252.7	252.4	252.0	251.8

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	285.9	286.2	286.7	287.2	287.7	288.2	287.7	287.2	286.7	286.2	285.9
115°	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7
117.5°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4
120°	389.9	389.8	389.5	389.3	389.0	388.8	389.0	389.3	389.5	389.8	389.9
122.5°	421.7	421.6	421.3	421.1	420.8	420.6	420.8	421.1	421.3	421.6	421.7
125°	451.9	452.0	452.1	452.2	452.3	452.4	452.3	452.2	452.1	452.0	451.9
127.5°	480.8	480.7	480.6	480.5	480.4	480.3	480.4	480.5	480.6	480.7	480.8
130°	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7
132.5°	535.4	535.3	535.2	535.1	534.9	534.8	534.9	535.1	535.2	535.3	535.4
135°	559.8	559.9	560.2	560.5	560.7	561.0	560.7	560.5	560.2	559.9	559.8
137.5°	583.7	583.6	583.5	583.4	583.2	583.1	583.2	583.4	583.5	583.6	583.7
140°	605.9	606.0	606.1	606.2	606.4	606.5	606.4	606.2	606.1	606.0	605.9
142.5°	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8
145°	644.5	644.6	644.9	645.2	645.4	645.7	645.4	645.2	644.9	644.6	644.5
147.5°	661.6	661.7	661.8	661.9	662.1	662.2	662.1	661.9	661.8	661.7	661.6
150°	677.5	677.6	677.7	677.8	678.0	678.1	678.0	677.8	677.7	677.6	677.5
152.5°	692.3	692.2	692.1	692.0	691.8	691.7	691.8	692.0	692.1	692.2	692.3
155°	705.3	705.1	704.7	704.4	704.0	703.6	704.0	704.4	704.7	705.1	705.3
157.5°	716.7	716.4	715.8	715.1	714.5	713.9	714.5	715.1	715.8	716.4	716.7
160°	727.5	727.1	726.4	725.6	724.9	724.1	724.9	725.6	726.4	727.1	727.5
162.5°	736.0	735.6	734.7	733.8	733.0	732.1	733.0	733.8	734.7	735.6	736.0
165°	744.6	744.0	742.9	741.7	740.6	739.4	740.6	741.7	742.9	744.0	744.6
167.5°	750.8	750.2	748.9	747.6	746.4	745.1	746.4	747.6	748.9	750.2	750.8
170°	755.9	755.3	754.0	752.7	751.5	750.2	751.5	752.7	754.0	755.3	755.9
172.5°	759.3	758.6	757.2	755.9	754.5	753.1	754.5	755.9	757.2	758.6	759.3
175°	762.2	761.4	759.9	758.4	756.9	755.4	756.9	758.4	759.9	761.4	762.2
177.5°	763.3	762.5	761.0	759.5	758.0	756.5	758.0	759.5	761.0	762.5	763.3
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1249.1	1254.4	1252.3	1244.9	1248.1	1254.4	1260.8	1269.3	1274.6	1278.9	1281.0
5°	1175.8	1185.3	1183.2	1183.2	1187.5	1198.1	1208.7	1226.8	1233.2	1240.6	1251.2
7.5°	1110.9	1118.4	1124.7	1126.9	1133.2	1147.1	1160.9	1181.1	1197.0	1205.5	1211.9
10°	1053.5	1058.8	1068.4	1073.7	1080.1	1097.1	1117.3	1138.6	1154.5	1169.4	1177.9
12.5°	980.2	1001.4	1014.2	1022.7	1031.2	1056.7	1072.7	1096.0	1115.2	1129.0	1141.8
15°	898.3	923.8	931.3	964.2	985.5	1005.7	1030.1	1057.8	1075.8	1091.8	1108.8
17.5°	829.2	847.3	855.8	890.9	908.9	940.8	975.9	1011.0	1038.6	1050.3	1067.3
20°	785.6	795.2	812.2	823.9	843.0	880.2	918.5	961.0	1002.5	1014.2	1031.2
22.5°	741.0	753.7	765.4	781.4	796.2	821.8	860.0	906.8	951.5	972.7	992.9
25°	700.6	713.3	720.8	737.8	751.6	777.1	803.7	851.5	904.7	922.8	954.6
27.5°	668.7	676.1	688.9	696.3	712.3	735.7	760.1	796.2	848.3	879.2	910.0
30°	636.8	642.1	652.7	663.4	675.1	691.0	718.6	753.7	801.6	828.1	859.0
32.5°	604.9	613.4	619.8	627.2	640.0	659.1	678.2	712.3	750.5	780.3	811.1
35°	578.3	581.5	590.0	598.5	607.0	624.0	644.2	677.2	711.2	734.6	762.2
37.5°	549.6	554.9	561.3	564.5	578.3	588.9	610.2	635.7	676.1	691.0	718.6
40°	527.3	526.2	532.6	537.9	544.3	561.3	574.1	601.7	633.6	657.0	674.0
42.5°	499.6	499.6	501.8	508.2	516.7	527.3	542.2	565.6	598.5	615.5	635.7
45°	477.3	474.1	475.2	479.5	484.8	495.4	510.3	530.5	563.4	577.3	598.5
47.5°	450.7	447.6	447.6	451.8	456.1	463.5	475.2	498.6	525.2	543.2	559.2
50°	421.0	422.0	421.0	424.2	426.3	433.7	446.5	465.6	490.1	505.0	523.0
52.5°	393.3	391.2	390.2	392.3	396.5	401.8	415.7	432.7	456.1	470.9	486.9
55°	359.3	361.4	361.4	361.4	367.8	370.0	380.6	397.6	421.0	432.7	447.6
57.5°	328.5	327.4	329.6	328.5	333.8	341.2	349.8	362.5	385.9	397.6	411.4
60°	294.5	295.5	296.6	296.6	300.9	308.3	317.9	329.6	348.7	360.4	373.1
62.5°	253.0	258.3	263.6	265.8	272.1	277.5	283.8	296.6	313.6	322.1	333.8
65°	213.7	221.1	228.6	233.9	238.1	243.4	252.0	263.6	277.5	286.0	297.7
67.5°	179.7	185.0	194.5	199.9	208.4	214.7	220.1	229.6	246.6	249.8	259.4
70°	155.2	157.3	161.6	165.8	175.4	180.7	187.1	196.7	209.4	216.9	222.2
72.5°	130.8	131.8	133.9	138.2	142.5	148.8	156.3	164.8	176.5	179.7	187.1
75°	104.2	110.6	110.6	113.7	116.9	120.1	126.5	135.0	142.5	147.8	152.0
77.5°	77.6	80.8	82.9	88.2	92.5	95.7	99.9	106.3	110.6	114.8	118.0
80°	60.6	61.7	62.7	62.7	64.8	69.1	73.4	77.6	82.9	85.0	88.2
82.5°	44.6	44.6	44.6	46.8	47.8	48.9	48.9	51.0	56.3	58.5	61.7
85°	28.7	28.7	28.7	28.7	29.8	30.8	31.9	33.0	33.0	33.0	35.1
87.5°	11.7	13.8	12.8	13.8	13.8	13.8	13.8	14.9	14.9	15.9	15.9
90°	15.5	14.8	14.0	13.3	12.5	11.5	10.5	9.5	8.5	8.0	7.3
92.5°	14.9	14.2	13.4	12.7	11.9	10.9	9.9	8.9	7.9	7.4	7.5
95°	15.5	14.8	14.0	13.3	12.5	12.4	12.2	12.1	12.0	11.9	14.1
97.5°	15.0	14.4	13.7	13.1	12.5	25.8	39.0	52.3	65.6	72.2	70.8
100°	16.4	18.5	20.7	22.8	25.0	42.4	59.8	77.3	94.7	103.4	102.3
102.5°	30.7	59.1	87.6	116.0	144.4	142.9	141.3	139.8	138.3	137.5	136.7
105°	181.8	180.7	179.6	178.4	177.3	176.7	176.1	175.4	174.8	174.5	174.1
107.5°	216.2	215.6	214.9	214.3	213.7	212.8	211.9	211.0	210.1	209.7	209.5
110°	251.7	251.4	251.2	250.9	250.7	249.9	249.1	248.4	247.6	247.2	247.0

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	286.0	286.1	286.2	286.4	286.5	286.2	286.0	285.7	285.4	285.3	284.9
115°	321.6	321.3	321.1	320.8	320.6	320.7	320.8	320.9	321.0	321.1	320.9
117.5°	356.5	356.6	356.7	356.8	356.9	356.5	356.1	355.8	355.4	355.2	355.0
120°	389.8	389.5	389.3	389.0	388.8	388.9	389.0	389.1	389.2	389.3	389.1
122.5°	421.6	421.5	421.4	421.3	421.2	420.9	420.7	420.4	420.1	420.0	419.9
125°	451.7	451.3	450.9	450.5	450.1	450.4	450.6	450.9	451.2	451.3	451.0
127.5°	480.9	481.0	481.1	481.3	481.4	480.8	480.2	479.5	478.9	478.6	478.5
130°	508.6	508.5	508.4	508.2	508.1	507.7	507.3	507.0	506.6	506.4	506.3
132.5°	535.3	535.2	535.1	534.9	534.8	534.3	533.8	533.3	532.8	532.6	532.5
135°	559.7	559.4	559.2	558.9	558.7	558.2	557.7	557.2	556.7	556.4	556.5
137.5°	583.6	583.3	583.1	582.8	582.6	582.0	581.3	580.7	580.0	579.7	579.7
140°	605.7	605.3	605.0	604.6	604.2	603.9	603.7	603.4	603.1	603.0	602.9
142.5°	625.7	625.4	625.1	624.9	624.6	624.5	624.4	624.3	624.2	624.1	623.8
145°	644.4	644.3	644.2	644.1	644.0	644.0	644.0	644.0	644.0	644.0	643.8
147.5°	661.5	661.4	661.3	661.1	661.0	661.1	661.3	661.4	661.5	661.6	661.2
150°	677.5	677.5	677.5	677.5	677.5	677.6	677.8	677.9	678.0	678.1	677.8
152.5°	692.2	691.9	691.6	691.4	691.1	691.4	691.6	691.9	692.2	692.3	692.1
155°	705.1	704.6	704.1	703.6	703.1	703.5	703.9	704.2	704.6	704.8	704.7
157.5°	716.4	715.8	715.1	714.5	713.9	714.4	714.9	715.4	715.9	716.1	716.1
160°	727.1	726.4	725.6	724.9	724.1	724.2	724.4	724.5	724.6	724.7	724.9
162.5°	735.6	734.9	734.1	733.4	732.6	732.7	732.9	733.0	733.1	733.2	733.5
165°	744.1	743.1	742.0	741.0	740.0	740.0	740.0	740.0	740.0	740.0	740.3
167.5°	750.2	749.1	748.0	746.8	745.7	745.8	746.0	746.1	746.2	746.3	746.6
170°	755.4	754.4	753.4	752.4	751.4	751.3	751.1	751.0	750.9	750.8	751.2
172.5°	758.8	757.8	756.8	755.8	754.8	754.7	754.5	754.4	754.3	754.2	754.6
175°	761.6	760.5	759.4	758.2	757.1	757.0	756.8	756.7	756.6	756.5	756.9
177.5°	762.8	761.8	760.8	759.8	758.8	758.5	758.3	758.0	757.7	757.6	758.0
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1319.3	1319.3	1319.3	1319.3
2.5°	1289.5	1295.9	1306.5	1321.4
5°	1259.8	1277.8	1294.8	1317.2
7.5°	1233.2	1254.4	1277.8	1309.7
10°	1202.3	1228.9	1258.7	1298.0
12.5°	1166.2	1203.4	1237.4	1280.0
15°	1139.6	1167.3	1210.9	1260.8
17.5°	1102.4	1139.6	1183.2	1239.6
20°	1067.3	1106.7	1155.6	1214.0
22.5°	1030.1	1074.8	1123.7	1186.4
25°	991.9	1039.7	1088.6	1155.6
27.5°	956.8	1000.4	1055.6	1123.7
30°	914.3	964.2	1017.4	1088.6
32.5°	872.8	924.9	979.1	1050.3
35°	828.1	880.2	939.8	1007.8
37.5°	784.6	842.0	896.2	962.1
40°	736.7	796.2	852.6	919.6
42.5°	689.9	751.6	807.9	865.3
45°	646.4	707.0	758.0	812.2
47.5°	604.9	659.1	711.2	760.1
50°	564.5	610.2	658.0	698.4
52.5°	522.0	565.6	603.8	640.0
55°	483.7	517.7	551.7	584.7
57.5°	438.0	472.0	501.8	527.3
60°	399.7	421.0	449.7	476.3
62.5°	356.1	380.6	402.9	419.9
65°	313.6	334.9	351.9	366.8
67.5°	277.5	290.2	303.0	318.9
70°	233.9	244.5	259.4	271.1
72.5°	196.7	205.2	212.6	226.4
75°	159.5	166.9	171.2	183.9
77.5°	123.3	130.8	133.9	141.4
80°	94.6	95.7	99.9	106.3
82.5°	64.8	67.0	68.0	73.4
85°	37.2	42.5	41.5	43.6
87.5°	15.9	17.0	19.1	21.3
90°	5.9	4.5	3.1	1.7
92.5°	7.8	8.0	8.3	8.5
95°	18.4	22.7	27.0	31.3
97.5°	68.0	65.3	62.5	59.7
100°	100.0	97.7	95.5	93.2
102.5°	135.2	133.7	132.2	130.7
105°	173.4	172.6	171.9	171.1
107.5°	209.1	208.8	208.4	208.0
110°	246.6	246.3	245.9	245.5

TEST NUMBER: P1026637

CATALOG NUMBER: S124RDIP-B795D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	284.2	283.4	282.7	281.9
115°	320.5	320.2	319.8	319.4
117.5°	354.5	354.0	353.5	353.0
120°	388.6	388.1	387.6	387.1
122.5°	419.6	419.4	419.1	418.9
125°	450.5	450.0	449.5	449.0
127.5°	478.4	478.3	478.1	478.0
130°	506.2	506.1	505.9	505.8
132.5°	532.2	531.9	531.7	531.4
135°	556.6	556.7	556.9	557.0
137.5°	579.7	579.7	579.7	579.7
140°	602.6	602.4	602.1	601.9
142.5°	623.3	622.8	622.3	621.8
145°	643.4	643.1	642.7	642.3
147.5°	660.5	659.7	659.0	658.2
150°	677.3	676.8	676.3	675.8
152.5°	691.7	691.4	691.0	690.6
155°	704.6	704.5	704.3	704.2
157.5°	716.1	716.1	716.1	716.1
160°	725.3	725.6	726.0	726.4
162.5°	734.0	734.5	735.0	735.5
165°	741.0	741.6	742.3	742.9
167.5°	747.2	747.9	748.5	749.1
170°	751.9	752.7	753.4	754.2
172.5°	755.3	756.1	756.8	757.6
175°	757.6	758.4	759.1	759.9
177.5°	758.9	759.8	760.7	761.6
180°	759.9	759.9	759.9	759.9

(END OF REPORT)