

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026822

Luminaire Tested: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026822
REPORT IS A COMBINATION OF REPORTS P1001776 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8058.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026822

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026822

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	99	94	90	86	92	87	84	80	75	73	70	64	62	60	54	53	51
2	89	81	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43
3	81	71	64	57	75	67	60	54	58	52	48	49	45	42	42	38	36
4	74	63	55	48	69	59	51	46	51	45	41	44	39	36	37	34	31
5	68	56	48	41	63	52	45	39	46	40	35	39	34	31	33	30	27
6	63	50	42	36	58	47	39	34	41	35	30	35	31	27	30	26	23
7	58	45	37	31	54	43	35	30	37	31	27	32	27	24	27	24	21
8	54	41	33	28	50	39	31	26	34	28	24	29	25	21	25	21	19
9	50	38	30	25	47	35	28	23	31	25	21	27	22	19	23	19	17
10	47	34	27	22	44	32	26	21	29	23	19	25	20	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10153	10153	10153
5°	10170	9940	9965
10°	10093	9737	9710
15°	9970	9502	9397
20°	9805	9217	9085
25°	9608	8914	8709
30°	9370	8583	8367
35°	9148	8279	8051
40°	8922	7957	7733
45°	8666	7679	7447
50°	8421	7377	7189
55°	8127	7089	6890
60°	7804	6761	6582
65°	7466	6414	6236
70°	7080	5952	5876
75°	6473	5494	5437
80°	5675	4937	4951
85°	4883	4493	4696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8666 cd/sqm

TEST NUMBER: P1026822

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.0	1.9
10°-20°	425.7	5.3
20°-30°	633.0	7.9
30°-40°	749.7	9.3
40°-50°	775.0	9.6
50°-60°	714.0	8.9
60°-70°	577.2	7.2
70°-80°	386.2	4.8
80°-90°	201.1	2.5
90°-100°	147.2	1.8
100°-110°	314.1	3.9
110°-120°	471.9	5.9
120°-130°	565.9	7.0
130°-140°	588.6	7.3
140°-150°	542.3	6.7
150°-160°	436.5	5.4
160°-170°	282.3	3.5
170°-180°	97.3	1.2
0°-30°	1208.7	15.0
0°-40°	1958.3	24.3
0°-60°	3447.3	42.8
0°-90°	4611.8	57.2
90°-120°	933.3	11.6
90°-150°	2630.1	32.6
90°-180°	3446.0	42.8
0°-180°	8058.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1585	1585	1585	1585	1585	
5°	1585	1582	1571	1583	1582	150
15°	1513	1515	1504	1513	1507	426
25°	1375	1380	1370	1376	1369	633
35°	1190	1201	1196	1201	1201	745
45°	980	997	1005	1016	1018	756
55°	754	778	803	820	826	673
65°	519	555	592	615	621	515
75°	286	326	376	407	415	303
85°	85	137	191	225	238	89
90°	26	81	140	179	192	19
95°	64	102	126	164	174	69
105°	237	265	312	343	353	251
115°	429	443	484	509	514	425
125°	602	606	637	659	665	538
135°	747	750	759	778	781	576
145°	864	864	864	872	874	540
155°	949	945	946	949	943	437
165°	1002	997	998	1003	996	283
175°	1025	1020	1021	1027	1020	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1026822

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1584.7	1584.7	1584.7	1584.7	1584.7
2.5°	1589.3	1586.2	1575.3	1586.2	1584.7
5°	1584.7	1581.6	1570.7	1583.1	1581.6
7.5°	1573.8	1572.2	1561.4	1572.2	1570.7
10°	1558.2	1558.2	1545.8	1556.7	1555.1
12.5°	1536.5	1538.1	1528.7	1536.5	1531.8
15°	1513.2	1514.7	1503.9	1513.2	1507.0
17.5°	1483.7	1486.8	1475.9	1483.7	1479.0
20°	1451.1	1454.2	1443.3	1447.9	1447.9
22.5°	1413.8	1420.0	1407.6	1413.8	1409.1
25°	1374.9	1379.6	1370.3	1376.5	1368.7
27.5°	1333.0	1339.2	1328.3	1333.0	1329.9
30°	1284.8	1294.1	1284.8	1287.9	1286.4
32.5°	1241.3	1249.1	1242.9	1246.0	1244.4
35°	1190.0	1200.9	1196.3	1200.9	1200.9
37.5°	1140.3	1149.7	1148.1	1154.3	1152.8
40°	1089.1	1101.5	1099.9	1106.2	1109.3
42.5°	1033.1	1050.2	1054.9	1062.7	1062.7
45°	980.3	997.4	1005.2	1016.0	1017.6
47.5°	925.9	941.5	953.9	969.4	972.5
50°	870.0	887.1	904.2	921.3	925.9
52.5°	811.0	832.7	854.5	873.1	876.2
55°	753.5	778.3	803.2	820.3	826.5
57.5°	694.5	724.0	751.9	770.6	775.2
60°	635.4	666.5	697.6	720.9	725.5
62.5°	577.9	609.0	643.2	669.6	675.8
65°	518.9	554.6	591.9	615.2	621.4
67.5°	464.5	498.7	536.0	564.0	571.7
70°	403.9	439.7	480.1	509.6	518.9
72.5°	344.9	382.2	427.2	459.9	466.1
75°	285.9	326.3	376.0	407.0	414.8
77.5°	228.4	275.0	321.6	355.8	362.0
80°	175.6	222.2	275.0	309.2	315.4
82.5°	127.4	177.1	231.5	264.1	276.5
85°	85.4	136.7	191.1	225.3	237.7
87.5°	54.4	104.1	156.9	192.6	203.5
90°	25.7	81.4	139.6	179.1	192.2
92.5°	36.2	74.4	133.4	171.4	182.9
95°	63.5	101.6	125.6	163.6	174.5
97.5°	99.9	141.7	120.9	155.0	166.7
100°	143.9	178.8	231.6	151.1	157.4
102.5°	188.7	221.3	270.9	303.6	249.1
105°	237.3	265.1	311.7	342.8	353.0
107.5°	287.4	309.2	355.7	387.5	393.8
110°	336.0	354.6	399.6	426.8	438.5

TEST NUMBER: P1026822

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	383.1	399.4	442.0	467.0	476.3
115°	428.6	443.3	484.4	509.4	514.1
117.5°	476.4	484.1	526.1	547.9	557.3
120°	522.0	525.9	563.9	588.8	594.3
122.5°	560.7	566.1	600.9	624.3	629.1
125°	602.5	606.3	637.3	659.1	664.7
127.5°	641.2	643.4	669.0	690.8	694.1
130°	677.7	679.9	702.4	721.8	725.8
132.5°	712.5	717.1	730.3	752.1	754.5
135°	746.7	749.8	759.0	777.7	781.0
137.5°	778.6	781.7	786.3	804.9	807.3
140°	808.2	809.8	810.5	829.1	830.8
142.5°	836.4	835.5	837.0	851.0	852.7
145°	863.7	863.6	863.6	872.2	873.8
147.5°	886.4	886.4	887.2	891.0	888.8
150°	909.2	907.7	909.2	910.7	906.2
152.5°	931.2	927.4	928.9	930.5	925.1
155°	949.4	944.9	946.4	948.7	942.6
157.5°	963.9	961.6	961.6	963.9	957.8
160°	979.1	974.5	975.3	978.3	972.2
162.5°	991.2	986.7	987.4	992.0	985.1
165°	1001.9	997.3	998.1	1002.6	996.5
167.5°	1010.2	1005.7	1006.4	1011.7	1004.9
170°	1017.0	1011.7	1012.5	1018.6	1011.7
172.5°	1021.6	1016.3	1017.8	1023.1	1016.3
175°	1024.6	1020.1	1020.8	1026.9	1020.1
177.5°	1026.9	1022.4	1023.1	1028.4	1022.4
180°	1024.6	1024.6	1024.6	1024.6	1024.6

(END OF REPORT)