

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026823

Luminaire Tested: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026823
REPORT IS A COMBINATION OF REPORTS P1001777 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7792.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026823

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026823

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	99	94	90	86	92	87	84	80	75	73	70	64	62	60	54	53	51
2	89	81	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43
3	81	71	64	57	75	67	60	54	58	52	48	49	45	42	42	38	36
4	74	63	55	48	69	59	51	46	51	45	41	44	39	36	37	34	31
5	68	56	48	41	63	52	45	39	46	40	35	39	34	31	33	30	27
6	63	50	42	36	58	47	39	34	41	35	30	35	31	27	30	26	23
7	58	45	37	31	54	43	35	30	37	31	27	32	27	24	27	24	21
8	54	41	33	28	50	39	31	26	34	28	24	29	25	21	25	21	19
9	50	38	30	25	47	35	28	23	31	25	21	27	22	19	23	19	17
10	47	34	27	22	44	32	26	21	29	23	19	25	20	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9818	9818	9818
5°	9834	9612	9636
10°	9760	9416	9389
15°	9642	9188	9086
20°	9481	8913	8786
25°	9291	8619	8421
30°	9061	8300	8091
35°	8846	8005	7785
40°	8627	7695	7478
45°	8380	7426	7201
50°	8143	7133	6952
55°	7858	6855	6662
60°	7546	6537	6365
65°	7220	6203	6031
70°	6847	5755	5683
75°	6258	5313	5258
80°	5487	4774	4788
85°	4723	4345	4541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8380 cd/sqm

TEST NUMBER: P1026823

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	1.9
10°-20°	411.6	5.3
20°-30°	612.1	7.9
30°-40°	724.9	9.3
40°-50°	749.5	9.6
50°-60°	690.4	8.9
60°-70°	558.1	7.2
70°-80°	373.4	4.8
80°-90°	194.5	2.5
90°-100°	142.4	1.8
100°-110°	303.8	3.9
110°-120°	456.3	5.9
120°-130°	547.3	7.0
130°-140°	569.2	7.3
140°-150°	524.4	6.7
150°-160°	422.0	5.4
160°-170°	272.9	3.5
170°-180°	94.1	1.2
0°-30°	1168.8	15.0
0°-40°	1893.7	24.3
0°-60°	3333.6	42.8
0°-90°	4459.6	57.2
90°-120°	902.4	11.6
90°-150°	2543.3	32.6
90°-180°	3332.0	42.8
0°-180°	7792.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1532	1532	1532	1532	1532	
5°	1532	1529	1519	1531	1529	145
15°	1463	1465	1454	1463	1457	412
25°	1330	1334	1325	1331	1324	612
35°	1151	1161	1157	1161	1161	720
45°	948	964	972	982	984	731
55°	729	753	777	793	799	651
65°	502	536	572	595	601	498
75°	276	316	364	394	401	293
85°	83	132	185	218	230	86
90°	25	79	135	173	186	19
95°	61	98	122	158	169	67
105°	229	256	302	332	341	243
115°	414	429	468	492	497	411
125°	583	586	616	637	643	520
135°	722	725	734	752	755	557
145°	835	835	835	843	845	522
155°	918	914	915	917	912	423
165°	969	964	965	970	964	274
175°	991	986	987	993	986	94
180°	991	991	991	991	991	

TEST NUMBER: P1026823

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1532.4	1532.4	1532.4	1532.4	1532.4
2.5°	1536.9	1533.9	1523.4	1533.9	1532.4
5°	1532.4	1529.4	1518.8	1530.9	1529.4
7.5°	1521.8	1520.3	1509.8	1520.3	1518.8
10°	1506.8	1506.8	1494.8	1505.3	1503.8
12.5°	1485.8	1487.3	1478.3	1485.8	1481.3
15°	1463.3	1464.8	1454.2	1463.3	1457.2
17.5°	1434.7	1437.7	1427.2	1434.7	1430.2
20°	1403.2	1406.2	1395.7	1400.2	1400.2
22.5°	1367.1	1373.1	1361.1	1367.1	1362.6
25°	1329.6	1334.1	1325.0	1331.1	1323.5
27.5°	1289.0	1295.0	1284.5	1289.0	1286.0
30°	1242.4	1251.4	1242.4	1245.4	1243.9
32.5°	1200.4	1207.9	1201.9	1204.9	1203.4
35°	1150.8	1161.3	1156.8	1161.3	1161.3
37.5°	1102.7	1111.7	1110.2	1116.2	1114.7
40°	1053.1	1065.1	1063.6	1069.7	1072.7
42.5°	999.0	1015.6	1020.1	1027.6	1027.6
45°	948.0	964.5	972.0	982.5	984.0
47.5°	895.4	910.4	922.4	937.4	940.5
50°	841.3	857.8	874.3	890.9	895.4
52.5°	784.2	805.2	826.3	844.3	847.3
55°	728.6	752.7	776.7	793.2	799.2
57.5°	671.5	700.1	727.1	745.2	749.7
60°	614.4	644.5	674.5	697.1	701.6
62.5°	558.9	588.9	622.0	647.5	653.5
65°	501.8	536.3	572.4	594.9	600.9
67.5°	449.2	482.2	518.3	545.3	552.9
70°	390.6	425.2	464.2	492.8	501.8
72.5°	333.5	369.6	413.1	444.7	450.7
75°	276.4	315.5	363.6	393.6	401.1
77.5°	220.8	265.9	311.0	344.0	350.0
80°	169.8	214.8	265.9	299.0	305.0
82.5°	123.2	171.3	223.8	255.4	267.4
85°	82.6	132.2	184.8	217.8	229.9
87.5°	52.6	100.7	151.7	186.3	196.8
90°	24.7	78.7	135.0	173.1	185.9
92.5°	35.0	71.9	129.0	165.6	176.9
95°	61.4	98.3	121.5	158.1	168.6
97.5°	96.6	137.1	116.9	149.9	161.1
100°	139.2	173.0	223.9	146.1	152.1
102.5°	182.5	214.0	262.0	293.5	240.8
105°	229.4	256.5	301.5	331.6	341.3
107.5°	277.9	299.0	343.9	374.8	380.8
110°	324.9	342.9	386.4	412.8	424.1



TEST NUMBER: P1026823

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.4	386.1	427.4	451.5	460.6
115°	414.4	428.6	468.4	492.5	497.1
117.5°	460.7	468.2	508.7	529.8	538.8
120°	504.7	508.5	545.3	569.3	574.7
122.5°	542.2	547.3	581.2	603.7	608.3
125°	582.6	586.2	616.3	637.4	642.7
127.5°	620.0	622.2	646.9	668.1	671.2
130°	655.2	657.4	679.1	698.0	701.9
132.5°	689.0	693.4	706.2	727.3	729.6
135°	722.0	725.0	734.0	752.0	755.2
137.5°	752.9	755.8	760.3	778.3	780.7
140°	781.5	783.0	783.7	801.7	803.3
142.5°	808.7	807.9	809.4	822.9	824.5
145°	835.1	835.1	835.1	843.3	844.9
147.5°	857.1	857.1	857.9	861.6	859.5
150°	879.2	877.7	879.2	880.6	876.3
152.5°	900.5	896.8	898.3	899.7	894.6
155°	918.1	913.7	915.2	917.4	911.5
157.5°	932.0	929.8	929.8	932.0	926.2
160°	946.7	942.3	943.1	946.0	940.1
162.5°	958.5	954.1	954.8	959.2	952.6
165°	968.8	964.4	965.1	969.5	963.6
167.5°	976.8	972.4	973.2	978.3	971.7
170°	983.5	978.3	979.0	984.9	978.3
172.5°	987.9	982.7	984.2	989.3	982.7
175°	990.8	986.4	987.1	993.0	986.4
177.5°	993.0	988.6	989.3	994.5	988.6
180°	990.8	990.8	990.8	990.8	990.8

(END OF REPORT)