

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026827

Luminaire Tested: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026827
REPORT IS A COMBINATION OF REPORTS P1001781 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8260.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026827

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026827

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12582	12582	12582
5°	12582	12289	12313
10°	12478	12008	11970
15°	12314	11671	11566
20°	12093	11280	11103
25°	11855	10854	10607
30°	11568	10410	10084
35°	11262	9944	9498
40°	10945	9452	8978
45°	10602	8973	8425
50°	10225	8429	7780
55°	9852	7829	7187
60°	9407	7197	6498
65°	8875	6465	5785
70°	8333	5623	4961
75°	7422	4630	4011
80°	6324	3458	2951
85°	4883	2046	1626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10602 cd/sqm

TEST NUMBER: P1026827

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.3	2.2
10°-20°	523.4	6.3
20°-30°	772.7	9.4
30°-40°	901.5	10.9
40°-50°	905.5	11.0
50°-60°	794.8	9.6
60°-70°	592.0	7.2
70°-80°	338.1	4.1
80°-90°	99.1	1.2
90°-100°	34.8	0.4
100°-110°	231.2	2.8
110°-120°	416.4	5.0
120°-130°	534.5	6.5
130°-140°	574.9	7.0
140°-150°	539.6	6.5
150°-160°	436.4	5.3
160°-170°	282.3	3.4
170°-180°	97.3	1.2
0°-30°	1481.4	17.9
0°-40°	2383.0	28.8
0°-60°	4083.2	49.4
0°-90°	5112.5	61.9
90°-120°	682.5	8.3
90°-150°	2331.4	28.2
90°-180°	3147.0	38.1
0°-180°	8260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1961	1958	1942	1956	1954	186
15°	1869	1864	1847	1855	1855	527
25°	1696	1689	1668	1672	1667	781
35°	1465	1459	1437	1429	1417	916
45°	1199	1193	1174	1156	1151	924
55°	914	909	887	873	862	815
65°	617	614	597	583	576	612
75°	328	325	317	312	306	349
85°	85	87	87	85	82	94
90°	1	7	12	16	18	8
95°	43	41	12	16	16	53
105°	223	226	226	226	226	237
115°	419	423	424	421	416	416
125°	596	602	602	598	596	533
135°	744	748	747	745	741	573
145°	862	864	864	864	860	539
155°	949	945	946	949	943	437
165°	1002	997	998	1003	996	283
175°	1025	1020	1021	1027	1020	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1026827

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1963.7	1963.7	1963.7	1963.7	1963.7
2.5°	1969.9	1965.2	1949.7	1965.2	1963.7
5°	1960.6	1957.5	1941.9	1955.9	1954.4
7.5°	1946.6	1943.5	1926.4	1940.4	1938.8
10°	1926.4	1923.3	1906.2	1918.6	1917.1
12.5°	1901.5	1895.3	1879.8	1889.1	1889.1
15°	1868.9	1864.3	1847.2	1854.9	1854.9
17.5°	1834.7	1827.0	1809.9	1819.2	1811.4
20°	1789.7	1786.6	1766.4	1777.3	1769.5
22.5°	1744.6	1738.4	1719.8	1726.0	1721.3
25°	1696.5	1688.7	1668.5	1671.6	1667.0
27.5°	1640.6	1635.9	1615.7	1617.2	1612.6
30°	1586.2	1581.5	1558.2	1555.1	1550.4
32.5°	1527.1	1519.4	1499.2	1493.0	1483.6
35°	1465.0	1458.8	1437.0	1429.3	1416.8
37.5°	1401.3	1393.5	1373.3	1362.5	1354.7
40°	1336.1	1328.3	1306.5	1292.6	1287.9
42.5°	1266.1	1259.9	1238.2	1225.8	1218.0
45°	1199.3	1193.1	1174.5	1155.8	1151.2
47.5°	1126.3	1127.9	1104.6	1085.9	1075.1
50°	1056.4	1051.8	1033.1	1012.9	1002.0
52.5°	985.0	981.8	961.6	944.6	932.1
55°	913.5	908.8	887.1	873.1	862.2
57.5°	837.4	835.8	817.2	798.5	793.9
60°	765.9	759.7	742.6	727.1	716.2
62.5°	691.3	686.7	672.7	655.6	647.8
65°	616.8	613.7	596.6	582.6	576.4
67.5°	543.7	537.5	525.1	512.7	509.6
70°	475.4	467.6	453.6	444.3	438.1
72.5°	400.8	396.2	388.4	377.5	371.3
75°	327.8	324.7	316.9	312.3	306.0
77.5°	259.4	257.9	253.2	250.1	245.5
80°	195.7	195.7	192.6	191.1	188.0
82.5°	139.8	136.7	136.7	133.6	133.6
85°	85.4	87.0	87.0	85.4	82.3
87.5°	41.9	41.9	40.4	40.4	37.3
90°	0.8	6.8	12.2	16.0	18.2
92.5°	14.4	7.6	12.2	16.0	16.7
95°	43.3	41.0	12.2	16.0	16.0
97.5°	81.3	85.8	13.7	15.2	16.0
100°	126.8	129.1	132.2	19.0	16.0
102.5°	173.2	176.2	177.7	179.3	115.5
105°	223.3	226.3	226.3	226.3	225.6
107.5°	275.0	275.0	276.5	277.2	274.2
110°	325.1	325.1	326.6	324.3	325.1



TEST NUMBER: P1026827

CATALOG NUMBER: S125DIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.2	374.5	375.2	372.2	370.7
115°	419.3	423.1	423.8	420.8	416.2
117.5°	468.6	468.6	471.7	467.1	465.6
120°	514.2	513.5	515.7	514.2	510.4
122.5°	554.5	558.3	559.0	557.5	553.0
125°	596.3	601.6	601.6	598.5	596.3
127.5°	636.5	640.3	639.5	638.0	632.0
130°	673.0	676.8	677.5	675.2	671.4
132.5°	709.4	714.0	711.7	711.7	707.9
135°	743.6	748.2	746.6	745.1	740.6
137.5°	775.5	780.1	778.5	778.5	774.7
140°	806.6	808.2	807.4	808.9	804.4
142.5°	834.8	835.5	837.0	837.0	832.5
145°	862.1	863.6	863.6	864.4	859.8
147.5°	886.4	886.4	887.2	887.9	882.6
150°	909.2	907.7	909.2	910.7	904.6
152.5°	931.2	927.4	928.9	930.5	925.1
155°	949.4	944.9	946.4	948.7	942.6
157.5°	963.9	961.6	961.6	963.9	957.8
160°	979.1	974.5	975.3	978.3	972.2
162.5°	991.2	986.7	987.4	992.0	985.1
165°	1001.9	997.3	998.1	1002.6	996.5
167.5°	1010.2	1005.7	1006.4	1011.7	1004.9
170°	1017.0	1011.7	1012.5	1018.6	1011.7
172.5°	1021.6	1016.3	1017.8	1023.1	1016.3
175°	1024.6	1020.1	1020.8	1026.9	1020.1
177.5°	1026.9	1022.4	1023.1	1028.4	1022.4
180°	1024.6	1024.6	1024.6	1024.6	1024.6

(END OF REPORT)