

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007624

Luminaire Tested: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K
Description: Define 4 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3563.0 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007624

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007624

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007624

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	83.6	2.3
100°-110°	250.5	7.0
110°-120°	425.6	11.9
120°-130°	561.3	15.8
130°-140°	630.4	17.7
140°-150°	619.6	17.4
150°-160°	521.1	14.6
160°-170°	346.7	9.7
170°-180°	121.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	759.7	21.3
90°-150°	2571.0	72.2
90°-180°	3560.0	99.9
0°-180°	3563.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	14	22	28	30	4
95°	60	68	75	78	78	64
105°	231	232	236	239	242	245
115°	433	433	431	430	429	427
125°	630	630	629	627	625	562
135°	813	819	819	817	814	629
145°	987	991	992	991	988	618
155°	1131	1131	1130	1134	1130	521
165°	1232	1229	1227	1232	1229	347
175°	1281	1276	1275	1282	1275	122
180°	1283	1283	1283	1283	1283	

TEST NUMBER: P1007624

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.0	13.9	21.8	27.8	29.8
92.5°	25.8	38.7	43.7	46.6	47.6
95°	59.5	68.5	75.4	78.4	78.4
97.5°	95.3	103.2	111.1	115.1	115.1
100°	138.9	142.9	151.8	153.8	153.8
102.5°	184.6	185.6	193.5	196.5	197.5
105°	231.2	232.2	236.2	239.2	242.1
107.5°	279.9	280.8	281.8	285.8	284.8
110°	329.5	331.5	330.5	328.5	331.5

TEST NUMBER: P1007624

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.1	381.1	379.1	379.1	379.1
115°	432.7	432.7	430.7	429.7	428.7
117.5°	481.3	481.3	480.3	477.3	474.4
120°	529.9	533.9	530.9	526.0	527.9
122.5°	580.5	581.5	580.5	577.6	572.6
125°	630.2	630.2	629.2	627.2	625.2
127.5°	674.8	677.8	675.8	673.8	672.8
130°	722.5	725.4	725.4	723.4	719.5
132.5°	771.1	773.1	772.1	770.1	769.1
135°	812.8	818.7	818.7	816.7	813.8
137.5°	859.4	862.4	864.4	861.4	862.4
140°	906.0	908.0	908.0	907.0	906.0
142.5°	948.7	950.7	949.7	949.7	949.7
145°	987.4	991.4	992.4	991.4	988.4
147.5°	1027.1	1032.1	1031.1	1030.1	1029.1
150°	1062.8	1066.8	1066.8	1066.8	1065.8
152.5°	1096.6	1098.6	1099.6	1102.5	1099.6
155°	1131.3	1131.3	1130.3	1134.3	1130.3
157.5°	1161.1	1159.1	1159.1	1162.1	1159.1
160°	1186.9	1185.9	1184.9	1187.9	1182.9
162.5°	1210.7	1207.7	1206.7	1212.7	1207.7
165°	1231.5	1228.6	1226.6	1232.5	1228.6
167.5°	1248.4	1244.4	1244.4	1250.4	1244.4
170°	1262.3	1257.3	1258.3	1264.3	1257.3
172.5°	1272.2	1268.3	1268.3	1275.2	1268.3
175°	1281.2	1276.2	1275.2	1282.2	1275.2
177.5°	1285.1	1280.2	1280.2	1287.1	1279.2
180°	1283.1	1283.1	1283.1	1283.1	1283.1

(END OF REPORT)