

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026842

Luminaire Tested: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026842
REPORT IS A COMBINATION OF REPORTS P1001841 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5547.0 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026842

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026842

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35			27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29			22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24			19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21			16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18			14
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	16			12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14			10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12			9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11			8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10			7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3624	3624	3624
5°	3624	3540	3546
10°	3594	3458	3447
15°	3547	3361	3331
20°	3482	3249	3198
25°	3414	3126	3055
30°	3331	2998	2904
35°	3243	2864	2736
40°	3152	2722	2586
45°	3053	2585	2426
50°	2945	2427	2241
55°	2838	2255	2070
60°	2709	2073	1872
65°	2555	1862	1666
70°	2400	1620	1429
75°	2137	1334	1155
80°	1823	996	849
85°	1407	590	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3053 cd/sqm

TEST NUMBER: P1026842

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.0
10°-20°	150.7	2.7
20°-30°	222.5	4.0
30°-40°	259.6	4.7
40°-50°	260.8	4.7
50°-60°	228.9	4.1
60°-70°	170.5	3.1
70°-80°	97.4	1.8
80°-90°	30.1	0.5
90°-100°	45.0	0.8
100°-110°	299.2	5.4
110°-120°	538.9	9.7
120°-130°	691.7	12.5
130°-140°	744.0	13.4
140°-150°	698.2	12.6
150°-160°	564.8	10.2
160°-170°	365.3	6.6
170°-180°	126.0	2.3
0°-30°	426.7	7.7
0°-40°	686.3	12.4
0°-60°	1176.0	21.2
0°-90°	1474.0	26.6
90°-120°	883.1	15.9
90°-150°	3017.0	54.4
90°-180°	4073.0	73.4
0°-180°	5547.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	565	564	559	563	563	54
15°	538	537	532	534	534	152
25°	489	486	480	481	480	225
35°	422	420	414	412	408	264
45°	345	344	338	333	332	266
55°	263	262	256	252	248	235
65°	178	177	172	168	166	176
75°	94	94	91	90	88	100
85°	25	25	25	25	24	27
90°	1	9	16	21	24	4
95°	56	53	16	21	21	69
105°	289	293	293	293	292	306
115°	543	548	548	544	539	538
125°	772	778	778	774	772	689
135°	962	968	966	964	958	742
145°	1116	1118	1118	1119	1113	698
155°	1229	1223	1225	1228	1220	566
165°	1296	1291	1292	1297	1290	366
175°	1326	1320	1321	1329	1320	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1026842

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	565.6	565.6	565.6	565.6	565.6
2.5°	567.3	566.0	561.5	566.0	565.6
5°	564.7	563.8	559.3	563.3	562.9
7.5°	560.6	559.7	554.8	558.8	558.4
10°	554.8	553.9	549.0	552.6	552.1
12.5°	547.7	545.9	541.4	544.1	544.1
15°	538.3	536.9	532.0	534.2	534.2
17.5°	528.4	526.2	521.3	523.9	521.7
20°	515.4	514.5	508.7	511.9	509.6
22.5°	502.5	500.7	495.3	497.1	495.8
25°	488.6	486.4	480.5	481.4	480.1
27.5°	472.5	471.1	465.3	465.8	464.4
30°	456.8	455.5	448.8	447.9	446.5
32.5°	439.8	437.6	431.8	430.0	427.3
35°	421.9	420.1	413.9	411.6	408.1
37.5°	403.6	401.3	395.5	392.4	390.2
40°	384.8	382.6	376.3	372.3	370.9
42.5°	364.7	362.9	356.6	353.0	350.8
45°	345.4	343.6	338.3	332.9	331.5
47.5°	324.4	324.8	318.1	312.8	309.6
50°	304.3	302.9	297.5	291.7	288.6
52.5°	283.7	282.8	277.0	272.0	268.5
55°	263.1	261.7	255.5	251.5	248.3
57.5°	241.2	240.7	235.3	230.0	228.6
60°	220.6	218.8	213.9	209.4	206.3
62.5°	199.1	197.8	193.7	188.8	186.6
65°	177.6	176.7	171.8	167.8	166.0
67.5°	156.6	154.8	151.2	147.7	146.8
70°	136.9	134.7	130.7	128.0	126.2
72.5°	115.4	114.1	111.9	108.7	106.9
75°	94.4	93.5	91.3	89.9	88.1
77.5°	74.7	74.3	72.9	72.0	70.7
80°	56.4	56.4	55.5	55.0	54.1
82.5°	40.3	39.4	39.4	38.5	38.5
85°	24.6	25.1	25.1	24.6	23.7
87.5°	12.1	12.1	11.6	11.6	10.7
90°	1.0	8.8	15.7	20.6	23.6
92.5°	18.7	9.8	15.7	20.6	21.6
95°	56.0	53.1	15.7	20.6	20.6
97.5°	105.2	111.1	17.7	19.7	20.6
100°	164.1	167.1	171.0	24.6	20.6
102.5°	224.1	228.0	230.0	232.0	149.4
105°	289.0	292.9	292.9	292.9	291.9
107.5°	355.8	355.8	357.8	358.8	354.8
110°	420.7	420.7	422.7	419.7	420.7

TEST NUMBER: P1026842

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	481.6	484.6	485.6	481.6	479.7
115°	542.6	547.5	548.5	544.5	538.6
117.5°	606.5	606.5	610.4	604.5	602.5
120°	665.4	664.4	667.4	665.4	660.5
122.5°	717.5	722.4	723.4	721.5	715.6
125°	771.6	778.5	778.5	774.5	771.6
127.5°	823.7	828.6	827.6	825.6	817.8
130°	870.9	875.8	876.8	873.8	868.9
132.5°	918.0	923.9	921.0	921.0	916.1
135°	962.3	968.2	966.2	964.2	958.3
137.5°	1003.6	1009.5	1007.5	1007.5	1002.6
140°	1043.9	1045.8	1044.8	1046.8	1040.9
142.5°	1080.2	1081.2	1083.2	1083.2	1077.3
145°	1115.6	1117.6	1117.6	1118.6	1112.7
147.5°	1147.1	1147.1	1148.0	1149.0	1142.1
150°	1176.5	1174.6	1176.5	1178.5	1170.6
152.5°	1205.1	1200.1	1202.1	1204.1	1197.2
155°	1228.6	1222.7	1224.7	1227.7	1219.8
157.5°	1247.3	1244.4	1244.4	1247.3	1239.5
160°	1267.0	1261.1	1262.1	1266.0	1258.1
162.5°	1282.7	1276.8	1277.8	1283.7	1274.8
165°	1296.5	1290.6	1291.5	1297.4	1289.6
167.5°	1307.3	1301.4	1302.4	1309.2	1300.4
170°	1316.1	1309.2	1310.2	1318.1	1309.2
172.5°	1322.0	1315.1	1317.1	1324.0	1315.1
175°	1325.9	1320.1	1321.0	1328.9	1320.1
177.5°	1328.9	1323.0	1324.0	1330.9	1323.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)