

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007636

Luminaire Tested: S124IP-B1035UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1035UB2750-4F0-XX-W2A_5000K
Description: Define 4 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3934.0 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007636

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007636

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007636

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	42.2	1.1
100°-110°	277.7	7.1
110°-120°	530.3	13.5
120°-130°	673.3	17.1
130°-140°	720.3	18.3
140°-150°	673.5	17.1
150°-160°	543.1	13.8
160°-170°	350.3	8.9
170°-180°	120.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	850.3	21.6
90°-150°	2917.3	74.2
90°-180°	3931.0	99.9
0°-180°	3934.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	13	21	27	28	3
95°	52	20	21	27	28	64
105°	286	292	296	305	271	299
115°	534	537	536	538	538	526
125°	751	754	753	756	756	670
135°	931	930	934	936	938	718
145°	1074	1077	1077	1078	1080	671
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1007636

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.9	13.3	20.9	26.6	28.5
92.5°	14.3	12.4	20.0	25.7	25.7
95°	52.3	20.0	20.9	26.6	27.6
97.5°	99.8	120.7	20.9	25.7	26.6
100°	155.8	172.9	41.8	25.7	26.6
102.5°	218.6	230.0	241.4	27.6	27.6
105°	286.0	291.7	296.5	305.0	270.8
107.5°	347.8	350.6	357.3	362.0	365.9
110°	410.5	413.4	419.1	421.0	423.8

TEST NUMBER: P1007636

CATALOG NUMBER: S124IP-B1035UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.3	477.0	478.9	478.0	481.8
115°	534.0	536.9	535.9	537.8	537.8
117.5°	590.1	593.9	596.8	595.8	595.8
120°	647.1	650.9	650.0	651.9	650.0
122.5°	700.3	702.2	704.1	705.1	703.2
125°	750.7	754.5	752.6	755.5	756.4
127.5°	799.2	800.1	804.9	803.9	803.0
130°	845.7	846.7	849.5	850.5	850.5
132.5°	888.5	890.4	894.2	895.1	894.2
135°	931.3	930.3	934.1	936.0	937.9
137.5°	969.3	969.3	974.0	975.9	975.0
140°	1006.3	1008.2	1010.1	1013.0	1013.9
142.5°	1039.6	1043.4	1044.3	1046.2	1046.2
145°	1073.8	1076.6	1076.6	1077.6	1079.5
147.5°	1100.4	1106.1	1105.2	1106.1	1107.1
150°	1129.9	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)