

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026856

Luminaire Tested: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026856
REPORT IS A COMBINATION OF REPORTS P1001900 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6322.0 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026856

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026856

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	76	71	66	74	68	63	59	52	49	46	38	36	34	25	23	22
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19
4	70	59	52	46	62	53	47	42	41	36	33	30	27	25	19	18	16
5	64	53	45	39	56	47	40	35	36	32	28	27	24	21	17	16	14
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	12
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	28	22	18	22	18	15	17	14	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3658	3658	3658
5°	3658	3573	3580
10°	3628	3491	3480
15°	3580	3393	3363
20°	3516	3280	3228
25°	3446	3156	3084
30°	3364	3026	2932
35°	3274	2891	2761
40°	3183	2748	2610
45°	3083	2609	2450
50°	2973	2451	2262
55°	2865	2276	2090
60°	2735	2092	1889
65°	2580	1879	1682
70°	2423	1635	1443
75°	2158	1346	1167
80°	1839	1005	859
85°	1418	595	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3083 cd/sqm

TEST NUMBER: P1026856

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	0.9
10°-20°	152.2	2.4
20°-30°	224.7	3.6
30°-40°	262.1	4.1
40°-50°	263.3	4.2
50°-60°	231.1	3.7
60°-70°	172.1	2.7
70°-80°	98.3	1.6
80°-90°	30.7	0.5
90°-100°	53.4	0.8
100°-110°	355.1	5.6
110°-120°	639.5	10.1
120°-130°	820.9	13.0
130°-140°	882.9	14.0
140°-150°	828.6	13.1
150°-160°	670.3	10.6
160°-170°	433.5	6.9
170°-180°	149.5	2.4
0°-30°	430.7	6.8
0°-40°	692.8	11.0
0°-60°	1187.2	18.8
0°-90°	1488.3	23.5
90°-120°	1048.1	16.6
90°-150°	3580.4	56.6
90°-180°	4834.0	76.5
0°-180°	6322.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	571	571	571	571	571	
5°	570	569	565	569	568	54
15°	543	542	537	539	539	153
25°	493	491	485	486	485	227
35°	426	424	418	416	412	266
45°	349	347	342	336	335	269
55°	266	264	258	254	251	237
65°	179	178	173	169	168	178
75°	95	94	92	91	89	101
85°	25	25	25	25	24	27
90°	1	10	19	24	28	5
95°	66	63	19	24	24	81
105°	343	348	348	348	346	363
115°	644	650	651	646	639	638
125°	916	924	924	919	916	818
135°	1142	1149	1147	1144	1137	880
145°	1324	1326	1326	1327	1320	828
155°	1458	1451	1453	1457	1448	672
165°	1539	1532	1533	1540	1530	435
175°	1574	1567	1568	1577	1567	150
180°	1574	1574	1574	1574	1574	

TEST NUMBER: P1026856

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.9	570.9	570.9	570.9	570.9
2.5°	572.7	571.4	566.9	571.4	570.9
5°	570.0	569.1	564.6	568.7	568.2
7.5°	566.0	565.1	560.1	564.2	563.7
10°	560.1	559.2	554.2	557.8	557.4
12.5°	552.9	551.1	546.5	549.3	549.3
15°	543.4	542.0	537.1	539.3	539.3
17.5°	533.4	531.2	526.2	528.9	526.7
20°	520.3	519.4	513.6	516.7	514.5
22.5°	507.2	505.4	500.0	501.8	500.5
25°	493.2	491.0	485.1	486.0	484.7
27.5°	477.0	475.6	469.8	470.2	468.9
30°	461.2	459.8	453.0	452.1	450.8
32.5°	444.0	441.8	435.9	434.1	431.4
35°	425.9	424.1	417.8	415.6	411.9
37.5°	407.4	405.2	399.3	396.1	393.9
40°	388.5	386.2	379.9	375.8	374.4
42.5°	368.1	366.3	360.0	356.4	354.1
45°	348.7	346.9	341.5	336.1	334.7
47.5°	327.5	327.9	321.2	315.7	312.6
50°	307.1	305.8	300.4	294.5	291.3
52.5°	286.4	285.5	279.6	274.6	271.0
55°	265.6	264.2	257.9	253.8	250.7
57.5°	243.5	243.0	237.6	232.2	230.8
60°	222.7	220.9	215.9	211.4	208.2
62.5°	201.0	199.6	195.6	190.6	188.4
65°	179.3	178.4	173.4	169.4	167.6
67.5°	158.1	156.3	152.7	149.1	148.2
70°	138.2	136.0	131.9	129.2	127.4
72.5°	116.5	115.2	112.9	109.8	108.0
75°	95.3	94.4	92.1	90.8	89.0
77.5°	75.4	75.0	73.6	72.7	71.4
80°	56.9	56.9	56.0	55.6	54.7
82.5°	40.7	39.7	39.7	38.8	38.8
85°	24.8	25.3	25.3	24.8	23.9
87.5°	12.2	12.2	11.7	11.7	10.8
90°	1.2	10.5	18.7	24.5	28.0
92.5°	22.2	11.7	18.7	24.5	25.7
95°	66.5	63.0	18.7	24.5	24.5
97.5°	124.8	131.8	21.0	23.3	24.5
100°	194.8	198.3	203.0	29.2	24.5
102.5°	266.0	270.6	273.0	275.3	177.3
105°	342.9	347.6	347.6	347.6	346.4
107.5°	422.3	422.3	424.6	425.8	421.1
110°	499.2	499.2	501.6	498.1	499.2

TEST NUMBER: P1026856

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.6	575.1	576.2	571.6	569.2
115°	643.9	649.7	650.9	646.2	639.2
117.5°	719.7	719.7	724.4	717.4	715.0
120°	789.7	788.5	792.0	789.7	783.9
122.5°	851.5	857.4	858.5	856.2	849.2
125°	915.7	923.8	923.8	919.2	915.7
127.5°	977.5	983.3	982.2	979.8	970.5
130°	1033.5	1039.3	1040.5	1037.0	1031.2
132.5°	1089.5	1096.5	1093.0	1093.0	1087.1
135°	1142.0	1149.0	1146.6	1144.3	1137.3
137.5°	1191.0	1198.0	1195.6	1195.6	1189.8
140°	1238.8	1241.1	1240.0	1242.3	1235.3
142.5°	1281.9	1283.1	1285.4	1285.4	1278.5
145°	1323.9	1326.3	1326.3	1327.4	1320.4
147.5°	1361.3	1361.3	1362.4	1363.6	1355.4
150°	1396.3	1393.9	1396.3	1398.6	1389.3
152.5°	1430.1	1424.3	1426.6	1428.9	1420.8
155°	1458.1	1451.1	1453.4	1456.9	1447.6
157.5°	1480.2	1476.8	1476.8	1480.2	1470.9
160°	1503.6	1496.6	1497.7	1502.4	1493.1
162.5°	1522.2	1515.2	1516.4	1523.4	1512.9
165°	1538.6	1531.6	1532.7	1539.7	1530.4
167.5°	1551.4	1544.4	1545.6	1553.7	1543.2
170°	1561.9	1553.7	1554.9	1564.2	1553.7
172.5°	1568.9	1560.7	1563.1	1571.2	1560.7
175°	1573.6	1566.6	1567.7	1577.1	1566.6
177.5°	1577.1	1570.1	1571.2	1579.4	1570.1
180°	1573.6	1573.6	1573.6	1573.6	1573.6

(END OF REPORT)