

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026858

Luminaire Tested: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026858
REPORT IS A COMBINATION OF REPORTS P1001902 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6053.0 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026858

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026858

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	76	71	66	74	68	63	59	52	49	46	38	36	34	25	23	22
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19
4	70	59	52	46	62	53	47	42	41	36	33	30	27	25	19	18	16
5	64	53	45	39	56	47	40	35	36	32	28	27	24	21	17	16	14
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	12
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	28	22	18	22	18	15	17	14	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2952 cd/sqm

TEST NUMBER: P1026858

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	0.9
10°-20°	145.7	2.4
20°-30°	215.1	3.6
30°-40°	251.0	4.1
40°-50°	252.1	4.2
50°-60°	221.3	3.7
60°-70°	164.8	2.7
70°-80°	94.1	1.6
80°-90°	29.4	0.5
90°-100°	51.2	0.8
100°-110°	340.0	5.6
110°-120°	612.3	10.1
120°-130°	785.9	13.0
130°-140°	845.3	14.0
140°-150°	793.3	13.1
150°-160°	641.7	10.6
160°-170°	415.0	6.9
170°-180°	143.1	2.4
0°-30°	412.5	6.8
0°-40°	663.5	11.0
0°-60°	1136.8	18.8
0°-90°	1425.2	23.5
90°-120°	1003.5	16.6
90°-150°	3428.0	56.6
90°-180°	4628.0	76.5
0°-180°	6053.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	1	10	18	24	27	5
95°	64	60	18	24	24	78
105°	328	333	333	333	332	348
115°	616	622	623	619	612	611
125°	877	884	884	880	877	783
135°	1093	1100	1098	1096	1089	843
145°	1268	1270	1270	1271	1264	793
155°	1396	1389	1392	1395	1386	643
165°	1473	1466	1468	1474	1465	416
175°	1506	1500	1501	1510	1500	143
180°	1506	1506	1506	1506	1506	

TEST NUMBER: P1026858

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	1.1	10.1	17.9	23.5	26.8
92.5°	21.2	11.2	17.9	23.5	24.6
95°	63.7	60.3	17.9	23.5	23.5
97.5°	119.5	126.2	20.1	22.3	23.5
100°	186.5	189.9	194.3	27.9	23.5
102.5°	254.6	259.1	261.3	263.6	169.8
105°	328.3	332.8	332.8	332.8	331.7
107.5°	404.3	404.3	406.5	407.6	403.2
110°	478.0	478.0	480.2	476.9	478.0

TEST NUMBER: P1026858

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	547.2	550.6	551.7	547.2	545.0
115°	616.5	622.0	623.2	618.7	612.0
117.5°	689.1	689.1	693.5	686.8	684.6
120°	756.1	754.9	758.3	756.1	750.5
122.5°	815.3	820.8	822.0	819.7	813.0
125°	876.7	884.5	884.5	880.0	876.7
127.5°	935.9	941.4	940.3	938.1	929.2
130°	989.5	995.1	996.2	992.8	987.2
132.5°	1043.1	1049.8	1046.4	1046.4	1040.8
135°	1093.3	1100.0	1097.8	1095.6	1088.9
137.5°	1140.2	1146.9	1144.7	1144.7	1139.1
140°	1186.0	1188.3	1187.1	1189.4	1182.7
142.5°	1227.3	1228.5	1230.7	1230.7	1224.0
145°	1267.5	1269.8	1269.8	1270.9	1264.2
147.5°	1303.3	1303.3	1304.4	1305.5	1297.7
150°	1336.8	1334.6	1336.8	1339.0	1330.1
152.5°	1369.2	1363.6	1365.8	1368.1	1360.2
155°	1396.0	1389.3	1391.5	1394.9	1385.9
157.5°	1417.2	1413.8	1413.8	1417.2	1408.3
160°	1439.5	1432.8	1433.9	1438.4	1429.5
162.5°	1457.4	1450.7	1451.8	1458.5	1448.5
165°	1473.0	1466.3	1467.5	1474.2	1465.2
167.5°	1485.3	1478.6	1479.7	1487.6	1477.5
170°	1495.4	1487.6	1488.7	1497.6	1487.6
172.5°	1502.1	1494.3	1496.5	1504.3	1494.3
175°	1506.5	1499.8	1501.0	1509.9	1499.8
177.5°	1509.9	1503.2	1504.3	1512.1	1503.2
180°	1506.5	1506.5	1506.5	1506.5	1506.5

(END OF REPORT)