

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007683

Luminaire Tested: S124IP-B365UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B365UB2750-4F0-XX-W2A-1_3000K
Description: Define 4 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1276.0 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007683

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007683

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007683

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	30.0	2.3
100°-110°	89.7	7.0
110°-120°	152.4	11.9
120°-130°	201.0	15.8
130°-140°	225.8	17.7
140°-150°	221.9	17.4
150°-160°	186.6	14.6
160°-170°	124.2	9.7
170°-180°	43.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	272.1	21.3
90°-150°	920.8	72.2
90°-180°	1275.0	99.9
0°-180°	1276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	8	10	11	2
95°	21	24	27	28	28	23
105°	83	83	85	86	87	88
115°	155	155	154	154	154	153
125°	226	226	225	225	224	201
135°	291	293	293	292	291	225
145°	354	355	355	355	354	221
155°	405	405	405	406	405	186
165°	441	440	439	441	440	124
175°	459	457	457	459	457	44
180°	460	460	460	460	460	

TEST NUMBER: P1007683

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	5.0	7.8	10.0	10.7
92.5°	9.2	13.9	15.6	16.7	17.1
95°	21.3	24.5	27.0	28.1	28.1
97.5°	34.1	37.0	39.8	41.2	41.2
100°	49.8	51.2	54.4	55.1	55.1
102.5°	66.1	66.5	69.3	70.4	70.7
105°	82.8	83.2	84.6	85.7	86.7
107.5°	100.2	100.6	100.9	102.4	102.0
110°	118.0	118.7	118.3	117.6	118.7

TEST NUMBER: P1007683

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	136.5	136.5	135.8	135.8	135.8
115°	155.0	155.0	154.2	153.9	153.5
117.5°	172.4	172.4	172.0	170.9	169.9
120°	189.8	191.2	190.1	188.4	189.1
122.5°	207.9	208.3	207.9	206.8	205.1
125°	225.7	225.7	225.3	224.6	223.9
127.5°	241.7	242.7	242.0	241.3	241.0
130°	258.7	259.8	259.8	259.1	257.7
132.5°	276.1	276.9	276.5	275.8	275.4
135°	291.1	293.2	293.2	292.5	291.4
137.5°	307.8	308.8	309.5	308.5	308.8
140°	324.5	325.2	325.2	324.8	324.5
142.5°	339.8	340.5	340.1	340.1	340.1
145°	353.6	355.0	355.4	355.0	354.0
147.5°	367.8	369.6	369.3	368.9	368.5
150°	380.6	382.1	382.1	382.1	381.7
152.5°	392.7	393.4	393.8	394.8	393.8
155°	405.2	405.2	404.8	406.2	404.8
157.5°	415.8	415.1	415.1	416.2	415.1
160°	425.1	424.7	424.3	425.4	423.6
162.5°	433.6	432.5	432.2	434.3	432.5
165°	441.0	440.0	439.3	441.4	440.0
167.5°	447.1	445.7	445.7	447.8	445.7
170°	452.1	450.3	450.6	452.8	450.3
172.5°	455.6	454.2	454.2	456.7	454.2
175°	458.8	457.0	456.7	459.2	456.7
177.5°	460.2	458.5	458.5	460.9	458.1
180°	459.5	459.5	459.5	459.5	459.5

(END OF REPORT)