

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007685

Luminaire Tested: S124IP-B365UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B365UB2750-4F0-XX-W2A-1_4000K
Description: Define 4 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1269.0 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007685

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007685

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007685

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	29.8	2.3
100°-110°	89.2	7.0
110°-120°	151.6	11.9
120°-130°	199.9	15.8
130°-140°	224.5	17.7
140°-150°	220.7	17.4
150°-160°	185.6	14.6
160°-170°	123.5	9.7
170°-180°	43.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	270.6	21.3
90°-150°	915.7	72.2
90°-180°	1268.0	99.9
0°-180°	1269.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	8	10	11	2
95°	21	24	27	28	28	23
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	290	292	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	403	404	403	185
165°	439	438	437	439	438	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1007685

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	4.9	7.8	9.9	10.6
92.5°	9.2	13.8	15.6	16.6	17.0
95°	21.2	24.4	26.9	27.9	27.9
97.5°	33.9	36.8	39.6	41.0	41.0
100°	49.5	50.9	54.1	54.8	54.8
102.5°	65.7	66.1	68.9	70.0	70.3
105°	82.4	82.7	84.1	85.2	86.2
107.5°	99.7	100.0	100.4	101.8	101.4
110°	117.3	118.1	117.7	117.0	118.1

TEST NUMBER: P1007685

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.7	135.7	135.0	135.0	135.0
115°	154.1	154.1	153.4	153.0	152.7
117.5°	171.4	171.4	171.1	170.0	168.9
120°	188.7	190.2	189.1	187.3	188.0
122.5°	206.8	207.1	206.8	205.7	203.9
125°	224.4	224.4	224.1	223.4	222.7
127.5°	240.3	241.4	240.7	240.0	239.6
130°	257.3	258.4	258.4	257.7	256.2
132.5°	274.6	275.3	275.0	274.3	273.9
135°	289.5	291.6	291.6	290.9	289.8
137.5°	306.1	307.1	307.9	306.8	307.1
140°	322.7	323.4	323.4	323.0	322.7
142.5°	337.9	338.6	338.2	338.2	338.2
145°	351.7	353.1	353.4	353.1	352.0
147.5°	365.8	367.6	367.2	366.9	366.5
150°	378.5	380.0	380.0	380.0	379.6
152.5°	390.6	391.3	391.6	392.7	391.6
155°	402.9	402.9	402.6	404.0	402.6
157.5°	413.5	412.8	412.8	413.9	412.8
160°	422.7	422.4	422.0	423.1	421.3
162.5°	431.2	430.1	429.8	431.9	430.1
165°	438.6	437.6	436.9	439.0	437.6
167.5°	444.6	443.2	443.2	445.3	443.2
170°	449.6	447.8	448.2	450.3	447.8
172.5°	453.1	451.7	451.7	454.2	451.7
175°	456.3	454.5	454.2	456.7	454.2
177.5°	457.7	455.9	455.9	458.4	455.6
180°	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)