

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007686

Luminaire Tested: S124IP-B365UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B365UB2750-4F0-XX-W2A-1_5000K
Description: Define 4 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1227.0 lumens
Efficiency: N/A
Efficacy: 131.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007686

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007686

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007686

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.1
90°-100°	28.8	2.3
100°-110°	86.3	7.0
110°-120°	146.5	11.9
120°-130°	193.3	15.8
130°-140°	217.1	17.7
140°-150°	213.4	17.4
150°-160°	179.5	14.6
160°-170°	119.4	9.7
170°-180°	41.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.1
90°-120°	261.6	21.3
90°-150°	885.4	72.2
90°-180°	1226.0	99.9
0°-180°	1227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	8	10	10	1
95°	20	24	26	27	27	22
105°	80	80	81	82	83	84
115°	149	149	148	148	148	147
125°	217	217	217	216	215	193
135°	280	282	282	281	280	217
145°	340	341	342	341	340	213
155°	390	390	389	391	389	179
165°	424	423	422	424	423	120
175°	441	440	439	442	439	42
180°	442	442	442	442	442	

TEST NUMBER: P1007686

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	4.8	7.5	9.6	10.3
92.5°	8.9	13.3	15.0	16.1	16.4
95°	20.5	23.6	26.0	27.0	27.0
97.5°	32.8	35.5	38.3	39.6	39.6
100°	47.8	49.2	52.3	53.0	53.0
102.5°	63.6	63.9	66.6	67.7	68.0
105°	79.6	80.0	81.3	82.4	83.4
107.5°	96.4	96.7	97.1	98.4	98.1
110°	113.5	114.1	113.8	113.1	114.1

TEST NUMBER: P1007686

CATALOG NUMBER: S124IP-B365UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	131.2	131.2	130.5	130.5	130.5
115°	149.0	149.0	148.3	148.0	147.6
117.5°	165.7	165.7	165.4	164.4	163.4
120°	182.5	183.9	182.8	181.1	181.8
122.5°	199.9	200.3	199.9	198.9	197.2
125°	217.0	217.0	216.7	216.0	215.3
127.5°	232.4	233.4	232.7	232.0	231.7
130°	248.8	249.8	249.8	249.1	247.8
132.5°	265.5	266.2	265.9	265.2	264.9
135°	279.9	281.9	281.9	281.3	280.2
137.5°	296.0	297.0	297.7	296.6	297.0
140°	312.0	312.7	312.7	312.4	312.0
142.5°	326.7	327.4	327.1	327.1	327.1
145°	340.0	341.4	341.7	341.4	340.4
147.5°	353.7	355.4	355.1	354.7	354.4
150°	366.0	367.4	367.4	367.4	367.0
152.5°	377.6	378.3	378.7	379.7	378.7
155°	389.6	389.6	389.3	390.6	389.3
157.5°	399.8	399.2	399.2	400.2	399.2
160°	408.7	408.4	408.0	409.1	407.4
162.5°	416.9	415.9	415.6	417.6	415.9
165°	424.1	423.1	422.4	424.5	423.1
167.5°	429.9	428.6	428.6	430.6	428.6
170°	434.7	433.0	433.3	435.4	433.0
172.5°	438.1	436.8	436.8	439.1	436.8
175°	441.2	439.5	439.1	441.5	439.1
177.5°	442.6	440.9	440.9	443.2	440.5
180°	441.9	441.9	441.9	441.9	441.9

(END OF REPORT)