

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026882

Luminaire Tested: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026882
REPORT IS A COMBINATION OF REPORTS P1002016 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3770.0 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026882

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026882

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35		
1	94	89	85	82	85	81	78	75	65	63	60	50	49	47	37	36	35	29		
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	24		
3	78	68	61	55	70	62	55	50	50	45	41	39	35	33	28	26	24	20		
4	71	60	52	46	64	55	48	42	44	39	35	34	31	28	25	23	21	17		
5	65	53	45	39	58	49	41	36	39	34	30	31	27	24	23	20	18	14		
6	60	48	40	34	54	43	36	31	35	30	26	28	24	21	20	18	16	13		
7	55	43	35	30	50	39	32	27	32	27	23	25	21	18	19	16	14	11		
8	51	39	31	26	46	35	29	24	29	24	20	23	19	16	17	14	12	10		
9	47	35	28	23	43	32	26	21	26	21	18	21	17	15	16	13	11	9		
10	44	32	25	21	40	30	23	19	24	19	16	19	16	13	15	12	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2922	2922	2922
5°	2927	2861	2868
10°	2905	2803	2795
15°	2870	2735	2705
20°	2822	2653	2615
25°	2766	2566	2507
30°	2697	2471	2408
35°	2633	2383	2318
40°	2568	2290	2226
45°	2495	2210	2144
50°	2424	2124	2069
55°	2339	2040	1983
60°	2246	1946	1894
65°	2150	1847	1795
70°	2039	1713	1692
75°	1863	1581	1565
80°	1632	1422	1425
85°	1407	1293	1351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2495 cd/sqm

TEST NUMBER: P1026882

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	1.1
10°-20°	122.5	3.3
20°-30°	182.2	4.8
30°-40°	215.8	5.7
40°-50°	223.1	5.9
50°-60°	205.5	5.5
60°-70°	166.1	4.4
70°-80°	111.2	2.9
80°-90°	58.6	1.6
90°-100°	58.4	1.5
100°-110°	196.9	5.2
110°-120°	327.7	8.7
120°-130°	409.1	10.9
130°-140°	434.3	11.5
140°-150°	404.6	10.7
150°-160°	326.7	8.7
160°-170°	211.3	5.6
170°-180°	72.9	1.9
0°-30°	347.9	9.2
0°-40°	563.7	15.0
0°-60°	992.3	26.3
0°-90°	1328.2	35.2
90°-120°	583.0	15.5
90°-150°	1831.0	48.6
90°-180°	2442.0	64.8
0°-180°	3770.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	456	456	456	456	456	
5°	456	455	452	456	455	43
15°	436	436	433	436	434	123
25°	396	397	394	396	394	182
35°	342	346	344	346	346	214
45°	282	287	289	292	293	218
55°	217	224	231	236	238	194
65°	149	160	170	177	179	148
75°	82	94	108	117	119	87
85°	25	39	55	65	68	26
90°	8	27	46	59	64	7
95°	38	48	42	54	58	44
105°	171	181	194	203	206	181
115°	316	322	335	340	340	314
125°	448	452	461	465	466	400
135°	558	560	562	567	566	430
145°	646	646	646	649	648	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	

TEST NUMBER: P1026882

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	456.1	456.1	456.1	456.1	456.1
2.5°	457.5	456.6	453.4	456.6	456.1
5°	456.1	455.2	452.1	455.7	455.2
7.5°	453.0	452.5	449.4	452.5	452.1
10°	448.5	448.5	444.9	448.1	447.6
12.5°	442.3	442.7	440.0	442.3	440.9
15°	435.6	436.0	432.9	435.6	433.8
17.5°	427.1	428.0	424.8	427.1	425.7
20°	417.7	418.6	415.4	416.8	416.8
22.5°	406.9	408.7	405.1	406.9	405.6
25°	395.8	397.1	394.4	396.2	394.0
27.5°	383.7	385.5	382.3	383.7	382.8
30°	369.8	372.5	369.8	370.7	370.3
32.5°	357.3	359.5	357.7	358.6	358.2
35°	342.5	345.7	344.3	345.7	345.7
37.5°	328.2	330.9	330.5	332.3	331.8
40°	313.5	317.1	316.6	318.4	319.3
42.5°	297.4	302.3	303.6	305.9	305.9
45°	282.2	287.1	289.3	292.5	292.9
47.5°	266.5	271.0	274.6	279.0	279.9
50°	250.4	255.3	260.3	265.2	266.5
52.5°	233.4	239.7	246.0	251.3	252.2
55°	216.9	224.0	231.2	236.1	237.9
57.5°	199.9	208.4	216.4	221.8	223.1
60°	182.9	191.8	200.8	207.5	208.8
62.5°	166.4	175.3	185.1	192.7	194.5
65°	149.4	159.6	170.4	177.1	178.9
67.5°	133.7	143.5	154.3	162.3	164.6
70°	116.3	126.6	138.2	146.7	149.4
72.5°	99.3	110.0	123.0	132.4	134.2
75°	82.3	93.9	108.2	117.2	119.4
77.5°	65.7	79.2	92.6	102.4	104.2
80°	50.5	63.9	79.2	89.0	90.8
82.5°	36.7	51.0	66.6	76.0	79.6
85°	24.6	39.4	55.0	64.8	68.4
87.5°	15.7	30.0	45.2	55.5	58.6
90°	7.8	26.6	45.8	58.9	63.7
92.5°	17.1	24.9	44.0	56.6	60.3
95°	38.2	48.1	41.7	54.4	57.5
97.5°	66.2	80.3	41.1	51.6	55.3
100°	99.8	110.9	127.5	52.2	52.6
102.5°	134.1	144.9	159.8	170.0	124.9
105°	171.1	180.6	194.0	202.9	205.6
107.5°	209.4	215.6	229.7	239.2	239.6
110°	246.4	251.8	265.5	272.3	275.9

TEST NUMBER: P1026882

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.7	287.5	300.0	305.9	307.8
115°	316.5	322.5	334.6	340.5	339.7
117.5°	353.0	355.3	368.8	372.9	374.9
120°	387.1	387.9	399.9	406.4	406.1
122.5°	416.8	420.1	430.5	436.5	435.8
125°	448.1	451.6	460.6	465.4	466.0
127.5°	477.7	480.2	487.2	492.8	490.9
130°	505.0	507.5	514.3	518.8	518.3
132.5°	531.9	535.3	538.1	544.3	543.3
135°	557.5	560.4	562.5	567.1	565.9
137.5°	581.4	584.3	584.9	590.3	589.3
140°	604.2	605.3	605.2	611.3	609.7
142.5°	625.2	625.4	626.5	630.5	628.9
145°	645.7	646.4	646.4	649.2	647.6
147.5°	663.5	663.5	664.0	665.5	662.4
150°	680.5	679.4	680.5	681.7	677.5
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)