

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026887

Luminaire Tested: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026887
REPORT IS A COMBINATION OF REPORTS P1002021 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3829.0 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026887

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026887

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	79	76	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	62	57	71	64	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	33	28	24	27	23	20	21	18	16
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14
9	48	36	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3624	3624	3624
5°	3624	3540	3546
10°	3594	3458	3447
15°	3547	3361	3331
20°	3482	3249	3198
25°	3414	3126	3055
30°	3331	2998	2904
35°	3243	2864	2736
40°	3152	2722	2586
45°	3053	2585	2426
50°	2945	2427	2241
55°	2838	2255	2070
60°	2709	2073	1872
65°	2555	1862	1666
70°	2400	1620	1429
75°	2137	1334	1155
80°	1823	996	849
85°	1407	590	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3053 cd/sqm

TEST NUMBER: P1026887

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.4
10°-20°	150.7	3.9
20°-30°	222.5	5.8
30°-40°	259.6	6.8
40°-50°	260.8	6.8
50°-60°	228.9	6.0
60°-70°	170.5	4.5
70°-80°	97.4	2.5
80°-90°	29.3	0.8
90°-100°	26.0	0.7
100°-110°	173.1	4.5
110°-120°	311.7	8.1
120°-130°	400.1	10.4
130°-140°	430.3	11.2
140°-150°	403.9	10.5
150°-160°	326.7	8.5
160°-170°	211.3	5.5
170°-180°	72.9	1.9
0°-30°	426.7	11.1
0°-40°	686.3	17.9
0°-60°	1176.0	30.7
0°-90°	1473.1	38.5
90°-120°	510.8	13.3
90°-150°	1745.0	45.6
90°-180°	2356.0	61.5
0°-180°	3829.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	565	564	559	563	563	54
15°	538	537	532	534	534	152
25°	489	486	480	481	480	225
35°	422	420	414	412	408	264
45°	345	344	338	333	332	266
55°	263	262	256	252	248	235
65°	178	177	172	168	166	176
75°	94	94	91	90	88	100
85°	25	25	25	25	24	27
90°	1	5	9	12	14	3
95°	32	31	9	12	12	40
105°	167	169	169	169	169	177
115°	314	317	317	315	312	311
125°	446	450	450	448	446	399
135°	557	560	559	558	554	429
145°	645	646	646	647	644	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	

TEST NUMBER: P1026887

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	565.6	565.6	565.6	565.6	565.6
2.5°	567.3	566.0	561.5	566.0	565.6
5°	564.7	563.8	559.3	563.3	562.9
7.5°	560.6	559.7	554.8	558.8	558.4
10°	554.8	553.9	549.0	552.6	552.1
12.5°	547.7	545.9	541.4	544.1	544.1
15°	538.3	536.9	532.0	534.2	534.2
17.5°	528.4	526.2	521.3	523.9	521.7
20°	515.4	514.5	508.7	511.9	509.6
22.5°	502.5	500.7	495.3	497.1	495.8
25°	488.6	486.4	480.5	481.4	480.1
27.5°	472.5	471.1	465.3	465.8	464.4
30°	456.8	455.5	448.8	447.9	446.5
32.5°	439.8	437.6	431.8	430.0	427.3
35°	421.9	420.1	413.9	411.6	408.1
37.5°	403.6	401.3	395.5	392.4	390.2
40°	384.8	382.6	376.3	372.3	370.9
42.5°	364.7	362.9	356.6	353.0	350.8
45°	345.4	343.6	338.3	332.9	331.5
47.5°	324.4	324.8	318.1	312.8	309.6
50°	304.3	302.9	297.5	291.7	288.6
52.5°	283.7	282.8	277.0	272.0	268.5
55°	263.1	261.7	255.5	251.5	248.3
57.5°	241.2	240.7	235.3	230.0	228.6
60°	220.6	218.8	213.9	209.4	206.3
62.5°	199.1	197.8	193.7	188.8	186.6
65°	177.6	176.7	171.8	167.8	166.0
67.5°	156.6	154.8	151.2	147.7	146.8
70°	136.9	134.7	130.7	128.0	126.2
72.5°	115.4	114.1	111.9	108.7	106.9
75°	94.4	93.5	91.3	89.9	88.1
77.5°	74.7	74.3	72.9	72.0	70.7
80°	56.4	56.4	55.5	55.0	54.1
82.5°	40.3	39.4	39.4	38.5	38.5
85°	24.6	25.1	25.1	24.6	23.7
87.5°	12.1	12.1	11.6	11.6	10.7
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.4	30.7	9.1	11.9	11.9
97.5°	60.8	64.2	10.2	11.4	11.9
100°	94.9	96.6	98.9	14.2	11.9
102.5°	129.6	131.9	133.0	134.2	86.4
105°	167.1	169.4	169.4	169.4	168.9
107.5°	205.8	205.8	206.9	207.5	205.2
110°	243.3	243.3	244.5	242.8	243.3

TEST NUMBER: P1026887

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.6	280.3	280.8	278.6	277.4
115°	313.8	316.7	317.2	315.0	311.5
117.5°	350.8	350.8	353.1	349.6	348.5
120°	384.9	384.3	386.0	384.9	382.0
122.5°	415.0	417.9	418.4	417.3	413.9
125°	446.3	450.3	450.3	448.0	446.3
127.5°	476.4	479.3	478.7	477.6	473.0
130°	503.7	506.6	507.1	505.4	502.6
132.5°	531.0	534.4	532.7	532.7	529.9
135°	556.6	560.0	558.9	557.7	554.3
137.5°	580.5	583.9	582.7	582.7	579.9
140°	603.8	604.9	604.3	605.5	602.1
142.5°	624.8	625.4	626.5	626.5	623.1
145°	645.3	646.4	646.4	647.0	643.6
147.5°	663.5	663.5	664.0	664.6	660.6
150°	680.5	679.4	680.5	681.7	677.1
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)