

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007713

Luminaire Tested: S124IP-B590UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B590UB2750-4F0-XX-W2A-1_3000K
Description: Define 4 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2052.0 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007713

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007713

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007713

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.6	0.1
90°-100°	48.2	2.3
100°-110°	144.3	7.0
110°-120°	245.1	11.9
120°-130°	323.2	15.8
130°-140°	363.1	17.7
140°-150°	356.8	17.4
150°-160°	300.1	14.6
160°-170°	199.7	9.7
170°-180°	69.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.6	0.1
90°-120°	437.5	21.3
90°-150°	1480.7	72.2
90°-180°	2050.0	99.9
0°-180°	2052.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	8	13	16	17	3
95°	34	39	43	45	45	37
105°	133	134	136	138	140	141
115°	249	249	248	248	247	246
125°	363	363	362	361	360	323
135°	468	472	472	470	469	362
145°	569	571	572	571	569	356
155°	652	652	651	653	651	300
165°	709	708	706	710	708	200
175°	738	735	734	738	734	70
180°	739	739	739	739	739	

TEST NUMBER: P1007713

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.7	8.0	12.6	16.0	17.1
92.5°	14.9	22.3	25.1	26.9	27.4
95°	34.3	39.4	43.4	45.2	45.2
97.5°	54.9	59.4	64.0	66.3	66.3
100°	80.0	82.3	87.4	88.6	88.6
102.5°	106.3	106.9	111.4	113.2	113.7
105°	133.2	133.7	136.0	137.7	139.5
107.5°	161.2	161.7	162.3	164.6	164.0
110°	189.7	190.9	190.3	189.2	190.9

TEST NUMBER: P1007713

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.5	219.5	218.3	218.3	218.3
115°	249.2	249.2	248.0	247.5	246.9
117.5°	277.2	277.2	276.6	274.9	273.2
120°	305.2	307.5	305.8	302.9	304.1
122.5°	334.3	334.9	334.3	332.6	329.8
125°	362.9	362.9	362.3	361.2	360.1
127.5°	388.6	390.4	389.2	388.1	387.5
130°	416.1	417.8	417.8	416.6	414.4
132.5°	444.1	445.2	444.7	443.5	442.9
135°	468.1	471.5	471.5	470.4	468.7
137.5°	494.9	496.7	497.8	496.1	496.7
140°	521.8	522.9	522.9	522.4	521.8
142.5°	546.4	547.5	547.0	547.0	547.0
145°	568.7	571.0	571.5	571.0	569.2
147.5°	591.5	594.4	593.8	593.2	592.7
150°	612.1	614.4	614.4	614.4	613.8
152.5°	631.5	632.7	633.3	635.0	633.3
155°	651.5	651.5	651.0	653.3	651.0
157.5°	668.7	667.5	667.5	669.3	667.5
160°	683.5	683.0	682.4	684.1	681.3
162.5°	697.3	695.6	695.0	698.4	695.6
165°	709.3	707.6	706.4	709.8	707.6
167.5°	719.0	716.7	716.7	720.1	716.7
170°	727.0	724.1	724.7	728.1	724.1
172.5°	732.7	730.4	730.4	734.4	730.4
175°	737.8	735.0	734.4	738.4	734.4
177.5°	740.1	737.3	737.3	741.3	736.7
180°	739.0	739.0	739.0	739.0	739.0

(END OF REPORT)