

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026895

Luminaire Tested: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026895
REPORT IS A COMBINATION OF REPORTS P1002074 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4589.2 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026895

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026895

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30
2	84	77	71	66	75	69	64	59	54	51	47	40	38	36	28	26	25
3	77	67	60	54	68	60	54	49	48	43	40	36	33	30	25	23	21
4	70	59	52	46	62	53	47	42	42	37	34	32	28	26	22	20	18
5	64	53	45	39	57	47	41	35	37	33	29	28	25	22	20	17	16
6	59	47	39	33	52	42	36	31	34	29	25	25	22	19	18	15	14
7	54	42	35	29	48	38	31	27	30	25	22	23	20	17	16	14	12
8	50	38	31	26	45	35	28	23	28	23	19	21	17	15	15	12	11
9	47	35	27	23	42	31	25	21	25	20	17	19	16	13	14	11	10
10	44	32	25	20	39	29	23	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2941	2941	2941
5°	2946	2879	2886
10°	2924	2821	2813
15°	2888	2752	2722
20°	2840	2670	2632
25°	2783	2582	2523
30°	2714	2487	2423
35°	2650	2398	2332
40°	2585	2305	2240
45°	2511	2225	2157
50°	2439	2137	2082
55°	2354	2054	1996
60°	2261	1959	1907
65°	2163	1859	1806
70°	2051	1724	1702
75°	1875	1591	1576
80°	1645	1431	1435
85°	1418	1303	1361

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2511 cd/sqm

TEST NUMBER: P1026895

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	0.9
10°-20°	123.3	2.7
20°-30°	183.4	4.0
30°-40°	217.2	4.7
40°-50°	224.5	4.9
50°-60°	206.8	4.5
60°-70°	167.2	3.6
70°-80°	111.9	2.4
80°-90°	59.4	1.3
90°-100°	67.6	1.5
100°-110°	256.6	5.6
110°-120°	434.9	9.5
120°-130°	546.7	11.9
130°-140°	582.2	12.7
140°-150°	543.4	11.8
150°-160°	438.9	9.6
160°-170°	283.9	6.2
170°-180°	97.9	2.1
0°-30°	350.1	7.6
0°-40°	567.3	12.4
0°-60°	998.6	21.8
0°-90°	1337.1	29.1
90°-120°	759.1	16.5
90°-150°	2431.4	53.0
90°-180°	3252.0	70.9
0°-180°	4589.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	459	459	459	459	459	
5°	459	458	455	459	458	44
15°	438	439	436	438	436	124
25°	398	400	397	399	396	183
35°	345	348	346	348	348	216
45°	284	289	291	294	295	219
55°	218	226	233	238	239	195
65°	150	161	172	178	180	149
75°	83	94	109	118	120	88
85°	25	40	55	65	69	26
90°	8	28	49	63	69	7
95°	49	59	45	59	62	58
105°	229	239	252	261	264	242
115°	424	431	444	449	447	421
125°	602	606	615	620	620	537
135°	749	753	754	759	756	577
145°	868	869	869	872	869	542
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1026895

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	459.0	459.0	459.0	459.0	459.0
2.5°	460.4	459.5	456.3	459.5	459.0
5°	459.0	458.1	455.0	458.6	458.1
7.5°	455.9	455.4	452.3	455.4	455.0
10°	451.4	451.4	447.8	450.9	450.5
12.5°	445.1	445.5	442.8	445.1	443.7
15°	438.3	438.8	435.6	438.3	436.5
17.5°	429.8	430.7	427.5	429.8	428.4
20°	420.3	421.2	418.1	419.4	419.4
22.5°	409.5	411.3	407.7	409.5	408.2
25°	398.3	399.6	396.9	398.7	396.5
27.5°	386.1	387.9	384.8	386.1	385.2
30°	372.2	374.9	372.2	373.1	372.6
32.5°	359.6	361.8	360.0	360.9	360.5
35°	344.7	347.9	346.5	347.9	347.9
37.5°	330.3	333.0	332.6	334.4	333.9
40°	315.5	319.1	318.6	320.4	321.3
42.5°	299.3	304.2	305.6	307.8	307.8
45°	284.0	288.9	291.2	294.3	294.8
47.5°	268.2	272.7	276.3	280.8	281.7
50°	252.0	257.0	261.9	266.9	268.2
52.5°	234.9	241.2	247.5	252.9	253.8
55°	218.3	225.5	232.7	237.6	239.4
57.5°	201.2	209.7	217.8	223.2	224.6
60°	184.1	193.1	202.1	208.8	210.2
62.5°	167.4	176.4	186.3	194.0	195.8
65°	150.3	160.7	171.5	178.2	180.0
67.5°	134.6	144.5	155.3	163.4	165.6
70°	117.0	127.4	139.1	147.6	150.3
72.5°	99.9	110.7	123.8	133.2	135.0
75°	82.8	94.5	108.9	117.9	120.2
77.5°	66.2	79.7	93.2	103.1	104.9
80°	50.9	64.4	79.7	89.6	91.4
82.5°	36.9	51.3	67.1	76.5	80.1
85°	24.8	39.6	55.4	65.3	68.9
87.5°	15.8	30.2	45.5	55.8	59.0
90°	8.0	28.5	49.1	63.3	68.7
92.5°	20.8	27.0	47.3	61.0	65.0
95°	49.4	58.9	45.1	58.8	61.9
97.5°	87.1	102.5	44.9	55.8	59.7
100°	132.6	144.3	161.7	57.4	57.0
102.5°	178.7	190.3	205.8	216.3	154.8
105°	228.7	238.9	252.4	261.4	263.8
107.5°	280.1	286.4	301.1	310.8	310.5
110°	330.1	335.5	349.7	355.9	359.8

TEST NUMBER: P1026895

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.5	383.8	396.8	401.8	403.4
115°	424.4	431.4	443.9	448.9	447.0
117.5°	473.6	475.8	490.2	493.2	494.9
120°	519.5	520.0	532.7	538.8	537.6
122.5°	559.4	563.8	574.4	580.1	578.2
125°	601.5	606.4	615.4	619.6	619.5
127.5°	641.5	644.9	651.8	657.0	653.6
130°	678.2	681.5	688.6	692.6	691.1
132.5°	714.4	719.0	721.2	727.5	725.5
135°	748.8	752.9	754.5	758.9	756.5
137.5°	780.8	785.0	785.3	790.7	788.7
140°	811.8	813.3	812.9	819.5	816.7
142.5°	840.0	840.3	841.8	845.9	843.1
145°	867.5	868.6	868.6	871.6	868.8
147.5°	891.5	891.5	892.2	893.9	889.4
150°	914.4	912.9	914.4	915.9	910.3
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)