

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007714

Luminaire Tested: S124IP-B590UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B590UB2750-4F0-XX-W2A-1_3500K
Description: Define 4 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2061.0 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007714

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1007714

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007714

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.6	0.1
90°-100°	48.4	2.3
100°-110°	144.9	7.0
110°-120°	246.2	11.9
120°-130°	324.7	15.8
130°-140°	364.7	17.7
140°-150°	358.4	17.4
150°-160°	301.4	14.6
160°-170°	200.6	9.7
170°-180°	70.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.6	0.1
90°-120°	439.5	21.3
90°-150°	1487.2	72.2
90°-180°	2059.0	99.9
0°-180°	2061.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	8	13	16	17	3
95°	34	40	44	45	45	37
105°	134	134	137	138	140	142
115°	250	250	249	249	248	247
125°	364	364	364	363	362	325
135°	470	474	474	472	471	364
145°	571	574	574	574	572	358
155°	654	654	654	656	654	301
165°	712	711	710	713	711	201
175°	741	738	738	742	738	70
180°	742	742	742	742	742	

TEST NUMBER: P1007714

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.7	8.0	12.6	16.1	17.2
92.5°	14.9	22.4	25.3	27.0	27.6
95°	34.4	39.6	43.6	45.3	45.3
97.5°	55.1	59.7	64.3	66.6	66.6
100°	80.4	82.7	87.8	89.0	89.0
102.5°	106.8	107.3	111.9	113.7	114.2
105°	133.8	134.3	136.6	138.3	140.1
107.5°	161.9	162.5	163.0	165.3	164.7
110°	190.6	191.7	191.2	190.0	191.7

TEST NUMBER: P1007714

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.4	220.4	219.3	219.3	219.3
115°	250.3	250.3	249.1	248.6	248.0
117.5°	278.4	278.4	277.8	276.1	274.4
120°	306.5	308.8	307.1	304.2	305.4
122.5°	335.8	336.4	335.8	334.1	331.2
125°	364.5	364.5	363.9	362.8	361.6
127.5°	390.3	392.1	390.9	389.8	389.2
130°	417.9	419.6	419.6	418.5	416.2
132.5°	446.0	447.2	446.6	445.5	444.9
135°	470.1	473.6	473.6	472.4	470.7
137.5°	497.1	498.8	500.0	498.3	498.8
140°	524.1	525.2	525.2	524.7	524.1
142.5°	548.8	549.9	549.4	549.4	549.4
145°	571.2	573.5	574.0	573.5	571.7
147.5°	594.1	597.0	596.4	595.8	595.3
150°	614.8	617.1	617.1	617.1	616.5
152.5°	634.3	635.5	636.0	637.8	636.0
155°	654.4	654.4	653.8	656.1	653.8
157.5°	671.6	670.5	670.5	672.2	670.5
160°	686.5	686.0	685.4	687.1	684.3
162.5°	700.3	698.6	698.0	701.5	698.6
165°	712.4	710.7	709.5	713.0	710.7
167.5°	722.1	719.8	719.8	723.3	719.8
170°	730.2	727.3	727.9	731.3	727.3
172.5°	735.9	733.6	733.6	737.6	733.6
175°	741.1	738.2	737.6	741.7	737.6
177.5°	743.4	740.5	740.5	744.5	739.9
180°	742.2	742.2	742.2	742.2	742.2

(END OF REPORT)