

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007725

Luminaire Tested: S124IP-B590UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B590UB2750-4F0-XX-W2A_4000K
Description: Define 4 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2353.0 lumens
Efficiency: N/A
Efficacy: 152.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007725

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007725

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007725

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.6	0.1
90°-100°	25.2	1.1
100°-110°	166.1	7.1
110°-120°	317.2	13.5
120°-130°	402.7	17.1
130°-140°	430.8	18.3
140°-150°	402.8	17.1
150°-160°	324.8	13.8
160°-170°	209.5	8.9
170°-180°	72.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.6	0.1
90°-120°	508.5	21.6
90°-150°	1744.9	74.2
90°-180°	2351.0	99.9
0°-180°	2353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	8	12	16	17	2
95°	31	12	12	16	16	39
105°	171	174	177	182	162	179
115°	319	321	321	322	322	314
125°	449	451	450	452	452	401
135°	557	556	559	560	561	429
145°	642	644	644	644	646	401
155°	704	705	703	705	704	325
165°	743	740	740	745	739	210
175°	760	756	757	762	755	72
180°	760	760	760	760	760	

TEST NUMBER: P1007725

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.7	8.0	12.5	15.9	17.1
92.5°	8.5	7.4	11.9	15.3	15.3
95°	31.3	11.9	12.5	15.9	16.5
97.5°	59.7	72.2	12.5	15.3	15.9
100°	93.2	103.4	25.0	15.3	15.9
102.5°	130.7	137.5	144.4	16.5	16.5
105°	171.1	174.5	177.3	182.4	162.0
107.5°	208.0	209.7	213.7	216.5	218.8
110°	245.5	247.2	250.7	251.8	253.5

TEST NUMBER: P1007725

CATALOG NUMBER: S124IP-B590UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	285.3	286.5	285.9	288.2
115°	319.4	321.1	320.6	321.7	321.7
117.5°	353.0	355.2	356.9	356.4	356.4
120°	387.1	389.3	388.8	389.9	388.8
122.5°	418.9	420.0	421.2	421.7	420.6
125°	449.0	451.3	450.1	451.9	452.4
127.5°	478.0	478.6	481.4	480.8	480.3
130°	505.8	506.4	508.1	508.7	508.7
132.5°	531.4	532.6	534.8	535.4	534.8
135°	557.0	556.4	558.7	559.8	561.0
137.5°	579.7	579.7	582.6	583.7	583.1
140°	601.9	603.0	604.2	605.9	606.5
142.5°	621.8	624.1	624.6	625.8	625.8
145°	642.3	644.0	644.0	644.5	645.7
147.5°	658.2	661.6	661.0	661.6	662.2
150°	675.8	678.1	677.5	677.5	678.1
152.5°	690.6	692.3	691.1	692.3	691.7
155°	704.2	704.8	703.1	705.3	703.6
157.5°	716.1	716.1	713.9	716.7	713.9
160°	726.4	724.7	724.1	727.5	724.1
162.5°	735.5	733.2	732.6	736.0	732.1
165°	742.9	740.0	740.0	744.6	739.4
167.5°	749.1	746.3	745.7	750.8	745.1
170°	754.2	750.8	751.4	755.9	750.2
172.5°	757.6	754.2	754.8	759.3	753.1
175°	759.9	756.5	757.1	762.2	755.4
177.5°	761.6	757.6	758.8	763.3	756.5
180°	759.9	759.9	759.9	759.9	759.9

(END OF REPORT)