

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007742

Luminaire Tested: S124IP-B810UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B810UB2750-4F0-XX-W2A-1_2700K
Description: Define 4 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2718.0 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007742

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007742

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007742

CATALOG NUMBER: S124IP-B810UB2750-4FO-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	63.8	2.3
100°-110°	191.1	7.0
110°-120°	324.7	11.9
120°-130°	428.2	15.8
130°-140°	480.9	17.7
140°-150°	472.7	17.4
150°-160°	397.5	14.6
160°-170°	264.5	9.7
170°-180°	92.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	579.5	21.3
90°-150°	1961.2	72.2
90°-180°	2716.0	99.9
0°-180°	2718.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	11	17	21	23	3
95°	45	52	58	60	60	49
105°	176	177	180	182	185	187
115°	330	330	328	328	327	326
125°	481	481	480	478	477	429
135°	620	624	624	623	621	480
145°	753	756	757	756	754	471
155°	863	863	862	865	862	397
165°	940	937	936	940	937	265
175°	977	974	973	978	973	93
180°	979	979	979	979	979	

TEST NUMBER: P1007742

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.3	10.6	16.7	21.2	22.7
92.5°	19.7	29.5	33.3	35.6	36.3
95°	45.4	52.2	57.5	59.8	59.8
97.5°	72.7	78.7	84.8	87.8	87.8
100°	106.0	109.0	115.8	117.3	117.3
102.5°	140.8	141.6	147.6	149.9	150.6
105°	176.4	177.1	180.2	182.4	184.7
107.5°	213.5	214.2	215.0	218.0	217.3
110°	251.3	252.8	252.1	250.6	252.8

TEST NUMBER: P1007742

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.7	290.7	289.2	289.2	289.2
115°	330.1	330.1	328.5	327.8	327.0
117.5°	367.2	367.2	366.4	364.1	361.9
120°	404.3	407.3	405.0	401.2	402.7
122.5°	442.9	443.6	442.9	440.6	436.8
125°	480.7	480.7	480.0	478.4	476.9
127.5°	514.8	517.0	515.5	514.0	513.3
130°	551.1	553.4	553.4	551.9	548.8
132.5°	588.2	589.7	589.0	587.5	586.7
135°	620.0	624.5	624.5	623.0	620.8
137.5°	655.6	657.9	659.4	657.1	657.9
140°	691.2	692.7	692.7	691.9	691.2
142.5°	723.7	725.2	724.5	724.5	724.5
145°	753.2	756.3	757.0	756.3	754.0
147.5°	783.5	787.3	786.6	785.8	785.0
150°	810.8	813.8	813.8	813.8	813.0
152.5°	836.5	838.0	838.8	841.1	838.8
155°	863.0	863.0	862.3	865.3	862.3
157.5°	885.7	884.2	884.2	886.5	884.2
160°	905.4	904.6	903.9	906.2	902.4
162.5°	923.6	921.3	920.5	925.1	921.3
165°	939.5	937.2	935.7	940.2	937.2
167.5°	952.3	949.3	949.3	953.9	949.3
170°	962.9	959.2	959.9	964.5	959.2
172.5°	970.5	967.5	967.5	972.8	967.5
175°	977.3	973.5	972.8	978.1	972.8
177.5°	980.3	976.6	976.6	981.9	975.8
180°	978.8	978.8	978.8	978.8	978.8

(END OF REPORT)