

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007754

Luminaire Tested: S124IP-B810UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B810UB2750-4F0-XX-W2A_3500K
Description: Define 4 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3175.0 lumens
Efficiency: N/A
Efficacy: 150.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007754

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007754

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 0°

Luminance: 0 cd/sqm

TEST NUMBER: P1007754

CATALOG NUMBER: S124IP-B810UB2750-4FO-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	34.0	1.1
100°-110°	224.1	7.1
110°-120°	428.0	13.5
120°-130°	543.4	17.1
130°-140°	581.3	18.3
140°-150°	543.6	17.1
150°-160°	438.3	13.8
160°-170°	282.7	8.9
170°-180°	97.4	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	686.2	21.6
90°-150°	2354.4	74.2
90°-180°	3173.0	99.9
0°-180°	3175.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	11	17	22	23	2
95°	42	16	17	22	22	52
105°	231	235	239	246	219	242
115°	431	433	432	434	434	424
125°	606	609	607	610	610	541
135°	752	751	754	755	757	579
145°	867	869	869	870	871	542
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1007754

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.3	10.7	16.9	21.5	23.0
92.5°	11.5	10.0	16.1	20.7	20.7
95°	42.2	16.1	16.9	21.5	22.2
97.5°	80.5	97.4	16.9	20.7	21.5
100°	125.8	139.6	33.7	20.7	21.5
102.5°	176.4	185.6	194.8	22.2	22.2
105°	230.8	235.4	239.3	246.2	218.6
107.5°	280.7	283.0	288.4	292.2	295.3
110°	331.3	333.6	338.2	339.7	342.0

TEST NUMBER: P1007754

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.4	385.0	386.5	385.8	388.8
115°	431.0	433.3	432.5	434.1	434.1
117.5°	476.3	479.3	481.6	480.9	480.9
120°	522.3	525.3	524.6	526.1	524.6
122.5°	565.2	566.8	568.3	569.1	567.5
125°	605.9	608.9	607.4	609.7	610.5
127.5°	645.0	645.8	649.6	648.8	648.1
130°	682.6	683.3	685.6	686.4	686.4
132.5°	717.1	718.6	721.7	722.4	721.7
135°	751.6	750.8	753.9	755.4	757.0
137.5°	782.3	782.3	786.1	787.6	786.9
140°	812.2	813.7	815.2	817.5	818.3
142.5°	839.0	842.1	842.9	844.4	844.4
145°	866.6	868.9	868.9	869.7	871.2
147.5°	888.1	892.7	891.9	892.7	893.5
150°	911.9	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)