

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026945

Luminaire Tested: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026945
REPORT IS A COMBINATION OF REPORTS P1002259 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3963.0 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026945

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026945

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	59	57	57	57	53
2	92	84	78	72	86	79	73	69	69	65	61	61	58	55	53	50	48	48	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41	41	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	35	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	38	34	31	31	31	28
6	65	52	44	38	61	49	42	36	44	38	33	39	34	30	34	30	27	27	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	24	24	22
8	56	43	35	30	52	41	34	28	36	30	26	32	27	24	29	25	22	22	22	19
9	52	39	32	27	49	37	30	26	34	28	23	30	25	21	26	22	20	20	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	19	25	21	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5163 cd/sqm

TEST NUMBER: P1026945

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	2.3
10°-20°	254.9	6.4
20°-30°	376.3	9.5
30°-40°	439.0	11.1
40°-50°	440.9	11.1
50°-60°	387.1	9.8
60°-70°	288.3	7.3
70°-80°	164.6	4.2
80°-90°	48.3	1.2
90°-100°	16.3	0.4
100°-110°	108.2	2.7
110°-120°	194.9	4.9
120°-130°	250.2	6.3
130°-140°	269.1	6.8
140°-150°	252.6	6.4
150°-160°	204.3	5.2
160°-170°	132.1	3.3
170°-180°	45.6	1.1
0°-30°	721.4	18.2
0°-40°	1160.5	29.3
0°-60°	1988.5	50.2
0°-90°	2489.7	62.8
90°-120°	319.5	8.1
90°-150°	1091.3	27.5
90°-180°	1473.0	37.2
0°-180°	3963.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	0	3	6	8	8	4
95°	20	19	6	8	8	25
105°	104	106	106	106	106	111
115°	196	198	198	197	195	195
125°	279	282	282	280	279	249
135°	348	350	350	349	347	268
145°	404	404	404	405	402	252
155°	444	442	443	444	441	205
165°	469	467	467	469	466	132
175°	480	478	478	481	478	46
180°	480	480	480	480	480	

TEST NUMBER: P1026945

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	0.4	3.2	5.7	7.5	8.5
92.5°	6.8	3.6	5.7	7.5	7.8
95°	20.3	19.2	5.7	7.5	7.5
97.5°	38.0	40.2	6.4	7.1	7.5
100°	59.4	60.4	61.9	8.9	7.5
102.5°	81.1	82.5	83.2	83.9	54.0
105°	104.5	105.9	105.9	105.9	105.6
107.5°	128.7	128.7	129.4	129.8	128.3
110°	152.2	152.2	152.9	151.8	152.2

TEST NUMBER: P1026945

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.2	175.3	175.6	174.2	173.5
115°	196.3	198.0	198.4	197.0	194.8
117.5°	219.4	219.4	220.8	218.7	217.9
120°	240.7	240.3	241.4	240.7	238.9
122.5°	259.5	261.3	261.7	261.0	258.8
125°	279.1	281.6	281.6	280.2	279.1
127.5°	297.9	299.7	299.4	298.7	295.8
130°	315.0	316.8	317.1	316.1	314.3
132.5°	332.1	334.2	333.1	333.1	331.4
135°	348.1	350.2	349.5	348.8	346.6
137.5°	363.0	365.1	364.4	364.4	362.6
140°	377.6	378.3	377.9	378.6	376.5
142.5°	390.7	391.1	391.8	391.8	389.7
145°	403.5	404.2	404.2	404.6	402.5
147.5°	414.9	414.9	415.3	415.6	413.1
150°	425.6	424.9	425.6	426.3	423.4
152.5°	435.9	434.1	434.8	435.5	433.0
155°	444.4	442.3	443.0	444.1	441.2
157.5°	451.2	450.1	450.1	451.2	448.3
160°	458.3	456.2	456.5	457.9	455.1
162.5°	464.0	461.8	462.2	464.3	461.1
165°	469.0	466.8	467.2	469.3	466.5
167.5°	472.9	470.7	471.1	473.6	470.4
170°	476.1	473.6	473.9	476.8	473.6
172.5°	478.2	475.7	476.4	478.9	475.7
175°	479.6	477.5	477.8	480.7	477.5
177.5°	480.7	478.6	478.9	481.4	478.6
180°	479.6	479.6	479.6	479.6	479.6

(END OF REPORT)