

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007756

Luminaire Tested: S124IP-B810UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B810UB2750-4F0-XX-W2A_5000K
Description: Define 4 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3040.0 lumens
Efficiency: N/A
Efficacy: 144.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007756

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007756

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007756

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	32.6	1.1
100°-110°	214.6	7.1
110°-120°	409.8	13.5
120°-130°	520.3	17.1
130°-140°	556.6	18.3
140°-150°	520.4	17.1
150°-160°	419.7	13.8
160°-170°	270.7	8.9
170°-180°	93.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	657.0	21.6
90°-150°	2254.3	74.2
90°-180°	3038.0	99.9
0°-180°	3040.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	10	16	21	22	2
95°	40	15	16	21	21	50
105°	221	225	229	236	209	231
115°	413	415	414	416	416	406
125°	580	583	582	584	584	518
135°	720	719	722	723	725	554
145°	830	832	832	833	834	518
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1007756

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.2	10.3	16.2	20.6	22.0
92.5°	11.0	9.5	15.4	19.8	19.8
95°	40.4	15.4	16.2	20.6	21.3
97.5°	77.1	93.3	16.2	19.8	20.6
100°	120.4	133.6	32.3	19.8	20.6
102.5°	168.9	177.7	186.5	21.3	21.3
105°	221.0	225.4	229.1	235.7	209.3
107.5°	268.8	271.0	276.1	279.8	282.7
110°	317.2	319.4	323.8	325.3	327.5

TEST NUMBER: P1007756

CATALOG NUMBER: S124IP-B810UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	368.6	370.1	369.4	372.3
115°	412.7	414.9	414.2	415.6	415.6
117.5°	456.0	458.9	461.2	460.4	460.4
120°	500.1	503.0	502.3	503.7	502.3
122.5°	541.2	542.7	544.1	544.9	543.4
125°	580.1	583.0	581.6	583.8	584.5
127.5°	617.6	618.3	622.0	621.2	620.5
130°	653.5	654.3	656.5	657.2	657.2
132.5°	686.6	688.1	691.0	691.7	691.0
135°	719.6	718.9	721.8	723.3	724.8
137.5°	749.0	749.0	752.7	754.1	753.4
140°	777.6	779.1	780.6	782.8	783.5
142.5°	803.3	806.3	807.0	808.5	808.5
145°	829.8	832.0	832.0	832.7	834.2
147.5°	850.3	854.7	854.0	854.7	855.5
150°	873.1	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)