

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007646

Luminaire Tested: S124IP-B1035UB50-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B1035UB50-4F0-XX-W2A-1
Description: Define 4 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3411.0 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007646

CATALOG NUMBER: S124IP-B1035UB50-4F0-XX-W2A-1

Luminous Intensity Polar Plot





TEST NUMBER: P1007646

CATALOG NUMBER: S124IP-B1035UB50-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007646

CATALOG NUMBER: S124IP-B1035UB50-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	80.1	2.3
100°-110°	239.8	7.0
110°-120°	407.4	11.9
120°-130°	537.3	15.8
130°-140°	603.5	17.7
140°-150°	593.2	17.4
150°-160°	498.9	14.6
160°-170°	332.0	9.7
170°-180°	116.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	727.4	21.3
90°-150°	2461.3	72.2
90°-180°	3408.0	99.9
0°-180°	3411.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	13	21	27	28	4
95°	57	66	72	75	75	62
105°	221	222	226	229	232	235
115°	414	414	412	411	410	409
125°	603	603	602	600	598	538
135°	778	784	784	782	779	602
145°	945	949	950	949	946	592
155°	1083	1083	1082	1086	1082	498
165°	1179	1176	1174	1180	1176	332
175°	1226	1222	1221	1228	1221	116
180°	1228	1228	1228	1228	1228	

TEST NUMBER: P1007646

CATALOG NUMBER: S124IP-B1035UB50-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.9	13.3	20.9	26.6	28.5
92.5°	24.7	37.1	41.8	44.7	45.6
95°	57.0	65.6	72.2	75.1	75.1
97.5°	91.2	98.8	106.4	110.2	110.2
100°	133.0	136.8	145.4	147.3	147.3
102.5°	176.7	177.7	185.3	188.1	189.1
105°	221.4	222.3	226.1	229.0	231.8
107.5°	267.9	268.9	269.8	273.6	272.7
110°	315.4	317.3	316.4	314.5	317.3

TEST NUMBER: P1007646

CATALOG NUMBER: S124IP-B1035UB50-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.8	364.8	362.9	362.9	362.9
115°	414.2	414.2	412.3	411.4	410.4
117.5°	460.8	460.8	459.8	457.0	454.1
120°	507.3	511.1	508.3	503.5	505.4
122.5°	555.8	556.7	555.8	552.9	548.2
125°	603.3	603.3	602.3	600.4	598.5
127.5°	646.0	648.9	647.0	645.1	644.1
130°	691.6	694.5	694.5	692.6	688.8
132.5°	738.2	740.1	739.1	737.2	736.3
135°	778.1	783.8	783.8	781.9	779.0
137.5°	822.7	825.6	827.5	824.6	825.6
140°	867.4	869.3	869.3	868.3	867.4
142.5°	908.2	910.1	909.2	909.2	909.2
145°	945.3	949.1	950.0	949.1	946.2
147.5°	983.3	988.0	987.1	986.1	985.2
150°	1017.5	1021.3	1021.3	1021.3	1020.3
152.5°	1049.8	1051.7	1052.6	1055.5	1052.6
155°	1083.0	1083.0	1082.1	1085.9	1082.1
157.5°	1111.6	1109.7	1109.7	1112.5	1109.7
160°	1136.3	1135.3	1134.4	1137.2	1132.5
162.5°	1159.1	1156.2	1155.3	1161.0	1156.2
165°	1179.0	1176.2	1174.3	1180.0	1176.2
167.5°	1195.2	1191.4	1191.4	1197.1	1191.4
170°	1208.5	1203.7	1204.7	1210.4	1203.7
172.5°	1218.0	1214.2	1214.2	1220.8	1214.2
175°	1226.5	1221.8	1220.8	1227.5	1220.8
177.5°	1230.3	1225.6	1225.6	1232.2	1224.6
180°	1228.4	1228.4	1228.4	1228.4	1228.4

(END OF REPORT)