

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026961

Luminaire Tested: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026961
REPORT IS A COMBINATION OF REPORTS P1002320 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4880.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026961

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026961

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	48	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	41	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	35	35	30
4	74	64	56	50	68	59	52	47	50	45	41	43	38	35	35	32	30	30	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	30	32	28	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	23	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	20	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	16
9	50	38	30	25	46	36	29	24	31	25	21	26	22	19	22	19	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6154	6154	6154
5°	6154	6012	6023
10°	6104	5873	5855
15°	6024	5708	5657
20°	5915	5517	5431
25°	5799	5309	5188
30°	5659	5092	4933
35°	5509	4864	4646
40°	5353	4624	4392
45°	5186	4389	4121
50°	5001	4123	3805
55°	4819	3829	3515
60°	4601	3520	3178
65°	4341	3162	2829
70°	4076	2751	2427
75°	3630	2265	1962
80°	3093	1691	1443
85°	2390	1002	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5186 cd/sqm

TEST NUMBER: P1026961

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.9
10°-20°	256.0	5.2
20°-30°	378.0	7.7
30°-40°	441.0	9.0
40°-50°	442.9	9.1
50°-60°	388.8	8.0
60°-70°	289.6	5.9
70°-80°	165.4	3.4
80°-90°	48.9	1.0
90°-100°	26.3	0.5
100°-110°	174.8	3.6
110°-120°	314.7	6.4
120°-130°	404.0	8.3
130°-140°	434.5	8.9
140°-150°	407.8	8.4
150°-160°	329.9	6.8
160°-170°	213.3	4.4
170°-180°	73.6	1.5
0°-30°	724.6	14.8
0°-40°	1165.6	23.9
0°-60°	1997.3	40.9
0°-90°	2501.2	51.3
90°-120°	515.8	10.6
90°-150°	1762.1	36.1
90°-180°	2379.0	48.7
0°-180°	4880.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	958	950	957	956	91
15°	914	912	904	907	907	258
25°	830	826	816	818	815	382
35°	717	714	703	699	693	448
45°	587	584	574	565	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	43	43	42	40	46
90°	1	5	9	12	14	4
95°	33	31	9	12	12	40
105°	169	171	171	171	170	179
115°	317	320	320	318	315	314
125°	451	455	455	452	451	403
135°	562	566	564	563	560	433
145°	652	653	653	653	650	408
155°	718	714	715	717	712	331
165°	757	754	754	758	753	214
175°	774	771	772	776	771	74
180°	774	774	774	774	774	

TEST NUMBER: P1026961

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	960.5	960.5	960.5	960.5	960.5
2.5°	963.6	961.3	953.7	961.3	960.5
5°	959.0	957.5	949.9	956.7	956.0
7.5°	952.2	950.6	942.3	949.1	948.4
10°	942.3	940.8	932.4	938.5	937.7
12.5°	930.1	927.1	919.5	924.0	924.0
15°	914.2	911.9	903.5	907.3	907.3
17.5°	897.4	893.6	885.3	889.8	886.1
20°	875.4	873.9	864.0	869.3	865.5
22.5°	853.4	850.3	841.2	844.3	842.0
25°	829.8	826.0	816.1	817.7	815.4
27.5°	802.5	800.2	790.3	791.1	788.8
30°	775.9	773.6	762.2	760.7	758.4
32.5°	747.0	743.2	733.3	730.3	725.7
35°	716.6	713.6	702.9	699.1	693.0
37.5°	685.4	681.6	671.8	666.4	662.6
40°	653.5	649.7	639.1	632.2	630.0
42.5°	619.3	616.3	605.6	599.6	595.8
45°	586.6	583.6	574.5	565.4	563.1
47.5°	550.9	551.7	540.3	531.2	525.9
50°	516.7	514.5	505.3	495.5	490.1
52.5°	481.8	480.3	470.4	462.0	455.9
55°	446.8	444.5	433.9	427.1	421.7
57.5°	409.6	408.8	399.7	390.6	388.3
60°	374.6	371.6	363.2	355.6	350.3
62.5°	338.2	335.9	329.0	320.7	316.9
65°	301.7	300.2	291.8	285.0	281.9
67.5°	266.0	262.9	256.8	250.8	249.2
70°	232.5	228.7	221.9	217.3	214.3
72.5°	196.1	193.8	190.0	184.7	181.6
75°	160.3	158.8	155.0	152.7	149.7
77.5°	126.9	126.1	123.9	122.3	120.1
80°	95.7	95.7	94.2	93.5	91.9
82.5°	68.4	66.9	66.9	65.4	65.4
85°	41.8	42.6	42.6	41.8	40.3
87.5°	20.5	20.5	19.8	19.8	18.2
90°	0.6	5.2	9.2	12.1	13.8
92.5°	10.9	5.7	9.2	12.1	12.6
95°	32.7	31.0	9.2	12.1	12.1
97.5°	61.4	64.9	10.3	11.5	12.1
100°	95.9	97.6	99.9	14.4	12.1
102.5°	130.9	133.2	134.3	135.5	87.3
105°	168.8	171.1	171.1	171.1	170.5
107.5°	207.8	207.8	209.0	209.5	207.2
110°	245.7	245.7	246.8	245.1	245.7

TEST NUMBER: P1026961

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.3	283.0	283.6	281.3	280.1
115°	316.9	319.8	320.3	318.0	314.6
117.5°	354.2	354.2	356.5	353.1	351.9
120°	388.6	388.1	389.8	388.6	385.8
122.5°	419.1	421.9	422.5	421.4	417.9
125°	450.6	454.7	454.7	452.4	450.6
127.5°	481.1	483.9	483.4	482.2	477.6
130°	508.6	511.5	512.1	510.3	507.5
132.5°	536.2	539.6	537.9	537.9	535.0
135°	562.0	565.5	564.3	563.2	559.7
137.5°	586.1	589.6	588.4	588.4	585.6
140°	609.7	610.8	610.2	611.4	607.9
142.5°	630.9	631.5	632.6	632.6	629.2
145°	651.6	652.7	652.7	653.3	649.8
147.5°	669.9	669.9	670.5	671.1	667.1
150°	687.2	686.0	687.2	688.3	683.7
152.5°	703.8	700.9	702.1	703.2	699.2
155°	717.6	714.1	715.3	717.0	712.4
157.5°	728.5	726.8	726.8	728.5	723.9
160°	740.0	736.5	737.1	739.4	734.8
162.5°	749.2	745.7	746.3	749.7	744.6
165°	757.2	753.8	754.3	757.8	753.2
167.5°	763.5	760.1	760.6	764.7	759.5
170°	768.7	764.7	765.2	769.8	764.7
172.5°	772.1	768.1	769.3	773.3	768.1
175°	774.4	771.0	771.5	776.1	771.0
177.5°	776.1	772.7	773.3	777.3	772.7
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)