

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007766

Luminaire Tested: S124IP-B810UB50-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IP-B810UB50-4F0-XX-W2A-1
Description: Define 4 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2636.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007766

CATALOG NUMBER: S124IP-B810UB50-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007766

CATALOG NUMBER: S124IP-B810UB50-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007766

CATALOG NUMBER: S124IP-B810UB50-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	61.9	2.3
100°-110°	185.3	7.0
110°-120°	314.8	11.9
120°-130°	415.2	15.8
130°-140°	466.4	17.7
140°-150°	458.4	17.4
150°-160°	385.5	14.6
160°-170°	256.5	9.7
170°-180°	89.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	562.1	21.3
90°-150°	1902.1	72.2
90°-180°	2634.0	99.9
0°-180°	2636.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	10	16	21	22	3
95°	44	51	56	58	58	48
105°	171	172	175	177	179	181
115°	320	320	319	318	317	316
125°	466	466	466	464	462	416
135°	601	606	606	604	602	465
145°	730	734	734	734	731	457
155°	837	837	836	839	836	385
165°	911	909	908	912	909	257
175°	948	944	943	949	943	90
180°	949	949	949	949	949	

TEST NUMBER: P1007766

CATALOG NUMBER: S124IP-B810UB50-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.2	10.3	16.2	20.6	22.0
92.5°	19.1	28.6	32.3	34.5	35.2
95°	44.1	50.7	55.8	58.0	58.0
97.5°	70.5	76.4	82.2	85.2	85.2
100°	102.8	105.7	112.3	113.8	113.8
102.5°	136.6	137.3	143.2	145.4	146.1
105°	171.1	171.8	174.7	176.9	179.1
107.5°	207.0	207.8	208.5	211.4	210.7
110°	243.8	245.2	244.5	243.0	245.2

TEST NUMBER: P1007766

CATALOG NUMBER: S124IP-B810UB50-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	281.9	280.5	280.5	280.5
115°	320.1	320.1	318.6	317.9	317.2
117.5°	356.1	356.1	355.3	353.1	350.9
120°	392.1	395.0	392.8	389.1	390.6
122.5°	429.5	430.2	429.5	427.3	423.6
125°	466.2	466.2	465.5	464.0	462.5
127.5°	499.2	501.5	500.0	498.5	497.8
130°	534.5	536.7	536.7	535.2	532.3
132.5°	570.5	571.9	571.2	569.7	569.0
135°	601.3	605.7	605.7	604.2	602.0
137.5°	635.8	638.0	639.5	637.3	638.0
140°	670.3	671.8	671.8	671.0	670.3
142.5°	701.9	703.4	702.6	702.6	702.6
145°	730.5	733.5	734.2	733.5	731.3
147.5°	759.9	763.6	762.8	762.1	761.4
150°	786.3	789.3	789.3	789.3	788.5
152.5°	811.3	812.7	813.5	815.7	813.5
155°	837.0	837.0	836.2	839.2	836.2
157.5°	859.0	857.5	857.5	859.7	857.5
160°	878.1	877.4	876.6	878.8	875.2
162.5°	895.7	893.5	892.8	897.2	893.5
165°	911.1	908.9	907.5	911.9	908.9
167.5°	923.6	920.7	920.7	925.1	920.7
170°	933.9	930.2	930.9	935.4	930.2
172.5°	941.2	938.3	938.3	943.4	938.3
175°	947.8	944.2	943.4	948.6	943.4
177.5°	950.8	947.1	947.1	952.2	946.4
180°	949.3	949.3	949.3	949.3	949.3

(END OF REPORT)