

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026974

Luminaire Tested: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026974
REPORT IS A COMBINATION OF REPORTS P1002378 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5607.0 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026974

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026974

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	68	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	31	52	41	34	29	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6075	5934	5946
10°	6025	5799	5780
15°	5947	5636	5585
20°	5839	5447	5362
25°	5725	5241	5122
30°	5586	5027	4870
35°	5438	4802	4587
40°	5285	4564	4335
45°	5119	4332	4068
50°	4937	4070	3757
55°	4757	3781	3470
60°	4542	3475	3137
65°	4285	3122	2793
70°	4025	2716	2396
75°	3584	2235	1937
80°	3054	1670	1425
85°	2361	988	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5119 cd/sqm

TEST NUMBER: P1026974

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.5	1.6
10°-20°	252.7	4.5
20°-30°	373.1	6.7
30°-40°	435.3	7.8
40°-50°	437.2	7.8
50°-60°	383.8	6.8
60°-70°	285.9	5.1
70°-80°	163.3	2.9
80°-90°	48.7	0.9
90°-100°	34.7	0.6
100°-110°	230.5	4.1
110°-120°	415.1	7.4
120°-130°	532.8	9.5
130°-140°	573.1	10.2
140°-150°	537.9	9.6
150°-160°	435.1	7.8
160°-170°	281.4	5.0
170°-180°	97.0	1.7
0°-30°	715.3	12.8
0°-40°	1150.7	20.5
0°-60°	1971.7	35.2
0°-90°	2469.5	44.0
90°-120°	680.3	12.1
90°-150°	2324.0	41.4
90°-180°	3137.0	55.9
0°-180°	5607.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	945	938	944	944	90
15°	902	900	892	896	896	254
25°	819	815	806	807	805	377
35°	707	704	694	690	684	443
45°	579	576	567	558	556	446
55°	441	439	428	422	416	394
65°	298	296	288	281	278	295
75°	158	157	153	151	148	169
85°	41	42	42	41	40	45
90°	1	7	12	16	18	5
95°	43	41	12	16	16	53
105°	223	226	226	226	225	236
115°	418	422	422	420	415	414
125°	594	600	600	597	594	531
135°	741	746	744	743	738	571
145°	859	861	861	862	857	537
155°	946	942	943	946	940	436
165°	999	994	995	999	993	282
175°	1021	1017	1018	1024	1017	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1026974

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	948.2	948.2	948.2	948.2	948.2
2.5°	951.2	949.0	941.5	949.0	948.2
5°	946.7	945.2	937.7	944.5	943.7
7.5°	940.0	938.5	930.2	937.0	936.2
10°	930.2	928.7	920.5	926.5	925.7
12.5°	918.2	915.2	907.7	912.2	912.2
15°	902.5	900.2	892.0	895.7	895.7
17.5°	886.0	882.2	874.0	878.5	874.7
20°	864.2	862.7	853.0	858.2	854.5
22.5°	842.5	839.5	830.4	833.4	831.2
25°	819.2	815.4	805.7	807.2	804.9
27.5°	792.2	789.9	780.2	780.9	778.7
30°	765.9	763.7	752.4	750.9	748.7
32.5°	737.4	733.7	723.9	720.9	716.4
35°	707.4	704.4	693.9	690.2	684.2
37.5°	676.7	672.9	663.2	657.9	654.2
40°	645.2	641.4	630.9	624.1	621.9
42.5°	611.4	608.4	597.9	591.9	588.1
45°	579.1	576.1	567.1	558.1	555.9
47.5°	543.9	544.6	533.4	524.4	519.1
50°	510.1	507.9	498.9	489.1	483.9
52.5°	475.6	474.1	464.4	456.1	450.1
55°	441.1	438.9	428.4	421.6	416.3
57.5°	404.3	403.6	394.6	385.6	383.3
60°	369.8	366.8	358.6	351.1	345.8
62.5°	333.8	331.6	324.8	316.6	312.8
65°	297.8	296.3	288.1	281.3	278.3
67.5°	262.6	259.6	253.6	247.6	246.1
70°	229.6	225.8	219.1	214.6	211.6
72.5°	193.5	191.3	187.5	182.3	179.3
75°	158.3	156.8	153.0	150.8	147.8
77.5°	125.3	124.5	122.3	120.8	118.5
80°	94.5	94.5	93.0	92.3	90.8
82.5°	67.5	66.0	66.0	64.5	64.5
85°	41.3	42.0	42.0	41.3	39.8
87.5°	20.3	20.3	19.5	19.5	18.0
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.2	40.9	12.1	15.9	15.9
97.5°	81.0	85.6	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.7	177.2	178.7	115.1
105°	222.6	225.6	225.6	225.6	224.9
107.5°	274.1	274.1	275.6	276.4	273.3
110°	324.1	324.1	325.6	323.3	324.1

TEST NUMBER: P1026974

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.0	373.3	374.0	371.0	369.5
115°	417.9	421.7	422.5	419.5	414.9
117.5°	467.2	467.2	470.2	465.6	464.1
120°	512.6	511.8	514.1	512.6	508.8
122.5°	552.7	556.5	557.3	555.7	551.2
125°	594.4	599.7	599.7	596.6	594.4
127.5°	634.5	638.3	637.5	636.0	629.9
130°	670.8	674.6	675.4	673.1	669.3
132.5°	707.2	711.7	709.4	709.4	705.7
135°	741.2	745.8	744.3	742.8	738.2
137.5°	773.0	777.6	776.1	776.1	772.3
140°	804.1	805.6	804.8	806.4	801.8
142.5°	832.1	832.9	834.4	834.4	829.8
145°	859.4	860.9	860.9	861.6	857.1
147.5°	883.6	883.6	884.3	885.1	879.8
150°	906.3	904.8	906.3	907.8	901.8
152.5°	928.3	924.5	926.0	927.5	922.2
155°	946.4	941.9	943.4	945.7	939.6
157.5°	960.8	958.5	958.5	960.8	954.8
160°	976.0	971.4	972.2	975.2	969.1
162.5°	988.1	983.5	984.3	988.8	982.0
165°	998.7	994.1	994.9	999.4	993.4
167.5°	1007.0	1002.5	1003.2	1008.5	1001.7
170°	1013.8	1008.5	1009.3	1015.3	1008.5
172.5°	1018.4	1013.1	1014.6	1019.9	1013.1
175°	1021.4	1016.8	1017.6	1023.7	1016.8
177.5°	1023.7	1019.1	1019.9	1025.2	1019.1
180°	1021.4	1021.4	1021.4	1021.4	1021.4

(END OF REPORT)