

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026975

Luminaire Tested: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026975
REPORT IS A COMBINATION OF REPORTS P1002379 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5656.0 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026975

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026975

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	31	52	41	34	29	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5163 cd/sqm

TEST NUMBER: P1026975

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	1.6
10°-20°	254.9	4.5
20°-30°	376.3	6.7
30°-40°	439.0	7.8
40°-50°	440.9	7.8
50°-60°	387.1	6.8
60°-70°	288.3	5.1
70°-80°	164.6	2.9
80°-90°	49.1	0.9
90°-100°	35.0	0.6
100°-110°	232.6	4.1
110°-120°	418.8	7.4
120°-130°	537.6	9.5
130°-140°	578.2	10.2
140°-150°	542.6	9.6
150°-160°	438.9	7.8
160°-170°	283.9	5.0
170°-180°	97.9	1.7
0°-30°	721.4	12.8
0°-40°	1160.5	20.5
0°-60°	1988.5	35.2
0°-90°	2490.5	44.0
90°-120°	686.3	12.1
90°-150°	2344.8	41.5
90°-180°	3165.0	56.0
0°-180°	5656.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	1	7	12	16	18	5
95°	44	41	12	16	16	53
105°	225	228	228	228	227	238
115°	422	426	426	423	419	418
125°	600	605	605	602	600	536
135°	748	752	751	749	745	577
145°	867	869	869	869	865	542
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1026975

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	0.8	6.9	12.2	16.0	18.3
92.5°	14.5	7.6	12.2	16.0	16.8
95°	43.5	41.3	12.2	16.0	16.0
97.5°	81.7	86.3	13.8	15.3	16.0
100°	127.6	129.9	132.9	19.1	16.0
102.5°	174.2	177.2	178.8	180.3	116.1
105°	224.6	227.6	227.6	227.6	226.9
107.5°	276.5	276.5	278.1	278.8	275.8
110°	326.9	326.9	328.5	326.2	326.9

TEST NUMBER: P1026975

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.3	376.6	377.4	374.3	372.8
115°	421.7	425.5	426.3	423.2	418.6
117.5°	471.3	471.3	474.4	469.8	468.3
120°	517.2	516.4	518.7	517.2	513.3
122.5°	557.6	561.5	562.2	560.7	556.1
125°	599.7	605.0	605.0	602.0	599.7
127.5°	640.1	644.0	643.2	641.7	635.6
130°	676.8	680.6	681.4	679.1	675.3
132.5°	713.5	718.1	715.8	715.8	712.0
135°	747.9	752.4	750.9	749.4	744.8
137.5°	779.9	784.5	783.0	783.0	779.2
140°	811.3	812.8	812.0	813.6	809.0
142.5°	839.5	840.3	841.8	841.8	837.2
145°	867.0	868.6	868.6	869.3	864.7
147.5°	891.5	891.5	892.2	893.0	887.6
150°	914.4	912.9	914.4	915.9	909.8
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)