

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026684

Luminaire Tested: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026684
REPORT IS A COMBINATION OF REPORTS P1001233 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8267.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026684

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026684

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	92	88	84	89	85	81	78	71	68	66	58	56	55	47	45	44
2	88	80	73	68	80	74	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	65	58	53	54	49	45	45	41	38	36	33	31
4	73	62	54	47	67	57	50	44	48	43	38	40	36	32	32	29	26
5	67	55	47	40	61	51	43	38	43	37	33	35	31	28	29	25	23
6	61	49	41	35	56	45	38	33	39	33	28	32	28	24	26	23	20
7	57	44	36	31	52	41	34	29	35	29	25	29	25	21	24	20	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	20	17	14
10	46	34	26	21	42	31	25	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8695	8695	8695
5°	8709	8513	8533
10°	8644	8339	8315
15°	8539	8137	8047
20°	8397	7893	7780
25°	8228	7634	7458
30°	8024	7351	7165
35°	7834	7090	6895
40°	7641	6815	6623
45°	7421	6576	6378
50°	7212	6317	6157
55°	6960	6071	5900
60°	6684	5790	5637
65°	6394	5493	5341
70°	6063	5096	5033
75°	5543	4705	4656
80°	4857	4228	4240
85°	4185	3847	4022

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7421 cd/sqm

TEST NUMBER: P1026684

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.6
10°-20°	364.6	4.4
20°-30°	542.1	6.6
30°-40°	642.0	7.8
40°-50°	663.7	8.0
50°-60°	611.4	7.4
60°-70°	494.3	6.0
70°-80°	330.7	4.0
80°-90°	172.9	2.1
90°-100°	141.2	1.7
100°-110°	369.3	4.5
110°-120°	584.8	7.1
120°-130°	716.6	8.7
130°-140°	753.5	9.1
140°-150°	698.5	8.4
150°-160°	563.1	6.8
160°-170°	364.2	4.4
170°-180°	125.6	1.5
0°-30°	1035.1	12.5
0°-40°	1677.1	20.3
0°-60°	2952.3	35.7
0°-90°	3950.2	47.8
90°-120°	1095.3	13.2
90°-150°	3263.9	39.5
90°-180°	4317.0	52.2
0°-180°	8267.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1357	1357	1357	1357	1357	
5°	1357	1354	1345	1356	1354	129
15°	1296	1297	1288	1296	1291	365
25°	1178	1182	1174	1179	1172	542
35°	1019	1028	1024	1028	1028	638
45°	840	854	861	870	872	648
55°	645	667	688	702	708	577
65°	444	475	507	527	532	441
75°	245	279	322	349	355	259
85°	73	117	164	193	204	76
90°	22	73	125	160	172	18
95°	73	105	113	147	156	82
105°	300	325	365	392	400	318
115°	549	563	599	619	621	544
125°	775	780	807	824	828	692
135°	962	967	974	989	990	742
145°	1114	1114	1114	1122	1121	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1026684

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1357.1	1357.1	1357.1	1357.1	1357.1
2.5°	1361.1	1358.4	1349.1	1358.4	1357.1
5°	1357.1	1354.4	1345.1	1355.8	1354.4
7.5°	1347.8	1346.4	1337.1	1346.4	1345.1
10°	1334.5	1334.5	1323.8	1333.1	1331.8
12.5°	1315.8	1317.2	1309.2	1315.8	1311.8
15°	1295.9	1297.2	1287.9	1295.9	1290.6
17.5°	1270.6	1273.3	1263.9	1270.6	1266.6
20°	1242.7	1245.3	1236.0	1240.0	1240.0
22.5°	1210.7	1216.1	1205.4	1210.7	1206.7
25°	1177.5	1181.5	1173.5	1178.8	1172.1
27.5°	1141.5	1146.9	1137.6	1141.5	1138.9
30°	1100.3	1108.3	1100.3	1103.0	1101.6
32.5°	1063.0	1069.7	1064.4	1067.0	1065.7
35°	1019.1	1028.5	1024.5	1028.5	1028.5
37.5°	976.6	984.5	983.2	988.5	987.2
40°	932.7	943.3	942.0	947.3	950.0
42.5°	884.8	899.4	903.4	910.0	910.0
45°	839.5	854.2	860.8	870.1	871.5
47.5°	793.0	806.3	816.9	830.2	832.9
50°	745.1	759.7	774.3	789.0	793.0
52.5°	694.5	713.1	731.8	747.7	750.4
55°	645.3	666.6	687.9	702.5	707.8
57.5°	594.7	620.0	643.9	659.9	663.9
60°	544.2	570.8	597.4	617.3	621.3
62.5°	494.9	521.5	550.8	573.4	578.8
65°	444.4	475.0	506.9	526.9	532.2
67.5°	397.8	427.1	459.0	483.0	489.6
70°	345.9	376.5	411.1	436.4	444.4
72.5°	295.4	327.3	365.9	393.8	399.1
75°	244.8	279.4	322.0	348.6	355.2
77.5°	195.6	235.5	275.4	304.7	310.0
80°	150.3	190.3	235.5	264.8	270.1
82.5°	109.1	151.7	198.2	226.2	236.8
85°	73.2	117.1	163.6	192.9	203.6
87.5°	46.6	89.1	134.4	165.0	174.3
90°	22.3	72.7	124.8	160.3	172.5
92.5°	37.2	67.0	119.5	153.6	164.0
95°	73.2	104.8	112.8	147.0	156.3
97.5°	120.9	158.6	109.4	139.3	149.7
100°	178.3	209.2	255.7	137.6	141.7
102.5°	236.7	266.0	309.1	337.7	263.4
105°	300.1	325.3	365.2	391.8	400.2
107.5°	365.4	384.1	424.6	452.2	456.2
110°	428.7	444.7	483.9	506.3	516.5

TEST NUMBER: P1026684

CATALOG NUMBER: S125DIP-B1090D1090UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	489.5	504.4	541.3	561.4	568.7
115°	549.0	563.2	598.7	618.7	620.8
117.5°	611.4	618.0	655.2	671.9	679.3
120°	670.2	673.1	706.6	727.4	730.4
122.5°	720.7	727.0	757.2	776.5	778.7
125°	774.6	780.2	806.8	824.2	827.8
127.5°	825.3	828.9	850.5	868.4	868.6
130°	872.3	875.9	895.5	911.1	912.9
132.5°	918.0	923.9	934.3	952.9	953.3
135°	962.1	966.6	974.0	989.3	990.1
137.5°	1003.3	1007.8	1011.2	1027.1	1027.5
140°	1042.1	1044.0	1044.5	1061.0	1060.4
142.5°	1078.3	1078.0	1080.0	1092.0	1091.4
145°	1113.6	1114.3	1114.3	1122.0	1121.4
147.5°	1143.7	1143.7	1144.7	1148.3	1144.1
150°	1173.1	1171.1	1173.1	1175.0	1168.5
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)