

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026977

Luminaire Tested: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026977
REPORT IS A COMBINATION OF REPORTS P1002381 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5624.0 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026977

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026977

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	68	64	61	58	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	31	52	41	34	29	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6093	6093	6093
5°	6093	5951	5963
10°	6043	5815	5796
15°	5963	5652	5601
20°	5856	5462	5377
25°	5741	5256	5136
30°	5602	5041	4883
35°	5453	4816	4600
40°	5300	4577	4348
45°	5134	4345	4080
50°	4952	4082	3767
55°	4771	3791	3480
60°	4556	3485	3146
65°	4298	3131	2801
70°	4035	2724	2403
75°	3593	2243	1943
80°	3063	1675	1429
85°	2367	990	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5134 cd/sqm

TEST NUMBER: P1026977

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.6
10°-20°	253.5	4.5
20°-30°	374.2	6.7
30°-40°	436.6	7.8
40°-50°	438.5	7.8
50°-60°	384.9	6.8
60°-70°	286.7	5.1
70°-80°	163.7	2.9
80°-90°	48.8	0.9
90°-100°	34.8	0.6
100°-110°	231.2	4.1
110°-120°	416.4	7.4
120°-130°	534.5	9.5
130°-140°	574.9	10.2
140°-150°	539.6	9.6
150°-160°	436.4	7.8
160°-170°	282.3	5.0
170°-180°	97.3	1.7
0°-30°	717.4	12.8
0°-40°	1154.0	20.5
0°-60°	1977.3	35.2
0°-90°	2476.5	44.0
90°-120°	682.5	12.1
90°-150°	2331.4	41.5
90°-180°	3147.0	56.0
0°-180°	5624.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	951	951	951	951	951	
5°	949	948	940	947	946	90
15°	905	903	894	898	898	255
25°	822	818	808	810	807	378
35°	709	706	696	692	686	444
45°	581	578	569	560	558	447
55°	442	440	430	423	418	395
65°	299	297	289	282	279	296
75°	159	157	154	151	148	169
85°	41	42	42	41	40	45
90°	1	7	12	16	18	5
95°	43	41	12	16	16	53
105°	223	226	226	226	226	237
115°	419	423	424	421	416	416
125°	596	602	602	598	596	533
135°	744	748	747	745	741	573
145°	862	864	864	864	860	539
155°	949	945	946	949	943	437
165°	1002	997	998	1003	996	283
175°	1025	1020	1021	1027	1020	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1026977

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	950.9	950.9	950.9	950.9	950.9
2.5°	953.9	951.7	944.1	951.7	950.9
5°	949.4	947.9	940.4	947.2	946.4
7.5°	942.6	941.1	932.9	939.6	938.9
10°	932.9	931.4	923.1	929.1	928.3
12.5°	920.8	917.8	910.3	914.8	914.8
15°	905.0	902.8	894.5	898.3	898.3
17.5°	888.5	884.7	876.4	881.0	877.2
20°	866.7	865.2	855.4	860.6	856.9
22.5°	844.8	841.8	832.8	835.8	833.6
25°	821.5	817.8	808.0	809.5	807.2
27.5°	794.4	792.2	782.4	783.2	780.9
30°	768.1	765.8	754.6	753.1	750.8
32.5°	739.5	735.8	726.0	723.0	718.5
35°	709.4	706.4	695.9	692.1	686.1
37.5°	678.6	674.8	665.0	659.8	656.0
40°	647.0	643.2	632.7	625.9	623.7
42.5°	613.1	610.1	599.6	593.6	589.8
45°	580.8	577.8	568.7	559.7	557.5
47.5°	545.4	546.2	534.9	525.9	520.6
50°	511.6	509.3	500.3	490.5	485.2
52.5°	477.0	475.5	465.7	457.4	451.4
55°	442.4	440.1	429.6	422.8	417.5
57.5°	405.5	404.7	395.7	386.7	384.4
60°	370.9	367.9	359.6	352.1	346.8
62.5°	334.8	332.5	325.7	317.5	313.7
65°	298.7	297.2	288.9	282.1	279.1
67.5°	263.3	260.3	254.3	248.3	246.8
70°	230.2	226.4	219.7	215.2	212.2
72.5°	194.1	191.8	188.1	182.8	179.8
75°	158.7	157.2	153.5	151.2	148.2
77.5°	125.6	124.9	122.6	121.1	118.9
80°	94.8	94.8	93.3	92.5	91.0
82.5°	67.7	66.2	66.2	64.7	64.7
85°	41.4	42.1	42.1	41.4	39.9
87.5°	20.3	20.3	19.6	19.6	18.1
90°	0.8	6.8	12.2	16.0	18.2
92.5°	14.4	7.6	12.2	16.0	16.7
95°	43.3	41.0	12.2	16.0	16.0
97.5°	81.3	85.8	13.7	15.2	16.0
100°	126.8	129.1	132.2	19.0	16.0
102.5°	173.2	176.2	177.7	179.3	115.5
105°	223.3	226.3	226.3	226.3	225.6
107.5°	275.0	275.0	276.5	277.2	274.2
110°	325.1	325.1	326.6	324.3	325.1

TEST NUMBER: P1026977

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.2	374.5	375.2	372.2	370.7
115°	419.3	423.1	423.8	420.8	416.2
117.5°	468.6	468.6	471.7	467.1	465.6
120°	514.2	513.5	515.7	514.2	510.4
122.5°	554.5	558.3	559.0	557.5	553.0
125°	596.3	601.6	601.6	598.5	596.3
127.5°	636.5	640.3	639.5	638.0	632.0
130°	673.0	676.8	677.5	675.2	671.4
132.5°	709.4	714.0	711.7	711.7	707.9
135°	743.6	748.2	746.6	745.1	740.6
137.5°	775.5	780.1	778.5	778.5	774.7
140°	806.6	808.2	807.4	808.9	804.4
142.5°	834.8	835.5	837.0	837.0	832.5
145°	862.1	863.6	863.6	864.4	859.8
147.5°	886.4	886.4	887.2	887.9	882.6
150°	909.2	907.7	909.2	910.7	904.6
152.5°	931.2	927.4	928.9	930.5	925.1
155°	949.4	944.9	946.4	948.7	942.6
157.5°	963.9	961.6	961.6	963.9	957.8
160°	979.1	974.5	975.3	978.3	972.2
162.5°	991.2	986.7	987.4	992.0	985.1
165°	1001.9	997.3	998.1	1002.6	996.5
167.5°	1010.2	1005.7	1006.4	1011.7	1004.9
170°	1017.0	1011.7	1012.5	1018.6	1011.7
172.5°	1021.6	1016.3	1017.8	1023.1	1016.3
175°	1024.6	1020.1	1020.8	1026.9	1020.1
177.5°	1026.9	1022.4	1023.1	1028.4	1022.4
180°	1024.6	1024.6	1024.6	1024.6	1024.6

(END OF REPORT)