

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026722

Luminaire Tested: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026722
REPORT IS A COMBINATION OF REPORTS P1001361 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5856.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026722

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026722

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	79	79	79
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	70	68	67	67	67	63
2	94	86	80	74	89	82	76	72	75	70	66	68	64	61	61	59	56	56	56	53
3	86	76	68	62	81	72	65	60	66	60	56	60	55	52	54	51	48	48	48	45
4	79	67	59	53	74	64	57	51	59	52	48	53	48	44	49	45	41	41	41	38
5	72	60	52	45	68	57	50	44	53	46	41	48	43	38	44	39	36	36	36	33
6	67	54	46	39	63	52	44	38	47	41	36	44	38	34	40	35	32	32	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28	28	28	26
8	57	45	36	31	55	43	35	30	39	33	28	36	31	27	33	29	25	25	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	23	23	21
10	50	38	30	25	48	36	29	24	34	27	23	31	26	22	29	24	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10807	10807	10807
5°	10807	10556	10576
10°	10717	10314	10281
15°	10577	10024	9935
20°	10387	9689	9537
25°	10183	9322	9111
30°	9936	8941	8662
35°	9673	8542	8159
40°	9401	8119	7711
45°	9107	7707	7237
50°	8783	7240	6683
55°	8462	6724	6174
60°	8081	6181	5582
65°	7623	5553	4969
70°	7157	4830	4262
75°	6376	3977	3446
80°	5432	2971	2535
85°	4197	1756	1397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9107 cd/sqm

TEST NUMBER: P1026722

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	2.7
10°-20°	449.6	7.7
20°-30°	663.7	11.3
30°-40°	774.4	13.2
40°-50°	777.7	13.3
50°-60°	682.7	11.7
60°-70°	508.5	8.7
70°-80°	290.4	5.0
80°-90°	84.5	1.4
90°-100°	16.2	0.3
100°-110°	107.7	1.8
110°-120°	193.9	3.3
120°-130°	248.8	4.2
130°-140°	267.6	4.6
140°-150°	251.2	4.3
150°-160°	203.2	3.5
160°-170°	131.4	2.2
170°-180°	45.3	0.8
0°-30°	1272.4	21.7
0°-40°	2046.8	35.0
0°-60°	3507.2	59.9
0°-90°	4390.7	75.0
90°-120°	317.7	5.4
90°-150°	1085.4	18.5
90°-180°	1465.0	25.0
0°-180°	5856.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1687	1687	1687	1687	1687	
5°	1684	1681	1668	1680	1679	160
15°	1605	1601	1587	1593	1593	453
25°	1457	1450	1433	1436	1432	670
35°	1258	1253	1234	1228	1217	787
45°	1030	1025	1009	993	989	794
55°	785	781	762	750	741	700
65°	530	527	512	500	495	525
75°	282	279	272	268	263	300
85°	73	75	75	73	71	80
90°	0	3	6	7	8	6
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	197	197	196	194	194
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	441	442	439	204
165°	466	464	465	467	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	

TEST NUMBER: P1026722

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1686.7	1686.7	1686.7	1686.7	1686.7
2.5°	1692.0	1688.0	1674.7	1688.0	1686.7
5°	1684.0	1681.3	1668.0	1680.0	1678.7
7.5°	1672.0	1669.3	1654.6	1666.7	1665.3
10°	1654.6	1652.0	1637.3	1648.0	1646.6
12.5°	1633.3	1628.0	1614.6	1622.6	1622.6
15°	1605.3	1601.3	1586.6	1593.3	1593.3
17.5°	1575.9	1569.2	1554.6	1562.6	1555.9
20°	1537.2	1534.6	1517.2	1526.5	1519.9
22.5°	1498.5	1493.2	1477.2	1482.5	1478.5
25°	1457.2	1450.5	1433.1	1435.8	1431.8
27.5°	1409.1	1405.1	1387.8	1389.1	1385.1
30°	1362.4	1358.4	1338.4	1335.7	1331.7
32.5°	1311.7	1305.0	1287.7	1282.4	1274.3
35°	1258.3	1253.0	1234.3	1227.6	1217.0
37.5°	1203.6	1197.0	1179.6	1170.3	1163.6
40°	1147.6	1140.9	1122.2	1110.2	1106.2
42.5°	1087.5	1082.2	1063.5	1052.8	1046.2
45°	1030.2	1024.8	1008.8	992.8	988.8
47.5°	967.4	968.8	948.8	932.7	923.4
50°	907.4	903.4	887.4	870.0	860.7
52.5°	846.0	843.3	826.0	811.3	800.6
55°	784.6	780.6	761.9	749.9	740.6
57.5°	719.2	717.9	701.9	685.9	681.9
60°	657.9	652.5	637.8	624.5	615.2
62.5°	593.8	589.8	577.8	563.1	556.4
65°	529.8	527.1	512.4	500.4	495.1
67.5°	467.0	461.7	451.0	440.4	437.7
70°	408.3	401.7	389.6	381.6	376.3
72.5°	344.3	340.3	333.6	324.3	318.9
75°	281.6	278.9	272.2	268.2	262.9
77.5°	222.8	221.5	217.5	214.8	210.8
80°	168.1	168.1	165.5	164.1	161.5
82.5°	120.1	117.4	117.4	114.8	114.8
85°	73.4	74.7	74.7	73.4	70.7
87.5°	36.0	36.0	34.7	34.7	32.0
90°	0.4	3.2	5.7	7.4	8.5
92.5°	6.7	3.5	5.7	7.4	7.8
95°	20.2	19.1	5.7	7.4	7.4
97.5°	37.8	40.0	6.4	7.1	7.4
100°	59.1	60.1	61.5	8.8	7.4
102.5°	80.6	82.0	82.7	83.5	53.7
105°	104.0	105.4	105.4	105.4	105.0
107.5°	128.0	128.0	128.7	129.1	127.7
110°	151.3	151.3	152.1	151.0	151.3



TEST NUMBER: P1026722

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.3	174.3	174.7	173.3	172.6
115°	195.2	197.0	197.3	195.9	193.8
117.5°	218.2	218.2	219.6	217.5	216.8
120°	239.4	239.0	240.1	239.4	237.6
122.5°	258.1	259.9	260.3	259.5	257.4
125°	277.6	280.1	280.1	278.6	277.6
127.5°	296.3	298.1	297.7	297.0	294.2
130°	313.3	315.1	315.4	314.4	312.6
132.5°	330.3	332.4	331.3	331.3	329.6
135°	346.2	348.3	347.6	346.9	344.8
137.5°	361.0	363.2	362.4	362.4	360.7
140°	375.5	376.2	375.9	376.6	374.5
142.5°	388.6	389.0	389.7	389.7	387.6
145°	401.3	402.1	402.1	402.4	400.3
147.5°	412.7	412.7	413.0	413.4	410.9
150°	423.3	422.6	423.3	424.0	421.1
152.5°	433.5	431.8	432.5	433.2	430.7
155°	442.0	439.9	440.6	441.7	438.8
157.5°	448.7	447.7	447.7	448.7	445.9
160°	455.8	453.7	454.0	455.4	452.6
162.5°	461.5	459.3	459.7	461.8	458.6
165°	466.4	464.3	464.6	466.8	463.9
167.5°	470.3	468.2	468.5	471.0	467.8
170°	473.5	471.0	471.4	474.2	471.0
172.5°	475.6	473.1	473.8	476.3	473.1
175°	477.0	474.9	475.2	478.1	474.9
177.5°	478.1	476.0	476.3	478.8	476.0
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)