

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026723

Luminaire Tested: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026723
REPORT IS A COMBINATION OF REPORTS P1001362 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5663.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026723

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026723

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75		
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	70	68	67	63		
2	94	86	80	74	89	82	76	72	75	70	66	68	64	61	61	59	56	53		
3	86	76	68	62	81	72	65	60	66	60	56	60	55	52	54	51	48	45		
4	79	67	59	53	74	64	57	51	59	52	48	53	48	44	49	45	41	38		
5	72	60	52	45	68	57	50	44	53	46	41	48	43	38	44	39	36	33		
6	67	54	46	39	63	52	44	38	47	41	36	44	38	34	40	35	32	29		
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28	26		
8	57	45	36	31	55	43	35	30	39	33	28	36	31	27	33	29	25	23		
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21		
10	50	38	30	25	48	36	29	24	34	27	23	31	26	22	29	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10450	10450	10450
5°	10450	10207	10227
10°	10364	9973	9942
15°	10228	9693	9606
20°	10043	9369	9222
25°	9846	9015	8810
30°	9608	8646	8375
35°	9354	8259	7889
40°	9091	7851	7457
45°	8806	7453	6997
50°	8493	7001	6462
55°	8183	6503	5969
60°	7813	5978	5396
65°	7372	5370	4804
70°	6920	4671	4121
75°	6166	3846	3332
80°	5254	2873	2451
85°	4059	1700	1351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8806 cd/sqm

TEST NUMBER: P1026723

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	2.7
10°-20°	434.7	7.7
20°-30°	641.8	11.3
30°-40°	748.8	13.2
40°-50°	752.0	13.3
50°-60°	660.2	11.7
60°-70°	491.7	8.7
70°-80°	280.8	5.0
80°-90°	81.8	1.4
90°-100°	15.7	0.3
100°-110°	104.1	1.8
110°-120°	187.5	3.3
120°-130°	240.7	4.3
130°-140°	258.9	4.6
140°-150°	243.0	4.3
150°-160°	196.5	3.5
160°-170°	127.1	2.2
170°-180°	43.8	0.8
0°-30°	1230.4	21.7
0°-40°	1979.2	34.9
0°-60°	3391.4	59.9
0°-90°	4245.7	75.0
90°-120°	307.3	5.4
90°-150°	1049.8	18.5
90°-180°	1417.0	25.0
0°-180°	5663.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1628	1626	1613	1624	1623	155
15°	1552	1548	1534	1541	1541	438
25°	1409	1403	1386	1388	1384	648
35°	1217	1212	1194	1187	1177	761
45°	996	991	976	960	956	767
55°	759	755	737	725	716	677
65°	512	510	496	484	479	508
75°	272	270	263	259	254	290
85°	71	72	72	71	68	78
90°	0	3	6	7	8	6
95°	20	18	6	7	7	24
105°	101	102	102	102	102	107
115°	189	190	191	190	187	187
125°	268	271	271	270	268	240
135°	335	337	336	336	334	258
145°	388	389	389	389	387	243
155°	428	426	426	427	424	197
165°	451	449	449	452	449	127
175°	461	459	460	462	459	44
180°	461	461	461	461	461	

TEST NUMBER: P1026723

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.0	1631.0	1631.0	1631.0	1631.0
2.5°	1636.1	1632.3	1619.4	1632.3	1631.0
5°	1628.4	1625.8	1612.9	1624.5	1623.2
7.5°	1616.8	1614.2	1600.0	1611.6	1610.3
10°	1600.0	1597.4	1583.2	1593.5	1592.3
12.5°	1579.4	1574.2	1561.3	1569.0	1569.0
15°	1552.3	1548.4	1534.2	1540.6	1540.6
17.5°	1523.9	1517.4	1503.2	1511.0	1504.5
20°	1486.4	1483.9	1467.1	1476.1	1469.7
22.5°	1449.0	1443.9	1428.4	1433.5	1429.7
25°	1409.0	1402.6	1385.8	1388.4	1384.5
27.5°	1362.6	1358.7	1341.9	1343.2	1339.4
30°	1317.4	1313.5	1294.2	1291.6	1287.7
32.5°	1268.4	1261.9	1245.2	1240.0	1232.3
35°	1216.8	1211.6	1193.5	1187.1	1176.8
37.5°	1163.9	1157.4	1140.6	1131.6	1125.2
40°	1109.7	1103.2	1085.2	1073.5	1069.7
42.5°	1051.6	1046.4	1028.4	1018.1	1011.6
45°	996.1	991.0	975.5	960.0	956.1
47.5°	935.5	936.8	917.4	901.9	892.9
50°	877.4	873.5	858.1	841.3	832.3
52.5°	818.1	815.5	798.7	784.5	774.2
55°	758.7	754.8	736.8	725.2	716.1
57.5°	695.5	694.2	678.7	663.2	659.4
60°	636.1	631.0	616.8	603.9	594.8
62.5°	574.2	570.3	558.7	544.5	538.1
65°	512.3	509.7	495.5	483.9	478.7
67.5°	451.6	446.5	436.1	425.8	423.2
70°	394.8	388.4	376.8	369.0	363.9
72.5°	332.9	329.0	322.6	313.5	308.4
75°	272.3	269.7	263.2	259.4	254.2
77.5°	215.5	214.2	210.3	207.7	203.9
80°	162.6	162.6	160.0	158.7	156.1
82.5°	116.1	113.5	113.5	111.0	111.0
85°	71.0	72.3	72.3	71.0	68.4
87.5°	34.8	34.8	33.5	33.5	31.0
90°	0.3	3.1	5.5	7.2	8.2
92.5°	6.5	3.4	5.5	7.2	7.5
95°	19.5	18.5	5.5	7.2	7.2
97.5°	36.6	38.6	6.2	6.8	7.2
100°	57.1	58.1	59.5	8.6	7.2
102.5°	78.0	79.4	80.0	80.7	52.0
105°	100.6	101.9	101.9	101.9	101.6
107.5°	123.8	123.8	124.5	124.8	123.5
110°	146.4	146.4	147.1	146.0	146.4



TEST NUMBER: P1026723

CATALOG NUMBER: S125DIP-B1090D375UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.6	168.6	169.0	167.6	166.9
115°	188.8	190.5	190.9	189.5	187.4
117.5°	211.0	211.0	212.4	210.3	209.7
120°	231.6	231.2	232.2	231.6	229.8
122.5°	249.7	251.4	251.7	251.0	249.0
125°	268.5	270.9	270.9	269.5	268.5
127.5°	286.6	288.3	288.0	287.3	284.6
130°	303.0	304.7	305.1	304.1	302.4
132.5°	319.5	321.5	320.5	320.5	318.8
135°	334.8	336.9	336.2	335.5	333.5
137.5°	349.2	351.3	350.6	350.6	348.9
140°	363.2	363.9	363.6	364.3	362.2
142.5°	375.9	376.2	376.9	376.9	374.9
145°	388.2	388.9	388.9	389.2	387.2
147.5°	399.1	399.1	399.5	399.8	397.4
150°	409.4	408.7	409.4	410.1	407.4
152.5°	419.3	417.6	418.3	419.0	416.6
155°	427.5	425.5	426.2	427.2	424.5
157.5°	434.0	433.0	433.0	434.0	431.3
160°	440.9	438.8	439.2	440.5	437.8
162.5°	446.3	444.3	444.6	446.7	443.6
165°	451.1	449.1	449.4	451.5	448.7
167.5°	454.9	452.8	453.2	455.6	452.5
170°	458.0	455.6	455.9	458.7	455.6
172.5°	460.0	457.6	458.3	460.7	457.6
175°	461.4	459.3	459.7	462.4	459.3
177.5°	462.4	460.4	460.7	463.1	460.4
180°	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)